

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010654

Luminaire Tested: S123DIP-B560D365UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010654
REPORT IS A COMBINATION OF REPORTS P990053 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D365UB2750-4F0-XX-W2A-D_2700K
Description: Define 3 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3780.0 lumens
Efficiency: N/A
Efficacy: 113.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 33.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010654

CATALOG NUMBER: S123DIP-B560D365UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1010654

CATALOG NUMBER: S123DIP-B560D365UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	98	93	89	85	91	87	83	79	75	72	69	63	61	59	53	52	50
2	89	81	74	68	82	75	69	64	65	60	56	55	52	49	46	44	41
3	81	71	63	56	75	66	59	53	57	51	47	48	44	41	40	37	35
4	74	62	54	47	68	58	51	45	50	44	40	43	38	34	36	32	30
5	68	55	47	40	62	52	44	38	45	39	34	38	33	30	32	29	26
6	62	50	41	35	58	46	39	33	40	34	29	35	30	26	29	25	22
7	58	45	36	31	53	42	34	29	36	30	26	31	26	23	27	23	20
8	53	41	33	27	49	38	31	26	33	27	23	29	24	20	24	21	18
9	50	37	29	24	46	35	28	23	30	25	21	26	22	18	23	19	16
10	46	34	26	22	43	32	25	21	28	22	18	24	20	16	21	17	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7472	7472	7472
5°	7492	7253	7247
10°	7423	7056	7003
15°	7325	6840	6743
20°	7184	6598	6464
25°	7013	6325	6177
30°	6838	6078	5887
35°	6641	5820	5651
40°	6452	5584	5402
45°	6243	5355	5196
50°	6038	5128	4974
55°	5809	4895	4769
60°	5586	4657	4558
65°	5357	4403	4313
70°	5009	4120	4059
75°	4572	3795	3797
80°	4066	3466	3499
85°	3564	3200	3285

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6243 cd/sqm

TEST NUMBER: P1010654

CATALOG NUMBER: S123DIP-B560D365UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.9	1.7
10°-20°	187.7	5.0
20°-30°	280.7	7.4
30°-40°	335.2	8.9
40°-50°	350.7	9.3
50°-60°	329.1	8.7
60°-70°	274.9	7.3
70°-80°	196.5	5.2
80°-90°	117.9	3.1
90°-100°	90.2	2.4
100°-110°	134.9	3.6
110°-120°	234.3	6.2
120°-130°	272.2	7.2
130°-140°	278.0	7.4
140°-150°	253.2	6.7
150°-160°	202.7	5.4
160°-170°	130.8	3.5
170°-180°	45.1	1.2
0°-30°	534.3	14.1
0°-40°	869.5	23.0
0°-60°	1549.3	41.0
0°-90°	2138.6	56.6
90°-120°	459.4	12.2
90°-150°	1262.8	33.4
90°-180°	1641.0	43.4
0°-180°	3780.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	694	694	694	694	694	
5°	695	693	689	695	694	66
15°	662	664	663	671	670	186
25°	597	605	607	617	617	275
35°	514	526	536	548	550	322
45°	420	439	458	472	478	324
55°	321	346	373	393	399	287
65°	222	251	284	307	315	219
75°	120	156	194	218	228	128
85°	37	75	115	141	148	38
90°	10	51	94	121	129	8
95°	30	45	86	112	119	32
105°	111	133	134	93	100	117
115°	201	212	242	264	272	198
125°	280	283	306	323	329	250
135°	347	349	358	373	376	267
145°	400	401	402	409	412	250
155°	439	439	439	441	439	202
165°	463	462	462	465	462	131
175°	474	473	473	475	473	45
180°	474	474	474	474	474	

TEST NUMBER: P1010654

CATALOG NUMBER: S123DIP-B560D365UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	694.2	694.2	694.2	694.2	694.2
2.5°	698.0	695.7	689.6	695.7	694.9
5°	694.9	693.4	688.9	694.9	694.2
7.5°	689.6	689.6	685.1	692.7	691.9
10°	682.1	683.6	679.8	687.4	685.9
12.5°	673.0	675.3	673.0	679.8	678.3
15°	661.7	663.9	663.2	670.7	670.0
17.5°	648.1	652.6	651.8	658.6	657.1
20°	632.9	637.5	639.0	645.8	646.5
22.5°	617.1	621.6	623.9	632.9	632.2
25°	597.4	605.0	607.2	617.1	617.1
27.5°	578.5	586.8	591.3	599.7	600.4
30°	558.1	567.9	573.9	583.0	583.0
32.5°	535.4	546.7	555.0	564.9	567.1
35°	514.2	526.3	536.1	547.5	550.5
37.5°	491.5	505.1	516.5	529.3	531.6
40°	468.8	482.4	497.6	510.4	513.5
42.5°	443.9	461.3	477.2	491.5	496.1
45°	420.4	438.6	457.5	471.9	477.9
47.5°	395.5	415.9	437.1	453.0	457.5
50°	371.3	392.5	415.9	433.3	438.6
52.5°	345.6	368.3	394.7	412.9	419.7
55°	320.6	345.6	372.8	393.2	399.3
57.5°	296.4	322.1	351.6	372.0	378.9
60°	270.7	297.9	328.9	350.1	358.4
62.5°	246.5	274.5	307.8	328.9	336.5
65°	221.6	251.1	284.3	307.0	314.6
67.5°	196.6	227.6	260.9	285.8	291.9
70°	170.1	202.7	239.0	263.2	270.7
72.5°	145.9	178.5	216.3	241.2	248.8
75°	120.2	155.8	193.6	218.5	227.6
77.5°	98.3	133.8	171.7	198.1	204.9
80°	74.9	111.9	151.2	176.9	184.5
82.5°	54.4	92.3	132.3	158.0	165.6
85°	37.1	74.9	114.9	140.7	148.2
87.5°	22.7	60.5	99.1	124.8	132.3
90°	10.2	50.8	93.9	121.1	129.3
92.5°	17.2	47.6	88.6	116.0	123.2
95°	29.8	44.8	85.8	111.7	119.3
97.5°	46.7	64.0	81.6	107.1	115.0
100°	66.4	97.6	77.4	102.1	110.1
102.5°	88.8	114.6	87.4	96.8	105.2
105°	111.0	133.1	133.9	92.7	100.2
107.5°	133.9	153.0	189.3	155.4	116.1
110°	156.7	173.2	207.3	215.4	171.0



TEST NUMBER: P1010654

CATALOG NUMBER: S123DIP-B560D365UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	179.3	192.4	225.0	247.1	253.2
115°	200.8	212.0	242.4	264.0	271.5
117.5°	222.6	231.1	258.6	279.6	285.9
120°	241.9	248.9	275.0	295.2	300.4
122.5°	262.4	266.3	291.2	309.6	315.3
125°	280.0	282.8	306.1	322.7	328.7
127.5°	298.3	300.3	321.0	337.2	341.8
130°	315.2	317.3	333.8	349.6	353.4
132.5°	330.6	333.5	345.9	360.9	365.2
135°	347.2	348.6	358.3	373.0	375.7
137.5°	361.3	363.4	369.3	383.2	386.3
140°	374.7	376.8	380.1	392.9	395.9
142.5°	387.7	389.1	390.1	401.0	403.7
145°	399.7	401.4	402.1	408.8	411.9
147.5°	410.6	412.3	413.0	416.0	417.3
150°	421.1	422.2	422.9	423.6	424.0
152.5°	430.6	431.0	431.3	432.8	431.0
155°	439.4	438.7	439.1	440.9	438.7
157.5°	446.5	446.5	446.1	448.3	445.4
160°	452.8	452.5	452.1	454.2	451.8
162.5°	458.8	457.8	457.4	459.9	457.8
165°	463.4	462.4	462.0	464.8	462.4
167.5°	467.3	465.9	465.9	468.7	465.9
170°	470.5	469.0	469.0	471.9	469.0
172.5°	472.6	470.8	471.2	474.0	470.8
175°	474.3	472.6	472.9	475.4	472.6
177.5°	475.0	473.3	473.6	476.5	472.9
180°	474.3	474.3	474.3	474.3	474.3

(END OF REPORT)