

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010659

Luminaire Tested: S123DIP-B560D365UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010659
REPORT IS A COMBINATION OF REPORTS P990058 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D365UB2750-4F0-XX-W2A-F_2700K
Description: Define 3 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3736.0 lumens
Efficiency: N/A
Efficacy: 112.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010659

CATALOG NUMBER: S123DIP-B560D365UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1010659

CATALOG NUMBER: S123DIP-B560D365UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	66	66	66
1	100	96	92	88	94	90	86	83	79	76	74	68	66	65	59	57	56
2	91	84	77	72	85	78	73	68	69	65	61	60	57	54	52	49	47
3	83	74	66	60	78	69	62	57	61	55	51	53	49	46	46	43	40
4	76	65	57	51	71	61	54	48	54	48	44	47	43	39	41	37	35
5	70	58	50	44	65	55	47	42	48	42	38	42	38	34	37	33	30
6	65	52	44	38	60	49	42	36	44	37	33	38	33	30	33	30	27
7	60	47	39	33	56	45	37	32	40	33	29	35	30	26	30	27	24
8	55	43	35	30	52	41	33	28	36	30	26	32	27	23	28	24	21
9	52	39	32	26	48	37	30	25	33	27	23	29	25	21	26	22	19
10	48	36	29	24	45	34	27	23	31	25	21	27	22	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9467	9467	9467
5°	9491	9141	9126
10°	9406	8831	8741
15°	9275	8509	8320
20°	9125	8152	7902
25°	8932	7775	7456
30°	8719	7385	6987
35°	8496	6987	6521
40°	8264	6568	6063
45°	8008	6161	5583
50°	7747	5706	5103
55°	7413	5233	4615
60°	7069	4712	4097
65°	6747	4146	3556
70°	6281	3520	2925
75°	5611	2788	2271
80°	4843	1960	1606
85°	3775	1053	805

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8008 cd/sqm

TEST NUMBER: P1010659

CATALOG NUMBER: S123DIP-B560D365UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.9	2.2
10°-20°	234.1	6.3
20°-30°	345.8	9.3
30°-40°	403.8	10.8
40°-50°	406.0	10.9
50°-60°	356.6	9.5
60°-70°	265.6	7.1
70°-80°	151.1	4.0
80°-90°	43.9	1.2
90°-100°	16.7	0.4
100°-110°	80.9	2.2
110°-120°	198.2	5.3
120°-130°	251.6	6.7
130°-140°	268.8	7.2
140°-150°	251.3	6.7
150°-160°	202.7	5.4
160°-170°	130.8	3.5
170°-180°	45.1	1.2
0°-30°	662.8	17.7
0°-40°	1066.7	28.6
0°-60°	1829.3	49.0
0°-90°	2290.0	61.3
90°-120°	295.8	7.9
90°-150°	1067.4	28.6
90°-180°	1446.0	38.7
0°-180°	3736.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	880	880	880	880	880	
5°	880	876	868	876	874	83
15°	838	835	825	831	827	236
25°	761	756	746	747	745	350
35°	658	653	644	639	635	412
45°	539	536	526	517	514	416
55°	409	408	398	390	386	367
65°	279	275	268	262	259	275
75°	148	144	142	138	136	158
85°	39	38	38	36	36	42
90°	0	4	8	10	11	4
95°	22	7	11	13	13	26
105°	105	109	77	15	16	111
115°	197	199	202	206	207	195
125°	278	280	282	283	283	248
135°	346	348	349	350	349	266
145°	399	401	402	403	403	250
155°	439	439	439	441	439	202
165°	463	462	462	465	462	131
175°	474	473	473	475	473	45
180°	474	474	474	474	474	

TEST NUMBER: P1010659

CATALOG NUMBER: S123DIP-B560D365UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	879.5	879.5	879.5	879.5	879.5
2.5°	883.3	880.3	872.0	879.5	878.8
5°	880.3	876.5	868.2	875.7	874.2
7.5°	873.5	869.7	861.4	868.2	867.4
10°	864.4	860.6	850.8	857.6	856.1
12.5°	852.3	849.3	840.2	844.7	844.0
15°	837.9	834.9	825.1	831.1	826.6
17.5°	822.0	818.3	808.4	813.0	811.5
20°	803.9	799.4	789.5	792.6	790.3
22.5°	783.5	778.9	769.1	771.4	768.4
25°	760.8	756.3	746.4	747.2	744.9
27.5°	737.3	732.8	722.2	723.0	720.7
30°	711.6	707.9	697.3	697.3	692.0
32.5°	685.9	680.6	673.1	667.8	665.5
35°	657.9	653.4	643.6	639.0	635.3
37.5°	630.0	623.9	614.1	608.8	606.5
40°	600.5	595.9	585.3	579.3	576.3
42.5°	571.0	565.7	555.1	549.0	546.0
45°	539.2	536.2	526.4	517.3	513.5
47.5°	508.2	503.7	494.6	485.5	482.5
50°	476.4	472.7	462.8	454.5	450.0
52.5°	443.2	440.9	430.3	423.5	419.0
55°	409.1	408.4	398.5	390.2	386.4
57.5°	377.4	374.3	366.8	359.2	354.7
60°	342.6	341.8	332.8	325.9	322.2
62.5°	311.6	309.3	300.2	293.4	291.2
65°	279.1	275.3	267.7	261.7	259.4
67.5°	244.3	241.2	235.2	229.9	226.9
70°	213.3	208.7	204.2	198.9	195.1
72.5°	180.7	177.7	172.4	167.9	166.4
75°	147.5	144.4	142.2	138.4	136.1
77.5°	118.0	116.5	113.4	110.4	110.4
80°	89.2	87.0	85.5	84.7	84.7
82.5°	61.3	61.3	61.3	59.7	59.0
85°	39.3	37.8	37.8	36.3	36.3
87.5°	19.7	17.4	16.6	15.9	15.9
90°	0.4	3.9	8.5	9.9	10.6
92.5°	8.1	6.0	9.2	11.6	12.0
95°	21.5	7.0	10.9	13.4	13.4
97.5°	39.1	29.2	11.3	14.1	14.4
100°	59.6	66.6	11.6	14.4	14.8
102.5°	82.8	87.4	26.1	14.4	15.2
105°	105.0	108.9	77.2	14.8	15.5
107.5°	128.6	131.8	137.1	82.8	36.7
110°	152.2	155.1	158.9	147.3	96.9

TEST NUMBER: P1010659

CATALOG NUMBER: S123DIP-B560D365UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	174.8	177.3	181.1	184.3	183.6
115°	197.0	199.1	202.3	205.8	207.2
117.5°	218.8	221.3	223.1	225.9	226.2
120°	238.9	242.1	243.2	246.0	246.0
122.5°	259.4	261.8	263.2	265.0	265.4
125°	277.7	280.5	281.9	282.6	283.3
127.5°	296.0	298.8	300.6	301.7	301.0
130°	312.9	315.8	317.2	318.6	317.9
132.5°	329.1	332.0	333.0	334.4	333.4
135°	345.7	347.8	349.2	350.3	349.2
137.5°	359.8	362.6	363.3	365.1	364.4
140°	373.9	376.0	377.1	378.5	377.8
142.5°	386.9	389.1	390.1	391.2	390.1
145°	398.9	401.4	402.1	402.8	402.8
147.5°	410.6	412.3	413.0	413.7	412.0
150°	421.1	422.2	422.9	423.6	422.5
152.5°	430.6	431.0	431.3	432.8	431.0
155°	439.4	438.7	439.1	440.9	438.7
157.5°	446.5	446.5	446.1	448.3	445.4
160°	452.8	452.5	452.1	454.2	451.8
162.5°	458.8	457.8	457.4	459.9	457.8
165°	463.4	462.4	462.0	464.8	462.4
167.5°	467.3	465.9	465.9	468.7	465.9
170°	470.5	469.0	469.0	471.9	469.0
172.5°	472.6	470.8	471.2	474.0	470.8
175°	474.3	472.6	472.9	475.4	472.6
177.5°	475.0	473.3	473.6	476.5	472.9
180°	474.3	474.3	474.3	474.3	474.3

(END OF REPORT)