

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010974

Luminaire Tested: S123RDIP-B775D1025UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010974
REPORT IS A COMBINATION OF REPORTS P993530 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B775D1025UB2750-4F0-XX-W2A-F_2700K
Description: Define 3 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6930.0 lumens
Efficiency: N/A
Efficacy: 107.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010974

CATALOG NUMBER: S123RDIP-B775D1025UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1010974

CATALOG NUMBER: S123RDIP-B775D1025UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49
1	96	92	88	85	88	84	81	78	70	67	65	56	54	53	44	43	42
2	88	81	75	70	80	74	69	65	61	58	54	49	47	45	39	37	36
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	34	32	31
4	74	63	55	50	67	58	51	46	48	43	39	39	36	33	31	28	26
5	68	56	48	43	61	52	45	40	43	38	34	35	32	29	28	25	23
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21
7	58	46	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	21	19	16
9	50	38	30	26	45	35	28	24	30	25	21	25	21	18	20	17	15
10	46	35	28	23	42	32	26	22	27	22	19	23	19	16	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13851	13851	13851
5°	13874	13360	13324
10°	13764	12858	12605
15°	13586	12238	11816
20°	13350	11562	10936
25°	13109	10861	10102
30°	12799	10114	9115
35°	12480	9381	8216
40°	12180	8585	7224
45°	11795	7806	6331
50°	11370	6974	5408
55°	10930	6085	4562
60°	10509	5172	3703
65°	9964	4234	2890
70°	9282	3203	2066
75°	8296	2168	1637
80°	7079	1506	1147
85°	5312	813	601

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11795 cd/sqm

TEST NUMBER: P1010974

CATALOG NUMBER: S123RDIP-B775D1025UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.0	1.7
10°-20°	336.5	4.9
20°-30°	484.5	7.0
30°-40°	545.6	7.9
40°-50°	521.9	7.5
50°-60°	427.2	6.2
60°-70°	288.0	4.2
70°-80°	144.5	2.1
80°-90°	40.4	0.6
90°-100°	46.5	0.7
100°-110°	224.8	3.2
110°-120°	551.0	8.0
120°-130°	699.5	10.1
130°-140°	747.2	10.8
140°-150°	698.7	10.1
150°-160°	563.6	8.1
160°-170°	363.7	5.2
170°-180°	125.3	1.8
0°-30°	942.0	13.6
0°-40°	1487.6	21.5
0°-60°	2436.7	35.2
0°-90°	2909.6	42.0
90°-120°	822.3	11.9
90°-150°	2967.7	42.8
90°-180°	4020.0	58.0
0°-180°	6930.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1287	1287	1287	1287	1287	
5°	1287	1282	1269	1278	1276	122
15°	1227	1216	1187	1181	1174	346
25°	1117	1091	1043	1021	1009	514
35°	966	929	864	819	800	605
45°	794	747	667	607	582	613
55°	603	552	463	403	382	541
65°	412	355	273	222	211	408
75°	218	168	111	100	98	232
85°	55	32	29	27	27	61
90°	1	11	24	27	29	7
95°	60	20	30	37	37	71
105°	292	303	215	41	43	310
115°	548	554	562	572	576	541
125°	772	780	784	786	788	690
135°	961	967	971	974	971	740
145°	1109	1116	1118	1120	1120	694
155°	1222	1220	1221	1226	1220	563
165°	1288	1286	1284	1292	1286	364
175°	1319	1314	1315	1322	1314	126
180°	1319	1319	1319	1319	1319	

TEST NUMBER: P1010974

CATALOG NUMBER: S123RDIP-B775D1025UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1286.8	1286.8	1286.8	1286.8	1286.8
2.5°	1292.0	1287.8	1275.3	1286.8	1284.7
5°	1286.8	1281.5	1269.0	1278.4	1276.3
7.5°	1277.4	1272.1	1256.5	1262.7	1259.6
10°	1264.8	1257.5	1238.7	1239.8	1234.6
12.5°	1247.1	1238.7	1214.7	1213.7	1207.4
15°	1227.3	1215.8	1186.6	1181.3	1174.0
17.5°	1203.3	1190.7	1154.2	1143.8	1133.3
20°	1176.1	1159.4	1119.8	1106.2	1093.7
22.5°	1145.9	1126.0	1083.3	1065.5	1054.0
25°	1116.6	1090.6	1042.6	1020.6	1009.2
27.5°	1081.2	1053.0	1000.8	971.6	953.8
30°	1044.6	1013.3	954.9	919.4	902.7
32.5°	1008.1	971.6	909.0	869.3	851.6
35°	966.4	928.8	864.1	819.2	800.4
37.5°	924.6	883.9	816.1	766.0	743.0
40°	885.0	839.0	765.0	710.7	686.7
42.5°	840.1	794.2	716.9	656.4	635.5
45°	794.2	747.2	666.9	607.4	582.3
47.5°	749.3	697.1	617.8	553.1	531.2
50°	699.2	650.2	565.6	500.9	476.9
52.5°	654.3	600.1	516.6	448.7	427.9
55°	603.2	552.1	463.4	402.8	382.0
57.5°	557.3	502.0	412.2	354.8	337.1
60°	509.3	451.9	365.3	308.9	291.2
62.5°	461.3	403.9	317.3	265.1	246.3
65°	412.2	354.8	273.4	222.3	210.8
67.5°	363.2	304.7	225.4	186.8	174.3
70°	315.2	258.8	185.8	149.2	137.8
72.5°	267.2	211.8	147.1	119.0	115.8
75°	218.1	168.0	110.6	100.2	98.1
77.5°	173.2	127.3	86.6	80.4	78.3
80°	130.4	87.7	65.7	62.6	60.5
82.5°	89.7	54.3	47.0	43.8	43.8
85°	55.3	32.4	29.2	27.1	27.1
87.5°	25.0	13.6	13.6	12.5	11.5
90°	1.0	10.8	23.5	27.4	29.4
92.5°	22.5	16.7	25.5	32.3	33.3
95°	59.8	19.6	30.4	37.2	37.2
97.5°	108.8	81.3	31.4	39.2	40.2
100°	165.6	185.2	32.3	40.2	41.2
102.5°	230.2	243.0	72.5	40.2	42.1
105°	292.0	302.7	214.6	41.2	43.1
107.5°	357.6	366.4	381.1	230.2	101.9
110°	423.3	431.1	441.9	409.5	269.4

TEST NUMBER: P1010974

CATALOG NUMBER: S123RDIP-B775D1025UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	486.0	492.8	503.6	512.4	510.5
115°	547.7	553.6	562.4	572.2	576.1
117.5°	608.4	615.3	620.2	628.0	629.0
120°	664.3	673.1	676.0	683.9	683.9
122.5°	721.1	728.0	731.9	736.8	737.8
125°	772.1	779.9	783.8	785.8	787.7
127.5°	823.0	830.8	835.7	838.7	836.7
130°	870.0	877.9	881.8	885.7	883.7
132.5°	915.1	922.9	925.9	929.8	926.9
135°	961.2	967.0	970.9	973.9	970.9
137.5°	1000.3	1008.2	1010.1	1015.0	1013.1
140°	1039.5	1045.4	1048.3	1052.3	1050.3
142.5°	1075.8	1081.7	1084.6	1087.5	1084.6
145°	1109.1	1116.0	1117.9	1119.9	1119.9
147.5°	1141.4	1146.3	1148.3	1150.2	1145.3
150°	1170.8	1173.8	1175.7	1177.7	1174.7
152.5°	1197.3	1198.3	1199.2	1203.2	1198.3
155°	1221.8	1219.8	1220.8	1225.7	1219.8
157.5°	1241.4	1241.4	1240.4	1246.3	1238.4
160°	1259.0	1258.0	1257.0	1262.9	1256.1
162.5°	1275.7	1272.7	1271.7	1278.6	1272.7
165°	1288.4	1285.5	1284.5	1292.3	1285.5
167.5°	1299.2	1295.3	1295.3	1303.1	1295.3
170°	1308.0	1304.1	1304.1	1311.9	1304.1
172.5°	1313.9	1309.0	1309.9	1317.8	1309.0
175°	1318.8	1313.9	1314.8	1321.7	1313.9
177.5°	1320.7	1315.8	1316.8	1324.6	1314.8
180°	1318.8	1318.8	1318.8	1318.8	1318.8

(END OF REPORT)