

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010977

Luminaire Tested: S123RDIP-B775D1025UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010977
REPORT IS A COMBINATION OF REPORTS P993533 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B775D1025UB2750-4F0-XX-W2A-F_4000K
Description: Define 3 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6949.0 lumens
Efficiency: N/A
Efficacy: 107.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010977

CATALOG NUMBER: S123RDIP-B775D1025UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010977

CATALOG NUMBER: S123RDIP-B775D1025UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49
1	96	92	88	85	88	84	81	78	70	67	65	56	54	53	44	43	42
2	88	81	75	70	80	74	69	65	61	58	54	49	47	45	39	37	36
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	34	32	31
4	74	63	55	50	67	58	51	46	48	43	39	39	36	33	31	28	26
5	68	56	48	43	61	52	45	40	43	38	34	35	32	29	28	25	23
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21
7	58	46	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	21	19	16
9	50	38	30	26	45	35	28	24	30	25	21	25	21	18	20	17	15
10	46	35	28	23	42	32	26	22	27	22	19	23	19	16	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13889	13889	13889
5°	13911	13397	13361
10°	13802	12894	12640
15°	13622	12271	11849
20°	13388	11594	10966
25°	13145	10890	10129
30°	12834	10141	9140
35°	12514	9407	8239
40°	12213	8608	7244
45°	11827	7827	6349
50°	11401	6993	5423
55°	10960	6101	4574
60°	10538	5186	3713
65°	9993	4247	2898
70°	9306	3212	2071
75°	8319	2174	1642
80°	7101	1511	1151
85°	5331	816	603

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11827 cd/sqm

TEST NUMBER: P1010977

CATALOG NUMBER: S123RDIP-B775D1025UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.3	1.7
10°-20°	337.4	4.9
20°-30°	485.8	7.0
30°-40°	547.1	7.9
40°-50°	523.3	7.5
50°-60°	428.4	6.2
60°-70°	288.8	4.2
70°-80°	144.9	2.1
80°-90°	40.5	0.6
90°-100°	46.6	0.7
100°-110°	225.5	3.2
110°-120°	552.5	8.0
120°-130°	701.4	10.1
130°-140°	749.3	10.8
140°-150°	700.6	10.1
150°-160°	565.1	8.1
160°-170°	364.7	5.2
170°-180°	125.7	1.8
0°-30°	944.5	13.6
0°-40°	1491.7	21.5
0°-60°	2443.4	35.2
0°-90°	2917.7	42.0
90°-120°	824.6	11.9
90°-150°	2975.8	42.8
90°-180°	4031.0	58.0
0°-180°	6949.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1290	1290	1290	1290	1290	
5°	1290	1285	1272	1282	1280	122
15°	1231	1219	1190	1185	1177	347
25°	1120	1094	1045	1023	1012	515
35°	969	931	866	822	803	607
45°	796	749	669	609	584	615
55°	605	554	465	404	383	542
65°	413	356	274	223	211	409
75°	219	168	111	100	98	233
85°	56	32	29	27	27	61
90°	1	11	24	28	30	7
95°	60	20	30	37	37	72
105°	293	304	215	41	43	310
115°	549	555	564	574	578	542
125°	774	782	786	788	790	692
135°	964	970	974	977	974	742
145°	1112	1119	1121	1123	1123	696
155°	1225	1223	1224	1229	1223	564
165°	1292	1289	1288	1296	1289	365
175°	1322	1318	1318	1325	1318	126
180°	1322	1322	1322	1322	1322	

TEST NUMBER: P1010977

CATALOG NUMBER: S123RDIP-B775D1025UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1290.3	1290.3	1290.3	1290.3	1290.3
2.5°	1295.5	1291.3	1278.8	1290.3	1288.2
5°	1290.3	1285.1	1272.5	1281.9	1279.8
7.5°	1280.9	1275.6	1259.9	1266.2	1263.1
10°	1268.3	1261.0	1242.2	1243.2	1238.0
12.5°	1250.5	1242.2	1218.1	1217.0	1210.8
15°	1230.6	1219.1	1189.8	1184.6	1177.3
17.5°	1206.6	1194.0	1157.4	1146.9	1136.5
20°	1179.4	1162.6	1122.9	1109.3	1096.7
22.5°	1149.0	1129.1	1086.2	1068.4	1056.9
25°	1119.7	1093.6	1045.4	1023.4	1011.9
27.5°	1084.1	1055.9	1003.6	974.3	956.5
30°	1047.5	1016.1	957.5	921.9	905.2
32.5°	1010.9	974.3	911.5	871.7	853.9
35°	969.0	931.4	866.5	821.5	802.6
37.5°	927.2	886.4	818.3	768.1	745.1
40°	887.4	841.4	767.1	712.6	688.6
42.5°	842.4	796.4	718.9	658.2	637.3
45°	796.4	749.3	668.7	609.0	583.9
47.5°	751.4	699.0	619.5	554.6	532.7
50°	701.1	651.9	567.2	502.3	478.2
52.5°	656.1	601.7	518.0	450.0	429.1
55°	604.9	553.6	464.6	403.9	383.0
57.5°	558.8	503.4	413.4	355.8	338.0
60°	510.7	453.1	366.3	309.8	292.0
62.5°	462.5	405.0	318.1	265.8	247.0
65°	413.4	355.8	274.2	222.9	211.4
67.5°	364.2	305.6	226.0	187.3	174.8
70°	316.0	259.5	186.3	149.6	138.1
72.5°	267.9	212.4	147.6	119.3	116.2
75°	218.7	168.5	110.9	100.5	98.4
77.5°	173.7	127.7	86.9	80.6	78.5
80°	130.8	87.9	65.9	62.8	60.7
82.5°	90.0	54.4	47.1	44.0	44.0
85°	55.5	32.4	29.3	27.2	27.2
87.5°	25.1	13.6	13.6	12.6	11.5
90°	1.0	10.8	23.6	27.5	29.5
92.5°	22.6	16.7	25.5	32.4	33.4
95°	59.9	19.6	30.5	37.3	37.3
97.5°	109.1	81.5	31.4	39.3	40.3
100°	166.0	185.7	32.4	40.3	41.3
102.5°	230.9	243.6	72.7	40.3	42.2
105°	292.8	303.6	215.2	41.3	43.2
107.5°	358.6	367.4	382.2	230.9	102.2
110°	424.4	432.3	443.1	410.7	270.2

TEST NUMBER: P1010977

CATALOG NUMBER: S123RDIP-B775D1025UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	487.3	494.2	505.0	513.8	511.9
115°	549.2	555.1	563.9	573.7	577.7
117.5°	610.1	617.0	621.9	629.7	630.7
120°	666.1	674.9	677.9	685.7	685.7
122.5°	723.1	730.0	733.9	738.8	739.8
125°	774.2	782.0	786.0	787.9	789.9
127.5°	825.3	833.1	838.0	841.0	839.0
130°	872.4	880.3	884.2	888.1	886.2
132.5°	917.6	925.5	928.4	932.3	929.4
135°	963.8	969.7	973.6	976.6	973.6
137.5°	1003.1	1010.9	1012.9	1017.8	1015.8
140°	1042.4	1048.3	1051.2	1055.1	1053.2
142.5°	1078.7	1084.6	1087.6	1090.5	1087.6
145°	1112.1	1119.0	1121.0	1122.9	1122.9
147.5°	1144.5	1149.5	1151.4	1153.4	1148.5
150°	1174.0	1177.0	1178.9	1180.9	1178.0
152.5°	1200.5	1201.5	1202.5	1206.4	1201.5
155°	1225.1	1223.1	1224.1	1229.0	1223.1
157.5°	1244.8	1244.8	1243.8	1249.7	1241.8
160°	1262.4	1261.5	1260.5	1266.4	1259.5
162.5°	1279.1	1276.2	1275.2	1282.1	1276.2
165°	1291.9	1289.0	1288.0	1295.8	1289.0
167.5°	1302.7	1298.8	1298.8	1306.7	1298.8
170°	1311.6	1307.6	1307.6	1315.5	1307.6
172.5°	1317.5	1312.5	1313.5	1321.4	1312.5
175°	1322.4	1317.5	1318.4	1325.3	1317.5
177.5°	1324.3	1319.4	1320.4	1328.3	1318.4
180°	1322.4	1322.4	1322.4	1322.4	1322.4

(END OF REPORT)