

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010672

Luminaire Tested: S123DIP-B560D585UB2750-4F0-XX-W2A-D_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010672
REPORT IS A COMBINATION OF REPORTS P990116 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D585UB2750-4F0-XX-W2A-D_4000K
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4673.0 lumens
Efficiency: N/A
Efficacy: 118.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010672

CATALOG NUMBER: S123DIP-B560D585UB2750-4F0-XX-W2A-D_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010672

CATALOG NUMBER: S123DIP-B560D585UB2750-4F0-XX-W2A-D_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52
1	96	91	87	83	88	84	80	77	70	67	64	57	55	53	45	43	42
2	87	79	73	67	79	73	67	62	60	56	53	49	46	44	39	37	35
3	79	69	62	55	72	64	57	51	53	48	44	43	39	36	34	31	29
4	72	61	53	47	66	56	49	43	47	41	37	38	34	31	30	27	25
5	66	54	46	40	60	50	43	37	42	36	32	34	30	27	27	24	22
6	61	48	40	34	55	45	37	32	38	32	28	31	26	23	25	21	19
7	56	44	36	30	51	40	33	28	34	28	24	28	24	20	22	19	17
8	52	40	32	26	48	37	30	25	31	25	21	26	21	18	21	17	15
9	48	36	28	23	44	33	27	22	28	23	19	23	19	16	19	16	13
10	45	33	26	21	41	31	24	20	26	21	17	22	18	15	18	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7495	7495	7495
5°	7515	7275	7269
10°	7444	7078	7023
15°	7347	6860	6764
20°	7206	6618	6484
25°	7034	6344	6195
30°	6858	6097	5905
35°	6661	5837	5668
40°	6471	5601	5418
45°	6263	5371	5212
50°	6056	5144	4988
55°	5827	4910	4783
60°	5602	4671	4572
65°	5371	4417	4325
70°	5027	4132	4071
75°	4588	3807	3809
80°	4077	3477	3510
85°	3573	3211	3296

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6263 cd/sqm

TEST NUMBER: P1010672

CATALOG NUMBER: S123DIP-B560D585UB2750-4F0-XX-W2A-D_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.0	1.4
10°-20°	188.3	4.0
20°-30°	281.6	6.0
30°-40°	336.2	7.2
40°-50°	351.8	7.5
50°-60°	330.1	7.1
60°-70°	275.7	5.9
70°-80°	197.1	4.2
80°-90°	118.8	2.5
90°-100°	100.7	2.2
100°-110°	184.6	3.9
110°-120°	355.7	7.6
120°-130°	426.3	9.1
130°-140°	442.6	9.5
140°-150°	407.1	8.7
150°-160°	326.8	7.0
160°-170°	210.9	4.5
170°-180°	72.7	1.6
0°-30°	535.9	11.5
0°-40°	872.1	18.7
0°-60°	1553.9	33.3
0°-90°	2145.6	45.9
90°-120°	641.0	13.7
90°-150°	1917.0	41.0
90°-180°	2527.0	54.1
0°-180°	4673.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	696	696	696	696	696	
5°	697	696	691	697	696	66
15°	664	666	665	673	672	187
25°	599	607	609	619	619	276
35°	516	528	538	549	552	323
45°	422	440	459	473	479	325
55°	322	347	374	394	400	288
65°	222	252	285	308	316	220
75°	121	156	194	219	228	129
85°	37	75	115	141	149	38
90°	10	53	99	127	136	9
95°	43	49	93	120	128	48
105°	175	200	181	102	110	186
115°	321	334	366	390	399	318
125°	450	455	479	496	502	402
135°	559	562	572	588	590	430
145°	644	647	648	656	658	403
155°	708	707	708	711	707	326
165°	747	746	745	749	746	211
175°	765	762	762	766	762	73
180°	765	765	765	765	765	

TEST NUMBER: P1010672

CATALOG NUMBER: S123DIP-B560D585UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	696.3	696.3	696.3	696.3	696.3
2.5°	700.1	697.8	691.7	697.8	697.0
5°	697.0	695.5	691.0	697.0	696.3
7.5°	691.7	691.7	687.2	694.7	694.0
10°	684.1	685.6	681.9	689.4	687.9
12.5°	675.0	677.3	675.0	681.9	680.3
15°	663.7	665.9	665.2	672.8	672.0
17.5°	650.0	654.6	653.8	660.6	659.1
20°	634.8	639.4	640.9	647.7	648.5
22.5°	618.9	623.5	625.7	634.8	634.1
25°	599.2	606.8	609.0	618.9	618.9
27.5°	580.2	588.6	593.1	601.5	602.2
30°	559.7	569.6	575.7	584.8	584.8
32.5°	537.0	548.4	556.7	566.6	568.8
35°	515.8	527.9	537.7	549.1	552.2
37.5°	493.0	506.7	518.0	530.9	533.2
40°	470.2	483.9	499.1	512.0	515.0
42.5°	445.2	462.7	478.6	493.0	497.5
45°	421.7	439.9	458.9	473.3	479.3
47.5°	396.7	417.2	438.4	454.3	458.9
50°	372.4	393.6	417.2	434.6	439.9
52.5°	346.6	369.4	395.9	414.1	420.9
55°	321.6	346.6	373.9	394.4	400.5
57.5°	297.3	323.1	352.7	373.2	380.0
60°	271.5	298.8	329.9	351.2	359.5
62.5°	247.3	275.3	308.7	329.9	337.5
65°	222.2	251.8	285.2	307.9	315.5
67.5°	197.2	228.3	261.7	286.7	292.8
70°	170.7	203.3	239.7	263.9	271.5
72.5°	146.4	179.0	216.9	241.9	249.5
75°	120.6	156.2	194.2	219.2	228.3
77.5°	98.6	134.2	172.2	198.7	205.5
80°	75.1	112.3	151.7	177.5	185.1
82.5°	54.6	92.5	132.7	158.5	166.1
85°	37.2	75.1	115.3	141.1	148.7
87.5°	22.8	60.7	99.4	125.1	132.7
90°	10.5	53.2	99.3	127.4	136.1
92.5°	22.2	51.4	94.4	123.4	130.8
95°	43.0	49.3	92.7	120.2	127.8
97.5°	70.7	82.1	88.7	116.0	124.2
100°	102.8	138.5	84.7	111.3	119.5
102.5°	139.6	168.2	103.4	106.0	114.7
105°	175.4	199.9	181.3	102.0	109.9
107.5°	212.7	233.7	273.3	206.3	138.7
110°	250.1	268.2	304.7	305.8	230.5

TEST NUMBER: P1010672

CATALOG NUMBER: S123DIP-B560D585UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	286.4	301.0	336.0	360.2	365.8
115°	321.4	333.9	366.3	390.2	398.6
117.5°	356.6	366.7	395.3	418.1	424.7
120°	388.2	397.1	423.9	445.9	451.2
122.5°	421.2	426.8	452.5	472.0	477.9
125°	450.0	454.6	478.8	495.9	502.3
127.5°	479.6	483.3	505.2	522.0	526.2
130°	506.8	510.6	528.1	544.7	548.1
132.5°	532.2	536.7	549.8	565.7	569.4
135°	558.9	561.6	572.2	587.6	589.6
137.5°	581.6	585.5	591.9	606.8	609.5
140°	603.6	607.0	611.0	624.6	627.3
142.5°	624.7	627.3	629.0	640.6	642.7
145°	644.0	647.2	648.3	655.5	658.5
147.5°	661.9	664.8	665.9	669.3	669.5
150°	679.0	680.7	681.8	683.0	682.7
152.5°	694.3	694.9	695.5	697.7	694.9
155°	708.5	707.4	708.0	710.8	707.4
157.5°	719.9	719.9	719.3	722.7	718.2
160°	730.1	729.5	729.0	732.4	728.4
162.5°	739.8	738.1	737.5	741.5	738.1
165°	747.2	745.5	744.9	749.4	745.5
167.5°	753.4	751.1	751.1	755.7	751.1
170°	758.5	756.2	756.2	760.8	756.2
172.5°	761.9	759.1	759.7	764.2	759.1
175°	764.8	761.9	762.5	766.5	761.9
177.5°	765.9	763.1	763.6	768.2	762.5
180°	764.8	764.8	764.8	764.8	764.8

(END OF REPORT)