

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010986

Luminaire Tested: S123RDIP-B775D1195UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010986
REPORT IS A COMBINATION OF REPORTS P993572 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B775D1195UB2750-4F0-XX-W2A-F_3500K
Description: Define 3 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7733.0 lumens
Efficiency: N/A
Efficacy: 109.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010986

CATALOG NUMBER: S123RDIP-B775D1195UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1010986

CATALOG NUMBER: S123RDIP-B775D1195UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45
1	95	91	88	84	86	83	80	77	68	65	63	53	52	51	40	39	39
2	87	80	74	69	79	73	68	64	59	56	53	47	45	43	36	34	33
3	80	70	63	58	72	64	58	53	53	48	45	42	39	36	32	30	28
4	73	62	55	49	66	57	50	45	47	42	38	37	34	31	29	26	25
5	67	56	48	42	60	51	44	39	42	37	33	34	30	27	26	23	21
6	62	50	42	36	56	46	39	34	38	33	29	30	27	24	24	21	19
7	57	45	37	32	52	41	35	30	34	29	25	28	24	21	22	19	17
8	53	41	33	28	48	38	31	26	31	26	23	25	22	19	20	17	15
9	49	37	30	25	45	34	28	23	29	24	20	23	20	17	18	16	14
10	46	34	27	22	42	31	25	21	26	22	18	22	18	15	17	14	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14032	14032	14032
5°	14055	13535	13499
10°	13944	13026	12769
15°	13763	12397	11971
20°	13525	11713	11079
25°	13280	11002	10233
30°	12967	10246	9234
35°	12643	9503	8324
40°	12338	8697	7319
45°	11949	7908	6414
50°	11518	7065	5479
55°	11073	6164	4621
60°	10645	5239	3752
65°	10095	4290	2928
70°	9403	3244	2093
75°	8407	2197	1658
80°	7177	1527	1163
85°	5379	824	610

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11949 cd/sqm

TEST NUMBER: P1010986

CATALOG NUMBER: S123RDIP-B775D1195UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.5	1.6
10°-20°	340.9	4.4
20°-30°	490.8	6.3
30°-40°	552.8	7.1
40°-50°	528.7	6.8
50°-60°	432.8	5.6
60°-70°	291.8	3.8
70°-80°	146.4	1.9
80°-90°	41.4	0.5
90°-100°	55.3	0.7
100°-110°	267.6	3.5
110°-120°	655.8	8.5
120°-130°	832.5	10.8
130°-140°	889.3	11.5
140°-150°	831.6	10.8
150°-160°	670.8	8.7
160°-170°	432.9	5.6
170°-180°	149.2	1.9
0°-30°	954.3	12.3
0°-40°	1507.0	19.5
0°-60°	2468.6	31.9
0°-90°	2948.2	38.1
90°-120°	978.7	12.7
90°-150°	3532.1	45.7
90°-180°	4785.0	61.9
0°-180°	7733.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1304	1304	1304	1304	1304	
5°	1304	1298	1286	1295	1293	124
15°	1243	1232	1202	1197	1189	350
25°	1131	1105	1056	1034	1022	520
35°	979	941	875	830	811	613
45°	805	757	676	615	590	621
55°	611	559	469	408	387	548
65°	418	360	277	225	214	413
75°	221	170	112	102	99	235
85°	56	33	30	28	28	61
90°	1	13	28	33	35	7
95°	71	23	36	44	44	85
105°	348	360	255	49	51	368
115°	652	659	669	681	686	644
125°	919	928	933	935	938	821
135°	1144	1151	1156	1159	1156	881
145°	1320	1328	1330	1333	1333	826
155°	1454	1452	1453	1459	1452	670
165°	1533	1530	1529	1538	1530	433
175°	1570	1564	1565	1573	1564	149
180°	1570	1570	1570	1570	1570	

TEST NUMBER: P1010986

CATALOG NUMBER: S123RDIP-B775D1195UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1303.6	1303.6	1303.6	1303.6	1303.6
2.5°	1308.9	1304.6	1291.9	1303.6	1301.5
5°	1303.6	1298.3	1285.6	1295.1	1293.0
7.5°	1294.1	1288.8	1272.9	1279.3	1276.1
10°	1281.4	1274.0	1254.9	1256.0	1250.7
12.5°	1263.4	1254.9	1230.6	1229.6	1223.2
15°	1243.3	1231.7	1202.1	1196.8	1189.4
17.5°	1219.0	1206.3	1169.3	1158.7	1148.2
20°	1191.5	1174.6	1134.4	1120.7	1108.0
22.5°	1160.8	1140.8	1097.4	1079.4	1067.8
25°	1131.2	1104.8	1056.2	1034.0	1022.3
27.5°	1095.3	1066.8	1013.9	984.3	966.3
30°	1058.3	1026.6	967.4	931.4	914.5
32.5°	1021.3	984.3	920.9	880.7	862.7
35°	979.0	940.9	875.4	829.9	810.9
37.5°	936.7	895.5	826.8	776.0	752.8
40°	896.5	850.0	775.0	720.0	695.7
42.5°	851.1	804.6	726.3	665.0	643.9
45°	804.6	757.0	675.6	615.3	589.9
47.5°	759.1	706.2	625.9	560.3	538.1
50°	708.3	658.7	573.0	507.5	483.2
52.5°	662.9	607.9	523.3	454.6	433.5
55°	611.1	559.3	469.4	408.1	386.9
57.5°	564.6	508.5	417.6	359.5	341.5
60°	515.9	457.8	370.0	312.9	295.0
62.5°	467.3	409.2	321.4	268.5	249.5
65°	417.6	359.5	277.0	225.2	213.6
67.5°	367.9	308.7	228.4	189.2	176.6
70°	319.3	262.2	188.2	151.2	139.6
72.5°	270.7	214.6	149.1	120.5	117.4
75°	221.0	170.2	112.1	101.5	99.4
77.5°	175.5	129.0	87.8	81.4	79.3
80°	132.2	88.8	66.6	63.4	61.3
82.5°	90.9	55.0	47.6	44.4	44.4
85°	56.0	32.8	29.6	27.5	27.5
87.5°	25.4	13.7	13.7	12.7	11.6
90°	1.2	12.8	28.0	32.7	35.0
92.5°	26.8	19.8	30.3	38.5	39.6
95°	71.1	23.3	36.1	44.3	44.3
97.5°	129.4	96.8	37.3	46.6	47.8
100°	197.1	220.4	38.5	47.8	49.0
102.5°	274.0	289.2	86.3	47.8	50.1
105°	347.5	360.3	255.4	49.0	51.3
107.5°	425.6	436.1	453.6	274.0	121.3
110°	503.7	513.1	525.9	487.4	320.7

TEST NUMBER: P1010986

CATALOG NUMBER: S123RDIP-B775D1195UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	578.4	586.5	599.4	609.9	607.5
115°	651.8	658.8	669.3	681.0	685.7
117.5°	724.1	732.3	738.1	747.5	748.6
120°	790.6	801.1	804.6	813.9	813.9
122.5°	858.2	866.4	871.1	876.9	878.1
125°	918.9	928.2	932.9	935.2	937.5
127.5°	979.5	988.8	994.7	998.2	995.8
130°	1035.5	1044.8	1049.5	1054.1	1051.8
132.5°	1089.1	1098.4	1101.9	1106.6	1103.1
135°	1143.9	1150.9	1155.6	1159.1	1155.6
137.5°	1190.6	1199.9	1202.2	1208.1	1205.7
140°	1237.2	1244.2	1247.7	1252.4	1250.0
142.5°	1280.4	1287.3	1290.8	1294.3	1290.8
145°	1320.0	1328.2	1330.5	1332.8	1332.8
147.5°	1358.5	1364.3	1366.6	1369.0	1363.1
150°	1393.5	1397.0	1399.3	1401.6	1398.1
152.5°	1424.9	1426.1	1427.3	1431.9	1426.1
155°	1454.1	1451.8	1452.9	1458.8	1451.8
157.5°	1477.4	1477.4	1476.3	1483.2	1473.9
160°	1498.4	1497.2	1496.1	1503.1	1494.9
162.5°	1518.2	1514.7	1513.6	1521.7	1514.7
165°	1533.4	1529.9	1528.7	1538.1	1529.9
167.5°	1546.2	1541.6	1541.6	1550.9	1541.6
170°	1556.7	1552.0	1552.0	1561.4	1552.0
172.5°	1563.7	1557.9	1559.0	1568.4	1557.9
175°	1569.5	1563.7	1564.9	1573.0	1563.7
177.5°	1571.9	1566.0	1567.2	1576.5	1564.9
180°	1569.5	1569.5	1569.5	1569.5	1569.5

(END OF REPORT)