

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010679

Luminaire Tested: S123DIP-B560D805UB2750-4F0-XX-W2A-A_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010679
REPORT IS A COMBINATION OF REPORTS P990168 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D805UB2750-4F0-XX-W2A-A_2700K
Description: Define 3 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5464.0 lumens
Efficiency: N/A
Efficacy: 121.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010679

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-A_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1010679

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-A_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50	43	43	43
1	97	92	89	85	88	85	81	78	70	68	66	57	55	54	44	43	43	37	37	37
2	88	81	75	70	80	74	69	65	62	58	55	50	47	45	39	38	36	31	31	31
3	80	71	64	58	73	65	59	54	55	50	46	44	41	38	35	33	31	27	27	27
4	74	63	55	50	67	58	51	46	49	43	40	40	36	33	31	29	27	23	23	23
5	68	56	48	42	62	52	45	40	43	38	34	36	32	29	28	26	23	20	20	20
6	62	50	43	37	57	47	40	34	39	34	30	32	28	25	26	23	21	18	18	18
7	58	46	38	32	53	42	35	30	35	30	26	29	25	22	24	21	18	16	16	16
8	53	41	34	28	49	38	31	27	32	27	23	27	23	20	22	19	17	14	14	14
9	50	38	30	25	45	35	28	24	30	24	21	25	21	18	20	17	15	13	13	13
10	46	34	27	23	42	32	26	21	27	22	19	23	19	16	18	16	14	12	12	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8402	8402	8402	8402
5°	8408	9682	8432	7225
10°	8354	11716	8363	6310
15°	8239	13894	8307	5680
20°	8140	15996	8157	5226
25°	7992	16400	8010	4990
30°	7887	13549	7887	4835
35°	7756	9061	7707	4697
40°	7600	6542	7506	4488
45°	7403	5181	7189	4227
50°	6926	4400	6678	3971
55°	6400	3866	6141	3686
60°	5868	3366	5557	3387
65°	5284	2883	5028	2986
70°	4676	2393	4367	2517
75°	3998	1805	3739	1944
80°	3160	1204	2915	1276
85°	2180	554	1748	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 13551 cd/sqm

TEST NUMBER: P1010679

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-A_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.8	1.4
10°-20°	246.6	4.5
20°-30°	414.9	7.6
30°-40°	468.9	8.6
40°-50°	419.9	7.7
50°-60°	339.0	6.2
60°-70°	236.2	4.3
70°-80°	124.0	2.3
80°-90°	31.8	0.6
90°-100°	35.9	0.7
100°-110°	173.7	3.2
110°-120°	425.7	7.8
120°-130°	540.4	9.9
130°-140°	577.3	10.6
140°-150°	539.8	9.9
150°-160°	435.4	8.0
160°-170°	281.0	5.1
170°-180°	96.8	1.8
0°-30°	738.2	13.5
0°-40°	1207.1	22.1
0°-60°	1966.1	36.0
0°-90°	2358.0	43.2
90°-120°	635.3	11.6
90°-150°	2292.7	42.0
90°-180°	3106.0	56.8
0°-180°	5464.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	781	781	781	781	781	
5°	780	927	782	692	780	74
15°	744	1380	750	564	744	210
25°	681	1638	682	498	681	314
35°	601	883	597	458	601	376
45°	498	476	484	389	498	381
55°	353	324	339	309	353	316
65°	219	210	208	218	219	218
75°	105	108	98	116	105	113
85°	23	25	18	23	23	26
90°	1	23	1	23	1	4
95°	46	29	46	29	46	55
105°	226	33	226	33	226	239
115°	423	445	423	445	423	418
125°	596	609	596	609	596	533
135°	742	750	742	750	742	572
145°	857	865	857	865	857	536
155°	944	942	944	942	944	435
165°	995	993	995	993	995	281
175°	1019	1015	1019	1015	1019	97
180°	1019	1019	1019	1019	1019	

TEST NUMBER: P1010679

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6
2.5°	782.9	788.9	792.0	796.5	801.0	807.8	810.1	813.9	812.4	815.4	816.9
5°	779.9	790.4	799.5	810.9	821.5	829.0	836.6	848.7	857.8	859.3	866.1
7.5°	774.6	789.7	805.6	821.5	841.9	854.0	867.6	884.2	897.9	919.8	928.1
10°	767.7	788.9	811.6	833.6	861.5	880.5	897.1	925.1	953.1	975.8	996.9
12.5°	757.2	783.6	813.1	845.7	882.0	903.9	926.6	963.7	1006.0	1040.8	1063.5
15°	744.3	777.6	815.4	850.2	890.3	931.1	955.3	996.9	1057.5	1090.0	1148.2
17.5°	733.7	767.7	805.6	860.0	914.5	955.3	972.7	1049.1	1090.7	1145.2	1211.0
20°	717.1	760.2	808.6	863.1	933.4	958.4	993.9	1071.1	1122.5	1193.6	1274.5
22.5°	699.7	745.8	804.1	860.8	939.5	965.9	1014.3	1075.6	1157.3	1227.6	1316.9
25°	680.8	730.7	789.7	857.0	934.2	972.7	1018.1	1093.8	1182.3	1270.8	1353.2
27.5°	661.9	716.3	777.6	844.9	919.8	965.2	1010.6	1089.2	1202.7	1298.7	1403.9
30°	643.7	698.2	759.4	828.3	906.9	950.8	993.9	1092.2	1218.6	1326.7	1432.6
32.5°	624.0	680.0	744.3	801.8	881.2	928.1	976.5	1092.2	1228.4	1343.4	1440.2
35°	600.6	658.1	713.3	770.8	849.4	901.6	956.1	1084.7	1237.5	1348.7	1408.4
37.5°	577.9	628.6	676.2	732.2	814.6	870.6	933.4	1075.6	1232.9	1326.0	1342.6
40°	552.2	602.9	641.4	693.6	780.6	845.7	909.2	1063.5	1213.3	1272.3	1223.9
42.5°	527.2	567.3	600.6	651.3	745.8	809.4	878.2	1041.6	1174.7	1186.8	1077.9
45°	498.5	527.2	556.7	614.2	708.0	773.0	849.4	1009.8	1112.7	1077.9	940.2
47.5°	461.4	487.1	519.6	572.6	667.9	735.2	807.8	969.0	1022.7	950.0	799.5
50°	425.9	447.8	478.0	529.5	625.5	691.4	768.5	904.7	931.1	816.9	689.1
52.5°	390.3	406.9	436.4	487.9	583.9	647.5	717.8	838.9	823.7	701.2	587.7
55°	353.2	367.6	395.6	446.3	535.5	596.0	663.4	757.9	718.6	602.1	511.3
57.5°	316.9	332.1	360.8	403.2	487.1	546.1	599.8	674.0	615.0	521.9	441.7
60°	284.4	297.3	319.2	360.8	437.2	484.9	534.0	584.7	535.5	445.5	384.3
62.5°	250.4	262.5	282.9	320.7	386.5	428.9	468.2	509.8	455.4	389.5	335.1
65°	218.6	228.4	247.3	282.1	335.8	370.6	402.4	431.1	387.3	326.8	285.9
67.5°	189.9	198.2	214.1	245.1	290.5	315.4	341.1	365.3	328.3	279.9	245.1
70°	158.8	165.7	180.0	202.7	239.0	264.7	283.7	301.8	268.5	229.9	206.5
72.5°	131.6	138.4	147.5	170.9	195.9	211.8	232.2	242.0	223.1	191.4	167.9
75°	105.1	110.4	118.8	133.9	157.3	167.9	180.8	188.3	170.9	149.8	135.4
77.5°	82.4	84.7	90.8	101.4	117.2	129.3	139.2	143.7	131.6	118.0	105.9
80°	58.2	61.3	65.8	74.9	87.0	90.8	96.8	102.1	94.6	82.4	74.9
82.5°	38.6	42.4	44.6	48.4	56.0	60.5	62.0	66.6	59.8	55.2	52.2
85°	22.7	24.2	25.0	27.2	31.0	33.3	35.6	36.3	34.8	34.0	31.0
87.5°	11.3	11.3	11.3	12.9	13.6	15.1	15.9	15.9	15.9	15.1	14.4
90°	0.8	2.5	4.1	5.8	7.5	8.3	9.4	11.6	13.8	16.0	18.2
92.5°	17.4	16.4	15.4	14.4	13.4	12.9	13.7	15.2	16.7	18.2	19.7
95°	46.2	39.3	32.4	25.5	18.6	15.1	16.0	17.9	19.8	21.6	23.5
97.5°	84.0	79.3	74.6	69.9	65.2	62.8	58.5	49.9	41.4	32.8	24.2
100°	127.9	131.3	134.7	138.0	141.4	143.1	130.0	103.7	77.5	51.2	25.0
102.5°	177.9	180.1	182.3	184.4	186.6	187.7	173.1	143.8	114.5	85.3	56.0
105°	225.6	227.4	229.3	231.1	233.0	233.9	226.3	211.2	196.1	180.9	165.8
107.5°	276.3	277.8	279.3	280.8	282.3	283.1	284.4	286.9	289.4	291.9	294.4
110°	327.0	328.3	329.7	331.0	332.3	333.0	333.9	335.8	337.7	339.5	341.4

TEST NUMBER: P1010679

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	375.4	376.6	377.8	378.9	380.1	380.7	381.6	383.5	385.4	387.2	389.1
115°	423.1	424.1	425.1	426.2	427.2	427.7	428.5	430.0	431.5	433.0	434.5
117.5°	470.1	471.3	472.4	473.6	474.7	475.3	475.7	476.6	477.4	478.3	479.1
120°	513.2	514.7	516.2	517.7	519.2	520.0	520.3	520.8	521.3	521.8	522.3
122.5°	557.1	558.3	559.5	560.6	561.8	562.4	562.7	563.4	564.1	564.7	565.4
125°	596.5	597.8	599.2	600.5	601.8	602.5	602.8	603.5	604.2	604.8	605.5
127.5°	635.8	637.2	638.5	639.9	641.2	641.9	642.3	643.2	644.0	644.9	645.7
130°	672.2	673.5	674.9	676.2	677.5	678.2	678.5	679.2	679.9	680.5	681.2
132.5°	707.0	708.3	709.7	711.0	712.3	713.0	713.3	713.8	714.3	714.8	715.3
135°	742.5	743.5	744.5	745.6	746.6	747.1	747.4	748.1	748.8	749.4	750.1
137.5°	772.8	774.2	775.5	776.9	778.2	778.9	779.1	779.4	779.7	780.1	780.4
140°	803.1	804.1	805.1	806.1	807.1	807.6	807.9	808.4	808.9	809.4	809.9
142.5°	831.1	832.1	833.1	834.1	835.1	835.6	835.9	836.4	836.9	837.4	837.9
145°	856.8	858.0	859.2	860.3	861.5	862.1	862.3	862.6	863.0	863.3	863.7
147.5°	881.8	882.6	883.5	884.3	885.2	885.6	885.8	886.1	886.4	886.8	887.1
150°	904.5	905.0	905.5	906.0	906.5	906.8	907.0	907.3	907.6	908.0	908.3
152.5°	925.0	925.2	925.3	925.5	925.6	925.7	925.8	926.0	926.1	926.3	926.5
155°	943.9	943.6	943.2	942.9	942.6	942.4	942.5	942.6	942.8	942.9	943.1
157.5°	959.0	959.0	959.0	959.0	959.0	959.0	958.9	958.8	958.6	958.5	958.3
160°	972.6	972.4	972.3	972.1	972.0	971.9	971.8	971.6	971.5	971.3	971.1
162.5°	985.5	985.0	984.5	984.0	983.5	983.2	983.1	983.0	982.8	982.7	982.5
165°	995.4	994.9	994.4	993.9	993.4	993.1	993.0	992.8	992.7	992.5	992.3
167.5°	1003.7	1003.0	1002.4	1001.7	1001.0	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7
170°	1010.5	1009.8	1009.2	1008.5	1007.8	1007.5	1007.5	1007.5	1007.5	1007.5	1007.5
172.5°	1015.0	1014.2	1013.4	1012.5	1011.7	1011.3	1011.4	1011.5	1011.7	1011.8	1012.0
175°	1018.8	1018.0	1017.1	1016.3	1015.4	1015.0	1015.1	1015.3	1015.4	1015.6	1015.8
177.5°	1020.3	1019.5	1018.7	1017.8	1017.0	1016.6	1016.7	1016.8	1017.0	1017.1	1017.3
180°	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8

TEST NUMBER: P1010679

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6
2.5°	822.2	823.7	829.0	832.8	840.4	839.6	839.6	838.9	836.6	840.4	842.6
5°	879.7	892.6	894.1	910.7	911.5	918.3	922.8	919.0	928.1	927.4	920.5
7.5°	950.8	968.2	976.5	992.4	1010.6	1006.0	1023.4	1026.4	1024.9	1032.5	1037.8
10°	1028.7	1059.0	1080.1	1109.6	1117.2	1121.7	1133.1	1142.9	1162.6	1147.5	1157.3
12.5°	1118.0	1139.9	1167.9	1214.8	1238.2	1253.4	1258.7	1265.5	1279.1	1270.8	1271.5
15°	1192.8	1222.3	1270.0	1328.2	1335.1	1354.0	1349.4	1390.3	1409.9	1380.4	1397.1
17.5°	1270.8	1310.1	1366.8	1417.5	1446.2	1459.1	1471.2	1510.5	1509.0	1504.5	1508.3
20°	1320.7	1385.0	1455.3	1522.6	1531.0	1540.8	1573.3	1590.0	1586.9	1599.8	1608.1
22.5°	1391.0	1459.1	1534.0	1578.6	1597.5	1608.9	1634.6	1645.2	1649.7	1652.7	1647.4
25°	1450.0	1522.6	1577.9	1617.2	1628.5	1634.6	1642.9	1645.9	1643.7	1638.4	1642.9
27.5°	1490.1	1548.4	1586.2	1604.3	1598.3	1588.4	1572.6	1562.0	1538.5	1527.2	1540.8
30°	1506.8	1532.5	1543.8	1513.6	1483.3	1459.1	1428.8	1372.9	1329.0	1341.9	1324.5
32.5°	1480.3	1463.6	1409.2	1331.3	1307.8	1268.5	1183.0	1117.2	1119.5	1084.7	1099.1
35°	1402.4	1326.7	1223.9	1105.9	1074.8	1053.7	959.9	945.5	915.2	882.7	891.8
37.5°	1264.7	1154.3	1029.5	942.5	896.3	850.2	797.2	765.5	747.3	733.7	744.3
40°	1096.8	962.1	859.3	781.4	742.0	712.5	676.2	644.5	624.0	621.8	625.5
42.5°	931.9	818.4	723.9	649.8	636.9	602.1	578.6	553.7	547.6	537.8	543.1
45°	788.9	696.6	618.7	558.2	543.1	534.0	505.3	489.4	482.6	476.5	485.6
47.5°	685.3	588.5	531.8	495.4	480.3	465.2	449.3	438.7	433.4	434.2	433.4
50°	585.5	514.4	464.4	436.4	427.4	416.8	403.9	397.1	394.8	388.0	393.3
52.5°	503.8	452.3	417.5	391.1	384.3	376.7	366.1	362.3	357.0	355.5	355.5
55°	438.0	397.9	369.9	352.5	344.2	338.1	332.1	327.5	323.7	323.7	323.7
57.5°	386.5	351.7	331.3	316.2	313.2	307.1	300.3	300.3	295.0	294.2	296.5
60°	342.7	311.6	295.8	282.9	278.4	276.8	270.0	270.0	268.5	264.7	267.8
62.5°	298.0	275.3	261.7	251.9	247.3	247.3	242.0	238.3	238.3	239.0	237.5
65°	257.2	240.5	228.4	220.9	218.6	215.6	214.8	211.8	209.5	210.3	209.5
67.5°	220.9	208.0	199.7	193.6	189.9	188.3	186.1	186.1	184.6	185.3	181.5
70°	188.3	175.5	168.7	162.6	161.1	161.1	158.1	158.8	157.3	159.6	158.1
72.5°	155.1	145.2	139.9	137.7	136.2	135.4	133.9	132.4	131.6	133.1	132.4
75°	125.6	117.2	113.5	111.9	110.4	110.4	109.7	108.9	108.2	108.2	108.2
77.5°	97.6	92.3	87.7	89.3	87.0	87.7	85.5	85.5	86.2	85.5	85.5
80°	71.9	68.1	68.1	66.6	63.5	65.1	65.1	62.8	62.0	63.5	61.3
82.5°	47.7	46.9	45.4	44.6	43.1	43.9	43.1	42.4	41.6	43.1	41.6
85°	28.0	28.0	27.2	25.7	27.2	26.5	25.7	25.7	25.0	25.0	25.0
87.5°	14.4	12.9	12.9	12.1	12.9	11.3	12.1	11.3	10.6	11.3	10.6
90°	18.9	19.5	20.2	20.9	21.2	21.4	21.7	22.0	22.4	22.7	22.4
92.5°	20.9	22.1	23.2	24.4	25.0	25.1	25.2	25.4	25.5	25.7	25.5
95°	24.7	25.9	27.0	28.2	28.8	28.8	28.8	28.8	28.8	28.8	28.8
97.5°	25.6	26.9	28.3	29.6	30.3	30.4	30.5	30.7	30.8	31.0	30.8
100°	26.3	27.7	29.0	30.3	31.0	31.1	31.3	31.4	31.6	31.8	31.6
102.5°	50.4	44.9	39.3	33.8	31.0	31.2	31.5	31.8	32.2	32.5	32.2
105°	136.0	106.2	76.5	46.7	31.8	32.0	32.3	32.6	33.0	33.3	33.0
107.5°	268.5	242.6	216.7	190.8	177.9	166.9	144.8	122.8	100.7	78.7	100.7
110°	335.8	330.3	324.7	319.2	316.4	304.4	280.3	256.3	232.2	208.2	232.2

TEST NUMBER: P1010679

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	390.6	392.1	393.6	395.1	395.9	395.7	395.4	395.1	394.7	394.4	394.7
115°	436.2	437.8	439.5	441.2	442.0	442.3	443.0	443.7	444.4	445.1	444.4
117.5°	480.5	481.8	483.2	484.5	485.2	485.3	485.4	485.6	485.7	485.9	485.7
120°	523.6	525.0	526.3	527.6	528.3	528.3	528.3	528.3	528.3	528.3	528.3
122.5°	566.2	567.1	567.9	568.8	569.2	569.3	569.5	569.6	569.8	570.0	569.8
125°	605.9	606.2	606.6	606.9	607.1	607.3	607.6	607.9	608.3	608.6	608.3
127.5°	646.2	646.7	647.2	647.7	647.9	647.7	647.4	647.1	646.7	646.4	646.7
130°	681.9	682.6	683.3	684.0	684.3	684.1	683.8	683.4	683.1	682.7	683.1
132.5°	716.0	716.6	717.3	718.0	718.3	718.1	717.6	717.1	716.6	716.1	716.6
135°	750.6	751.1	751.6	752.1	752.4	752.1	751.6	751.1	750.6	750.1	750.6
137.5°	781.2	782.1	782.9	783.8	784.2	784.0	783.7	783.4	783.0	782.7	783.0
140°	810.6	811.2	811.9	812.6	812.9	812.7	812.4	812.1	811.7	811.4	811.7
142.5°	838.4	838.9	839.4	839.9	840.2	839.9	839.4	838.9	838.4	837.9	838.4
145°	864.0	864.4	864.7	865.0	865.2	865.2	865.2	865.2	865.2	865.2	865.2
147.5°	887.4	887.8	888.1	888.4	888.6	888.2	887.3	886.5	885.6	884.8	885.6
150°	908.6	909.0	909.3	909.6	909.8	909.6	909.1	908.6	908.1	907.6	908.1
152.5°	927.2	927.8	928.5	929.2	929.5	929.1	928.2	927.4	926.5	925.7	926.5
155°	943.9	944.8	945.6	946.5	946.9	946.4	945.4	944.4	943.4	942.4	943.4
157.5°	959.3	960.3	961.3	962.3	962.8	962.1	960.8	959.5	958.1	956.8	958.1
160°	972.1	973.1	974.2	975.2	975.7	975.1	973.9	972.8	971.6	970.4	971.6
162.5°	983.7	984.9	986.0	987.2	987.8	987.3	986.3	985.2	984.2	983.2	984.2
165°	993.7	995.0	996.4	997.7	998.4	997.8	996.6	995.5	994.3	993.1	994.3
167.5°	1002.0	1003.4	1004.7	1006.0	1006.7	1006.0	1004.7	1003.4	1002.0	1000.7	1002.0
170°	1008.8	1010.2	1011.5	1012.8	1013.5	1012.8	1011.5	1010.2	1008.8	1007.5	1008.8
172.5°	1013.4	1014.7	1016.1	1017.4	1018.1	1017.3	1015.8	1014.3	1012.8	1011.3	1012.8
175°	1017.0	1018.2	1019.3	1020.5	1021.1	1020.4	1019.1	1017.7	1016.4	1015.0	1016.4
177.5°	1018.7	1020.0	1021.4	1022.7	1023.4	1022.6	1020.9	1019.2	1017.5	1015.8	1017.5
180°	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8

TEST NUMBER: P1010679

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6
2.5°	836.6	838.9	832.8	831.3	831.3	834.3	832.0	811.6	815.4	810.9	809.4
5°	928.9	924.3	918.3	915.2	911.5	900.9	900.1	876.7	872.1	857.0	850.2
7.5°	1030.2	1026.4	1008.3	1006.0	1004.5	994.7	969.7	944.7	926.6	909.2	892.6
10°	1146.0	1134.6	1126.3	1109.6	1101.3	1087.7	1055.2	1031.7	1000.7	974.2	939.5
12.5°	1285.1	1272.3	1244.3	1232.2	1221.6	1183.8	1151.2	1124.8	1064.3	1046.1	1003.0
15°	1387.2	1360.0	1357.0	1330.5	1329.0	1287.4	1225.4	1196.6	1149.7	1083.2	1038.5
17.5°	1497.7	1473.5	1454.6	1422.8	1418.3	1378.9	1333.5	1263.2	1211.8	1148.2	1091.5
20°	1578.6	1565.8	1533.2	1520.4	1493.9	1460.6	1413.7	1326.7	1263.9	1200.4	1130.8
22.5°	1642.9	1630.0	1604.3	1586.9	1571.8	1528.7	1472.7	1398.6	1312.4	1229.2	1157.3
25°	1642.2	1638.4	1627.8	1619.5	1608.1	1576.3	1529.4	1458.3	1362.3	1270.8	1170.9
27.5°	1549.1	1559.7	1577.9	1586.9	1584.7	1580.1	1553.7	1493.9	1407.7	1298.7	1186.8
30°	1355.5	1394.1	1428.1	1473.5	1487.1	1520.4	1535.5	1501.5	1432.6	1331.3	1207.2
32.5°	1124.0	1180.0	1254.1	1279.1	1322.2	1386.5	1458.3	1471.2	1428.1	1350.2	1220.1
35°	922.1	968.2	1025.7	1065.0	1103.6	1208.0	1298.7	1377.4	1391.8	1340.3	1217.1
37.5°	763.2	795.7	846.4	879.7	915.2	1004.5	1131.6	1233.7	1305.6	1307.1	1208.7
40°	648.2	662.6	706.5	730.7	764.7	841.9	955.3	1088.5	1193.6	1242.0	1186.8
42.5°	549.1	568.1	604.4	622.5	644.5	711.8	786.7	913.0	1043.1	1146.7	1146.0
45°	490.1	503.8	520.4	535.5	560.5	600.6	686.1	780.6	905.4	1022.7	1068.8
47.5°	438.0	450.8	467.5	472.0	488.6	526.5	578.6	661.1	777.6	894.1	981.1
50°	394.1	404.7	416.0	424.3	431.9	462.9	502.3	571.8	664.9	777.6	885.7
52.5°	360.0	367.6	377.4	382.0	388.8	411.5	441.7	493.2	569.6	672.4	777.6
55°	328.3	333.6	339.6	347.2	350.2	366.9	390.3	434.2	490.9	583.2	683.0
57.5°	298.8	301.0	304.8	309.4	313.2	327.5	347.9	377.4	427.4	498.5	593.0
60°	265.5	271.5	273.8	278.4	280.6	292.0	307.9	332.8	371.4	432.7	503.8
62.5°	237.5	241.3	245.1	247.3	252.6	256.4	269.3	292.0	323.7	369.1	433.4
65°	212.5	214.1	216.3	218.6	220.1	224.7	236.8	251.9	276.1	316.2	366.1
67.5°	183.8	185.3	188.3	189.1	190.6	196.7	203.5	216.3	236.8	267.0	307.9
70°	155.8	158.1	159.6	161.1	163.4	165.7	173.2	183.8	199.7	220.9	252.6
72.5°	131.6	133.9	133.9	135.4	134.6	137.7	145.2	152.8	163.4	180.8	208.8
75°	107.4	107.4	108.9	109.7	110.4	113.5	116.5	122.5	130.9	144.5	161.9
77.5°	84.7	84.0	85.5	85.5	85.5	87.7	90.8	93.8	99.1	108.9	122.5
80°	62.0	62.0	63.5	64.3	62.8	63.5	65.1	68.1	71.9	78.7	86.2
82.5°	40.8	43.9	43.1	43.9	43.1	44.6	45.4	46.1	47.7	50.7	56.0
85°	25.0	25.0	25.0	25.7	25.0	25.7	25.7	25.7	26.5	28.0	30.3
87.5°	10.6	10.6	10.6	11.3	10.6	10.6	11.3	10.6	11.3	11.3	12.1
90°	22.0	21.7	21.4	21.2	20.9	20.2	19.5	18.9	18.2	16.0	13.8
92.5°	25.4	25.2	25.1	25.0	24.4	23.2	22.1	20.9	19.7	18.2	16.7
95°	28.8	28.8	28.8	28.8	28.2	27.0	25.9	24.7	23.5	21.6	19.8
97.5°	30.7	30.5	30.4	30.3	29.6	28.3	26.9	25.6	24.2	32.8	41.4
100°	31.4	31.3	31.1	31.0	30.3	29.0	27.7	26.3	25.0	51.2	77.5
102.5°	31.8	31.5	31.2	31.0	33.8	39.3	44.9	50.4	56.0	85.3	114.5
105°	32.6	32.3	32.0	31.8	46.7	76.5	106.2	136.0	165.8	180.9	196.1
107.5°	122.8	144.8	166.9	177.9	190.8	216.7	242.6	268.5	294.4	291.9	289.4
110°	256.3	280.3	304.4	316.4	319.2	324.7	330.3	335.8	341.4	339.5	337.7

TEST NUMBER: P1010679

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	395.1	395.4	395.7	395.9	395.1	393.6	392.1	390.6	389.1	387.2	385.4
115°	443.7	443.0	442.3	442.0	441.2	439.5	437.8	436.2	434.5	433.0	431.5
117.5°	485.6	485.4	485.3	485.2	484.5	483.2	481.8	480.5	479.1	478.3	477.4
120°	528.3	528.3	528.3	528.3	527.6	526.3	525.0	523.6	522.3	521.8	521.3
122.5°	569.6	569.5	569.3	569.2	568.8	567.9	567.1	566.2	565.4	564.7	564.1
125°	607.9	607.6	607.3	607.1	606.9	606.6	606.2	605.9	605.5	604.8	604.2
127.5°	647.1	647.4	647.7	647.9	647.7	647.2	646.7	646.2	645.7	644.9	644.0
130°	683.4	683.8	684.1	684.3	684.0	683.3	682.6	681.9	681.2	680.5	679.9
132.5°	717.1	717.6	718.1	718.3	718.0	717.3	716.6	716.0	715.3	714.8	714.3
135°	751.1	751.6	752.1	752.4	752.1	751.6	751.1	750.6	750.1	749.4	748.8
137.5°	783.4	783.7	784.0	784.2	783.8	782.9	782.1	781.2	780.4	780.1	779.7
140°	812.1	812.4	812.7	812.9	812.6	811.9	811.2	810.6	809.9	809.4	808.9
142.5°	838.9	839.4	839.9	840.2	839.9	839.4	838.9	838.4	837.9	837.4	836.9
145°	865.2	865.2	865.2	865.2	865.0	864.7	864.4	864.0	863.7	863.3	863.0
147.5°	886.5	887.3	888.2	888.6	888.4	888.1	887.8	887.4	887.1	886.8	886.4
150°	908.6	909.1	909.6	909.8	909.6	909.3	909.0	908.6	908.3	908.0	907.6
152.5°	927.4	928.2	929.1	929.5	929.2	928.5	927.8	927.2	926.5	926.3	926.1
155°	944.4	945.4	946.4	946.9	946.5	945.6	944.8	943.9	943.1	942.9	942.8
157.5°	959.5	960.8	962.1	962.8	962.3	961.3	960.3	959.3	958.3	958.5	958.6
160°	972.8	973.9	975.1	975.7	975.2	974.2	973.1	972.1	971.1	971.3	971.5
162.5°	985.2	986.3	987.3	987.8	987.2	986.0	984.9	983.7	982.5	982.7	982.8
165°	995.5	996.6	997.8	998.4	997.7	996.4	995.0	993.7	992.3	992.5	992.7
167.5°	1003.4	1004.7	1006.0	1006.7	1006.0	1004.7	1003.4	1002.0	1000.7	1000.7	1000.7
170°	1010.2	1011.5	1012.8	1013.5	1012.8	1011.5	1010.2	1008.8	1007.5	1007.5	1007.5
172.5°	1014.3	1015.8	1017.3	1018.1	1017.4	1016.1	1014.7	1013.4	1012.0	1011.8	1011.7
175°	1017.7	1019.1	1020.4	1021.1	1020.5	1019.3	1018.2	1017.0	1015.8	1015.6	1015.4
177.5°	1019.2	1020.9	1022.6	1023.4	1022.7	1021.4	1020.0	1018.7	1017.3	1017.1	1017.0
180°	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8

TEST NUMBER: P1010679

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6
2.5°	801.8	799.5	799.5	798.0	793.5	785.1	784.4	785.9	781.4	776.8	770.0
5°	841.1	826.7	822.2	817.7	808.6	793.5	787.4	782.1	773.8	764.0	753.4
7.5°	874.4	854.0	847.9	839.6	821.5	800.3	786.7	775.3	764.0	750.4	737.5
10°	916.0	886.5	872.1	860.0	835.1	805.6	785.1	768.5	750.4	733.7	717.1
12.5°	962.9	915.2	910.7	881.2	852.5	808.6	783.6	759.4	735.2	714.8	697.4
15°	1002.2	950.0	931.1	911.5	856.2	801.8	777.6	750.4	722.4	700.4	674.7
17.5°	1027.2	984.1	944.0	917.5	860.0	811.6	764.7	733.7	704.2	674.0	652.8
20°	1057.5	994.7	959.9	924.3	867.6	804.1	757.2	718.6	682.3	655.0	629.3
22.5°	1087.7	1003.0	974.2	935.7	869.1	796.5	743.5	705.0	663.4	636.1	608.1
25°	1084.7	1015.1	967.4	934.9	854.0	789.7	727.7	682.3	643.7	608.9	580.9
27.5°	1087.0	1001.5	953.1	915.2	843.4	779.9	711.0	663.4	623.3	587.0	557.5
30°	1087.7	981.1	938.7	893.3	823.7	756.4	692.1	643.7	601.3	562.0	535.5
32.5°	1085.4	964.4	911.5	870.6	792.7	733.7	670.2	618.7	575.6	539.3	514.4
35°	1080.1	944.7	883.5	832.0	760.9	701.2	649.8	596.8	550.7	517.4	488.6
37.5°	1065.8	923.6	854.0	803.3	723.9	663.4	618.0	574.1	529.5	490.1	465.9
40°	1055.2	894.8	824.5	769.3	683.8	624.8	587.0	545.4	501.5	465.9	442.5
42.5°	1031.0	867.6	794.2	728.4	644.5	583.9	548.4	515.1	477.3	442.5	421.3
45°	991.6	838.1	757.2	690.6	601.3	543.9	511.3	484.1	450.8	417.5	396.4
47.5°	936.4	795.7	717.8	651.3	559.0	500.7	468.2	447.8	421.3	393.3	375.2
50°	876.7	749.6	677.7	611.9	518.1	461.4	429.6	410.7	393.3	367.6	350.2
52.5°	798.8	700.4	631.6	568.8	474.3	419.8	391.8	378.2	360.0	341.9	326.8
55°	723.1	636.9	580.2	520.4	431.1	380.5	353.2	338.9	328.3	313.2	301.0
57.5°	635.4	577.9	525.7	471.2	391.1	344.9	319.2	301.8	295.0	288.2	276.8
60°	554.4	510.6	468.2	422.8	349.5	307.9	282.9	269.3	262.5	257.9	250.4
62.5°	480.3	446.3	410.0	373.7	307.1	269.3	250.4	236.8	230.7	229.9	223.1
65°	409.2	385.0	355.5	320.0	267.8	234.5	216.3	208.0	201.2	201.2	195.9
67.5°	338.1	321.5	298.0	273.1	232.2	201.2	184.6	177.0	173.2	173.2	169.4
70°	281.4	270.0	248.9	226.9	191.4	167.9	155.1	148.3	146.0	146.7	143.7
72.5°	228.4	216.3	198.9	183.0	156.6	139.2	130.1	122.5	118.8	119.5	118.8
75°	177.0	170.9	155.8	143.7	122.5	110.4	102.1	98.3	95.3	96.1	94.6
77.5°	133.1	124.1	115.7	107.4	94.6	84.7	77.9	74.1	71.9	71.9	71.9
80°	90.8	89.3	82.4	77.9	67.3	59.8	54.5	53.7	51.4	51.4	51.4
82.5°	59.0	55.2	51.4	48.4	42.4	37.8	35.6	34.0	33.3	32.5	34.0
85°	32.5	30.3	28.7	25.7	23.4	21.2	18.9	18.2	17.4	18.2	17.4
87.5°	12.9	10.6	10.6	9.8	9.1	8.3	8.3	6.8	6.8	6.1	6.1
90°	11.6	9.4	8.3	7.5	5.8	4.1	2.5	0.8	2.5	4.1	5.8
92.5°	15.2	13.7	12.9	13.4	14.4	15.4	16.4	17.4	16.4	15.4	14.4
95°	17.9	16.0	15.1	18.6	25.5	32.4	39.3	46.2	39.3	32.4	25.5
97.5°	49.9	58.5	62.8	65.2	69.9	74.6	79.3	84.0	79.3	74.6	69.9
100°	103.7	130.0	143.1	141.4	138.0	134.7	131.3	127.9	131.3	134.7	138.0
102.5°	143.8	173.1	187.7	186.6	184.4	182.3	180.1	177.9	180.1	182.3	184.4
105°	211.2	226.3	233.9	233.0	231.1	229.3	227.4	225.6	227.4	229.3	231.1
107.5°	286.9	284.4	283.1	282.3	280.8	279.3	277.8	276.3	277.8	279.3	280.8
110°	335.8	333.9	333.0	332.3	331.0	329.7	328.3	327.0	328.3	329.7	331.0

TEST NUMBER: P1010679

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	383.5	381.6	380.7	380.1	378.9	377.8	376.6	375.4	376.6	377.8	378.9
115°	430.0	428.5	427.7	427.2	426.2	425.1	424.1	423.1	424.1	425.1	426.2
117.5°	476.6	475.7	475.3	474.7	473.6	472.4	471.3	470.1	471.3	472.4	473.6
120°	520.8	520.3	520.0	519.2	517.7	516.2	514.7	513.2	514.7	516.2	517.7
122.5°	563.4	562.7	562.4	561.8	560.6	559.5	558.3	557.1	558.3	559.5	560.6
125°	603.5	602.8	602.5	601.8	600.5	599.2	597.8	596.5	597.8	599.2	600.5
127.5°	643.2	642.3	641.9	641.2	639.9	638.5	637.2	635.8	637.2	638.5	639.9
130°	679.2	678.5	678.2	677.5	676.2	674.9	673.5	672.2	673.5	674.9	676.2
132.5°	713.8	713.3	713.0	712.3	711.0	709.7	708.3	707.0	708.3	709.7	711.0
135°	748.1	747.4	747.1	746.6	745.6	744.5	743.5	742.5	743.5	744.5	745.6
137.5°	779.4	779.1	778.9	778.2	776.9	775.5	774.2	772.8	774.2	775.5	776.9
140°	808.4	807.9	807.6	807.1	806.1	805.1	804.1	803.1	804.1	805.1	806.1
142.5°	836.4	835.9	835.6	835.1	834.1	833.1	832.1	831.1	832.1	833.1	834.1
145°	862.6	862.3	862.1	861.5	860.3	859.2	858.0	856.8	858.0	859.2	860.3
147.5°	886.1	885.8	885.6	885.2	884.3	883.5	882.6	881.8	882.6	883.5	884.3
150°	907.3	907.0	906.8	906.5	906.0	905.5	905.0	904.5	905.0	905.5	906.0
152.5°	926.0	925.8	925.7	925.6	925.5	925.3	925.2	925.0	925.2	925.3	925.5
155°	942.6	942.5	942.4	942.6	942.9	943.2	943.6	943.9	943.6	943.2	942.9
157.5°	958.8	958.9	959.0	959.0	959.0	959.0	959.0	959.0	959.0	959.0	959.0
160°	971.6	971.8	971.9	972.0	972.1	972.3	972.4	972.6	972.4	972.3	972.1
162.5°	983.0	983.1	983.2	983.5	984.0	984.5	985.0	985.5	985.0	984.5	984.0
165°	992.8	993.0	993.1	993.4	993.9	994.4	994.9	995.4	994.9	994.4	993.9
167.5°	1000.7	1000.7	1000.7	1001.0	1001.7	1002.4	1003.0	1003.7	1003.0	1002.4	1001.7
170°	1007.5	1007.5	1007.5	1007.8	1008.5	1009.2	1009.8	1010.5	1009.8	1009.2	1008.5
172.5°	1011.5	1011.4	1011.3	1011.7	1012.5	1013.4	1014.2	1015.0	1014.2	1013.4	1012.5
175°	1015.3	1015.1	1015.0	1015.4	1016.3	1017.1	1018.0	1018.8	1018.0	1017.1	1016.3
177.5°	1016.8	1016.7	1016.6	1017.0	1017.8	1018.7	1019.5	1020.3	1019.5	1018.7	1017.8
180°	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8

TEST NUMBER: P1010679

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6
2.5°	768.5	767.7	769.3	764.7	757.2	753.4	742.8	740.5	739.8	740.5	741.3
5°	747.3	746.6	744.3	736.7	727.7	720.9	708.0	707.2	702.7	698.2	700.4
7.5°	726.9	723.9	719.3	709.5	697.4	689.8	679.2	671.7	665.6	661.9	658.8
10°	706.5	701.9	697.4	684.5	669.4	658.1	645.2	639.2	632.4	629.3	626.3
12.5°	680.0	675.5	667.1	652.0	642.9	628.6	615.7	609.7	605.9	599.8	596.0
15°	658.8	649.8	645.2	629.3	610.4	608.9	585.5	583.9	576.4	576.4	570.3
17.5°	634.6	627.8	619.5	603.6	590.0	576.4	564.3	559.7	552.9	551.4	548.4
20°	611.2	602.1	599.1	583.2	568.8	552.2	539.3	534.8	531.8	528.7	531.0
22.5°	587.0	579.4	571.8	557.5	546.9	530.2	522.7	518.1	513.6	512.1	512.8
25°	563.5	556.7	549.1	534.8	523.4	509.8	503.0	500.7	498.5	498.5	497.7
27.5°	540.8	534.0	527.2	514.4	503.0	493.2	487.9	485.6	483.3	484.9	486.4
30°	517.4	511.3	505.3	493.9	484.9	475.8	472.8	471.2	470.5	474.3	474.3
32.5°	496.2	490.9	486.4	475.8	466.7	459.1	456.9	457.6	458.4	460.6	462.2
35°	474.3	470.5	465.9	456.9	449.3	442.5	443.3	443.3	444.8	448.5	451.6
37.5°	454.6	449.3	445.5	438.0	431.9	425.9	428.1	430.4	431.9	436.4	438.0
40°	431.1	428.9	425.9	418.3	413.0	412.2	413.0	414.5	417.5	419.8	422.1
42.5°	412.2	409.2	405.4	399.4	394.8	395.6	396.4	397.9	399.4	403.2	405.4
45°	391.1	388.8	385.8	380.5	376.7	377.4	378.2	378.2	379.7	384.3	385.8
47.5°	367.6	368.4	364.6	359.3	357.0	357.0	357.0	358.5	362.3	363.8	364.6
50°	344.9	343.4	342.7	337.4	335.8	335.1	335.8	336.6	341.9	341.1	343.4
52.5°	320.7	320.7	320.0	316.9	314.7	314.7	313.2	316.9	318.4	320.0	322.2
55°	297.3	295.0	294.2	292.7	289.7	288.9	290.5	295.0	296.5	298.0	300.3
57.5°	271.5	271.5	270.0	267.8	267.8	267.8	267.8	270.8	273.1	274.6	279.1
60°	248.1	245.1	242.8	242.8	242.8	242.0	246.6	246.6	251.1	251.9	253.4
62.5°	220.1	218.6	217.1	217.8	217.1	218.6	220.1	223.1	223.9	226.2	228.4
65°	193.6	193.6	192.1	196.7	193.6	193.6	197.4	197.4	198.9	201.2	204.2
67.5°	167.9	168.7	167.2	167.2	168.7	169.4	170.2	173.2	174.0	177.0	180.8
70°	141.4	143.0	143.7	142.2	143.7	145.2	146.7	147.5	150.5	152.0	154.3
72.5°	118.0	119.5	117.2	118.0	118.8	120.3	121.0	122.5	124.1	128.6	130.1
75°	94.6	93.8	93.0	96.1	94.6	97.6	98.3	98.3	99.8	103.6	105.1
77.5°	72.6	72.6	73.4	71.9	74.1	73.4	74.1	76.4	78.7	78.7	84.7
80°	50.7	52.2	52.2	52.2	52.9	53.7	52.2	56.0	56.7	56.7	59.0
82.5°	32.5	33.3	32.5	34.0	34.0	35.6	34.8	35.6	37.1	38.6	39.3
85°	17.4	17.4	18.9	18.9	18.2	18.9	18.2	18.9	20.4	20.4	21.2
87.5°	6.1	6.1	6.1	6.1	6.8	6.1	6.8	6.8	6.1	6.1	8.3
90°	7.5	8.3	9.4	11.6	13.8	16.0	18.2	18.9	19.5	20.2	20.9
92.5°	13.4	12.9	13.7	15.2	16.7	18.2	19.7	20.9	22.1	23.2	24.4
95°	18.6	15.1	16.0	17.9	19.8	21.6	23.5	24.7	25.9	27.0	28.2
97.5°	65.2	62.8	58.5	49.9	41.4	32.8	24.2	25.6	26.9	28.3	29.6
100°	141.4	143.1	130.0	103.7	77.5	51.2	25.0	26.3	27.7	29.0	30.3
102.5°	186.6	187.7	173.1	143.8	114.5	85.3	56.0	50.4	44.9	39.3	33.8
105°	233.0	233.9	226.3	211.2	196.1	180.9	165.8	136.0	106.2	76.5	46.7
107.5°	282.3	283.1	284.4	286.9	289.4	291.9	294.4	268.5	242.6	216.7	190.8
110°	332.3	333.0	333.9	335.8	337.7	339.5	341.4	335.8	330.3	324.7	319.2

TEST NUMBER: P1010679

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	380.1	380.7	381.6	383.5	385.4	387.2	389.1	390.6	392.1	393.6	395.1
115°	427.2	427.7	428.5	430.0	431.5	433.0	434.5	436.2	437.8	439.5	441.2
117.5°	474.7	475.3	475.7	476.6	477.4	478.3	479.1	480.5	481.8	483.2	484.5
120°	519.2	520.0	520.3	520.8	521.3	521.8	522.3	523.6	525.0	526.3	527.6
122.5°	561.8	562.4	562.7	563.4	564.1	564.7	565.4	566.2	567.1	567.9	568.8
125°	601.8	602.5	602.8	603.5	604.2	604.8	605.5	605.9	606.2	606.6	606.9
127.5°	641.2	641.9	642.3	643.2	644.0	644.9	645.7	646.2	646.7	647.2	647.7
130°	677.5	678.2	678.5	679.2	679.9	680.5	681.2	681.9	682.6	683.3	684.0
132.5°	712.3	713.0	713.3	713.8	714.3	714.8	715.3	716.0	716.6	717.3	718.0
135°	746.6	747.1	747.4	748.1	748.8	749.4	750.1	750.6	751.1	751.6	752.1
137.5°	778.2	778.9	779.1	779.4	779.7	780.1	780.4	781.2	782.1	782.9	783.8
140°	807.1	807.6	807.9	808.4	808.9	809.4	809.9	810.6	811.2	811.9	812.6
142.5°	835.1	835.6	835.9	836.4	836.9	837.4	837.9	838.4	838.9	839.4	839.9
145°	861.5	862.1	862.3	862.6	863.0	863.3	863.7	864.0	864.4	864.7	865.0
147.5°	885.2	885.6	885.8	886.1	886.4	886.8	887.1	887.4	887.8	888.1	888.4
150°	906.5	906.8	907.0	907.3	907.6	908.0	908.3	908.6	909.0	909.3	909.6
152.5°	925.6	925.7	925.8	926.0	926.1	926.3	926.5	927.2	927.8	928.5	929.2
155°	942.6	942.4	942.5	942.6	942.8	942.9	943.1	943.9	944.8	945.6	946.5
157.5°	959.0	959.0	958.9	958.8	958.6	958.5	958.3	959.3	960.3	961.3	962.3
160°	972.0	971.9	971.8	971.6	971.5	971.3	971.1	972.1	973.1	974.2	975.2
162.5°	983.5	983.2	983.1	983.0	982.8	982.7	982.5	983.7	984.9	986.0	987.2
165°	993.4	993.1	993.0	992.8	992.7	992.5	992.3	993.7	995.0	996.4	997.7
167.5°	1001.0	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1002.0	1003.4	1004.7	1006.0
170°	1007.8	1007.5	1007.5	1007.5	1007.5	1007.5	1007.5	1008.8	1010.2	1011.5	1012.8
172.5°	1011.7	1011.3	1011.4	1011.5	1011.7	1011.8	1012.0	1013.4	1014.7	1016.1	1017.4
175°	1015.4	1015.0	1015.1	1015.3	1015.4	1015.6	1015.8	1017.0	1018.2	1019.3	1020.5
177.5°	1017.0	1016.6	1016.7	1016.8	1017.0	1017.1	1017.3	1018.7	1020.0	1021.4	1022.7
180°	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8

TEST NUMBER: P1010679

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6
2.5°	740.5	741.3	738.2	736.0	742.0	738.2	738.2	739.0	737.5	739.8	739.0
5°	698.9	699.7	694.4	695.9	692.9	692.1	691.4	695.9	695.1	694.4	695.9
7.5°	658.1	658.1	655.8	654.3	654.3	652.0	655.0	654.3	655.8	655.8	658.1
10°	624.0	625.5	621.8	618.0	617.2	618.0	618.0	618.7	619.5	624.8	624.0
12.5°	596.0	593.8	593.0	590.8	587.0	585.5	583.9	592.3	590.0	590.0	590.0
15°	565.0	570.3	569.6	562.8	561.3	564.3	562.8	562.8	570.3	569.6	568.8
17.5°	548.4	546.9	545.4	541.6	542.3	541.6	542.3	542.3	546.9	546.9	546.9
20°	529.5	526.5	526.5	524.9	524.9	522.7	525.7	526.5	529.5	529.5	530.2
22.5°	512.8	510.6	510.6	509.8	511.3	508.3	511.3	512.1	512.1	514.4	514.4
25°	498.5	497.0	497.0	498.5	498.5	498.5	498.5	501.5	499.2	500.0	499.2
27.5°	485.6	486.4	487.1	487.9	487.1	487.9	488.6	490.1	490.9	490.1	488.6
30°	473.5	475.8	476.5	476.5	478.0	478.8	479.6	479.6	480.3	478.0	479.6
32.5°	464.4	464.4	465.9	466.7	468.2	469.0	469.0	470.5	469.7	467.5	468.2
35°	451.6	451.6	454.6	456.1	458.4	457.6	458.4	458.4	459.1	457.6	455.4
37.5°	438.7	440.2	440.2	443.3	444.0	444.8	444.0	445.5	444.8	443.3	442.5
40°	423.6	422.8	423.6	425.9	426.6	426.6	426.6	428.1	428.1	428.1	427.4
42.5°	404.7	406.9	406.2	408.5	407.7	407.7	409.2	410.7	411.5	409.2	410.0
45°	386.5	386.5	388.0	388.0	388.8	388.8	391.8	390.3	391.8	390.3	391.1
47.5°	366.9	367.6	367.6	368.4	369.9	371.4	369.9	370.6	370.6	371.4	369.9
50°	344.9	344.9	346.4	348.7	351.7	350.2	349.5	352.5	350.2	350.2	348.7
52.5°	322.2	324.5	325.3	327.5	329.8	330.5	331.3	329.8	330.5	328.3	329.0
55°	300.3	301.0	304.1	306.3	308.6	308.6	307.9	308.6	309.4	306.3	306.3
57.5°	278.4	280.6	283.7	283.7	286.7	286.7	285.9	285.9	286.7	284.4	283.7
60°	254.9	257.2	261.0	261.0	265.5	266.3	264.7	263.2	263.2	261.0	261.7
62.5°	229.9	232.2	234.5	238.3	241.3	239.8	242.8	239.8	240.5	236.0	236.0
65°	208.0	208.8	212.5	216.3	216.3	217.8	216.3	217.1	214.8	214.8	211.8
67.5°	182.3	182.3	186.1	189.9	193.6	193.6	193.6	191.4	191.4	189.1	189.1
70°	159.6	158.8	162.6	164.9	167.2	167.9	166.4	165.7	164.1	161.9	161.1
72.5°	131.6	133.1	136.9	138.4	142.2	141.4	145.2	140.7	140.7	136.9	136.2
75°	106.7	108.2	111.9	114.2	116.5	116.5	118.8	116.5	113.5	111.9	111.2
77.5°	84.7	84.0	87.0	90.8	91.5	90.8	92.3	91.5	88.5	88.5	87.0
80°	60.5	62.8	65.8	65.1	68.1	67.3	67.3	65.8	65.8	63.5	65.1
82.5°	40.1	42.4	43.1	42.4	43.1	44.6	45.4	44.6	44.6	43.1	43.9
85°	21.2	21.2	22.7	23.4	22.7	22.7	23.4	25.7	24.2	22.7	24.2
87.5°	6.8	6.1	6.1	6.8	6.1	6.1	6.8	6.8	7.6	7.6	7.6
90°	21.2	21.4	21.7	22.0	22.4	22.7	22.4	22.0	21.7	21.4	21.2
92.5°	25.0	25.1	25.2	25.4	25.5	25.7	25.5	25.4	25.2	25.1	25.0
95°	28.8	28.8	28.8	28.8	28.8	28.8	28.8	28.8	28.8	28.8	28.8
97.5°	30.3	30.4	30.5	30.7	30.8	31.0	30.8	30.7	30.5	30.4	30.3
100°	31.0	31.1	31.3	31.4	31.6	31.8	31.6	31.4	31.3	31.1	31.0
102.5°	31.0	31.2	31.5	31.8	32.2	32.5	32.2	31.8	31.5	31.2	31.0
105°	31.8	32.0	32.3	32.6	33.0	33.3	33.0	32.6	32.3	32.0	31.8
107.5°	177.9	166.9	144.8	122.8	100.7	78.7	100.7	122.8	144.8	166.9	177.9
110°	316.4	304.4	280.3	256.3	232.2	208.2	232.2	256.3	280.3	304.4	316.4

TEST NUMBER: P1010679

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	395.9	395.7	395.4	395.1	394.7	394.4	394.7	395.1	395.4	395.7	395.9
115°	442.0	442.3	443.0	443.7	444.4	445.1	444.4	443.7	443.0	442.3	442.0
117.5°	485.2	485.3	485.4	485.6	485.7	485.9	485.7	485.6	485.4	485.3	485.2
120°	528.3	528.3	528.3	528.3	528.3	528.3	528.3	528.3	528.3	528.3	528.3
122.5°	569.2	569.3	569.5	569.6	569.8	570.0	569.8	569.6	569.5	569.3	569.2
125°	607.1	607.3	607.6	607.9	608.3	608.6	608.3	607.9	607.6	607.3	607.1
127.5°	647.9	647.7	647.4	647.1	646.7	646.4	646.7	647.1	647.4	647.7	647.9
130°	684.3	684.1	683.8	683.4	683.1	682.7	683.1	683.4	683.8	684.1	684.3
132.5°	718.3	718.1	717.6	717.1	716.6	716.1	716.6	717.1	717.6	718.1	718.3
135°	752.4	752.1	751.6	751.1	750.6	750.1	750.6	751.1	751.6	752.1	752.4
137.5°	784.2	784.0	783.7	783.4	783.0	782.7	783.0	783.4	783.7	784.0	784.2
140°	812.9	812.7	812.4	812.1	811.7	811.4	811.7	812.1	812.4	812.7	812.9
142.5°	840.2	839.9	839.4	838.9	838.4	837.9	838.4	838.9	839.4	839.9	840.2
145°	865.2	865.2	865.2	865.2	865.2	865.2	865.2	865.2	865.2	865.2	865.2
147.5°	888.6	888.2	887.3	886.5	885.6	884.8	885.6	886.5	887.3	888.2	888.6
150°	909.8	909.6	909.1	908.6	908.1	907.6	908.1	908.6	909.1	909.6	909.8
152.5°	929.5	929.1	928.2	927.4	926.5	925.7	926.5	927.4	928.2	929.1	929.5
155°	946.9	946.4	945.4	944.4	943.4	942.4	943.4	944.4	945.4	946.4	946.9
157.5°	962.8	962.1	960.8	959.5	958.1	956.8	958.1	959.5	960.8	962.1	962.8
160°	975.7	975.1	973.9	972.8	971.6	970.4	971.6	972.8	973.9	975.1	975.7
162.5°	987.8	987.3	986.3	985.2	984.2	983.2	984.2	985.2	986.3	987.3	987.8
165°	998.4	997.8	996.6	995.5	994.3	993.1	994.3	995.5	996.6	997.8	998.4
167.5°	1006.7	1006.0	1004.7	1003.4	1002.0	1000.7	1002.0	1003.4	1004.7	1006.0	1006.7
170°	1013.5	1012.8	1011.5	1010.2	1008.8	1007.5	1008.8	1010.2	1011.5	1012.8	1013.5
172.5°	1018.1	1017.3	1015.8	1014.3	1012.8	1011.3	1012.8	1014.3	1015.8	1017.3	1018.1
175°	1021.1	1020.4	1019.1	1017.7	1016.4	1015.0	1016.4	1017.7	1019.1	1020.4	1021.1
177.5°	1023.4	1022.6	1020.9	1019.2	1017.5	1015.8	1017.5	1019.2	1020.9	1022.6	1023.4
180°	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8

TEST NUMBER: P1010679

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6
2.5°	741.3	742.8	743.5	740.5	738.2	742.0	747.3	751.1	754.1	757.9	760.2
5°	697.4	702.7	702.7	704.2	706.5	710.3	720.1	726.9	733.0	737.5	741.3
7.5°	660.3	664.1	666.4	670.2	674.0	679.2	690.6	700.4	709.5	714.8	720.9
10°	627.1	630.1	633.9	636.1	642.9	650.5	664.9	673.2	683.8	692.1	699.7
12.5°	595.3	605.9	608.1	607.4	613.4	621.8	636.1	649.0	660.3	668.7	677.0
15°	572.6	576.4	580.9	580.2	593.0	595.3	607.4	622.5	637.6	642.9	650.5
17.5°	547.6	553.7	558.2	560.5	564.3	572.6	583.9	595.3	615.0	615.7	635.4
20°	528.0	534.0	537.0	540.1	542.3	552.2	562.0	574.9	590.8	599.1	609.7
22.5°	515.1	518.1	520.4	522.7	525.7	531.0	543.1	557.5	568.1	577.1	583.9
25°	500.0	503.0	506.0	507.5	509.8	512.8	521.9	533.3	548.4	554.4	561.3
27.5°	489.4	489.4	490.9	490.9	493.9	497.0	503.8	514.4	526.5	534.0	543.1
30°	478.0	477.3	478.0	477.3	476.5	481.1	487.1	496.2	504.5	513.6	519.6
32.5°	466.7	465.9	465.9	466.7	463.7	465.9	469.0	477.3	486.4	490.9	497.7
35°	454.6	453.1	453.1	453.1	451.6	450.1	453.1	460.6	466.7	472.8	478.0
37.5°	442.5	440.2	440.2	438.7	437.2	434.9	434.9	441.0	449.3	451.6	458.4
40°	425.9	425.9	424.3	423.6	422.1	420.6	418.3	423.6	431.1	433.4	438.7
42.5°	409.2	406.9	406.2	406.2	406.2	403.9	402.4	406.2	410.7	414.5	417.5
45°	390.3	388.8	389.5	388.8	387.3	386.5	385.8	387.3	392.6	394.1	397.9
47.5°	369.9	369.1	369.1	368.4	367.6	368.4	365.3	369.1	370.6	372.2	375.2
50°	348.7	347.9	347.2	346.4	346.4	347.2	346.4	346.4	349.5	351.0	354.0
52.5°	327.5	325.3	325.3	324.5	324.5	323.0	324.5	325.3	326.8	328.3	329.8
55°	304.8	304.8	302.6	302.6	301.0	301.0	301.8	301.0	304.1	305.6	305.6
57.5°	282.9	279.9	280.6	279.1	277.6	276.8	276.8	278.4	279.9	279.9	281.4
60°	259.4	256.4	255.7	252.6	254.2	251.9	252.6	252.6	255.7	254.2	255.7
62.5°	236.0	232.2	229.9	228.4	228.4	229.2	227.7	226.9	228.4	229.9	233.0
65°	211.0	208.8	206.5	204.2	204.2	203.5	205.0	202.7	202.0	202.7	204.2
67.5°	185.3	183.0	180.8	178.5	179.3	177.0	175.5	177.8	176.2	177.0	178.5
70°	160.4	158.8	154.3	152.8	152.0	152.8	152.0	150.5	152.8	152.0	152.8
72.5°	135.4	133.9	131.6	127.8	127.8	127.1	126.3	126.3	125.6	125.6	125.6
75°	111.2	108.2	105.9	105.1	103.6	102.9	102.1	100.6	101.4	102.1	100.6
77.5°	86.2	82.4	81.7	81.7	79.4	79.4	80.2	79.4	78.7	78.7	78.7
80°	63.5	60.5	60.5	59.0	57.5	57.5	57.5	57.5	56.7	56.0	56.7
82.5°	40.8	40.1	39.3	39.3	40.8	37.8	39.3	38.6	37.8	37.8	37.1
85°	22.7	23.4	22.7	23.4	21.9	22.7	22.7	22.7	21.9	22.7	21.2
87.5°	8.3	8.3	8.3	9.1	9.1	9.1	9.1	9.1	9.8	9.1	9.1
90°	20.9	20.2	19.5	18.9	18.2	16.0	13.8	11.6	9.4	8.3	7.5
92.5°	24.4	23.2	22.1	20.9	19.7	18.2	16.7	15.2	13.7	12.9	13.4
95°	28.2	27.0	25.9	24.7	23.5	21.6	19.8	17.9	16.0	15.1	18.6
97.5°	29.6	28.3	26.9	25.6	24.2	32.8	41.4	49.9	58.5	62.8	65.2
100°	30.3	29.0	27.7	26.3	25.0	51.2	77.5	103.7	130.0	143.1	141.4
102.5°	33.8	39.3	44.9	50.4	56.0	85.3	114.5	143.8	173.1	187.7	186.6
105°	46.7	76.5	106.2	136.0	165.8	180.9	196.1	211.2	226.3	233.9	233.0
107.5°	190.8	216.7	242.6	268.5	294.4	291.9	289.4	286.9	284.4	283.1	282.3
110°	319.2	324.7	330.3	335.8	341.4	339.5	337.7	335.8	333.9	333.0	332.3

TEST NUMBER: P1010679

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	395.1	393.6	392.1	390.6	389.1	387.2	385.4	383.5	381.6	380.7	380.1
115°	441.2	439.5	437.8	436.2	434.5	433.0	431.5	430.0	428.5	427.7	427.2
117.5°	484.5	483.2	481.8	480.5	479.1	478.3	477.4	476.6	475.7	475.3	474.7
120°	527.6	526.3	525.0	523.6	522.3	521.8	521.3	520.8	520.3	520.0	519.2
122.5°	568.8	567.9	567.1	566.2	565.4	564.7	564.1	563.4	562.7	562.4	561.8
125°	606.9	606.6	606.2	605.9	605.5	604.8	604.2	603.5	602.8	602.5	601.8
127.5°	647.7	647.2	646.7	646.2	645.7	644.9	644.0	643.2	642.3	641.9	641.2
130°	684.0	683.3	682.6	681.9	681.2	680.5	679.9	679.2	678.5	678.2	677.5
132.5°	718.0	717.3	716.6	716.0	715.3	714.8	714.3	713.8	713.3	713.0	712.3
135°	752.1	751.6	751.1	750.6	750.1	749.4	748.8	748.1	747.4	747.1	746.6
137.5°	783.8	782.9	782.1	781.2	780.4	780.1	779.7	779.4	779.1	778.9	778.2
140°	812.6	811.9	811.2	810.6	809.9	809.4	808.9	808.4	807.9	807.6	807.1
142.5°	839.9	839.4	838.9	838.4	837.9	837.4	836.9	836.4	835.9	835.6	835.1
145°	865.0	864.7	864.4	864.0	863.7	863.3	863.0	862.6	862.3	862.1	861.5
147.5°	888.4	888.1	887.8	887.4	887.1	886.8	886.4	886.1	885.8	885.6	885.2
150°	909.6	909.3	909.0	908.6	908.3	908.0	907.6	907.3	907.0	906.8	906.5
152.5°	929.2	928.5	927.8	927.2	926.5	926.3	926.1	926.0	925.8	925.7	925.6
155°	946.5	945.6	944.8	943.9	943.1	942.9	942.8	942.6	942.5	942.4	942.6
157.5°	962.3	961.3	960.3	959.3	958.3	958.5	958.6	958.8	958.9	959.0	959.0
160°	975.2	974.2	973.1	972.1	971.1	971.3	971.5	971.6	971.8	971.9	972.0
162.5°	987.2	986.0	984.9	983.7	982.5	982.7	982.8	983.0	983.1	983.2	983.5
165°	997.7	996.4	995.0	993.7	992.3	992.5	992.7	992.8	993.0	993.1	993.4
167.5°	1006.0	1004.7	1003.4	1002.0	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1001.0
170°	1012.8	1011.5	1010.2	1008.8	1007.5	1007.5	1007.5	1007.5	1007.5	1007.5	1007.8
172.5°	1017.4	1016.1	1014.7	1013.4	1012.0	1011.8	1011.7	1011.5	1011.4	1011.3	1011.7
175°	1020.5	1019.3	1018.2	1017.0	1015.8	1015.6	1015.4	1015.3	1015.1	1015.0	1015.4
177.5°	1022.7	1021.4	1020.0	1018.7	1017.3	1017.1	1017.0	1016.8	1016.7	1016.6	1017.0
180°	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8

TEST NUMBER: P1010679

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	780.6	780.6	780.6	780.6
2.5°	764.0	766.2	773.8	782.9
5°	748.8	754.9	765.5	779.9
7.5°	732.2	741.3	756.4	774.6
10°	713.3	726.1	745.1	767.7
12.5°	692.9	709.5	733.7	757.2
15°	680.0	696.6	718.6	744.3
17.5°	655.0	674.7	697.4	733.7
20°	629.3	651.3	680.8	717.1
22.5°	609.7	633.1	661.1	699.7
25°	586.2	610.4	640.7	680.8
27.5°	561.3	585.5	619.5	661.9
30°	542.3	565.8	598.3	643.7
32.5°	519.6	542.3	576.4	624.0
35°	493.9	519.6	552.2	600.6
37.5°	474.3	497.7	531.8	577.9
40°	453.1	473.5	506.8	552.2
42.5°	430.4	453.1	481.8	527.2
45°	409.2	425.9	455.4	498.5
47.5°	386.5	405.4	428.1	461.4
50°	362.3	378.2	403.2	425.9
52.5°	338.9	351.7	372.9	390.3
55°	313.9	326.8	342.7	353.2
57.5°	290.5	299.5	310.1	316.9
60°	261.7	270.8	277.6	284.4
62.5°	236.0	242.8	246.6	250.4
65°	209.5	213.3	215.6	218.6
67.5°	180.8	184.6	185.3	189.9
70°	154.3	155.1	156.6	158.8
72.5°	129.3	130.9	130.1	131.6
75°	103.6	105.1	103.6	105.1
77.5°	78.7	80.2	80.2	82.4
80°	56.7	57.5	58.2	58.2
82.5°	37.1	39.3	37.8	38.6
85°	21.2	21.9	21.9	22.7
87.5°	9.8	10.6	9.8	11.3
90°	5.8	4.1	2.5	0.8
92.5°	14.4	15.4	16.4	17.4
95°	25.5	32.4	39.3	46.2
97.5°	69.9	74.6	79.3	84.0
100°	138.0	134.7	131.3	127.9
102.5°	184.4	182.3	180.1	177.9
105°	231.1	229.3	227.4	225.6
107.5°	280.8	279.3	277.8	276.3
110°	331.0	329.7	328.3	327.0



TEST NUMBER: P1010679

CATALOG NUMBER: S123DIP-B560D805UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	378.9	377.8	376.6	375.4
115°	426.2	425.1	424.1	423.1
117.5°	473.6	472.4	471.3	470.1
120°	517.7	516.2	514.7	513.2
122.5°	560.6	559.5	558.3	557.1
125°	600.5	599.2	597.8	596.5
127.5°	639.9	638.5	637.2	635.8
130°	676.2	674.9	673.5	672.2
132.5°	711.0	709.7	708.3	707.0
135°	745.6	744.5	743.5	742.5
137.5°	776.9	775.5	774.2	772.8
140°	806.1	805.1	804.1	803.1
142.5°	834.1	833.1	832.1	831.1
145°	860.3	859.2	858.0	856.8
147.5°	884.3	883.5	882.6	881.8
150°	906.0	905.5	905.0	904.5
152.5°	925.5	925.3	925.2	925.0
155°	942.9	943.2	943.6	943.9
157.5°	959.0	959.0	959.0	959.0
160°	972.1	972.3	972.4	972.6
162.5°	984.0	984.5	985.0	985.5
165°	993.9	994.4	994.9	995.4
167.5°	1001.7	1002.4	1003.0	1003.7
170°	1008.5	1009.2	1009.8	1010.5
172.5°	1012.5	1013.4	1014.2	1015.0
175°	1016.3	1017.1	1018.0	1018.8
177.5°	1017.8	1018.7	1019.5	1020.3
180°	1018.8	1018.8	1018.8	1018.8

(END OF REPORT)