

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010701

Luminaire Tested: S123DIP-B775D1025UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010701
REPORT IS A COMBINATION OF REPORTS P990235 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D1025UB2750-4F0-XX-W2A-D_3500K
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7336.0 lumens
Efficiency: N/A
Efficacy: 113.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010701

CATALOG NUMBER: S123DIP-B775D1025UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1010701

CATALOG NUMBER: S123DIP-B775D1025UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48
1	95	90	86	82	86	82	79	75	67	65	62	53	52	50	41	40	38
2	86	78	72	66	78	71	66	61	58	54	51	46	44	41	35	33	32
3	78	68	61	55	71	62	56	51	51	46	42	41	37	34	31	29	27
4	71	60	52	46	65	55	48	43	45	40	36	36	32	29	28	25	23
5	65	54	45	39	59	49	42	36	40	35	31	32	28	25	25	22	20
6	60	48	40	34	54	44	37	31	36	31	27	29	25	22	22	19	17
7	56	43	35	30	50	40	32	27	33	27	23	26	22	19	20	17	15
8	51	39	31	26	47	36	29	24	30	24	21	24	20	17	19	16	14
9	48	36	28	23	43	33	26	21	27	22	18	22	18	15	17	14	12
10	45	33	25	21	41	30	24	19	25	20	16	20	16	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10444	10444	10444
5°	10473	10138	10130
10°	10375	9863	9788
15°	10238	9560	9426
20°	10043	9222	9036
25°	9803	8842	8633
30°	9558	8496	8228
35°	9281	8135	7899
40°	9019	7805	7550
45°	8728	7485	7263
50°	8440	7167	6951
55°	8121	6842	6666
60°	7808	6510	6371
65°	7487	6155	6028
70°	7003	5758	5674
75°	6394	5305	5309
80°	5679	4846	4891
85°	4976	4475	4593

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8728 cd/sqm

TEST NUMBER: P1010701

CATALOG NUMBER: S123DIP-B775D1025UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.0	1.3
10°-20°	262.4	3.6
20°-30°	392.4	5.3
30°-40°	468.5	6.4
40°-50°	490.2	6.7
50°-60°	460.0	6.3
60°-70°	384.2	5.2
70°-80°	274.7	3.7
80°-90°	166.2	2.3
90°-100°	149.8	2.0
100°-110°	303.3	4.1
110°-120°	608.5	8.3
120°-130°	737.3	10.0
130°-140°	769.8	10.5
140°-150°	710.4	9.7
150°-160°	570.9	7.8
160°-170°	368.4	5.0
170°-180°	127.0	1.7
0°-30°	746.8	10.2
0°-40°	1215.3	16.6
0°-60°	2165.5	29.5
0°-90°	2990.6	40.8
90°-120°	1061.6	14.5
90°-150°	3279.1	44.7
90°-180°	4345.0	59.2
0°-180°	7336.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	970	970	970	970	970	
5°	971	969	963	971	970	92
15°	925	928	927	938	936	261
25°	835	846	849	862	862	385
35°	719	736	749	765	770	449
45°	588	613	640	660	668	453
55°	448	483	521	550	558	401
65°	310	351	397	429	440	306
75°	168	218	271	306	318	180
85°	52	105	161	197	207	53
90°	15	76	143	183	196	13
95°	72	73	135	175	186	81
105°	304	340	297	151	162	322
115°	560	579	626	661	673	553
125°	785	793	828	852	861	702
135°	976	981	996	1018	1020	751
145°	1124	1130	1132	1143	1147	704
155°	1238	1236	1237	1242	1236	570
165°	1305	1302	1301	1309	1302	369
175°	1336	1331	1332	1339	1331	127
180°	1336	1336	1336	1336	1336	

TEST NUMBER: P1010701

CATALOG NUMBER: S123DIP-B775D1025UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	970.3	970.3	970.3	970.3	970.3
2.5°	975.6	972.4	964.0	972.4	971.4
5°	971.4	969.3	962.9	971.4	970.3
7.5°	964.0	964.0	957.6	968.2	967.1
10°	953.4	955.5	950.2	960.8	958.7
12.5°	940.7	943.9	940.7	950.2	948.1
15°	924.9	928.0	927.0	937.5	936.5
17.5°	905.8	912.2	911.1	920.6	918.5
20°	884.7	891.0	893.1	902.7	903.7
22.5°	862.5	868.8	872.0	884.7	883.6
25°	835.0	845.6	848.8	862.5	862.5
27.5°	808.6	820.2	826.6	838.2	839.2
30°	780.1	793.8	802.2	814.9	814.9
32.5°	748.3	764.2	775.8	789.6	792.7
35°	718.7	735.7	749.4	765.3	769.5
37.5°	687.0	706.1	721.9	739.9	743.1
40°	655.3	674.4	695.5	713.5	717.7
42.5°	620.4	644.8	667.0	687.0	693.4
45°	587.7	613.0	639.5	659.6	668.0
47.5°	552.8	581.3	610.9	633.1	639.5
50°	519.0	548.6	581.3	605.7	613.0
52.5°	483.0	514.8	551.7	577.1	586.6
55°	448.2	483.0	521.1	549.6	558.1
57.5°	414.3	450.3	491.5	520.0	529.5
60°	378.4	416.5	459.8	489.4	501.0
62.5°	344.6	383.7	430.2	459.8	470.4
65°	309.7	350.9	397.4	429.1	439.7
67.5°	274.8	318.2	364.7	399.5	408.0
70°	237.8	283.3	334.0	367.8	378.4
72.5°	204.0	249.4	302.3	337.2	347.7
75°	168.1	217.7	270.6	305.5	318.2
77.5°	137.4	187.1	239.9	276.9	286.4
80°	104.6	156.4	211.4	247.3	257.9
82.5°	76.1	129.0	185.0	220.9	231.5
85°	51.8	104.6	160.7	196.6	207.2
87.5°	31.7	84.6	138.5	174.4	185.0
90°	14.7	76.4	143.2	183.2	195.7
92.5°	35.5	75.0	136.8	178.7	189.1
95°	72.1	72.6	135.4	175.1	185.7
97.5°	120.8	131.0	130.1	169.7	181.3
100°	177.2	230.9	124.8	163.3	174.9
102.5°	241.7	284.2	159.0	155.9	168.5
105°	304.2	340.5	296.6	150.6	162.1
107.5°	369.6	400.8	459.0	334.7	214.2
110°	435.0	462.1	515.2	509.9	376.5

TEST NUMBER: P1010701

CATALOG NUMBER: S123DIP-B775D1025UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	498.5	520.3	571.4	606.7	614.3
115°	560.1	578.7	625.7	661.0	673.3
117.5°	621.6	636.9	677.9	711.1	720.6
120°	677.1	691.3	729.2	761.4	768.8
122.5°	734.6	743.7	780.4	808.7	817.1
125°	785.2	793.2	827.7	851.9	861.3
127.5°	836.8	843.7	875.0	899.2	904.6
130°	884.5	891.3	916.5	940.5	944.9
132.5°	929.0	937.0	955.8	978.8	983.2
135°	975.7	980.6	996.2	1018.2	1020.5
137.5°	1015.4	1022.3	1031.7	1053.6	1056.9
140°	1054.1	1060.0	1066.1	1086.0	1089.3
142.5°	1090.8	1095.6	1098.6	1115.3	1117.6
145°	1124.5	1130.4	1132.4	1142.8	1147.0
147.5°	1156.2	1161.1	1163.1	1168.3	1167.6
150°	1186.0	1188.9	1190.9	1192.9	1192.0
152.5°	1212.7	1213.7	1214.7	1218.7	1213.7
155°	1237.6	1235.6	1236.6	1241.5	1235.6
157.5°	1257.4	1257.4	1256.4	1262.4	1254.4
160°	1275.3	1274.3	1273.3	1279.2	1272.3
162.5°	1292.1	1289.2	1288.2	1295.1	1289.2
165°	1305.0	1302.1	1301.1	1309.0	1302.1
167.5°	1316.0	1312.0	1312.0	1319.9	1312.0
170°	1324.9	1320.9	1320.9	1328.9	1320.9
172.5°	1330.8	1325.9	1326.9	1334.8	1325.9
175°	1335.8	1330.8	1331.8	1338.8	1330.8
177.5°	1337.8	1332.8	1333.8	1341.8	1331.8
180°	1335.8	1335.8	1335.8	1335.8	1335.8

(END OF REPORT)