

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011005

Luminaire Tested: S123RDIP-B775D585UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011005
REPORT IS A COMBINATION OF REPORTS P993651 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B775D585UB2750-4F0-XX-W2A-F_3000K
Description: Define 3 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5279.0 lumens
Efficiency: N/A
Efficacy: 102.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011005

CATALOG NUMBER: S123RDIP-B775D585UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1011005

CATALOG NUMBER: S123RDIP-B775D585UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	108	108	108	108		101	101	101	101		86	86	86		73	73	73		61	61	61
1	99	95	91	88		92	89	85	82		76	74	72		65	63	62		55	54	52
2	91	84	78	72		84	78	73	68		67	63	60		58	55	52		49	47	45
3	83	74	67	61		77	69	63	57		60	55	51		51	48	45		43	41	38
4	76	66	58	52		71	61	54	49		53	48	44		46	42	38		39	36	33
5	70	59	51	45		65	55	48	42		48	42	38		41	37	34		35	32	29
6	65	53	45	39		60	49	42	37		43	38	33		37	33	30		32	29	26
7	60	48	40	34		56	45	38	33		39	34	29		34	30	26		29	26	23
8	56	43	36	30		52	41	34	29		36	30	26		31	27	24		27	24	21
9	52	40	32	27		48	37	31	26		33	28	24		29	24	21		25	22	19
10	49	37	29	25		45	34	28	23		31	25	21		27	22	19		23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13969	13969	13969
5°	13992	13475	13439
10°	13882	12969	12713
15°	13702	12343	11918
20°	13465	11661	11030
25°	13221	10953	10188
30°	12909	10201	9194
35°	12588	9461	8287
40°	12284	8657	7286
45°	11896	7873	6386
50°	11467	7034	5455
55°	11024	6136	4601
60°	10600	5216	3735
65°	10051	4272	2915
70°	9362	3230	2083
75°	8369	2188	1650
80°	7145	1520	1157
85°	5360	821	607

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11896 cd/sqm

TEST NUMBER: P1011005

CATALOG NUMBER: S123RDIP-B775D585UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.0	2.3
10°-20°	339.4	6.4
20°-30°	488.7	9.3
30°-40°	550.3	10.4
40°-50°	526.4	10.0
50°-60°	430.9	8.2
60°-70°	290.5	5.5
70°-80°	145.7	2.8
80°-90°	39.6	0.8
90°-100°	27.1	0.5
100°-110°	131.2	2.5
110°-120°	321.4	6.1
120°-130°	408.1	7.7
130°-140°	435.9	8.3
140°-150°	407.6	7.7
150°-160°	328.8	6.2
160°-170°	212.2	4.0
170°-180°	73.1	1.4
0°-30°	950.1	18.0
0°-40°	1500.4	28.4
0°-60°	2457.7	46.6
0°-90°	2933.5	55.6
90°-120°	479.7	9.1
90°-150°	1731.3	32.8
90°-180°	2345.0	44.4
0°-180°	5279.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1298	1298	1298	1298	1298	
5°	1298	1293	1280	1289	1287	123
15°	1238	1226	1197	1192	1184	349
25°	1126	1100	1052	1029	1018	518
35°	975	937	872	826	807	610
45°	801	754	673	613	587	618
55°	608	557	467	406	385	546
65°	416	358	276	224	213	411
75°	220	170	112	101	99	234
85°	56	33	30	27	27	61
90°	1	6	14	16	17	5
95°	35	11	18	22	22	42
105°	170	177	125	24	25	181
115°	320	323	328	334	336	316
125°	450	455	457	458	460	402
135°	561	564	566	568	566	432
145°	647	651	652	653	653	405
155°	713	712	712	715	712	328
165°	752	750	749	754	750	212
175°	769	766	767	771	766	73
180°	769	769	769	769	769	

TEST NUMBER: P1011005

CATALOG NUMBER: S123RDIP-B775D585UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1297.8	1297.8	1297.8	1297.8	1297.8
2.5°	1303.1	1298.9	1286.2	1297.8	1295.7
5°	1297.8	1292.6	1279.9	1289.4	1287.3
7.5°	1288.3	1283.1	1267.3	1273.6	1270.5
10°	1275.7	1268.3	1249.4	1250.5	1245.2
12.5°	1257.8	1249.4	1225.2	1224.1	1217.8
15°	1237.8	1226.2	1196.8	1191.5	1184.1
17.5°	1213.6	1201.0	1164.1	1153.6	1143.1
20°	1186.2	1169.4	1129.4	1115.7	1103.1
22.5°	1155.7	1135.7	1092.6	1074.7	1063.1
25°	1126.2	1099.9	1051.5	1029.4	1017.8
27.5°	1090.5	1062.0	1009.4	979.9	962.0
30°	1053.6	1022.0	963.1	927.3	910.5
32.5°	1016.8	979.9	916.8	876.8	858.9
35°	974.7	936.8	871.5	826.3	807.3
37.5°	932.6	891.5	823.1	772.6	749.4
40°	892.6	846.3	771.5	716.8	692.6
42.5°	847.3	801.0	723.1	662.1	641.0
45°	801.0	753.6	672.6	612.6	587.3
47.5°	755.7	703.1	623.1	557.9	535.8
50°	705.2	655.8	570.5	505.2	481.0
52.5°	660.0	605.2	521.0	452.6	431.6
55°	608.4	556.8	467.3	406.3	385.2
57.5°	562.1	506.3	415.8	357.9	340.0
60°	513.7	455.8	368.4	311.6	293.7
62.5°	465.2	407.3	320.0	267.4	248.4
65°	415.8	357.9	275.8	224.2	212.6
67.5°	366.3	307.4	227.4	188.4	175.8
70°	317.9	261.0	187.4	150.5	138.9
72.5°	269.5	213.7	148.4	120.0	116.8
75°	220.0	169.5	111.6	101.0	98.9
77.5°	174.7	128.4	87.4	81.0	78.9
80°	131.6	88.4	66.3	63.2	61.0
82.5°	90.5	54.7	47.4	44.2	44.2
85°	55.8	32.6	29.5	27.4	27.4
87.5°	25.3	13.7	13.7	12.6	11.6
90°	0.6	6.3	13.7	16.0	17.1
92.5°	13.1	9.7	14.9	18.9	19.4
95°	34.9	11.4	17.7	21.7	21.7
97.5°	63.4	47.4	18.3	22.9	23.4
100°	96.6	108.0	18.9	23.4	24.0
102.5°	134.3	141.8	42.3	23.4	24.6
105°	170.3	176.6	125.2	24.0	25.2
107.5°	208.6	213.8	222.3	134.3	59.4
110°	246.9	251.5	257.8	238.9	157.2



TEST NUMBER: P1011005

CATALOG NUMBER: S123RDIP-B775D585UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	283.5	287.5	293.8	298.9	297.8
115°	319.5	322.9	328.1	333.8	336.1
117.5°	355.0	359.0	361.8	366.4	367.0
120°	387.5	392.7	394.4	399.0	399.0
122.5°	420.7	424.7	427.0	429.8	430.4
125°	450.4	455.0	457.3	458.4	459.6
127.5°	480.1	484.7	487.6	489.3	488.1
130°	507.6	512.1	514.4	516.7	515.6
132.5°	533.9	538.4	540.2	542.4	540.7
135°	560.7	564.2	566.4	568.2	566.4
137.5°	583.6	588.2	589.3	592.2	591.0
140°	606.5	609.9	611.6	613.9	612.7
142.5°	627.6	631.0	632.8	634.5	632.8
145°	647.0	651.0	652.2	653.3	653.3
147.5°	665.9	668.8	669.9	671.0	668.2
150°	683.1	684.8	685.9	687.1	685.3
152.5°	698.5	699.1	699.6	701.9	699.1
155°	712.8	711.6	712.2	715.1	711.6
157.5°	724.2	724.2	723.6	727.1	722.5
160°	734.5	733.9	733.4	736.8	732.8
162.5°	744.2	742.5	741.9	745.9	742.5
165°	751.6	749.9	749.4	753.9	749.9
167.5°	757.9	755.6	755.6	760.2	755.6
170°	763.1	760.8	760.8	765.4	760.8
172.5°	766.5	763.6	764.2	768.8	763.6
175°	769.4	766.5	767.1	771.1	766.5
177.5°	770.5	767.6	768.2	772.8	767.1
180°	769.4	769.4	769.4	769.4	769.4

(END OF REPORT)