

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011012

Luminaire Tested: S123RDIP-B775D805UB2750-4F0-XX-W2A-A_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011012
REPORT IS A COMBINATION OF REPORTS P993688 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B775D805UB2750-4F0-XX-W2A-A_4000K
Description: Define 3 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6161.0 lumens
Efficiency: N/A
Efficacy: 108.1 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011012

CATALOG NUMBER: S123RDIP-B775D805UB2750-4F0-XX-W2A-A_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1011012

CATALOG NUMBER: S123RDIP-B775D805UB2750-4F0-XX-W2A-A_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	94	90	87	90	87	84	81	74	71	69	61	60	58	50	49	48
2	90	83	77	72	83	77	72	67	65	62	58	55	52	50	45	43	41
3	82	73	66	61	76	68	62	57	58	53	50	49	45	43	40	38	36
4	76	65	58	52	70	61	54	49	52	47	43	44	40	37	36	34	31
5	70	58	51	45	64	54	47	42	47	41	37	40	36	32	33	30	28
6	64	53	45	39	59	49	42	37	42	37	33	36	32	29	30	27	25
7	60	48	40	35	55	44	38	33	38	33	29	33	29	26	28	24	22
8	55	43	36	31	51	41	34	29	35	30	26	30	26	23	25	22	20
9	52	40	32	27	48	37	31	26	32	27	23	28	24	21	24	20	18
10	48	36	29	25	45	34	28	23	30	25	21	26	22	19	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13159	13159	13159	13159
5°	13168	15155	13203	11244
10°	13052	18294	13110	9821
15°	12918	20763	12918	8659
20°	12653	22396	12724	7681
25°	12459	21277	12435	7009
30°	12234	14742	12208	6351
35°	11962	9466	11908	5855
40°	11624	6684	11566	5362
45°	11036	5349	11021	4882
50°	10314	4475	10280	4321
55°	9502	3688	9426	3663
60°	8704	3048	8617	3114
65°	7767	2439	7818	2640
70°	6903	1694	7088	2134
75°	5854	1258	6090	1642
80°	4658	834	5054	1231
85°	3314	395	3621	765

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 17567 cd/sqm

TEST NUMBER: P1011012

CATALOG NUMBER: S123RDIP-B775D805UB2750-4F0-XX-W2A-A_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.1	1.9
10°-20°	375.8	6.1
20°-30°	591.9	9.6
30°-40°	615.5	10.0
40°-50°	526.5	8.5
50°-60°	401.4	6.5
60°-70°	257.2	4.2
70°-80°	123.2	2.0
80°-90°	34.4	0.6
90°-100°	36.0	0.6
100°-110°	174.2	2.8
110°-120°	426.9	6.9
120°-130°	541.9	8.8
130°-140°	578.9	9.4
140°-150°	541.4	8.8
150°-160°	436.7	7.1
160°-170°	281.8	4.6
170°-180°	97.1	1.6
0°-30°	1087.7	17.7
0°-40°	1703.2	27.6
0°-60°	2631.2	42.7
0°-90°	3046.0	49.4
90°-120°	637.1	10.3
90°-150°	2299.4	37.3
90°-180°	3115.0	50.6
0°-180°	6161.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1222	1222	1222	1222	1222	
5°	1221	1452	1225	1077	1221	116
15°	1167	2063	1167	860	1167	328
25°	1061	2126	1059	700	1061	489
35°	926	922	922	570	926	580
45°	743	492	742	449	743	572
55°	524	309	520	307	524	470
65°	321	178	323	193	321	321
75°	154	75	160	98	154	166
85°	34	18	38	34	34	39
90°	1	23	1	23	1	4
95°	46	29	46	29	46	55
105°	226	33	226	33	226	240
115°	424	446	424	446	424	419
125°	598	610	598	610	598	534
135°	745	752	745	752	745	573
145°	859	868	859	868	859	538
155°	947	945	947	945	947	436
165°	998	996	998	996	998	282
175°	1022	1018	1022	1018	1022	97
180°	1022	1022	1022	1022	1022	

TEST NUMBER: P1011012

CATALOG NUMBER: S123RDIP-B775D805UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5
2.5°	1225.6	1234.0	1240.3	1244.4	1254.9	1261.2	1266.4	1275.8	1275.8	1277.9	1282.1
5°	1221.4	1239.2	1251.8	1268.5	1290.5	1301.0	1315.6	1328.2	1346.0	1355.4	1364.8
7.5°	1212.0	1237.1	1263.3	1288.4	1320.8	1341.8	1356.4	1388.9	1411.9	1440.2	1462.1
10°	1199.4	1234.0	1267.5	1306.2	1350.2	1381.6	1403.5	1446.4	1490.4	1530.2	1563.7
12.5°	1183.7	1225.6	1273.7	1320.8	1382.6	1414.0	1449.6	1503.0	1565.8	1616.0	1661.0
15°	1167.0	1215.1	1269.6	1327.1	1404.6	1448.5	1499.8	1564.7	1634.8	1707.1	1768.8
17.5°	1140.8	1201.5	1262.2	1346.0	1437.0	1463.2	1507.1	1596.1	1683.0	1747.9	1823.2
20°	1114.7	1182.7	1259.1	1334.5	1432.8	1493.5	1534.4	1628.6	1721.7	1800.2	1872.4
22.5°	1090.6	1161.8	1241.3	1336.5	1428.6	1489.4	1540.6	1639.0	1746.8	1834.7	1923.7
25°	1061.3	1138.7	1226.6	1316.7	1428.6	1474.7	1531.2	1645.3	1759.4	1860.9	1970.8
27.5°	1029.9	1108.4	1195.3	1287.4	1389.9	1458.0	1513.4	1635.9	1775.1	1883.9	1997.0
30°	998.5	1079.1	1162.8	1245.5	1360.6	1425.5	1489.4	1624.4	1783.5	1908.0	1994.9
32.5°	968.1	1036.2	1118.8	1199.4	1313.5	1384.7	1456.9	1612.9	1786.6	1891.3	1933.1
35°	926.3	997.4	1064.4	1150.2	1265.4	1335.5	1420.3	1611.8	1773.0	1837.9	1816.9
37.5°	887.5	947.2	1011.0	1087.4	1205.7	1296.8	1384.7	1584.6	1728.0	1732.2	1613.9
40°	844.6	893.8	947.2	1027.8	1155.5	1245.5	1340.7	1542.7	1646.3	1584.6	1376.3
42.5°	795.4	839.4	881.3	959.8	1099.0	1199.4	1302.0	1490.4	1528.1	1385.7	1169.1
45°	743.1	778.7	817.4	900.1	1039.3	1138.7	1241.3	1409.8	1371.1	1170.1	963.9
47.5°	688.7	719.0	756.7	832.1	975.5	1077.0	1174.3	1294.7	1196.3	980.7	808.0
50°	634.3	658.3	695.0	772.4	910.6	1002.7	1092.7	1171.2	1033.0	841.5	667.7
52.5°	580.9	599.7	637.4	703.3	837.3	925.2	990.1	1020.5	880.2	695.0	579.8
55°	524.4	545.3	570.4	637.4	770.3	835.2	878.1	877.1	732.6	589.3	479.4
57.5°	469.9	488.8	510.8	577.7	685.5	729.5	766.1	748.3	611.2	482.5	411.3
60°	421.8	432.3	456.3	512.8	594.5	632.2	653.1	622.7	499.2	407.1	340.2
62.5°	369.5	379.9	399.8	453.2	503.4	523.3	541.1	502.4	412.4	331.8	291.0
65°	321.3	334.9	347.5	390.4	417.6	441.7	439.6	407.1	322.4	270.0	236.5
67.5°	279.4	284.7	295.1	321.3	333.9	351.7	352.7	316.1	259.6	219.8	199.9
70°	234.4	239.7	247.0	259.6	267.9	272.1	270.0	237.6	195.7	171.6	153.9
72.5°	195.7	194.7	199.9	199.9	208.3	207.2	201.0	175.8	148.6	128.7	118.3
75°	153.9	154.9	155.9	153.9	150.7	146.5	141.3	122.5	104.7	95.2	85.8
77.5°	120.4	118.3	119.3	112.0	107.8	103.6	96.3	86.9	72.2	70.1	65.9
80°	85.8	84.8	83.7	80.6	71.2	67.0	61.8	56.5	53.4	51.3	50.2
82.5°	57.6	57.6	55.5	49.2	44.0	40.8	39.8	37.7	34.5	34.5	33.5
85°	34.5	33.5	31.4	25.1	22.0	22.0	22.0	22.0	19.9	19.9	18.8
87.5°	13.6	12.6	9.4	9.4	8.4	8.4	8.4	7.3	7.3	6.3	6.3
90°	0.8	2.5	4.2	5.9	7.6	8.4	9.5	11.7	13.8	16.0	18.2
92.5°	17.5	16.5	15.5	14.4	13.4	12.9	13.7	15.2	16.7	18.2	19.7
95°	46.3	39.4	32.5	25.6	18.7	15.2	16.1	18.0	19.8	21.7	23.5
97.5°	84.3	79.6	74.8	70.1	65.4	63.0	58.7	50.1	41.5	32.9	24.3
100°	128.3	131.7	135.1	138.4	141.8	143.5	130.3	104.0	77.7	51.4	25.1
102.5°	178.4	180.6	182.8	185.0	187.2	188.3	173.6	144.3	114.9	85.6	56.2
105°	226.2	228.1	229.9	231.8	233.7	234.6	227.0	211.8	196.6	181.4	166.2
107.5°	277.1	278.6	280.1	281.6	283.1	283.9	285.2	287.7	290.2	292.8	295.3
110°	327.9	329.3	330.6	332.0	333.3	334.0	334.9	336.8	338.7	340.5	342.4

TEST NUMBER: P1011012

CATALOG NUMBER: S123RDIP-B775D805UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	376.5	377.7	378.9	380.0	381.2	381.8	382.7	384.6	386.5	388.3	390.2
115°	424.3	425.3	426.3	427.4	428.4	428.9	429.7	431.2	432.7	434.2	435.7
117.5°	471.4	472.6	473.8	474.9	476.1	476.7	477.1	478.0	478.8	479.7	480.5
120°	514.7	516.2	517.7	519.2	520.7	521.5	521.8	522.3	522.8	523.3	523.8
122.5°	558.7	559.9	561.1	562.2	563.4	564.0	564.3	565.0	565.7	566.4	567.1
125°	598.2	599.6	600.9	602.3	603.6	604.3	604.6	605.3	606.0	606.6	607.3
127.5°	637.7	639.0	640.4	641.7	643.0	643.7	644.1	645.0	645.8	646.7	647.5
130°	674.1	675.5	676.8	678.2	679.5	680.2	680.5	681.2	681.9	682.5	683.2
132.5°	709.0	710.4	711.7	713.1	714.4	715.1	715.4	715.9	716.4	716.9	717.4
135°	744.7	745.7	746.7	747.7	748.7	749.2	749.5	750.2	750.9	751.6	752.3
137.5°	775.1	776.4	777.8	779.1	780.4	781.1	781.3	781.6	782.0	782.3	782.7
140°	805.4	806.4	807.4	808.5	809.5	810.0	810.3	810.8	811.3	811.8	812.3
142.5°	833.5	834.5	835.5	836.6	837.6	838.1	838.3	838.8	839.3	839.8	840.3
145°	859.3	860.5	861.7	862.8	864.0	864.6	864.8	865.1	865.5	865.8	866.2
147.5°	884.4	885.2	886.1	886.9	887.8	888.2	888.4	888.7	889.0	889.4	889.7
150°	907.1	907.6	908.1	908.6	909.1	909.4	909.6	909.9	910.2	910.6	910.9
152.5°	927.6	927.8	928.0	928.1	928.3	928.4	928.5	928.7	928.8	929.0	929.2
155°	946.6	946.3	945.9	945.6	945.3	945.1	945.2	945.4	945.5	945.7	945.9
157.5°	961.8	961.8	961.8	961.8	961.8	961.8	961.7	961.5	961.4	961.2	961.0
160°	975.5	975.3	975.1	975.0	974.8	974.7	974.6	974.4	974.3	974.1	973.9
162.5°	988.4	987.9	987.4	986.9	986.4	986.1	986.0	985.8	985.7	985.5	985.3
165°	998.2	997.7	997.2	996.7	996.2	996.0	995.9	995.7	995.6	995.4	995.2
167.5°	1006.6	1005.9	1005.3	1004.6	1003.9	1003.6	1003.6	1003.6	1003.6	1003.6	1003.6
170°	1013.4	1012.7	1012.1	1011.4	1010.7	1010.4	1010.4	1010.4	1010.4	1010.4	1010.4
172.5°	1018.0	1017.2	1016.3	1015.5	1014.6	1014.2	1014.3	1014.4	1014.6	1014.7	1014.9
175°	1021.8	1021.0	1020.1	1019.3	1018.4	1018.0	1018.1	1018.2	1018.4	1018.5	1018.7
177.5°	1023.3	1022.5	1021.6	1020.8	1019.9	1019.5	1019.6	1019.8	1019.9	1020.1	1020.3
180°	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8



TEST NUMBER: P1011012

CATALOG NUMBER: S123RDIP-B775D805UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5
2.5°	1290.5	1290.5	1299.9	1309.3	1304.1	1307.2	1318.8	1314.6	1322.9	1321.9	1325.0
5°	1387.8	1399.3	1408.8	1428.6	1431.8	1428.6	1448.5	1453.8	1463.2	1451.7	1456.9
7.5°	1497.7	1521.8	1544.8	1574.1	1583.5	1585.6	1596.1	1610.8	1623.3	1600.3	1611.8
10°	1604.5	1641.1	1688.2	1714.4	1737.4	1745.8	1754.2	1763.6	1778.2	1791.8	1781.4
12.5°	1719.6	1773.0	1818.0	1865.1	1893.4	1890.2	1914.3	1920.6	1932.1	1935.2	1939.4
15°	1813.8	1889.2	1917.4	1987.5	1993.8	2014.8	2042.0	2066.0	2069.2	2062.9	2062.9
17.5°	1903.8	1968.7	2018.9	2075.5	2087.0	2104.8	2139.3	2150.8	2155.0	2154.0	2154.0
20°	1977.1	2020.0	2104.8	2151.9	2170.7	2193.7	2217.8	2232.5	2235.6	2239.8	2233.5
22.5°	2025.2	2090.1	2159.2	2197.9	2213.6	2222.0	2237.7	2241.9	2236.6	2237.7	2238.7
25°	2062.9	2126.8	2168.6	2179.1	2178.0	2167.6	2156.1	2136.2	2134.1	2125.7	2109.0
27.5°	2073.4	2097.4	2092.2	2049.3	2006.4	2002.2	1933.1	1895.4	1852.5	1858.8	1834.7
30°	2016.9	1985.5	1911.1	1802.3	1757.3	1684.0	1606.6	1526.0	1494.6	1460.0	1523.9
32.5°	1878.7	1766.7	1634.8	1493.5	1418.2	1353.3	1270.6	1212.0	1178.5	1150.2	1204.7
35°	1670.4	1495.6	1320.8	1186.9	1125.1	1066.5	989.1	959.8	917.9	922.1	927.3
37.5°	1402.5	1209.9	1078.0	946.2	905.3	881.3	824.7	779.7	765.1	760.9	760.9
40°	1151.3	993.3	876.0	772.4	741.0	721.1	676.1	655.2	639.5	635.3	640.5
42.5°	952.4	817.4	726.4	657.3	635.3	610.2	591.3	565.2	562.0	554.7	564.1
45°	799.6	682.4	614.4	564.1	545.3	535.9	514.9	499.2	493.0	491.9	499.2
47.5°	678.2	587.2	527.5	496.1	481.4	472.0	454.2	448.0	441.7	443.8	440.6
50°	569.4	501.3	462.6	434.4	424.9	415.5	404.0	397.7	394.6	394.6	393.5
52.5°	488.8	432.3	407.1	381.0	376.8	371.6	359.0	354.8	349.6	348.5	352.7
55°	418.7	379.9	354.8	339.1	334.9	324.5	319.2	314.0	310.8	308.8	309.8
57.5°	357.9	328.6	311.9	298.3	291.0	286.8	277.4	276.3	274.2	274.2	273.2
60°	307.7	286.8	266.9	258.5	253.3	248.1	247.0	240.7	237.6	239.7	238.6
62.5°	260.6	243.9	232.4	222.9	219.8	215.6	212.5	210.4	207.2	208.3	208.3
65°	217.7	204.1	195.7	187.3	186.3	182.1	181.1	179.0	179.0	177.9	180.0
67.5°	179.0	169.6	162.2	157.0	153.9	154.9	150.7	147.6	147.6	146.5	149.7
70°	142.3	137.1	129.8	123.5	119.3	119.3	114.1	113.0	113.0	113.0	112.0
72.5°	109.9	100.5	97.3	95.2	95.2	95.2	93.1	93.1	92.1	93.1	92.1
75°	81.6	80.6	78.5	77.5	77.5	76.4	75.4	75.4	75.4	75.4	75.4
77.5°	63.8	63.8	61.8	60.7	60.7	60.7	59.7	59.7	58.6	58.6	58.6
80°	47.1	47.1	45.0	45.0	45.0	44.0	44.0	44.0	45.0	44.0	44.0
82.5°	32.4	32.4	31.4	32.4	31.4	30.4	30.4	30.4	29.3	30.4	30.4
85°	18.8	18.8	17.8	16.7	17.8	17.8	16.7	17.8	16.7	17.8	16.7
87.5°	7.3	6.3	6.3	6.3	5.2	6.3	5.2	5.2	6.3	5.2	6.3
90°	18.9	19.6	20.3	21.0	21.3	21.5	21.8	22.1	22.5	22.8	22.5
92.5°	20.9	22.1	23.3	24.5	25.1	25.2	25.3	25.5	25.6	25.8	25.6
95°	24.7	25.9	27.0	28.2	28.8	28.8	28.8	28.8	28.8	28.8	28.8
97.5°	25.7	27.0	28.4	29.7	30.4	30.5	30.6	30.8	30.9	31.1	30.9
100°	26.4	27.8	29.1	30.4	31.1	31.2	31.4	31.5	31.7	31.9	31.7
102.5°	50.6	45.0	39.5	33.9	31.1	31.3	31.6	31.9	32.3	32.6	32.3
105°	136.4	106.5	76.7	46.8	31.9	32.1	32.4	32.7	33.1	33.4	33.1
107.5°	269.3	243.3	217.4	191.4	178.4	167.3	145.2	123.1	101.0	78.9	101.0
110°	336.8	331.2	325.7	320.1	317.3	305.2	281.1	257.0	232.9	208.8	232.9



TEST NUMBER: P1011012

CATALOG NUMBER: S123RDIP-B775D805UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	391.7	393.2	394.7	396.2	397.0	396.8	396.5	396.2	395.8	395.5	395.8
115°	437.4	439.1	440.8	442.5	443.3	443.6	444.3	445.0	445.7	446.4	445.7
117.5°	481.9	483.2	484.6	485.9	486.6	486.7	486.9	487.0	487.2	487.4	487.2
120°	525.2	526.5	527.9	529.2	529.9	529.9	529.9	529.9	529.9	529.9	529.9
122.5°	567.9	568.8	569.6	570.5	570.9	571.0	571.1	571.3	571.4	571.6	571.4
125°	607.6	608.0	608.3	608.6	608.8	609.0	609.3	609.6	610.0	610.3	610.0
127.5°	648.0	648.5	649.0	649.5	649.8	649.6	649.3	649.0	648.6	648.3	648.6
130°	683.9	684.5	685.2	685.9	686.2	686.0	685.7	685.4	685.0	684.7	685.0
132.5°	718.1	718.7	719.4	720.1	720.4	720.1	719.6	719.1	718.6	718.1	718.6
135°	752.8	753.3	753.8	754.3	754.6	754.3	753.8	753.3	752.8	752.3	752.8
137.5°	783.5	784.3	785.2	786.0	786.4	786.2	785.9	785.6	785.2	784.9	785.2
140°	813.0	813.6	814.3	815.0	815.3	815.1	814.8	814.5	814.1	813.8	814.1
142.5°	840.8	841.3	841.8	842.3	842.6	842.3	841.8	841.3	840.8	840.3	840.8
145°	866.5	866.9	867.2	867.5	867.7	867.7	867.7	867.7	867.7	867.7	867.7
147.5°	890.0	890.4	890.7	891.0	891.2	890.8	889.9	889.1	888.2	887.4	888.2
150°	911.3	911.6	912.0	912.3	912.5	912.2	911.7	911.2	910.7	910.2	910.7
152.5°	929.9	930.5	931.2	931.9	932.2	931.8	930.9	930.1	929.2	928.4	929.2
155°	946.7	947.6	948.4	949.3	949.7	949.2	948.2	947.1	946.1	945.1	946.1
157.5°	962.0	963.0	964.1	965.1	965.6	964.9	963.6	962.2	960.9	959.5	960.9
160°	974.9	975.9	977.0	978.0	978.5	977.9	976.7	975.6	974.4	973.2	974.4
162.5°	986.5	987.7	988.8	990.0	990.6	990.1	989.1	988.1	987.1	986.1	987.1
165°	996.6	997.9	999.3	1000.6	1001.3	1000.7	999.5	998.4	997.2	996.0	997.2
167.5°	1004.9	1006.3	1007.6	1008.9	1009.6	1008.9	1007.6	1006.3	1004.9	1003.6	1004.9
170°	1011.8	1013.1	1014.5	1015.8	1016.5	1015.8	1014.5	1013.1	1011.8	1010.4	1011.8
172.5°	1016.3	1017.6	1019.0	1020.3	1021.0	1020.2	1018.7	1017.2	1015.7	1014.2	1015.7
175°	1019.9	1021.1	1022.2	1023.4	1024.0	1023.3	1022.0	1020.7	1019.3	1018.0	1019.3
177.5°	1021.6	1023.0	1024.3	1025.6	1026.3	1025.5	1023.8	1022.1	1020.4	1018.7	1020.4
180°	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8

TEST NUMBER: P1011012

CATALOG NUMBER: S123RDIP-B775D805UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5
2.5°	1319.8	1313.5	1309.3	1306.2	1303.1	1312.5	1299.9	1286.3	1276.9	1270.6	1268.5
5°	1458.0	1444.3	1432.8	1423.4	1425.5	1425.5	1403.5	1379.5	1358.5	1347.0	1334.5
7.5°	1618.1	1603.4	1580.4	1575.2	1571.0	1544.8	1522.8	1478.9	1452.7	1426.6	1403.5
10°	1777.2	1758.3	1736.4	1729.0	1718.6	1686.1	1652.6	1596.1	1563.7	1515.5	1485.2
12.5°	1925.8	1902.8	1880.8	1875.6	1859.9	1831.6	1774.0	1715.4	1660.0	1608.7	1555.3
15°	2050.3	2044.1	2010.6	1989.6	1955.1	1916.4	1903.8	1824.3	1754.2	1700.8	1604.5
17.5°	2155.0	2125.7	2094.3	2080.7	2067.1	2022.1	1977.1	1895.4	1820.1	1741.6	1679.8
20°	2238.7	2206.3	2184.3	2164.4	2158.1	2106.9	2035.7	1963.5	1880.8	1792.9	1712.3
22.5°	2242.9	2238.7	2224.1	2212.6	2200.0	2166.5	2110.0	2020.0	1932.1	1835.8	1730.1
25°	2156.1	2149.8	2191.6	2181.2	2189.5	2177.0	2146.6	2071.3	1968.7	1855.7	1748.9
27.5°	1894.4	1958.2	2024.2	2047.2	2062.9	2107.9	2122.6	2080.7	1998.0	1877.7	1758.3
30°	1538.5	1623.3	1730.1	1787.6	1831.6	1915.3	2024.2	2037.8	1999.1	1902.8	1756.2
32.5°	1207.8	1285.3	1371.1	1439.1	1497.7	1669.4	1815.9	1921.6	1940.5	1890.2	1761.5
35°	973.4	1006.9	1088.5	1153.4	1232.9	1379.5	1552.2	1722.8	1837.9	1844.2	1745.8
37.5°	802.8	820.6	891.7	928.4	975.5	1104.2	1265.4	1488.3	1667.3	1752.1	1701.8
40°	664.6	705.4	746.2	767.2	800.7	889.6	1044.5	1219.3	1441.2	1598.2	1633.8
42.5°	576.7	594.5	620.7	650.0	670.9	748.3	852.0	1012.1	1212.0	1430.7	1529.1
45°	508.7	514.9	542.2	561.0	583.0	637.4	710.7	844.6	1020.5	1236.1	1403.5
47.5°	452.1	464.7	479.4	490.9	505.5	547.4	610.2	707.5	862.4	1055.0	1235.0
50°	401.9	409.2	428.1	433.3	443.8	473.1	521.2	595.5	723.2	877.1	1063.4
52.5°	354.8	368.4	375.7	383.1	392.5	416.6	448.0	508.7	605.0	749.4	907.4
55°	318.2	322.4	332.8	339.1	346.4	363.2	390.4	435.4	510.8	625.9	775.6
57.5°	282.6	282.6	293.1	298.3	305.6	318.2	342.2	376.8	431.2	517.0	654.1
60°	244.9	246.0	254.3	260.6	262.7	275.3	295.1	322.4	364.2	427.0	539.0
62.5°	211.4	216.7	220.8	222.9	230.3	237.6	254.3	273.2	302.5	357.9	437.5
65°	183.2	184.2	187.3	189.4	192.6	201.0	213.5	226.1	251.2	292.0	356.9
67.5°	150.7	154.9	159.1	159.1	162.2	166.4	179.0	189.4	208.3	232.4	276.3
70°	113.0	115.1	121.4	124.5	128.7	136.1	142.3	148.6	163.3	181.1	214.6
72.5°	94.2	94.2	96.3	97.3	97.3	102.6	112.0	118.3	125.6	138.2	161.2
75°	75.4	75.4	78.5	77.5	79.5	81.6	82.7	86.9	91.1	100.5	114.1
77.5°	59.7	60.7	60.7	61.8	61.8	62.8	63.8	65.9	68.0	73.3	79.5
80°	44.0	45.0	45.0	46.1	46.1	47.1	48.1	49.2	51.3	53.4	56.5
82.5°	30.4	31.4	31.4	32.4	31.4	32.4	33.5	33.5	34.5	36.6	37.7
85°	17.8	17.8	18.8	17.8	17.8	17.8	18.8	18.8	19.9	23.0	23.0
87.5°	5.2	6.3	5.2	6.3	6.3	6.3	6.3	7.3	7.3	8.4	9.4
90°	22.1	21.8	21.5	21.3	21.0	20.3	19.6	18.9	18.2	16.0	13.8
92.5°	25.5	25.3	25.2	25.1	24.5	23.3	22.1	20.9	19.7	18.2	16.7
95°	28.8	28.8	28.8	28.8	28.2	27.0	25.9	24.7	23.5	21.7	19.8
97.5°	30.8	30.6	30.5	30.4	29.7	28.4	27.0	25.7	24.3	32.9	41.5
100°	31.5	31.4	31.2	31.1	30.4	29.1	27.8	26.4	25.1	51.4	77.7
102.5°	31.9	31.6	31.3	31.1	33.9	39.5	45.0	50.6	56.2	85.6	114.9
105°	32.7	32.4	32.1	31.9	46.8	76.7	106.5	136.4	166.2	181.4	196.6
107.5°	123.1	145.2	167.3	178.4	191.4	217.4	243.3	269.3	295.3	292.8	290.2
110°	257.0	281.1	305.2	317.3	320.1	325.7	331.2	336.8	342.4	340.5	338.7

TEST NUMBER: P1011012

CATALOG NUMBER: S123RDIP-B775D805UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	396.2	396.5	396.8	397.0	396.2	394.7	393.2	391.7	390.2	388.3	386.5
115°	445.0	444.3	443.6	443.3	442.5	440.8	439.1	437.4	435.7	434.2	432.7
117.5°	487.0	486.9	486.7	486.6	485.9	484.6	483.2	481.9	480.5	479.7	478.8
120°	529.9	529.9	529.9	529.9	529.2	527.9	526.5	525.2	523.8	523.3	522.8
122.5°	571.3	571.1	571.0	570.9	570.5	569.6	568.8	567.9	567.1	566.4	565.7
125°	609.6	609.3	609.0	608.8	608.6	608.3	608.0	607.6	607.3	606.6	606.0
127.5°	649.0	649.3	649.6	649.8	649.5	649.0	648.5	648.0	647.5	646.7	645.8
130°	685.4	685.7	686.0	686.2	685.9	685.2	684.5	683.9	683.2	682.5	681.9
132.5°	719.1	719.6	720.1	720.4	720.1	719.4	718.7	718.1	717.4	716.9	716.4
135°	753.3	753.8	754.3	754.6	754.3	753.8	753.3	752.8	752.3	751.6	750.9
137.5°	785.6	785.9	786.2	786.4	786.0	785.2	784.3	783.5	782.7	782.3	782.0
140°	814.5	814.8	815.1	815.3	815.0	814.3	813.6	813.0	812.3	811.8	811.3
142.5°	841.3	841.8	842.3	842.6	842.3	841.8	841.3	840.8	840.3	839.8	839.3
145°	867.7	867.7	867.7	867.7	867.5	867.2	866.9	866.5	866.2	865.8	865.5
147.5°	889.1	889.9	890.8	891.2	891.0	890.7	890.4	890.0	889.7	889.4	889.0
150°	911.2	911.7	912.2	912.5	912.3	912.0	911.6	911.3	910.9	910.6	910.2
152.5°	930.1	930.9	931.8	932.2	931.9	931.2	930.5	929.9	929.2	929.0	928.8
155°	947.1	948.2	949.2	949.7	949.3	948.4	947.6	946.7	945.9	945.7	945.5
157.5°	962.2	963.6	964.9	965.6	965.1	964.1	963.0	962.0	961.0	961.2	961.4
160°	975.6	976.7	977.9	978.5	978.0	977.0	975.9	974.9	973.9	974.1	974.3
162.5°	988.1	989.1	990.1	990.6	990.0	988.8	987.7	986.5	985.3	985.5	985.7
165°	998.4	999.5	1000.7	1001.3	1000.6	999.3	997.9	996.6	995.2	995.4	995.6
167.5°	1006.3	1007.6	1008.9	1009.6	1008.9	1007.6	1006.3	1004.9	1003.6	1003.6	1003.6
170°	1013.1	1014.5	1015.8	1016.5	1015.8	1014.5	1013.1	1011.8	1010.4	1010.4	1010.4
172.5°	1017.2	1018.7	1020.2	1021.0	1020.3	1019.0	1017.6	1016.3	1014.9	1014.7	1014.6
175°	1020.7	1022.0	1023.3	1024.0	1023.4	1022.2	1021.1	1019.9	1018.7	1018.5	1018.4
177.5°	1022.1	1023.8	1025.5	1026.3	1025.6	1024.3	1023.0	1021.6	1020.3	1020.1	1019.9
180°	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8

TEST NUMBER: P1011012

CATALOG NUMBER: S123RDIP-B775D805UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5
2.5°	1265.4	1260.1	1254.9	1254.9	1243.4	1232.9	1227.7	1229.8	1223.5	1215.1	1206.8
5°	1320.8	1299.9	1295.7	1284.2	1268.5	1246.5	1235.0	1224.6	1212.0	1195.3	1179.6
7.5°	1372.1	1344.9	1330.3	1318.8	1288.4	1258.0	1232.9	1216.2	1194.2	1169.1	1150.2
10°	1439.1	1388.9	1373.2	1347.0	1304.1	1261.2	1231.9	1204.7	1174.3	1145.0	1119.9
12.5°	1492.5	1434.9	1405.6	1379.5	1324.0	1269.6	1220.4	1186.9	1150.2	1117.8	1085.4
15°	1553.2	1488.3	1437.0	1405.6	1335.5	1269.6	1214.1	1167.0	1126.2	1086.4	1058.1
17.5°	1582.5	1500.9	1477.8	1432.8	1331.3	1265.4	1197.3	1147.1	1097.9	1051.9	1018.4
20°	1628.6	1533.3	1475.7	1445.4	1355.4	1258.0	1178.5	1120.9	1069.7	1020.5	984.9
22.5°	1631.7	1528.1	1490.4	1432.8	1321.9	1236.1	1161.8	1091.6	1032.0	985.9	949.3
25°	1624.4	1518.7	1466.3	1420.3	1328.2	1223.5	1128.3	1059.2	1000.6	947.2	904.3
27.5°	1621.2	1491.4	1442.3	1396.2	1292.6	1186.9	1108.4	1029.9	962.9	915.8	871.8
30°	1617.0	1462.1	1402.5	1349.1	1253.9	1158.6	1064.4	996.4	932.5	872.9	828.9
32.5°	1589.8	1422.4	1361.7	1305.1	1202.6	1107.3	1033.0	960.8	891.7	836.3	796.5
35°	1581.5	1385.7	1306.2	1245.5	1145.0	1060.2	981.7	922.1	857.2	801.7	754.6
37.5°	1557.4	1348.1	1262.2	1184.8	1080.1	999.5	942.0	882.3	819.5	759.9	722.2
40°	1515.5	1304.1	1206.8	1127.2	1019.4	937.8	884.4	840.4	778.7	725.3	679.3
42.5°	1453.8	1259.1	1154.4	1070.7	951.4	875.0	831.0	789.2	736.8	681.4	643.7
45°	1382.6	1199.4	1102.1	1009.0	887.5	813.2	767.2	742.1	693.9	646.8	602.9
47.5°	1285.3	1137.7	1041.4	945.1	821.6	749.4	712.8	687.6	654.1	602.9	567.3
50°	1162.8	1058.1	967.1	881.3	756.7	687.6	651.0	632.2	603.9	567.3	532.7
52.5°	1026.7	966.0	890.7	811.1	690.8	625.9	592.4	577.7	556.8	522.3	493.0
55°	889.6	863.5	812.2	733.7	621.7	568.3	539.0	520.2	504.5	479.4	454.2
57.5°	767.2	754.6	719.0	658.3	564.1	508.7	483.5	471.0	458.4	439.6	414.5
60°	640.5	654.1	617.5	587.2	501.3	453.2	431.2	417.6	411.3	394.6	378.9
62.5°	530.6	543.2	522.3	499.2	438.5	395.6	382.0	369.5	365.3	350.6	334.9
65°	431.2	446.9	431.2	418.7	382.0	346.4	329.7	323.4	319.2	309.8	297.2
67.5°	343.3	359.0	351.7	336.0	324.5	295.1	285.7	279.4	277.4	270.0	259.6
70°	258.5	280.5	282.6	273.2	262.7	249.1	242.8	240.7	235.5	229.2	222.9
72.5°	186.3	211.4	212.5	212.5	206.2	206.2	199.9	196.8	196.8	190.5	183.2
75°	137.1	153.9	155.9	158.0	161.2	164.3	160.1	160.1	159.1	152.8	149.7
77.5°	91.1	105.7	110.9	118.3	122.5	122.5	124.5	126.6	124.5	121.4	119.3
80°	58.6	69.1	75.4	79.5	85.8	89.0	92.1	93.1	91.1	90.0	86.9
82.5°	38.7	41.9	45.0	50.2	57.6	62.8	62.8	61.8	63.8	62.8	61.8
85°	22.0	24.1	25.1	26.2	30.4	35.6	36.6	37.7	39.8	37.7	35.6
87.5°	8.4	9.4	9.4	9.4	11.5	12.6	15.7	19.9	18.8	16.7	16.7
90°	11.7	9.5	8.4	7.6	5.9	4.2	2.5	0.8	2.5	4.2	5.9
92.5°	15.2	13.7	12.9	13.4	14.4	15.5	16.5	17.5	16.5	15.5	14.4
95°	18.0	16.1	15.2	18.7	25.6	32.5	39.4	46.3	39.4	32.5	25.6
97.5°	50.1	58.7	63.0	65.4	70.1	74.8	79.6	84.3	79.6	74.8	70.1
100°	104.0	130.3	143.5	141.8	138.4	135.1	131.7	128.3	131.7	135.1	138.4
102.5°	144.3	173.6	188.3	187.2	185.0	182.8	180.6	178.4	180.6	182.8	185.0
105°	211.8	227.0	234.6	233.7	231.8	229.9	228.1	226.2	228.1	229.9	231.8
107.5°	287.7	285.2	283.9	283.1	281.6	280.1	278.6	277.1	278.6	280.1	281.6
110°	336.8	334.9	334.0	333.3	332.0	330.6	329.3	327.9	329.3	330.6	332.0

TEST NUMBER: P1011012

CATALOG NUMBER: S123RDIP-B775D805UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	384.6	382.7	381.8	381.2	380.0	378.9	377.7	376.5	377.7	378.9	380.0
115°	431.2	429.7	428.9	428.4	427.4	426.3	425.3	424.3	425.3	426.3	427.4
117.5°	478.0	477.1	476.7	476.1	474.9	473.8	472.6	471.4	472.6	473.8	474.9
120°	522.3	521.8	521.5	520.7	519.2	517.7	516.2	514.7	516.2	517.7	519.2
122.5°	565.0	564.3	564.0	563.4	562.2	561.1	559.9	558.7	559.9	561.1	562.2
125°	605.3	604.6	604.3	603.6	602.3	600.9	599.6	598.2	599.6	600.9	602.3
127.5°	645.0	644.1	643.7	643.0	641.7	640.4	639.0	637.7	639.0	640.4	641.7
130°	681.2	680.5	680.2	679.5	678.2	676.8	675.5	674.1	675.5	676.8	678.2
132.5°	715.9	715.4	715.1	714.4	713.1	711.7	710.4	709.0	710.4	711.7	713.1
135°	750.2	749.5	749.2	748.7	747.7	746.7	745.7	744.7	745.7	746.7	747.7
137.5°	781.6	781.3	781.1	780.4	779.1	777.8	776.4	775.1	776.4	777.8	779.1
140°	810.8	810.3	810.0	809.5	808.5	807.4	806.4	805.4	806.4	807.4	808.5
142.5°	838.8	838.3	838.1	837.6	836.6	835.5	834.5	833.5	834.5	835.5	836.6
145°	865.1	864.8	864.6	864.0	862.8	861.7	860.5	859.3	860.5	861.7	862.8
147.5°	888.7	888.4	888.2	887.8	886.9	886.1	885.2	884.4	885.2	886.1	886.9
150°	909.9	909.6	909.4	909.1	908.6	908.1	907.6	907.1	907.6	908.1	908.6
152.5°	928.7	928.5	928.4	928.3	928.1	928.0	927.8	927.6	927.8	928.0	928.1
155°	945.4	945.2	945.1	945.3	945.6	945.9	946.3	946.6	946.3	945.9	945.6
157.5°	961.5	961.7	961.8	961.8	961.8	961.8	961.8	961.8	961.8	961.8	961.8
160°	974.4	974.6	974.7	974.8	975.0	975.1	975.3	975.5	975.3	975.1	975.0
162.5°	985.8	986.0	986.1	986.4	986.9	987.4	987.9	988.4	987.9	987.4	986.9
165°	995.7	995.9	996.0	996.2	996.7	997.2	997.7	998.2	997.7	997.2	996.7
167.5°	1003.6	1003.6	1003.6	1003.9	1004.6	1005.3	1005.9	1006.6	1005.9	1005.3	1004.6
170°	1010.4	1010.4	1010.4	1010.7	1011.4	1012.1	1012.7	1013.4	1012.7	1012.1	1011.4
172.5°	1014.4	1014.3	1014.2	1014.6	1015.5	1016.3	1017.2	1018.0	1017.2	1016.3	1015.5
175°	1018.2	1018.1	1018.0	1018.4	1019.3	1020.1	1021.0	1021.8	1021.0	1020.1	1019.3
177.5°	1019.8	1019.6	1019.5	1019.9	1020.8	1021.6	1022.5	1023.3	1022.5	1021.6	1020.8
180°	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8

TEST NUMBER: P1011012

CATALOG NUMBER: S123RDIP-B775D805UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5
2.5°	1206.8	1201.5	1199.4	1194.2	1181.6	1173.3	1163.9	1157.6	1158.6	1153.4	1156.5
5°	1169.1	1168.0	1160.7	1150.2	1132.5	1123.0	1106.3	1097.9	1093.7	1094.8	1088.5
7.5°	1137.7	1128.3	1123.0	1106.3	1089.5	1069.7	1056.0	1048.7	1042.4	1036.2	1032.0
10°	1102.1	1093.7	1085.4	1067.6	1044.5	1025.7	1006.9	999.5	990.1	985.9	982.8
12.5°	1064.4	1059.2	1048.7	1027.8	1001.6	983.8	961.9	957.7	945.1	936.7	934.6
15°	1029.9	1026.7	1007.9	983.8	957.7	939.9	921.0	908.5	887.5	891.7	884.4
17.5°	993.3	979.6	968.1	935.7	923.1	895.9	873.9	867.7	853.0	843.6	834.2
20°	952.4	944.1	929.4	908.5	878.1	846.7	830.0	819.5	811.1	796.5	792.3
22.5°	913.7	903.2	890.7	863.5	837.3	811.1	788.1	778.7	768.2	757.8	751.5
25°	883.4	867.7	854.0	820.6	794.4	772.4	757.8	742.1	727.4	721.1	719.0
27.5°	836.3	826.8	813.2	781.8	757.8	733.7	720.1	709.6	693.9	686.6	680.3
30°	805.9	787.1	771.4	746.2	722.2	696.0	683.4	670.9	661.5	652.0	644.7
32.5°	765.1	750.4	737.9	712.8	688.7	664.6	651.0	632.2	626.9	619.6	611.2
35°	725.3	715.9	702.3	675.1	648.9	632.2	617.5	599.7	593.4	588.2	580.9
37.5°	687.6	674.0	664.6	638.4	615.4	595.5	584.0	569.4	565.2	558.9	553.7
40°	655.2	641.6	632.2	606.0	581.9	561.0	553.7	539.0	532.7	525.4	522.3
42.5°	618.6	607.0	594.5	575.6	550.5	529.6	514.9	506.6	498.2	495.1	488.8
45°	579.8	569.4	559.9	539.0	512.8	498.2	485.6	474.1	467.8	462.6	458.4
47.5°	546.3	536.9	524.4	501.3	480.4	466.8	454.2	442.7	436.4	430.2	424.9
50°	507.6	502.4	488.8	466.8	446.9	431.2	419.7	409.2	405.0	397.7	389.3
52.5°	473.1	463.7	452.1	434.4	416.6	397.7	382.0	375.7	368.4	364.2	356.9
55°	432.3	426.0	413.4	397.7	378.9	363.2	351.7	343.3	333.9	329.7	320.3
57.5°	397.7	386.2	379.9	360.0	342.2	326.5	318.2	309.8	299.3	293.1	288.9
60°	360.0	349.6	340.2	323.4	310.8	294.1	281.5	274.2	266.9	258.5	254.3
62.5°	323.4	315.0	303.5	289.9	274.2	260.6	251.2	240.7	236.5	228.2	225.0
65°	283.6	277.4	267.9	252.2	239.7	228.2	218.7	210.4	206.2	203.0	201.0
67.5°	248.1	239.7	233.4	219.8	206.2	196.8	191.5	186.3	181.1	177.9	174.8
70°	211.4	205.1	198.9	186.3	176.9	168.5	164.3	160.1	157.0	153.9	150.7
72.5°	173.7	170.6	164.3	155.9	148.6	142.3	139.2	134.0	130.8	125.6	123.5
75°	143.4	138.2	135.0	127.7	121.4	116.2	112.0	105.7	101.5	99.4	98.4
77.5°	113.0	110.9	106.8	100.5	97.3	92.1	85.8	83.7	81.6	81.6	80.6
80°	84.8	81.6	78.5	73.3	70.1	65.9	65.9	65.9	64.9	65.9	64.9
82.5°	57.6	55.5	53.4	50.2	49.2	49.2	50.2	50.2	50.2	50.2	50.2
85°	33.5	33.5	33.5	34.5	33.5	33.5	34.5	35.6	34.5	34.5	33.5
87.5°	15.7	15.7	16.7	16.7	17.8	17.8	17.8	17.8	17.8	17.8	18.8
90°	7.6	8.4	9.5	11.7	13.8	16.0	18.2	18.9	19.6	20.3	21.0
92.5°	13.4	12.9	13.7	15.2	16.7	18.2	19.7	20.9	22.1	23.3	24.5
95°	18.7	15.2	16.1	18.0	19.8	21.7	23.5	24.7	25.9	27.0	28.2
97.5°	65.4	63.0	58.7	50.1	41.5	32.9	24.3	25.7	27.0	28.4	29.7
100°	141.8	143.5	130.3	104.0	77.7	51.4	25.1	26.4	27.8	29.1	30.4
102.5°	187.2	188.3	173.6	144.3	114.9	85.6	56.2	50.6	45.0	39.5	33.9
105°	233.7	234.6	227.0	211.8	196.6	181.4	166.2	136.4	106.5	76.7	46.8
107.5°	283.1	283.9	285.2	287.7	290.2	292.8	295.3	269.3	243.3	217.4	191.4
110°	333.3	334.0	334.9	336.8	338.7	340.5	342.4	336.8	331.2	325.7	320.1

TEST NUMBER: P1011012

CATALOG NUMBER: S123RDIP-B775D805UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	381.2	381.8	382.7	384.6	386.5	388.3	390.2	391.7	393.2	394.7	396.2
115°	428.4	428.9	429.7	431.2	432.7	434.2	435.7	437.4	439.1	440.8	442.5
117.5°	476.1	476.7	477.1	478.0	478.8	479.7	480.5	481.9	483.2	484.6	485.9
120°	520.7	521.5	521.8	522.3	522.8	523.3	523.8	525.2	526.5	527.9	529.2
122.5°	563.4	564.0	564.3	565.0	565.7	566.4	567.1	567.9	568.8	569.6	570.5
125°	603.6	604.3	604.6	605.3	606.0	606.6	607.3	607.6	608.0	608.3	608.6
127.5°	643.0	643.7	644.1	645.0	645.8	646.7	647.5	648.0	648.5	649.0	649.5
130°	679.5	680.2	680.5	681.2	681.9	682.5	683.2	683.9	684.5	685.2	685.9
132.5°	714.4	715.1	715.4	715.9	716.4	716.9	717.4	718.1	718.7	719.4	720.1
135°	748.7	749.2	749.5	750.2	750.9	751.6	752.3	752.8	753.3	753.8	754.3
137.5°	780.4	781.1	781.3	781.6	782.0	782.3	782.7	783.5	784.3	785.2	786.0
140°	809.5	810.0	810.3	810.8	811.3	811.8	812.3	813.0	813.6	814.3	815.0
142.5°	837.6	838.1	838.3	838.8	839.3	839.8	840.3	840.8	841.3	841.8	842.3
145°	864.0	864.6	864.8	865.1	865.5	865.8	866.2	866.5	866.9	867.2	867.5
147.5°	887.8	888.2	888.4	888.7	889.0	889.4	889.7	890.0	890.4	890.7	891.0
150°	909.1	909.4	909.6	909.9	910.2	910.6	910.9	911.3	911.6	912.0	912.3
152.5°	928.3	928.4	928.5	928.7	928.8	929.0	929.2	929.9	930.5	931.2	931.9
155°	945.3	945.1	945.2	945.4	945.5	945.7	945.9	946.7	947.6	948.4	949.3
157.5°	961.8	961.8	961.7	961.5	961.4	961.2	961.0	962.0	963.0	964.1	965.1
160°	974.8	974.7	974.6	974.4	974.3	974.1	973.9	974.9	975.9	977.0	978.0
162.5°	986.4	986.1	986.0	985.8	985.7	985.5	985.3	986.5	987.7	988.8	990.0
165°	996.2	996.0	995.9	995.7	995.6	995.4	995.2	996.6	997.9	999.3	1000.6
167.5°	1003.9	1003.6	1003.6	1003.6	1003.6	1003.6	1003.6	1004.9	1006.3	1007.6	1008.9
170°	1010.7	1010.4	1010.4	1010.4	1010.4	1010.4	1010.4	1011.8	1013.1	1014.5	1015.8
172.5°	1014.6	1014.2	1014.3	1014.4	1014.6	1014.7	1014.9	1016.3	1017.6	1019.0	1020.3
175°	1018.4	1018.0	1018.1	1018.2	1018.4	1018.5	1018.7	1019.9	1021.1	1022.2	1023.4
177.5°	1019.9	1019.5	1019.6	1019.8	1019.9	1020.1	1020.3	1021.6	1023.0	1024.3	1025.6
180°	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8

TEST NUMBER: P1011012

CATALOG NUMBER: S123RDIP-B775D805UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5
2.5°	1155.5	1156.5	1153.4	1147.1	1146.1	1148.2	1154.4	1152.3	1147.1	1156.5	1148.2
5°	1091.6	1086.4	1084.3	1086.4	1080.1	1077.0	1083.3	1080.1	1083.3	1084.3	1087.4
7.5°	1029.9	1030.9	1024.6	1025.7	1017.3	1019.4	1019.4	1019.4	1022.6	1024.6	1028.8
10°	976.5	978.6	971.3	972.3	966.0	961.9	965.0	971.3	971.3	971.3	973.4
12.5°	933.6	924.2	918.9	917.9	910.6	908.5	914.8	916.8	922.1	922.1	925.2
15°	880.2	878.1	873.9	873.9	856.1	860.3	862.4	869.7	880.2	871.8	873.9
17.5°	832.1	826.8	821.6	819.5	817.4	811.1	819.5	818.5	824.7	825.8	828.9
20°	789.2	785.0	774.5	775.6	777.6	768.2	773.5	773.5	779.7	786.0	793.3
22.5°	747.3	743.1	737.9	740.0	733.7	731.6	731.6	736.8	744.2	749.4	748.3
25°	714.8	707.5	704.4	701.2	698.1	700.2	697.1	702.3	707.5	710.7	707.5
27.5°	678.2	675.1	668.8	665.7	660.4	662.5	664.6	668.8	671.9	671.9	675.1
30°	642.6	638.4	636.4	633.2	633.2	629.0	630.1	634.3	637.4	640.5	644.7
32.5°	608.1	605.0	601.8	601.8	599.7	598.7	597.6	603.9	603.9	610.2	610.2
35°	579.8	574.6	574.6	569.4	571.5	570.4	568.3	572.5	573.6	577.7	576.7
37.5°	548.4	548.4	546.3	541.1	536.9	538.0	543.2	543.2	546.3	545.3	548.4
40°	517.0	514.9	514.9	511.8	510.8	509.7	510.8	511.8	517.0	516.0	517.0
42.5°	485.6	486.7	481.4	481.4	481.4	478.3	479.4	480.4	482.5	484.6	487.7
45°	455.3	453.2	452.1	450.1	448.0	449.0	448.0	452.1	451.1	453.2	456.3
47.5°	422.8	419.7	418.7	414.5	414.5	416.6	415.5	418.7	419.7	422.8	420.7
50°	391.4	387.3	384.1	385.2	378.9	381.0	381.0	384.1	387.3	388.3	390.4
52.5°	354.8	353.8	352.7	347.5	346.4	345.4	346.4	347.5	351.7	354.8	355.9
55°	319.2	318.2	311.9	309.8	306.7	306.7	308.8	309.8	317.1	318.2	322.4
57.5°	286.8	283.6	276.3	275.3	275.3	275.3	272.1	276.3	278.4	283.6	283.6
60°	251.2	251.2	244.9	244.9	246.0	244.9	244.9	246.0	246.0	250.1	252.2
62.5°	222.9	221.9	221.9	219.8	218.7	219.8	218.7	218.7	219.8	222.9	226.1
65°	197.8	196.8	195.7	194.7	192.6	192.6	193.6	195.7	195.7	197.8	198.9
67.5°	173.7	173.7	171.6	171.6	170.6	169.6	170.6	169.6	173.7	173.7	174.8
70°	149.7	148.6	145.5	144.4	141.3	142.3	142.3	145.5	146.5	148.6	150.7
72.5°	120.4	120.4	118.3	116.2	117.2	115.1	115.1	116.2	116.2	119.3	120.4
75°	99.4	97.3	96.3	97.3	96.3	98.4	96.3	96.3	98.4	98.4	98.4
77.5°	81.6	81.6	80.6	80.6	81.6	80.6	81.6	81.6	81.6	80.6	81.6
80°	67.0	65.9	65.9	65.9	64.9	64.9	64.9	64.9	64.9	64.9	64.9
82.5°	50.2	50.2	49.2	50.2	50.2	49.2	50.2	49.2	49.2	50.2	50.2
85°	33.5	35.6	33.5	33.5	34.5	34.5	35.6	34.5	35.6	33.5	34.5
87.5°	17.8	18.8	18.8	17.8	17.8	18.8	18.8	18.8	19.9	17.8	18.8
90°	21.3	21.5	21.8	22.1	22.5	22.8	22.5	22.1	21.8	21.5	21.3
92.5°	25.1	25.2	25.3	25.5	25.6	25.8	25.6	25.5	25.3	25.2	25.1
95°	28.8	28.8	28.8	28.8	28.8	28.8	28.8	28.8	28.8	28.8	28.8
97.5°	30.4	30.5	30.6	30.8	30.9	31.1	30.9	30.8	30.6	30.5	30.4
100°	31.1	31.2	31.4	31.5	31.7	31.9	31.7	31.5	31.4	31.2	31.1
102.5°	31.1	31.3	31.6	31.9	32.3	32.6	32.3	31.9	31.6	31.3	31.1
105°	31.9	32.1	32.4	32.7	33.1	33.4	33.1	32.7	32.4	32.1	31.9
107.5°	178.4	167.3	145.2	123.1	101.0	78.9	101.0	123.1	145.2	167.3	178.4
110°	317.3	305.2	281.1	257.0	232.9	208.8	232.9	257.0	281.1	305.2	317.3

TEST NUMBER: P1011012

CATALOG NUMBER: S123RDIP-B775D805UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	397.0	396.8	396.5	396.2	395.8	395.5	395.8	396.2	396.5	396.8	397.0
115°	443.3	443.6	444.3	445.0	445.7	446.4	445.7	445.0	444.3	443.6	443.3
117.5°	486.6	486.7	486.9	487.0	487.2	487.4	487.2	487.0	486.9	486.7	486.6
120°	529.9	529.9	529.9	529.9	529.9	529.9	529.9	529.9	529.9	529.9	529.9
122.5°	570.9	571.0	571.1	571.3	571.4	571.6	571.4	571.3	571.1	571.0	570.9
125°	608.8	609.0	609.3	609.6	610.0	610.3	610.0	609.6	609.3	609.0	608.8
127.5°	649.8	649.6	649.3	649.0	648.6	648.3	648.6	649.0	649.3	649.6	649.8
130°	686.2	686.0	685.7	685.4	685.0	684.7	685.0	685.4	685.7	686.0	686.2
132.5°	720.4	720.1	719.6	719.1	718.6	718.1	718.6	719.1	719.6	720.1	720.4
135°	754.6	754.3	753.8	753.3	752.8	752.3	752.8	753.3	753.8	754.3	754.6
137.5°	786.4	786.2	785.9	785.6	785.2	784.9	785.2	785.6	785.9	786.2	786.4
140°	815.3	815.1	814.8	814.5	814.1	813.8	814.1	814.5	814.8	815.1	815.3
142.5°	842.6	842.3	841.8	841.3	840.8	840.3	840.8	841.3	841.8	842.3	842.6
145°	867.7	867.7	867.7	867.7	867.7	867.7	867.7	867.7	867.7	867.7	867.7
147.5°	891.2	890.8	889.9	889.1	888.2	887.4	888.2	889.1	889.9	890.8	891.2
150°	912.5	912.2	911.7	911.2	910.7	910.2	910.7	911.2	911.7	912.2	912.5
152.5°	932.2	931.8	930.9	930.1	929.2	928.4	929.2	930.1	930.9	931.8	932.2
155°	949.7	949.2	948.2	947.1	946.1	945.1	946.1	947.1	948.2	949.2	949.7
157.5°	965.6	964.9	963.6	962.2	960.9	959.5	960.9	962.2	963.6	964.9	965.6
160°	978.5	977.9	976.7	975.6	974.4	973.2	974.4	975.6	976.7	977.9	978.5
162.5°	990.6	990.1	989.1	988.1	987.1	986.1	987.1	988.1	989.1	990.1	990.6
165°	1001.3	1000.7	999.5	998.4	997.2	996.0	997.2	998.4	999.5	1000.7	1001.3
167.5°	1009.6	1008.9	1007.6	1006.3	1004.9	1003.6	1004.9	1006.3	1007.6	1008.9	1009.6
170°	1016.5	1015.8	1014.5	1013.1	1011.8	1010.4	1011.8	1013.1	1014.5	1015.8	1016.5
172.5°	1021.0	1020.2	1018.7	1017.2	1015.7	1014.2	1015.7	1017.2	1018.7	1020.2	1021.0
175°	1024.0	1023.3	1022.0	1020.7	1019.3	1018.0	1019.3	1020.7	1022.0	1023.3	1024.0
177.5°	1026.3	1025.5	1023.8	1022.1	1020.4	1018.7	1020.4	1022.1	1023.8	1025.5	1026.3
180°	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8

TEST NUMBER: P1011012

CATALOG NUMBER: S123RDIP-B775D805UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5
2.5°	1156.5	1160.7	1156.5	1148.2	1156.5	1161.8	1167.0	1175.4	1179.6	1179.6	1185.8
5°	1090.6	1099.0	1095.8	1093.7	1102.1	1107.3	1115.7	1126.2	1137.7	1145.0	1153.4
7.5°	1032.0	1037.2	1042.4	1042.4	1050.8	1062.3	1074.9	1087.4	1102.1	1112.6	1118.8
10°	980.7	984.9	988.0	992.2	1004.8	1017.3	1034.1	1049.8	1062.3	1073.8	1084.3
12.5°	931.5	937.8	945.1	948.2	957.7	973.4	989.1	1007.9	1027.8	1039.3	1049.8
15°	884.4	887.5	895.9	905.3	913.7	930.5	950.3	970.2	987.0	1004.8	1014.2
17.5°	836.3	837.3	859.3	854.0	881.3	897.0	907.4	926.3	953.5	968.1	982.8
20°	789.2	799.6	809.0	814.3	828.9	846.7	877.1	891.7	913.7	927.3	939.9
22.5°	752.5	768.2	768.2	780.8	788.1	804.9	826.8	855.1	879.2	888.6	906.4
25°	720.1	727.4	740.0	744.2	757.8	772.4	787.1	817.4	843.6	856.1	868.7
27.5°	678.2	687.6	704.4	704.4	722.2	737.9	755.7	775.6	801.7	819.5	833.1
30°	645.8	655.2	662.5	674.0	681.4	696.0	727.4	742.1	765.1	780.8	797.5
32.5°	615.4	622.7	629.0	641.6	650.0	666.7	683.4	709.6	729.5	744.2	761.9
35°	581.9	589.3	597.6	607.0	619.6	635.3	651.0	673.0	692.9	706.5	721.1
37.5°	550.5	555.8	568.3	574.6	585.1	599.7	619.6	642.6	660.4	670.9	685.5
40°	520.2	524.4	533.8	545.3	552.6	564.1	585.1	605.0	626.9	639.5	651.0
42.5°	487.7	493.0	501.3	512.8	524.4	536.9	548.4	571.5	591.3	601.8	614.4
45°	459.5	462.6	468.9	480.4	491.9	501.3	519.1	540.1	558.9	567.3	580.9
47.5°	426.0	429.1	438.5	443.8	456.3	468.9	486.7	507.6	524.4	532.7	545.3
50°	391.4	394.6	400.9	412.4	420.7	434.4	450.1	467.8	488.8	500.3	507.6
52.5°	357.9	364.2	369.5	378.9	389.3	403.0	417.6	434.4	452.1	463.7	472.0
55°	324.5	329.7	336.0	341.2	353.8	366.3	383.1	398.8	414.5	424.9	434.4
57.5°	286.8	294.1	300.4	310.8	320.3	330.7	349.6	362.1	381.0	388.3	396.7
60°	254.3	261.7	266.9	275.3	283.6	297.2	309.8	325.5	341.2	350.6	361.1
62.5°	227.1	230.3	233.4	241.8	250.1	262.7	275.3	291.0	307.7	312.9	321.3
65°	199.9	203.0	208.3	215.6	221.9	229.2	242.8	255.4	271.1	279.4	282.6
67.5°	176.9	180.0	181.1	186.3	191.5	199.9	207.2	219.8	234.4	239.7	246.0
70°	150.7	155.9	157.0	161.2	163.3	168.5	176.9	186.3	197.8	207.2	212.5
72.5°	120.4	127.7	129.8	136.1	139.2	144.4	150.7	158.0	165.4	169.6	173.7
75°	98.4	100.5	101.5	106.8	112.0	119.3	122.5	126.6	132.9	138.2	142.3
77.5°	81.6	82.7	83.7	83.7	84.8	89.0	95.2	100.5	104.7	106.8	109.9
80°	65.9	64.9	64.9	65.9	65.9	65.9	68.0	75.4	77.5	82.7	81.6
82.5°	51.3	49.2	50.2	49.2	49.2	49.2	49.2	50.2	50.2	53.4	55.5
85°	33.5	34.5	33.5	33.5	32.4	33.5	32.4	32.4	31.4	31.4	30.4
87.5°	17.8	18.8	17.8	17.8	16.7	17.8	16.7	16.7	15.7	15.7	13.6
90°	21.0	20.3	19.6	18.9	18.2	16.0	13.8	11.7	9.5	8.4	7.6
92.5°	24.5	23.3	22.1	20.9	19.7	18.2	16.7	15.2	13.7	12.9	13.4
95°	28.2	27.0	25.9	24.7	23.5	21.7	19.8	18.0	16.1	15.2	18.7
97.5°	29.7	28.4	27.0	25.7	24.3	32.9	41.5	50.1	58.7	63.0	65.4
100°	30.4	29.1	27.8	26.4	25.1	51.4	77.7	104.0	130.3	143.5	141.8
102.5°	33.9	39.5	45.0	50.6	56.2	85.6	114.9	144.3	173.6	188.3	187.2
105°	46.8	76.7	106.5	136.4	166.2	181.4	196.6	211.8	227.0	234.6	233.7
107.5°	191.4	217.4	243.3	269.3	295.3	292.8	290.2	287.7	285.2	283.9	283.1
110°	320.1	325.7	331.2	336.8	342.4	340.5	338.7	336.8	334.9	334.0	333.3

TEST NUMBER: P1011012

CATALOG NUMBER: S123RDIP-B775D805UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	396.2	394.7	393.2	391.7	390.2	388.3	386.5	384.6	382.7	381.8	381.2
115°	442.5	440.8	439.1	437.4	435.7	434.2	432.7	431.2	429.7	428.9	428.4
117.5°	485.9	484.6	483.2	481.9	480.5	479.7	478.8	478.0	477.1	476.7	476.1
120°	529.2	527.9	526.5	525.2	523.8	523.3	522.8	522.3	521.8	521.5	520.7
122.5°	570.5	569.6	568.8	567.9	567.1	566.4	565.7	565.0	564.3	564.0	563.4
125°	608.6	608.3	608.0	607.6	607.3	606.6	606.0	605.3	604.6	604.3	603.6
127.5°	649.5	649.0	648.5	648.0	647.5	646.7	645.8	645.0	644.1	643.7	643.0
130°	685.9	685.2	684.5	683.9	683.2	682.5	681.9	681.2	680.5	680.2	679.5
132.5°	720.1	719.4	718.7	718.1	717.4	716.9	716.4	715.9	715.4	715.1	714.4
135°	754.3	753.8	753.3	752.8	752.3	751.6	750.9	750.2	749.5	749.2	748.7
137.5°	786.0	785.2	784.3	783.5	782.7	782.3	782.0	781.6	781.3	781.1	780.4
140°	815.0	814.3	813.6	813.0	812.3	811.8	811.3	810.8	810.3	810.0	809.5
142.5°	842.3	841.8	841.3	840.8	840.3	839.8	839.3	838.8	838.3	838.1	837.6
145°	867.5	867.2	866.9	866.5	866.2	865.8	865.5	865.1	864.8	864.6	864.0
147.5°	891.0	890.7	890.4	890.0	889.7	889.4	889.0	888.7	888.4	888.2	887.8
150°	912.3	912.0	911.6	911.3	910.9	910.6	910.2	909.9	909.6	909.4	909.1
152.5°	931.9	931.2	930.5	929.9	929.2	929.0	928.8	928.7	928.5	928.4	928.3
155°	949.3	948.4	947.6	946.7	945.9	945.7	945.5	945.4	945.2	945.1	945.3
157.5°	965.1	964.1	963.0	962.0	961.0	961.2	961.4	961.5	961.7	961.8	961.8
160°	978.0	977.0	975.9	974.9	973.9	974.1	974.3	974.4	974.6	974.7	974.8
162.5°	990.0	988.8	987.7	986.5	985.3	985.5	985.7	985.8	986.0	986.1	986.4
165°	1000.6	999.3	997.9	996.6	995.2	995.4	995.6	995.7	995.9	996.0	996.2
167.5°	1008.9	1007.6	1006.3	1004.9	1003.6	1003.6	1003.6	1003.6	1003.6	1003.6	1003.9
170°	1015.8	1014.5	1013.1	1011.8	1010.4	1010.4	1010.4	1010.4	1010.4	1010.4	1010.7
172.5°	1020.3	1019.0	1017.6	1016.3	1014.9	1014.7	1014.6	1014.4	1014.3	1014.2	1014.6
175°	1023.4	1022.2	1021.1	1019.9	1018.7	1018.5	1018.4	1018.2	1018.1	1018.0	1018.4
177.5°	1025.6	1024.3	1023.0	1021.6	1020.3	1020.1	1019.9	1019.8	1019.6	1019.5	1019.9
180°	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8	1021.8

TEST NUMBER: P1011012

CATALOG NUMBER: S123RDIP-B775D805UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1222.5	1222.5	1222.5	1222.5
2.5°	1191.1	1198.4	1213.0	1225.6
5°	1165.9	1177.5	1199.4	1221.4
7.5°	1135.6	1153.4	1181.6	1212.0
10°	1106.3	1129.3	1163.9	1199.4
12.5°	1077.0	1101.1	1137.7	1183.7
15°	1042.4	1067.6	1111.5	1167.0
17.5°	1012.1	1045.6	1085.4	1140.8
20°	979.6	1004.8	1056.0	1114.7
22.5°	938.8	980.7	1028.8	1090.6
25°	906.4	943.0	991.2	1061.3
27.5°	866.6	909.5	968.1	1029.9
30°	834.2	869.7	924.2	998.5
32.5°	796.5	838.3	894.9	968.1
35°	763.0	798.6	852.0	926.3
37.5°	723.2	761.9	821.6	887.5
40°	688.7	726.4	782.9	844.6
42.5°	646.8	686.6	743.1	795.4
45°	613.3	650.0	695.0	743.1
47.5°	572.5	611.2	655.2	688.7
50°	535.9	571.5	606.0	634.3
52.5°	496.1	528.5	559.9	580.9
55°	459.5	484.6	509.7	524.4
57.5°	416.6	440.6	461.6	469.9
60°	378.9	398.8	412.4	421.8
62.5°	339.1	353.8	364.2	369.5
65°	300.4	310.8	316.1	321.3
67.5°	260.6	270.0	273.2	279.4
70°	218.7	229.2	231.3	234.4
72.5°	187.3	187.3	191.5	195.7
75°	149.7	151.8	153.9	153.9
77.5°	117.2	117.2	119.3	120.4
80°	85.8	86.9	86.9	85.8
82.5°	58.6	60.7	58.6	57.6
85°	32.4	36.6	34.5	34.5
87.5°	13.6	13.6	15.7	13.6
90°	5.9	4.2	2.5	0.8
92.5°	14.4	15.5	16.5	17.5
95°	25.6	32.5	39.4	46.3
97.5°	70.1	74.8	79.6	84.3
100°	138.4	135.1	131.7	128.3
102.5°	185.0	182.8	180.6	178.4
105°	231.8	229.9	228.1	226.2
107.5°	281.6	280.1	278.6	277.1
110°	332.0	330.6	329.3	327.9

TEST NUMBER: P1011012

CATALOG NUMBER: S123RDIP-B775D805UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	380.0	378.9	377.7	376.5
115°	427.4	426.3	425.3	424.3
117.5°	474.9	473.8	472.6	471.4
120°	519.2	517.7	516.2	514.7
122.5°	562.2	561.1	559.9	558.7
125°	602.3	600.9	599.6	598.2
127.5°	641.7	640.4	639.0	637.7
130°	678.2	676.8	675.5	674.1
132.5°	713.1	711.7	710.4	709.0
135°	747.7	746.7	745.7	744.7
137.5°	779.1	777.8	776.4	775.1
140°	808.5	807.4	806.4	805.4
142.5°	836.6	835.5	834.5	833.5
145°	862.8	861.7	860.5	859.3
147.5°	886.9	886.1	885.2	884.4
150°	908.6	908.1	907.6	907.1
152.5°	928.1	928.0	927.8	927.6
155°	945.6	945.9	946.3	946.6
157.5°	961.8	961.8	961.8	961.8
160°	975.0	975.1	975.3	975.5
162.5°	986.9	987.4	987.9	988.4
165°	996.7	997.2	997.7	998.2
167.5°	1004.6	1005.3	1005.9	1006.6
170°	1011.4	1012.1	1012.7	1013.4
172.5°	1015.5	1016.3	1017.2	1018.0
175°	1019.3	1020.1	1021.0	1021.8
177.5°	1020.8	1021.6	1022.5	1023.3
180°	1021.8	1021.8	1021.8	1021.8

(END OF REPORT)