

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010718

Luminaire Tested: S123DIP-B775D1195UB2750-4F0-XX-W2A-D_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010718
REPORT IS A COMBINATION OF REPORTS P990297 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D1195UB2750-4F0-XX-W2A-D_5000K
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7707.0 lumens
Efficiency: N/A
Efficacy: 108.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010718

CATALOG NUMBER: S123DIP-B775D1195UB2750-4F0-XX-W2A-D_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010718

CATALOG NUMBER: S123DIP-B775D1195UB2750-4F0-XX-W2A-D_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	44	44	44
1	94	90	85	82	85	81	78	75	66	63	61	51	49	48	38	37	36
2	85	78	71	66	77	70	65	60	57	53	50	44	42	39	33	31	30
3	78	68	61	55	70	62	55	50	50	45	41	39	36	33	29	27	25
4	71	60	52	46	64	55	48	42	44	39	35	35	31	28	26	23	21
5	65	53	45	39	58	48	41	36	39	34	30	31	27	24	23	20	18
6	60	48	39	34	54	43	36	31	35	30	26	28	24	21	21	18	16
7	55	43	35	29	50	39	32	27	32	27	23	25	21	18	19	16	14
8	51	39	31	26	46	35	29	24	29	24	20	23	19	16	17	15	13
9	47	35	28	23	43	32	26	21	27	21	18	21	17	15	16	13	11
10	44	32	25	20	40	30	23	19	24	19	16	19	16	13	15	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10002	10002	10002
5°	10030	9709	9701
10°	9936	9446	9374
15°	9804	9155	9027
20°	9618	8832	8654
25°	9388	8467	8268
30°	9152	8137	7880
35°	8889	7791	7564
40°	8637	7475	7231
45°	8358	7168	6956
50°	8082	6864	6658
55°	7777	6552	6384
60°	7478	6234	6102
65°	7170	5895	5773
70°	6708	5515	5434
75°	6121	5079	5083
80°	5440	4642	4684
85°	4764	4286	4397

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8358 cd/sqm

TEST NUMBER: P1010718

CATALOG NUMBER: S123DIP-B775D1195UB2750-4F0-XX-W2A-D_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.2	1.1
10°-20°	251.3	3.3
20°-30°	375.8	4.9
30°-40°	448.7	5.8
40°-50°	469.4	6.1
50°-60°	440.5	5.7
60°-70°	368.0	4.8
70°-80°	263.1	3.4
80°-90°	159.6	2.1
90°-100°	151.4	2.0
100°-110°	328.5	4.3
110°-120°	676.1	8.8
120°-130°	824.5	10.7
130°-140°	863.8	11.2
140°-150°	798.7	10.4
150°-160°	642.2	8.3
160°-170°	414.4	5.4
170°-180°	142.8	1.9
0°-30°	715.2	9.3
0°-40°	1163.9	15.1
0°-60°	2073.9	26.9
0°-90°	2864.5	37.2
90°-120°	1156.0	15.0
90°-150°	3643.0	47.3
90°-180°	4842.0	62.8
0°-180°	7707.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	929	929	929	929	929	
5°	930	928	922	930	929	88
15°	886	889	888	898	897	250
25°	800	810	813	826	826	369
35°	688	704	718	733	737	430
45°	563	587	612	632	640	434
55°	429	463	499	526	534	384
65°	297	336	381	411	421	293
75°	161	208	259	292	305	172
85°	50	100	154	188	198	51
90°	14	75	141	180	192	13
95°	79	73	135	174	184	90
105°	341	377	320	151	162	361
115°	629	648	694	730	742	622
125°	883	892	926	949	958	789
135°	1097	1103	1118	1140	1142	845
145°	1265	1272	1274	1284	1288	792
155°	1392	1390	1391	1397	1390	641
165°	1468	1465	1464	1472	1465	415
175°	1503	1497	1498	1506	1497	143
180°	1503	1503	1503	1503	1503	

TEST NUMBER: P1010718

CATALOG NUMBER: S123DIP-B775D1195UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	929.2	929.2	929.2	929.2	929.2
2.5°	934.3	931.3	923.2	931.3	930.3
5°	930.3	928.2	922.2	930.3	929.2
7.5°	923.2	923.2	917.1	927.2	926.2
10°	913.1	915.1	910.0	920.1	918.1
12.5°	900.9	903.9	900.9	910.0	908.0
15°	885.7	888.8	887.7	897.9	896.9
17.5°	867.5	873.6	872.6	881.7	879.6
20°	847.3	853.3	855.4	864.5	865.5
22.5°	826.0	832.1	835.1	847.3	846.2
25°	799.7	809.8	812.8	826.0	826.0
27.5°	774.4	785.5	791.6	802.7	803.7
30°	747.0	760.2	768.3	780.4	780.4
32.5°	716.7	731.9	743.0	756.2	759.2
35°	688.3	704.5	717.7	732.9	736.9
37.5°	658.0	676.2	691.4	708.6	711.6
40°	627.6	645.8	666.1	683.3	687.3
42.5°	594.2	617.5	638.7	658.0	664.0
45°	562.8	587.1	612.4	631.6	639.7
47.5°	529.4	556.7	585.1	606.3	612.4
50°	497.0	525.4	556.7	580.0	587.1
52.5°	462.6	493.0	528.4	552.7	561.8
55°	429.2	462.6	499.0	526.4	534.5
57.5°	396.8	431.2	470.7	498.0	507.1
60°	362.4	398.8	440.3	468.7	479.8
62.5°	330.0	367.4	412.0	440.3	450.5
65°	296.6	336.1	380.6	411.0	421.1
67.5°	263.2	304.7	349.2	382.6	390.7
70°	227.8	271.3	319.9	352.3	362.4
72.5°	195.4	238.9	289.5	322.9	333.0
75°	160.9	208.5	259.1	292.5	304.7
77.5°	131.6	179.2	229.8	265.2	274.3
80°	100.2	149.8	202.5	236.9	247.0
82.5°	72.9	123.5	177.1	211.6	221.7
85°	49.6	100.2	153.9	188.3	198.4
87.5°	30.4	81.0	132.6	167.0	177.1
90°	14.3	75.1	141.2	180.1	192.4
92.5°	37.8	74.7	135.3	176.5	186.8
95°	79.2	72.9	134.8	174.0	184.1
97.5°	134.0	139.3	129.8	169.2	180.4
100°	197.8	252.5	124.9	163.2	174.4
102.5°	270.5	313.3	164.6	156.1	168.5
105°	340.8	377.4	320.4	151.2	162.5
107.5°	414.6	445.8	504.1	359.6	222.4
110°	488.4	515.5	568.3	557.8	406.2

TEST NUMBER: P1010718

CATALOG NUMBER: S123DIP-B775D1195UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	559.8	581.7	632.5	667.9	674.7
115°	629.2	648.0	694.4	729.9	742.4
117.5°	698.4	714.3	754.3	787.5	796.7
120°	760.9	776.1	812.8	845.0	852.1
122.5°	825.7	835.6	871.4	899.2	907.4
125°	882.7	891.6	925.5	948.9	958.3
127.5°	940.8	948.7	979.6	1003.2	1008.1
130°	994.4	1002.3	1027.1	1050.7	1054.6
132.5°	1044.7	1053.6	1072.2	1094.9	1098.6
135°	1097.2	1102.9	1118.4	1140.1	1141.7
137.5°	1141.8	1149.8	1159.1	1180.9	1183.7
140°	1185.5	1192.2	1198.5	1218.2	1221.1
142.5°	1226.8	1232.5	1235.8	1252.4	1254.0
145°	1264.8	1271.6	1273.8	1284.1	1288.1
147.5°	1300.6	1306.2	1308.4	1313.6	1312.2
150°	1334.1	1337.4	1339.7	1341.9	1340.6
152.5°	1364.2	1365.3	1366.5	1370.9	1365.3
155°	1392.1	1389.9	1391.0	1396.6	1389.9
157.5°	1414.5	1414.5	1413.4	1420.1	1411.1
160°	1434.6	1433.4	1432.3	1439.0	1431.2
162.5°	1453.5	1450.2	1449.1	1456.9	1450.2
165°	1468.1	1464.7	1463.6	1472.5	1464.7
167.5°	1480.3	1475.9	1475.9	1484.8	1475.9
170°	1490.4	1485.9	1485.9	1494.8	1485.9
172.5°	1497.1	1491.5	1492.6	1501.5	1491.5
175°	1502.7	1497.1	1498.2	1506.0	1497.1
177.5°	1504.9	1499.3	1500.4	1509.4	1498.2
180°	1502.7	1502.7	1502.7	1502.7	1502.7

(END OF REPORT)