

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010723

Luminaire Tested: S123DIP-B775D1195UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010723
REPORT IS A COMBINATION OF REPORTS P990302 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D1195UB2750-4F0-XX-W2A-F_5000K
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7647.0 lumens
Efficiency: N/A
Efficacy: 107.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010723

CATALOG NUMBER: S123DIP-B775D1195UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010723

CATALOG NUMBER: S123DIP-B775D1195UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47			40
1	96	91	87	84	87	83	80	77	68	66	64	54	53	51	41	40	40			34
2	87	80	74	68	79	73	67	63	60	56	53	48	45	43	36	35	33			28
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	32	30	28			24
4	72	62	54	48	66	57	50	45	47	42	38	37	34	31	29	26	24			20
5	66	55	47	41	60	50	43	38	42	36	32	34	30	27	26	23	21			18
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	24	21	19			16
7	56	44	37	31	51	41	34	29	34	29	25	27	24	21	21	19	17			14
8	52	40	33	27	48	37	30	26	31	26	22	25	21	18	20	17	15			12
9	49	37	29	24	44	34	27	23	28	23	20	23	19	16	18	15	13			11
10	45	34	26	22	41	31	25	20	26	21	18	21	17	15	17	14	12			10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12668	12668	12668
5°	12699	12231	12212
10°	12587	11818	11695
15°	12412	11387	11133
20°	12211	10909	10574
25°	11951	10404	9978
30°	11668	9882	9350
35°	11370	9349	8726
40°	11058	8790	8112
45°	10715	8244	7471
50°	10367	7636	6828
55°	9920	7003	6176
60°	9459	6305	5482
65°	9026	5548	4759
70°	8405	4710	3915
75°	7505	3730	3040
80°	6482	2622	2149
85°	5052	1409	1077

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10715 cd/sqm

TEST NUMBER: P1010723

CATALOG NUMBER: S123DIP-B775D1195UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.0	1.5
10°-20°	313.3	4.1
20°-30°	462.7	6.1
30°-40°	540.4	7.1
40°-50°	543.3	7.1
50°-60°	477.2	6.2
60°-70°	355.4	4.6
70°-80°	202.3	2.6
80°-90°	60.5	0.8
90°-100°	53.0	0.7
100°-110°	256.2	3.4
110°-120°	627.8	8.2
120°-130°	797.0	10.4
130°-140°	851.4	11.1
140°-150°	796.2	10.4
150°-160°	642.2	8.4
160°-170°	414.4	5.4
170°-180°	142.8	1.9
0°-30°	886.9	11.6
0°-40°	1427.3	18.7
0°-60°	2447.8	32.0
0°-90°	3066.0	40.1
90°-120°	937.0	12.3
90°-150°	3381.6	44.2
90°-180°	4581.0	59.9
0°-180°	7647.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1177	1177	1177	1177	1177	
5°	1178	1173	1162	1172	1170	112
15°	1121	1117	1104	1112	1106	316
25°	1018	1012	999	1000	997	469
35°	880	874	861	855	850	551
45°	722	718	704	692	687	557
55°	548	546	533	522	517	490
65°	373	368	358	350	347	368
75°	197	193	190	185	182	211
85°	53	51	51	49	49	56
90°	1	12	27	31	34	7
95°	68	22	35	42	42	81
105°	333	345	244	47	49	353
115°	624	631	641	652	656	616
125°	880	889	893	895	898	786
135°	1095	1102	1106	1110	1106	843
145°	1264	1272	1274	1276	1276	791
155°	1392	1390	1391	1397	1390	641
165°	1468	1465	1464	1472	1465	415
175°	1503	1497	1498	1506	1497	143
180°	1503	1503	1503	1503	1503	

TEST NUMBER: P1010723

CATALOG NUMBER: S123DIP-B775D1195UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1176.9	1176.9	1176.9	1176.9	1176.9
2.5°	1182.0	1177.9	1166.8	1176.9	1175.9
5°	1177.9	1172.9	1161.7	1171.9	1169.8
7.5°	1168.8	1163.8	1152.6	1161.7	1160.7
10°	1156.7	1151.6	1138.5	1147.6	1145.5
12.5°	1140.5	1136.4	1124.3	1130.4	1129.4
15°	1121.3	1117.2	1104.1	1112.2	1106.1
17.5°	1100.0	1095.0	1081.8	1087.9	1085.8
20°	1075.7	1069.7	1056.5	1060.5	1057.5
22.5°	1048.4	1042.3	1029.2	1032.2	1028.2
25°	1018.0	1012.0	998.8	999.8	996.8
27.5°	986.7	980.6	966.4	967.4	964.4
30°	952.3	947.2	933.0	933.0	926.0
32.5°	917.9	910.8	900.7	893.6	890.5
35°	880.4	874.3	861.2	855.1	850.1
37.5°	843.0	834.9	821.7	814.6	811.6
40°	803.5	797.4	783.3	775.2	771.1
42.5°	764.0	757.0	742.8	734.7	730.6
45°	721.5	717.5	704.3	692.2	687.1
47.5°	680.0	674.0	661.8	649.7	645.6
50°	637.5	632.5	619.3	608.2	602.1
52.5°	593.0	590.0	575.8	566.7	560.6
55°	547.5	546.5	533.3	522.2	517.1
57.5°	505.0	500.9	490.8	480.7	474.6
60°	458.4	457.4	445.3	436.2	431.1
62.5°	416.9	413.9	401.8	392.6	389.6
65°	373.4	368.4	358.2	350.1	347.1
67.5°	326.9	322.8	314.7	307.6	303.6
70°	285.4	279.3	273.2	266.1	261.1
72.5°	241.9	237.8	230.7	224.7	222.6
75°	197.3	193.3	190.3	185.2	182.2
77.5°	157.9	155.8	151.8	147.7	147.7
80°	119.4	116.4	114.4	113.3	113.3
82.5°	82.0	82.0	82.0	79.9	78.9
85°	52.6	50.6	50.6	48.6	48.6
87.5°	26.3	23.3	22.3	21.3	21.3
90°	1.1	12.3	26.8	31.3	33.5
92.5°	25.7	19.0	29.0	36.8	38.0
95°	68.1	22.3	34.6	42.4	42.4
97.5°	123.9	92.7	35.7	44.7	45.8
100°	188.7	211.0	36.8	45.8	46.9
102.5°	262.4	276.9	82.6	45.8	48.0
105°	332.7	345.0	244.5	46.9	49.1
107.5°	407.5	417.5	434.3	262.4	116.1
110°	482.3	491.2	503.5	466.7	307.0

TEST NUMBER: P1010723

CATALOG NUMBER: S123DIP-B775D1195UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	553.7	561.5	573.8	583.9	581.6
115°	624.1	630.8	640.8	652.0	656.4
117.5°	693.3	701.1	706.7	715.6	716.7
120°	756.9	767.0	770.3	779.2	779.2
122.5°	821.7	829.5	833.9	839.5	840.6
125°	879.7	888.6	893.1	895.3	897.6
127.5°	937.8	946.7	952.3	955.6	953.4
130°	991.4	1000.3	1004.8	1009.2	1007.0
132.5°	1042.7	1051.6	1055.0	1059.5	1056.1
135°	1095.2	1101.9	1106.3	1109.7	1106.3
137.5°	1139.8	1148.8	1151.0	1156.6	1154.3
140°	1184.5	1191.2	1194.5	1199.0	1196.8
142.5°	1225.8	1232.5	1235.8	1239.2	1235.8
145°	1263.8	1271.6	1273.8	1276.0	1276.0
147.5°	1300.6	1306.2	1308.4	1310.6	1305.1
150°	1334.1	1337.4	1339.7	1341.9	1338.6
152.5°	1364.2	1365.3	1366.5	1370.9	1365.3
155°	1392.1	1389.9	1391.0	1396.6	1389.9
157.5°	1414.5	1414.5	1413.4	1420.1	1411.1
160°	1434.6	1433.4	1432.3	1439.0	1431.2
162.5°	1453.5	1450.2	1449.1	1456.9	1450.2
165°	1468.1	1464.7	1463.6	1472.5	1464.7
167.5°	1480.3	1475.9	1475.9	1484.8	1475.9
170°	1490.4	1485.9	1485.9	1494.8	1485.9
172.5°	1497.1	1491.5	1492.6	1501.5	1491.5
175°	1502.7	1497.1	1498.2	1506.0	1497.1
177.5°	1504.9	1499.3	1500.4	1509.4	1498.2
180°	1502.7	1502.7	1502.7	1502.7	1502.7

(END OF REPORT)