

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010731

Luminaire Tested: S123DIP-B775D365UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010731
REPORT IS A COMBINATION OF REPORTS P990355 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D365UB2750-4F0-XX-W2A-D_3500K
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4727.0 lumens
Efficiency: N/A
Efficacy: 104.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010731

CATALOG NUMBER: S123DIP-B775D365UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1010731

CATALOG NUMBER: S123DIP-B775D365UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68
1	99	94	90	86	93	89	85	81	78	75	72	68	65	63	58	57	55
2	90	82	75	69	84	77	71	65	67	63	58	59	55	52	51	48	45
3	82	71	63	57	76	67	60	54	59	53	49	51	47	43	44	41	38
4	75	63	54	48	70	59	52	46	52	46	41	46	41	37	39	36	32
5	69	56	47	41	64	53	45	39	47	40	35	41	36	32	35	31	28
6	63	50	42	35	59	47	40	34	42	35	31	37	32	28	32	28	25
7	58	45	37	31	54	43	35	30	38	32	27	33	28	24	29	25	22
8	54	41	33	27	51	39	31	26	35	28	24	31	25	22	27	23	19
9	50	38	30	24	47	36	28	23	32	26	21	28	23	19	25	21	18
10	47	35	27	22	44	33	26	21	29	23	19	26	21	18	23	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10444	10444	10444
5°	10473	10138	10130
10°	10375	9863	9788
15°	10238	9560	9426
20°	10043	9222	9036
25°	9803	8842	8633
30°	9558	8496	8228
35°	9281	8135	7899
40°	9019	7805	7550
45°	8728	7485	7263
50°	8440	7167	6951
55°	8121	6842	6666
60°	7808	6510	6371
65°	7487	6155	6028
70°	7003	5758	5674
75°	6394	5305	5309
80°	5679	4846	4891
85°	4976	4475	4593

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8728 cd/sqm

TEST NUMBER: P1010731

CATALOG NUMBER: S123DIP-B775D365UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.0	1.9
10°-20°	262.4	5.6
20°-30°	392.4	8.3
30°-40°	468.5	9.9
40°-50°	490.2	10.4
50°-60°	460.0	9.7
60°-70°	384.2	8.1
70°-80°	274.7	5.8
80°-90°	164.4	3.5
90°-100°	119.7	2.5
100°-110°	157.4	3.3
110°-120°	251.2	5.3
120°-130°	283.7	6.0
130°-140°	285.2	6.0
140°-150°	257.3	5.4
150°-160°	205.4	4.3
160°-170°	132.5	2.8
170°-180°	45.7	1.0
0°-30°	746.8	15.8
0°-40°	1215.3	25.7
0°-60°	2165.5	45.8
0°-90°	2988.9	63.2
90°-120°	528.3	11.2
90°-150°	1354.5	28.7
90°-180°	1738.0	36.8
0°-180°	4727.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	970	970	970	970	970	
5°	971	969	963	971	970	92
15°	925	928	927	938	936	261
25°	835	846	849	862	862	385
35°	719	736	749	765	770	449
45°	588	613	640	660	668	453
55°	448	483	521	550	558	401
65°	310	351	397	429	440	306
75°	168	218	271	306	318	180
85°	52	105	161	197	207	53
90°	14	69	128	165	177	11
95°	33	60	116	151	162	35
105°	115	144	158	124	134	121
115°	205	220	261	290	300	203
125°	284	287	319	342	350	255
135°	352	354	366	387	391	271
145°	405	407	407	417	421	253
155°	445	444	445	447	444	205
165°	470	468	468	471	468	133
175°	481	479	479	482	479	46
180°	481	481	481	481	481	

TEST NUMBER: P1010731

CATALOG NUMBER: S123DIP-B775D365UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	970.3	970.3	970.3	970.3	970.3
2.5°	975.6	972.4	964.0	972.4	971.4
5°	971.4	969.3	962.9	971.4	970.3
7.5°	964.0	964.0	957.6	968.2	967.1
10°	953.4	955.5	950.2	960.8	958.7
12.5°	940.7	943.9	940.7	950.2	948.1
15°	924.9	928.0	927.0	937.5	936.5
17.5°	905.8	912.2	911.1	920.6	918.5
20°	884.7	891.0	893.1	902.7	903.7
22.5°	862.5	868.8	872.0	884.7	883.6
25°	835.0	845.6	848.8	862.5	862.5
27.5°	808.6	820.2	826.6	838.2	839.2
30°	780.1	793.8	802.2	814.9	814.9
32.5°	748.3	764.2	775.8	789.6	792.7
35°	718.7	735.7	749.4	765.3	769.5
37.5°	687.0	706.1	721.9	739.9	743.1
40°	655.3	674.4	695.5	713.5	717.7
42.5°	620.4	644.8	667.0	687.0	693.4
45°	587.7	613.0	639.5	659.6	668.0
47.5°	552.8	581.3	610.9	633.1	639.5
50°	519.0	548.6	581.3	605.7	613.0
52.5°	483.0	514.8	551.7	577.1	586.6
55°	448.2	483.0	521.1	549.6	558.1
57.5°	414.3	450.3	491.5	520.0	529.5
60°	378.4	416.5	459.8	489.4	501.0
62.5°	344.6	383.7	430.2	459.8	470.4
65°	309.7	350.9	397.4	429.1	439.7
67.5°	274.8	318.2	364.7	399.5	408.0
70°	237.8	283.3	334.0	367.8	378.4
72.5°	204.0	249.4	302.3	337.2	347.7
75°	168.1	217.7	270.6	305.5	318.2
77.5°	137.4	187.1	239.9	276.9	286.4
80°	104.6	156.4	211.4	247.3	257.9
82.5°	76.1	129.0	185.0	220.9	231.5
85°	51.8	104.6	160.7	196.6	207.2
87.5°	31.7	84.6	138.5	174.4	185.0
90°	14.1	69.4	128.0	165.4	176.6
92.5°	20.9	64.2	120.3	157.7	167.5
95°	33.4	59.9	115.7	151.0	161.6
97.5°	50.2	78.2	109.7	144.3	155.2
100°	69.8	110.8	103.8	137.2	148.2
102.5°	92.4	126.6	112.0	129.8	141.2
105°	114.9	144.1	157.5	123.9	134.1
107.5°	137.7	163.1	211.8	185.4	148.1
110°	160.5	182.5	228.6	244.3	201.8

TEST NUMBER: P1010731

CATALOG NUMBER: S123DIP-B775D365UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	183.4	200.7	244.8	274.4	283.2
115°	204.9	219.7	260.9	289.9	299.7
117.5°	227.0	237.9	275.7	303.9	312.7
120°	246.3	254.8	290.8	317.9	325.3
122.5°	267.0	271.6	305.8	330.9	338.6
125°	284.5	287.4	319.4	342.3	350.5
127.5°	303.1	304.9	333.0	355.3	362.0
130°	320.2	322.0	344.6	366.1	371.7
132.5°	335.6	338.4	355.4	375.8	382.2
135°	352.3	353.5	366.5	386.6	390.8
137.5°	366.6	368.5	376.6	395.3	399.9
140°	379.9	382.1	386.2	403.6	408.1
142.5°	393.1	394.2	395.2	410.0	414.2
145°	405.3	406.7	407.4	416.6	420.8
147.5°	415.9	417.7	418.4	422.4	424.8
150°	426.7	427.7	428.4	429.2	430.2
152.5°	436.3	436.6	437.0	438.4	436.6
155°	445.2	444.5	444.9	446.6	444.5
157.5°	452.4	452.4	452.0	454.1	451.3
160°	458.8	458.4	458.1	460.2	457.7
162.5°	464.9	463.8	463.4	465.9	463.8
165°	469.5	468.4	468.1	470.9	468.4
167.5°	473.4	472.0	472.0	474.9	472.0
170°	476.6	475.2	475.2	478.1	475.2
172.5°	478.8	477.0	477.4	480.2	477.0
175°	480.6	478.8	479.1	481.6	478.8
177.5°	481.3	479.5	479.8	482.7	479.1
180°	480.6	480.6	480.6	480.6	480.6

(END OF REPORT)