

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011032

Luminaire Tested: S123DIP-B1000D1025UB30-4F0-XX-W2A-D1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011032
REPORT IS A COMBINATION OF REPORTS P989047 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D1025UB30-4F0-XX-W2A-D1
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7662.0 lumens
Efficiency: N/A
Efficacy: 101.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011032

CATALOG NUMBER: S123DIP-B1000D1025UB30-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1011032

CATALOG NUMBER: S123DIP-B1000D1025UB30-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	97	92	88	84	89	85	81	78	71	69	66	59	57	55	48	47	45
2	88	80	73	68	80	74	68	63	62	58	54	51	48	45	42	39	37
3	80	70	62	56	73	64	58	52	54	49	45	45	41	38	36	34	31
4	73	61	53	47	67	57	50	44	48	42	38	40	36	32	32	29	27
5	67	55	46	40	61	51	43	37	43	37	33	36	31	28	29	26	23
6	61	49	41	35	56	45	38	32	39	33	28	32	28	24	26	23	20
7	57	44	36	30	52	41	34	28	35	29	25	29	25	21	24	21	18
8	53	40	32	27	48	37	30	25	32	26	22	27	22	19	22	19	16
9	49	36	29	24	45	34	27	22	29	24	20	25	20	17	20	17	14
10	46	33	26	21	42	31	24	20	27	21	18	23	18	15	19	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13369	13369	13369
5°	13405	12976	12966
10°	13279	12625	12529
15°	13104	12237	12065
20°	12854	11804	11566
25°	12548	11317	11051
30°	12233	10876	10532
35°	11881	10413	10110
40°	11544	9989	9664
45°	11171	9580	9297
50°	10802	9175	8898
55°	10393	8758	8531
60°	9993	8332	8156
65°	9582	7879	7716
70°	8964	7369	7261
75°	8182	6788	6793
80°	7269	6203	6260
85°	6368	5725	5878

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11171 cd/sqm

TEST NUMBER: P1011032

CATALOG NUMBER: S123DIP-B1000D1025UB30-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.8	1.5
10°-20°	335.9	4.4
20°-30°	502.3	6.6
30°-40°	599.7	7.8
40°-50°	627.4	8.2
50°-60°	588.8	7.7
60°-70°	491.8	6.4
70°-80°	351.7	4.6
80°-90°	211.9	2.8
90°-100°	212.5	2.8
100°-110°	341.7	4.5
110°-120°	481.8	6.3
120°-130°	585.7	7.6
130°-140°	633.5	8.3
140°-150°	610.0	8.0
150°-160°	510.7	6.7
160°-170°	340.0	4.4
170°-180°	119.0	1.6
0°-30°	955.9	12.5
0°-40°	1555.6	20.3
0°-60°	2771.8	36.2
0°-90°	3827.2	49.9
90°-120°	1036.0	13.5
90°-150°	2865.2	37.4
90°-180°	3835.0	50.1
0°-180°	7662.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1242	1242	1242	1242	1242	
5°	1243	1241	1232	1243	1242	118
15°	1184	1188	1186	1200	1199	333
25°	1069	1082	1086	1104	1104	493
35°	920	942	959	980	985	575
45°	752	785	818	844	855	580
55°	574	618	667	704	714	514
65°	396	449	509	549	563	392
75°	215	279	346	391	407	230
85°	66	134	206	252	265	68
90°	19	95	177	227	242	17
95°	73	133	207	253	266	76
105°	233	268	335	372	387	249
115°	427	446	493	526	536	423
125°	619	622	659	683	689	552
135°	800	805	819	839	844	617
145°	969	969	972	982	984	605
155°	1108	1108	1109	1113	1106	510
165°	1206	1204	1204	1210	1202	340
175°	1255	1251	1251	1257	1250	119
180°	1258	1258	1258	1258	1258	

TEST NUMBER: P1011032

CATALOG NUMBER: S123DIP-B1000D1025UB30-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1242.0	1242.0	1242.0	1242.0	1242.0
2.5°	1248.7	1244.7	1233.9	1244.7	1243.3
5°	1243.3	1240.6	1232.5	1243.3	1242.0
7.5°	1233.9	1233.9	1225.7	1239.3	1237.9
10°	1220.3	1223.0	1216.3	1229.8	1227.1
12.5°	1204.1	1208.1	1204.1	1216.3	1213.6
15°	1183.8	1187.9	1186.5	1200.0	1198.7
17.5°	1159.4	1167.6	1166.2	1178.4	1175.7
20°	1132.4	1140.5	1143.2	1155.4	1156.7
22.5°	1104.0	1112.1	1116.2	1132.4	1131.0
25°	1068.8	1082.3	1086.4	1104.0	1104.0
27.5°	1035.0	1049.9	1058.0	1072.9	1074.2
30°	998.4	1016.0	1026.9	1043.1	1043.1
32.5°	957.9	978.2	993.0	1010.6	1014.7
35°	920.0	941.6	959.2	979.5	984.9
37.5°	879.4	903.7	924.0	947.0	951.1
40°	838.8	863.2	890.2	913.2	918.6
42.5°	794.2	825.3	853.7	879.4	887.5
45°	752.2	784.7	818.5	844.2	855.0
47.5°	707.6	744.1	782.0	810.4	818.5
50°	664.3	702.2	744.1	775.2	784.7
52.5°	618.3	658.9	706.2	738.7	750.9
55°	573.6	618.3	667.0	703.5	714.3
57.5°	530.3	576.3	629.1	665.6	677.8
60°	484.3	533.0	588.5	626.4	641.3
62.5°	441.0	491.1	550.6	588.5	602.0
65°	396.4	449.2	508.7	549.3	562.8
67.5°	351.8	407.2	466.8	511.4	522.2
70°	304.4	362.6	427.5	470.8	484.3
72.5°	261.1	319.3	386.9	431.6	445.1
75°	215.1	278.7	346.3	391.0	407.2
77.5°	175.9	239.5	307.1	354.5	366.6
80°	133.9	200.2	270.6	316.6	330.1
82.5°	97.4	165.1	236.8	282.8	296.3
85°	66.3	133.9	205.6	251.6	265.2
87.5°	40.6	108.2	177.2	223.2	236.8
90°	18.6	94.8	176.6	226.6	242.0
92.5°	45.8	110.0	183.6	231.2	241.4
95°	73.2	132.8	207.0	253.0	266.5
97.5°	109.3	163.0	232.5	278.1	290.6
100°	146.6	195.8	263.0	305.1	320.7
102.5°	189.6	230.5	298.3	339.2	351.7
105°	233.1	267.6	334.7	372.5	386.7
107.5°	283.2	312.6	372.0	411.5	422.7
110°	329.2	355.6	411.7	450.8	459.7

TEST NUMBER: P1011032

CATALOG NUMBER: S123DIP-B1000D1025UB30-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	378.6	398.6	450.0	488.8	501.0
115°	426.8	445.9	492.6	526.1	535.9
117.5°	477.1	488.9	533.0	565.5	573.3
120°	522.2	534.9	574.6	604.7	612.2
122.5°	570.6	577.3	617.3	644.0	650.6
125°	618.7	621.7	658.9	683.3	688.9
127.5°	664.2	668.7	700.5	721.7	727.2
130°	709.6	716.1	740.3	762.0	763.2
132.5°	753.7	761.6	779.9	799.4	803.8
135°	800.1	804.7	818.6	839.0	843.8
137.5°	842.6	846.2	858.6	875.4	879.1
140°	885.8	890.7	895.7	915.0	914.9
142.5°	926.3	929.8	931.8	948.4	950.3
145°	968.8	969.3	972.3	982.1	983.6
147.5°	1003.9	1007.9	1010.8	1014.9	1014.4
150°	1042.5	1044.4	1046.4	1046.4	1043.2
152.5°	1074.1	1077.0	1078.0	1080.0	1075.1
155°	1107.7	1107.7	1108.7	1112.6	1105.7
157.5°	1136.3	1135.3	1136.3	1140.3	1134.4
160°	1163.0	1161.0	1161.0	1166.0	1162.0
162.5°	1186.7	1183.8	1184.8	1189.7	1182.8
165°	1206.5	1203.5	1203.5	1209.5	1202.5
167.5°	1223.3	1219.3	1220.3	1226.3	1220.3
170°	1237.1	1233.2	1233.2	1240.1	1233.2
172.5°	1248.0	1244.0	1244.0	1250.0	1243.1
175°	1254.9	1251.0	1251.0	1256.9	1250.0
177.5°	1258.9	1254.9	1254.9	1260.8	1253.9
180°	1257.9	1257.9	1257.9	1257.9	1257.9

(END OF REPORT)