

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010732

Luminaire Tested: S123DIP-B775D365UB2750-4F0-XX-W2A-D_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010732
REPORT IS A COMBINATION OF REPORTS P990356 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D365UB2750-4F0-XX-W2A-D_4000K
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4680.0 lumens
Efficiency: N/A
Efficacy: 103.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010732

CATALOG NUMBER: S123DIP-B775D365UB2750-4F0-XX-W2A-D_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010732

CATALOG NUMBER: S123DIP-B775D365UB2750-4F0-XX-W2A-D_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68	68	68	68
1	99	94	90	86	93	89	85	81	78	75	72	68	65	63	58	57	55	55	55	51
2	90	82	75	69	84	77	71	65	67	63	58	59	55	52	51	48	45	45	45	41
3	82	71	63	57	76	67	60	54	59	53	49	51	47	43	44	41	38	38	38	34
4	75	63	54	48	70	59	52	46	52	46	41	46	41	37	39	36	32	32	32	29
5	69	56	47	41	64	53	45	39	47	40	35	41	36	32	35	31	28	28	28	25
6	63	50	42	35	59	47	40	34	42	35	31	37	32	28	32	28	25	25	25	22
7	58	45	37	31	54	43	35	30	38	32	27	33	28	24	29	25	22	22	22	19
8	54	41	33	27	51	39	31	26	35	28	24	31	25	22	27	23	19	19	19	17
9	50	38	30	24	47	36	28	23	32	26	21	28	23	19	25	21	18	18	18	15
10	47	35	27	22	44	33	26	21	29	23	19	26	21	18	23	19	16	16	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10342	10342	10342
5°	10370	10039	10030
10°	10273	9766	9692
15°	10137	9466	9333
20°	9944	9132	8948
25°	9706	8754	8548
30°	9464	8414	8147
35°	9191	8055	7821
40°	8931	7728	7476
45°	8642	7412	7193
50°	8357	7097	6883
55°	8041	6775	6600
60°	7732	6446	6309
65°	7414	6095	5969
70°	6935	5701	5618
75°	6330	5252	5255
80°	5624	4797	4844
85°	4928	4431	4546

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8642 cd/sqm

TEST NUMBER: P1010732

CATALOG NUMBER: S123DIP-B775D365UB2750-4F0-XX-W2A-D_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.1	1.9
10°-20°	259.8	5.6
20°-30°	388.5	8.3
30°-40°	463.9	9.9
40°-50°	485.4	10.4
50°-60°	455.5	9.7
60°-70°	380.5	8.1
70°-80°	272.0	5.8
80°-90°	162.8	3.5
90°-100°	118.5	2.5
100°-110°	155.9	3.3
110°-120°	248.7	5.3
120°-130°	280.8	6.0
130°-140°	282.3	6.0
140°-150°	254.7	5.4
150°-160°	203.3	4.3
160°-170°	131.2	2.8
170°-180°	45.2	1.0
0°-30°	739.5	15.8
0°-40°	1203.4	25.7
0°-60°	2144.3	45.8
0°-90°	2959.6	63.2
90°-120°	523.0	11.2
90°-150°	1340.7	28.6
90°-180°	1720.0	36.8
0°-180°	4680.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	961	961	961	961	961	
5°	962	960	954	962	961	91
15°	916	919	918	928	927	258
25°	827	837	840	854	854	381
35°	712	728	742	758	762	445
45°	582	607	633	653	662	449
55°	444	478	516	544	553	397
65°	307	348	394	425	435	303
75°	166	216	268	302	315	178
85°	51	104	159	195	205	53
90°	14	69	127	164	175	11
95°	33	59	115	150	160	35
105°	114	143	156	123	133	120
115°	203	218	258	287	297	201
125°	282	284	316	339	347	252
135°	349	350	363	383	387	269
145°	401	402	403	412	416	251
155°	441	440	440	442	440	203
165°	465	464	463	466	464	131
175°	476	474	474	477	474	45
180°	476	476	476	476	476	

TEST NUMBER: P1010732

CATALOG NUMBER: S123DIP-B775D365UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	960.8	960.8	960.8	960.8	960.8
2.5°	966.0	962.9	954.5	962.9	961.8
5°	961.8	959.7	953.5	961.8	960.8
7.5°	954.5	954.5	948.2	958.7	957.6
10°	944.0	946.1	940.9	951.4	949.3
12.5°	931.5	934.6	931.5	940.9	938.8
15°	915.8	918.9	917.9	928.3	927.3
17.5°	896.9	903.2	902.2	911.6	909.5
20°	876.0	882.3	884.4	893.8	894.9
22.5°	854.0	860.3	863.5	876.0	875.0
25°	826.8	837.3	840.4	854.0	854.0
27.5°	800.7	812.2	818.4	830.0	831.0
30°	772.4	786.0	794.4	806.9	806.9
32.5°	741.0	756.7	768.2	781.8	785.0
35°	711.7	728.4	742.0	757.7	761.9
37.5°	680.3	699.1	714.8	732.6	735.8
40°	648.9	667.7	688.7	706.5	710.6
42.5°	614.4	638.4	660.4	680.3	686.6
45°	581.9	607.0	633.2	653.1	661.5
47.5°	547.4	575.6	604.9	626.9	633.2
50°	513.9	543.2	575.6	599.7	607.0
52.5°	478.3	509.7	546.3	571.4	580.9
55°	443.8	478.3	516.0	544.2	552.6
57.5°	410.3	445.9	486.7	514.9	524.4
60°	374.7	412.4	455.3	484.6	496.1
62.5°	341.2	379.9	426.0	455.3	465.7
65°	306.7	347.5	393.5	424.9	435.4
67.5°	272.1	315.0	361.1	395.6	404.0
70°	235.5	280.5	330.7	364.2	374.7
72.5°	202.0	247.0	299.3	333.9	344.3
75°	166.4	215.6	267.9	302.5	315.0
77.5°	136.1	185.2	237.6	274.2	283.6
80°	103.6	154.9	209.3	244.9	255.4
82.5°	75.4	127.7	183.2	218.7	229.2
85°	51.3	103.6	159.1	194.7	205.1
87.5°	31.4	83.7	137.1	172.7	183.2
90°	14.0	68.8	126.8	163.8	174.9
92.5°	20.7	63.6	119.1	156.1	165.9
95°	33.1	59.4	114.6	149.5	159.9
97.5°	49.7	77.4	108.6	142.8	153.7
100°	69.1	109.7	102.8	135.9	146.7
102.5°	91.4	125.3	110.9	128.6	139.7
105°	113.7	142.7	155.9	122.6	132.7
107.5°	136.3	161.5	209.7	183.5	146.7
110°	159.0	180.6	226.4	241.9	199.8



TEST NUMBER: P1010732

CATALOG NUMBER: S123DIP-B775D365UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	181.6	198.6	242.3	271.7	280.4
115°	202.7	217.5	258.3	287.0	296.8
117.5°	224.6	235.5	272.9	300.8	309.6
120°	243.8	252.2	287.8	314.7	322.1
122.5°	264.3	268.9	302.7	327.4	335.2
125°	281.6	284.4	316.2	338.9	346.9
127.5°	299.9	301.8	329.7	351.7	358.3
130°	316.9	318.7	341.0	362.4	367.9
132.5°	332.2	335.0	351.7	372.0	378.3
135°	348.8	349.8	362.8	382.7	386.8
137.5°	362.9	364.6	372.7	391.2	395.8
140°	375.9	378.1	382.3	399.4	403.9
142.5°	389.0	390.1	391.2	405.8	410.0
145°	401.0	402.5	403.2	412.3	416.5
147.5°	411.7	413.5	414.2	418.0	420.4
150°	422.3	423.3	424.1	424.8	425.8
152.5°	431.8	432.2	432.5	433.9	432.2
155°	440.7	440.0	440.3	442.1	440.0
157.5°	447.7	447.7	447.4	449.5	446.7
160°	454.1	453.7	453.4	455.5	453.0
162.5°	460.1	459.0	458.7	461.2	459.0
165°	464.7	463.6	463.3	466.1	463.6
167.5°	468.6	467.2	467.2	470.0	467.2
170°	471.8	470.3	470.3	473.2	470.3
172.5°	473.9	472.1	472.5	475.3	472.1
175°	475.6	473.9	474.2	476.7	473.9
177.5°	476.4	474.6	474.9	477.8	474.2
180°	475.6	475.6	475.6	475.6	475.6

(END OF REPORT)