

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010735

Luminaire Tested: S123DIP-B775D365UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010735
REPORT IS A COMBINATION OF REPORTS P990359 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D365UB2750-4F0-XX-W2A-F_3000K
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4646.0 lumens
Efficiency: N/A
Efficacy: 102.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010735

CATALOG NUMBER: S123DIP-B775D365UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010735

CATALOG NUMBER: S123DIP-B775D365UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	69		
1	102	97	93	90	96	92	89	85	82	79	77	73	71	69	65	63	62	58		
2	93	85	79	73	87	80	75	70	72	68	64	64	61	58	57	54	52	48		
3	85	75	67	61	80	71	64	59	63	58	54	57	52	49	50	47	44	41		
4	77	66	58	52	73	63	55	50	56	50	46	51	46	42	45	41	38	35		
5	71	59	51	44	67	56	49	43	51	44	40	45	40	36	41	36	33	30		
6	66	53	45	39	62	51	43	37	46	39	35	41	36	32	37	33	29	27		
7	61	48	40	34	57	46	38	33	41	35	31	37	32	28	34	29	26	24		
8	57	44	36	30	53	42	34	29	38	32	27	34	29	25	31	27	23	21		
9	53	40	32	27	50	38	31	26	35	29	24	32	26	23	29	24	21	19		
10	49	37	29	24	47	35	28	24	32	26	22	29	24	21	26	22	19	17		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13177	13177	13177
5°	13209	12722	12703
10°	13092	12292	12165
15°	12910	11844	11580
20°	12701	11347	10999
25°	12431	10822	10378
30°	12136	10279	9725
35°	11827	9725	9076
40°	11503	9142	8438
45°	11146	8575	7771
50°	10783	7943	7102
55°	10319	7284	6424
60°	9838	6557	5702
65°	9389	5771	4949
70°	8740	4899	4072
75°	7809	3879	3161
80°	6743	2725	2236
85°	5254	1465	1119

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11146 cd/sqm

TEST NUMBER: P1010735

CATALOG NUMBER: S123DIP-B775D365UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.4	2.5
10°-20°	325.9	7.0
20°-30°	481.3	10.4
30°-40°	562.1	12.1
40°-50°	565.1	12.2
50°-60°	496.4	10.7
60°-70°	369.7	8.0
70°-80°	210.4	4.5
80°-90°	60.8	1.3
90°-100°	16.9	0.4
100°-110°	81.6	1.8
110°-120°	200.0	4.3
120°-130°	253.8	5.5
130°-140°	271.2	5.8
140°-150°	253.6	5.5
150°-160°	204.5	4.4
160°-170°	132.0	2.8
170°-180°	45.5	1.0
0°-30°	922.6	19.9
0°-40°	1484.6	32.0
0°-60°	2546.1	54.8
0°-90°	3187.0	68.6
90°-120°	298.5	6.4
90°-150°	1077.0	23.2
90°-180°	1459.0	31.4
0°-180°	4646.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1224	1224	1224	1224	1224	
5°	1225	1220	1208	1219	1217	116
15°	1166	1162	1148	1157	1150	329
25°	1059	1053	1039	1040	1037	488
35°	916	910	896	890	884	573
45°	750	746	733	720	715	579
55°	570	568	555	543	538	510
65°	388	383	373	364	361	383
75°	205	201	198	193	190	219
85°	55	53	53	50	50	59
90°	0	4	8	10	11	5
95°	22	7	11	14	14	26
105°	106	110	78	15	16	112
115°	199	201	204	208	209	196
125°	280	283	284	285	286	250
135°	349	351	352	353	352	269
145°	402	405	406	406	406	252
155°	443	443	443	445	443	204
165°	468	466	466	469	466	132
175°	479	477	477	480	477	46
180°	479	479	479	479	479	

TEST NUMBER: P1010735

CATALOG NUMBER: S123DIP-B775D365UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1224.2	1224.2	1224.2	1224.2	1224.2
2.5°	1229.4	1225.2	1213.7	1224.2	1223.1
5°	1225.2	1220.0	1208.4	1218.9	1216.8
7.5°	1215.8	1210.5	1198.9	1208.4	1207.3
10°	1203.1	1197.9	1184.2	1193.7	1191.5
12.5°	1186.3	1182.1	1169.4	1175.8	1174.7
15°	1166.3	1162.1	1148.4	1156.8	1150.5
17.5°	1144.2	1138.9	1125.2	1131.6	1129.4
20°	1118.9	1112.6	1098.9	1103.1	1100.0
22.5°	1090.5	1084.2	1070.5	1073.7	1069.4
25°	1058.9	1052.6	1038.9	1040.0	1036.8
27.5°	1026.3	1020.0	1005.2	1006.3	1003.1
30°	990.5	985.2	970.5	970.5	963.1
32.5°	954.7	947.3	936.8	929.5	926.3
35°	915.8	909.5	895.8	889.5	884.2
37.5°	876.8	868.4	854.7	847.3	844.2
40°	835.8	829.5	814.7	806.3	802.1
42.5°	794.7	787.3	772.6	764.2	760.0
45°	750.5	746.3	732.6	720.0	714.7
47.5°	707.4	701.0	688.4	675.8	671.6
50°	663.1	657.9	644.2	632.6	626.3
52.5°	616.8	613.7	598.9	589.5	583.1
55°	569.5	568.4	554.7	543.1	537.9
57.5°	525.3	521.0	510.5	500.0	493.7
60°	476.8	475.8	463.1	453.7	448.4
62.5°	433.7	430.5	417.9	408.4	405.3
65°	388.4	383.1	372.6	364.2	361.0
67.5°	340.0	335.8	327.4	320.0	315.8
70°	296.8	290.5	284.2	276.8	271.6
72.5°	251.6	247.4	240.0	233.7	231.6
75°	205.3	201.0	197.9	192.6	189.5
77.5°	164.2	162.1	157.9	153.7	153.7
80°	124.2	121.0	118.9	117.9	117.9
82.5°	85.3	85.3	85.3	83.2	82.1
85°	54.7	52.6	52.6	50.5	50.5
87.5°	27.4	24.2	23.2	22.1	22.1
90°	0.4	3.9	8.5	10.0	10.7
92.5°	8.2	6.0	9.2	11.7	12.1
95°	21.7	7.1	11.0	13.5	13.5
97.5°	39.5	29.5	11.4	14.2	14.6
100°	60.1	67.2	11.7	14.6	14.9
102.5°	83.6	88.2	26.3	14.6	15.3
105°	106.0	109.9	77.9	14.9	15.6
107.5°	129.8	133.0	138.3	83.6	37.0
110°	153.6	156.5	160.4	148.6	97.8



TEST NUMBER: P1010735

CATALOG NUMBER: S123DIP-B775D365UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	176.4	178.9	182.8	186.0	185.3
115°	198.8	200.9	204.1	207.7	209.1
117.5°	220.8	223.3	225.1	227.9	228.3
120°	241.1	244.3	245.3	248.2	248.2
122.5°	261.7	264.2	265.6	267.4	267.7
125°	280.2	283.0	284.5	285.2	285.9
127.5°	298.7	301.5	303.3	304.4	303.7
130°	315.7	318.6	320.0	321.4	320.7
132.5°	332.1	334.9	336.0	337.4	336.4
135°	348.8	350.9	352.4	353.4	352.4
137.5°	363.0	365.9	366.6	368.4	367.7
140°	377.3	379.4	380.5	381.9	381.2
142.5°	390.4	392.5	393.6	394.7	393.6
145°	402.5	405.0	405.7	406.4	406.4
147.5°	414.2	416.0	416.7	417.4	415.7
150°	424.9	426.0	426.7	427.4	426.3
152.5°	434.5	434.9	435.2	436.6	434.9
155°	443.4	442.7	443.0	444.8	442.7
157.5°	450.5	450.5	450.2	452.3	449.4
160°	456.9	456.6	456.2	458.3	455.8
162.5°	463.0	461.9	461.5	464.0	461.9
165°	467.6	466.5	466.2	469.0	466.5
167.5°	471.5	470.1	470.1	472.9	470.1
170°	474.7	473.3	473.3	476.1	473.3
172.5°	476.8	475.0	475.4	478.2	475.0
175°	478.6	476.8	477.2	479.7	476.8
177.5°	479.3	477.5	477.9	480.7	477.2
180°	478.6	478.6	478.6	478.6	478.6

(END OF REPORT)