

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010737

Luminaire Tested: S123DIP-B775D365UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010737
REPORT IS A COMBINATION OF REPORTS P990361 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D365UB2750-4F0-XX-W2A-F_4000K
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4619.0 lumens
Efficiency: N/A
Efficacy: 102.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010737

CATALOG NUMBER: S123DIP-B775D365UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010737

CATALOG NUMBER: S123DIP-B775D365UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	69		
1	102	97	93	90	96	92	89	85	82	79	77	73	71	69	65	63	62	58		
2	93	85	79	73	87	81	75	70	72	68	64	64	61	58	57	54	52	48		
3	85	75	67	61	80	71	64	59	63	58	54	57	52	49	50	47	44	41		
4	77	66	58	52	73	63	55	50	56	50	46	51	46	42	45	41	38	35		
5	71	59	51	44	67	56	49	43	51	44	40	45	40	36	41	36	33	30		
6	66	53	45	39	62	51	43	37	46	39	35	41	36	32	37	33	29	27		
7	61	48	40	34	57	46	38	33	41	35	31	37	32	28	34	29	26	24		
8	57	44	36	30	53	42	34	29	38	32	27	34	29	25	31	27	23	21		
9	53	40	32	27	50	38	31	26	35	29	24	32	26	23	29	24	21	19		
10	49	37	29	24	47	35	28	24	32	26	22	29	24	21	26	22	19	17		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13103	13103	13103
5°	13135	12651	12631
10°	13018	12222	12097
15°	12837	11777	11514
20°	12630	11282	10937
25°	12361	10762	10320
30°	12067	10221	9670
35°	11760	9669	9025
40°	11437	9091	8391
45°	11083	8527	7728
50°	10723	7898	7063
55°	10259	7243	6387
60°	9783	6520	5671
65°	9336	5738	4922
70°	8693	4872	4048
75°	7764	3858	3143
80°	6705	2712	2223
85°	5225	1456	1113

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11083 cd/sqm

TEST NUMBER: P1010737

CATALOG NUMBER: S123DIP-B775D365UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.8	2.5
10°-20°	324.0	7.0
20°-30°	478.6	10.4
30°-40°	558.9	12.1
40°-50°	561.9	12.2
50°-60°	493.6	10.7
60°-70°	367.6	8.0
70°-80°	209.2	4.5
80°-90°	60.4	1.3
90°-100°	16.8	0.4
100°-110°	81.1	1.8
110°-120°	198.7	4.3
120°-130°	252.3	5.5
130°-140°	269.5	5.8
140°-150°	252.0	5.5
150°-160°	203.3	4.4
160°-170°	131.2	2.8
170°-180°	45.2	1.0
0°-30°	917.4	19.9
0°-40°	1476.3	32.0
0°-60°	2531.7	54.8
0°-90°	3169.0	68.6
90°-120°	296.6	6.4
90°-150°	1070.4	23.2
90°-180°	1450.0	31.4
0°-180°	4619.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1217	1217	1217	1217	1217	
5°	1218	1213	1202	1212	1210	116
15°	1160	1156	1142	1150	1144	327
25°	1053	1047	1033	1034	1031	485
35°	911	904	891	884	879	570
45°	746	742	728	716	711	576
55°	566	565	552	540	535	507
65°	386	381	370	362	359	381
75°	204	200	197	192	188	218
85°	54	52	52	50	50	58
90°	0	4	8	10	11	5
95°	22	7	11	13	13	26
105°	105	109	77	15	16	112
115°	198	200	203	206	208	195
125°	278	281	283	283	284	249
135°	347	349	350	351	350	267
145°	400	402	403	404	404	250
155°	441	440	440	442	440	203
165°	465	464	463	466	464	131
175°	476	474	474	477	474	45
180°	476	476	476	476	476	

TEST NUMBER: P1010737

CATALOG NUMBER: S123DIP-B775D365UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1217.3	1217.3	1217.3	1217.3	1217.3
2.5°	1222.5	1218.3	1206.8	1217.3	1216.2
5°	1218.3	1213.1	1201.6	1212.0	1209.9
7.5°	1208.9	1203.7	1192.1	1201.6	1200.5
10°	1196.3	1191.1	1177.5	1186.9	1184.8
12.5°	1179.6	1175.4	1162.8	1169.1	1168.1
15°	1159.7	1155.5	1141.9	1150.3	1144.0
17.5°	1137.7	1132.5	1118.9	1125.2	1123.1
20°	1112.6	1106.3	1092.7	1096.9	1093.8
22.5°	1084.3	1078.1	1064.5	1067.6	1063.4
25°	1052.9	1046.7	1033.1	1034.1	1031.0
27.5°	1020.5	1014.2	999.6	1000.6	997.5
30°	984.9	979.7	965.0	965.0	957.7
32.5°	949.3	942.0	931.5	924.2	921.1
35°	910.6	904.3	890.7	884.4	879.2
37.5°	871.9	863.5	849.9	842.6	839.4
40°	831.0	824.8	810.1	801.7	797.6
42.5°	790.2	782.9	768.2	759.9	755.7
45°	746.3	742.1	728.5	715.9	710.7
47.5°	703.4	697.1	684.5	672.0	667.8
50°	659.4	654.2	640.6	629.0	622.8
52.5°	613.3	610.2	595.5	586.1	579.8
55°	566.2	565.2	551.6	540.1	534.8
57.5°	522.3	518.1	507.6	497.2	490.9
60°	474.1	473.1	460.5	451.1	445.9
62.5°	431.2	428.1	415.5	406.1	403.0
65°	386.2	381.0	370.5	362.1	359.0
67.5°	338.1	333.9	325.5	318.2	314.0
70°	295.2	288.9	282.6	275.3	270.0
72.5°	250.2	246.0	238.6	232.4	230.3
75°	204.1	199.9	196.8	191.5	188.4
77.5°	163.3	161.2	157.0	152.8	152.8
80°	123.5	120.4	118.3	117.2	117.2
82.5°	84.8	84.8	84.8	82.7	81.6
85°	54.4	52.3	52.3	50.2	50.2
87.5°	27.2	24.1	23.0	22.0	22.0
90°	0.4	3.9	8.5	9.9	10.6
92.5°	8.1	6.0	9.2	11.7	12.0
95°	21.6	7.1	11.0	13.4	13.4
97.5°	39.2	29.3	11.3	14.1	14.5
100°	59.7	66.8	11.7	14.5	14.8
102.5°	83.0	87.6	26.1	14.5	15.2
105°	105.3	109.2	77.4	14.8	15.5
107.5°	129.0	132.2	137.5	83.0	36.8
110°	152.7	155.5	159.4	147.7	97.2



TEST NUMBER: P1010737

CATALOG NUMBER: S123DIP-B775D365UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	175.3	177.7	181.6	184.8	184.1
115°	197.5	199.7	202.8	206.4	207.8
117.5°	219.4	221.9	223.7	226.5	226.9
120°	239.6	242.8	243.8	246.7	246.7
122.5°	260.1	262.6	264.0	265.7	266.1
125°	278.5	281.3	282.7	283.4	284.1
127.5°	296.8	299.7	301.4	302.5	301.8
130°	313.8	316.6	318.0	319.5	318.7
132.5°	330.1	332.9	333.9	335.4	334.3
135°	346.7	348.8	350.2	351.3	350.2
137.5°	360.8	363.6	364.3	366.1	365.4
140°	374.9	377.1	378.1	379.5	378.8
142.5°	388.0	390.1	391.2	392.2	391.2
145°	400.0	402.5	403.2	403.9	403.9
147.5°	411.7	413.5	414.2	414.9	413.1
150°	422.3	423.3	424.1	424.8	423.7
152.5°	431.8	432.2	432.5	433.9	432.2
155°	440.7	440.0	440.3	442.1	440.0
157.5°	447.7	447.7	447.4	449.5	446.7
160°	454.1	453.7	453.4	455.5	453.0
162.5°	460.1	459.0	458.7	461.2	459.0
165°	464.7	463.6	463.3	466.1	463.6
167.5°	468.6	467.2	467.2	470.0	467.2
170°	471.8	470.3	470.3	473.2	470.3
172.5°	473.9	472.1	472.5	475.3	472.1
175°	475.6	473.9	474.2	476.7	473.9
177.5°	476.4	474.6	474.9	477.8	474.2
180°	475.6	475.6	475.6	475.6	475.6

(END OF REPORT)