

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011047

Luminaire Tested: S123DIP-B1000D1025UB40-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011047
REPORT IS A COMBINATION OF REPORTS P989062 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D1025UB40-4F0-XX-W2A-A1
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7659.0 lumens
Efficiency: N/A
Efficacy: 101.7 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011047

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1011047

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	52
2	91	83	77	72	84	78	72	68	67	63	59	57	54	52	48	46	44
3	83	73	66	60	77	68	62	57	59	54	50	51	47	44	43	40	38
4	76	65	57	51	70	61	54	49	53	47	43	45	41	38	38	35	33
5	70	58	50	44	64	54	47	42	47	42	37	41	36	33	35	31	29
6	64	52	44	38	60	49	42	36	43	37	33	37	32	29	31	28	25
7	59	47	39	34	55	44	37	32	39	33	29	34	29	26	29	25	22
8	55	43	35	30	51	40	33	28	35	30	26	31	26	23	26	23	20
9	51	39	32	27	48	37	30	25	32	27	23	28	24	21	24	21	18
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14944	14944	14944	14944
5°	14953	17217	14997	12850
10°	14858	20835	14872	11221
15°	14653	24709	14772	10100
20°	14476	28448	14507	9294
25°	14213	29165	14245	8874
30°	14026	24096	14026	8598
35°	13794	16115	13707	8355
40°	13515	11633	13348	7982
45°	13166	9215	12785	7518
50°	12316	7826	11879	7063
55°	11383	6877	10921	6555
60°	10437	5987	9882	6022
65°	9399	5127	8942	5311
70°	8319	4255	7766	4477
75°	7113	3210	6653	3457
80°	5624	2143	5185	2270
85°	3881	984	3103	895

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 24100 cd/sqm

TEST NUMBER: P1011047

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.5	1.8
10°-20°	438.5	5.7
20°-30°	737.9	9.6
30°-40°	833.9	10.9
40°-50°	746.8	9.8
50°-60°	602.9	7.9
60°-70°	420.1	5.5
70°-80°	220.5	2.9
80°-90°	55.5	0.7
90°-100°	80.5	1.1
100°-110°	243.7	3.2
110°-120°	415.0	5.4
120°-130°	545.9	7.1
130°-140°	613.6	8.0
140°-150°	603.2	7.9
150°-160°	507.9	6.6
160°-170°	338.1	4.4
170°-180°	118.4	1.5
0°-30°	1312.9	17.1
0°-40°	2146.8	28.0
0°-60°	3496.5	45.7
0°-90°	4192.6	54.7
90°-120°	739.2	9.7
90°-150°	2502.0	32.7
90°-180°	3466.0	45.3
0°-180°	7659.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1388	1388	1388	1388	1388	
5°	1387	1649	1391	1231	1387	132
15°	1324	2455	1334	1004	1324	374
25°	1211	2914	1213	886	1211	559
35°	1068	1570	1061	814	1068	668
45°	886	848	861	691	886	678
55°	628	576	603	549	628	562
65°	389	374	370	387	389	387
75°	187	192	175	207	187	201
85°	40	44	32	40	40	46
90°	1	30	1	30	1	7
95°	58	77	58	77	58	64
105°	221	234	221	234	221	237
115°	418	419	418	419	418	413
125°	611	604	611	604	611	545
135°	793	792	793	792	793	611
145°	962	962	962	962	962	601
155°	1102	1100	1102	1100	1102	507
165°	1200	1196	1200	1196	1200	338
175°	1248	1243	1248	1243	1248	119
180°	1251	1251	1251	1251	1251	

TEST NUMBER: P1011047

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3
2.5°	1392.3	1403.1	1408.4	1416.5	1424.6	1436.7	1440.7	1447.5	1444.8	1450.1	1452.8
5°	1386.9	1405.8	1421.9	1442.1	1460.9	1474.4	1487.8	1509.3	1525.5	1528.2	1540.3
7.5°	1377.5	1404.4	1432.7	1460.9	1497.2	1518.7	1543.0	1572.6	1596.8	1635.8	1650.6
10°	1365.4	1403.1	1443.4	1482.4	1532.2	1565.8	1595.4	1645.2	1695.0	1735.3	1773.0
12.5°	1346.6	1393.6	1446.1	1504.0	1568.5	1607.5	1647.9	1713.8	1789.1	1851.0	1891.4
15°	1323.7	1382.9	1450.1	1512.0	1583.3	1656.0	1699.0	1773.0	1880.6	1938.5	2042.0
17.5°	1304.9	1365.4	1432.7	1529.5	1626.4	1699.0	1729.9	1865.8	1939.8	2036.7	2153.7
20°	1275.3	1351.9	1438.0	1534.9	1660.0	1704.4	1767.6	1904.8	1996.3	2122.8	2266.7
22.5°	1244.3	1326.4	1430.0	1530.9	1670.8	1717.8	1803.9	1912.9	2058.2	2183.3	2342.0
25°	1210.7	1299.5	1404.4	1524.1	1661.3	1729.9	1810.7	1945.2	2102.6	2260.0	2406.6
27.5°	1177.1	1273.9	1382.9	1502.6	1635.8	1716.5	1797.2	1937.1	2138.9	2309.7	2496.7
30°	1144.8	1241.6	1350.6	1473.0	1612.9	1690.9	1767.6	1942.5	2167.1	2359.5	2547.8
32.5°	1109.8	1209.3	1323.7	1425.9	1567.2	1650.6	1736.7	1942.5	2184.6	2389.1	2561.3
35°	1068.1	1170.3	1268.5	1370.8	1510.7	1603.5	1700.4	1929.0	2200.8	2398.5	2504.8
37.5°	1027.7	1117.9	1202.6	1302.2	1448.8	1548.3	1660.0	1912.9	2192.7	2358.2	2387.8
40°	982.0	1072.1	1140.7	1233.6	1388.3	1504.0	1616.9	1891.4	2157.7	2262.7	2176.6
42.5°	937.6	1008.9	1068.1	1158.2	1326.4	1439.4	1561.8	1852.4	2089.1	2110.6	1916.9
45°	886.5	937.6	990.1	1092.3	1259.1	1374.8	1510.7	1795.9	1978.8	1916.9	1672.1
47.5°	820.6	866.3	924.2	1018.3	1187.8	1307.5	1436.7	1723.2	1818.7	1689.6	1421.9
50°	757.4	796.4	850.2	941.7	1112.5	1229.5	1366.7	1608.9	1656.0	1452.8	1225.5
52.5°	694.1	723.7	776.2	867.7	1038.5	1151.5	1276.6	1491.8	1464.9	1247.0	1045.2
55°	628.2	653.8	703.5	793.7	952.4	1060.0	1179.8	1347.9	1278.0	1070.8	909.4
57.5°	563.6	590.5	641.7	717.0	866.3	971.2	1066.8	1198.6	1093.7	928.2	785.6
60°	505.8	528.7	567.7	641.7	777.5	862.3	949.7	1039.9	952.4	792.3	683.4
62.5°	445.3	466.8	503.1	570.4	687.4	762.7	832.7	906.7	809.8	692.8	595.9
65°	388.8	406.3	439.9	501.8	597.3	659.2	715.7	766.8	688.8	581.1	508.5
67.5°	337.6	352.4	380.7	435.8	516.6	561.0	606.7	649.7	583.8	497.7	435.8
70°	282.5	294.6	320.2	360.5	425.1	470.8	504.5	536.7	477.6	408.9	367.2
72.5°	234.1	246.2	262.3	304.0	348.4	376.7	413.0	430.5	396.8	340.3	298.6
75°	187.0	196.4	211.2	238.1	279.8	298.6	321.5	335.0	304.0	266.4	240.8
77.5°	146.6	150.7	161.4	180.3	208.5	230.0	247.5	255.6	234.1	209.9	188.3
80°	103.6	109.0	117.0	133.2	154.7	161.4	172.2	181.6	168.2	146.6	133.2
82.5°	68.6	75.3	79.4	86.1	99.5	107.6	110.3	118.4	106.3	98.2	92.8
85°	40.4	43.0	44.4	48.4	55.2	59.2	63.2	64.6	61.9	60.5	55.2
87.5°	20.2	20.2	20.2	22.9	24.2	26.9	28.2	28.2	28.2	26.9	25.6
90°	1.0	3.2	5.4	7.5	9.7	10.8	12.2	15.1	17.9	20.8	23.6
92.5°	29.5	30.8	32.1	33.4	34.7	35.4	36.1	37.4	38.7	40.0	41.3
95°	58.0	59.5	61.1	62.6	64.1	64.9	65.8	67.5	69.2	71.0	72.7
97.5°	95.3	96.4	97.5	98.6	99.7	100.2	100.9	102.2	103.5	104.8	106.1
100°	133.7	135.0	136.3	137.6	138.9	139.5	140.1	141.2	142.3	143.4	144.5
102.5°	177.9	178.5	179.2	179.8	180.5	180.8	181.6	183.1	184.6	186.2	187.7
105°	221.1	221.5	222.0	222.4	222.9	223.1	224.1	226.0	228.0	229.9	231.9
107.5°	272.2	272.4	272.6	272.9	273.1	273.2	273.6	274.5	275.4	276.2	277.1
110°	319.4	319.8	320.3	320.7	321.2	321.4	321.6	322.0	322.5	322.9	323.3



TEST NUMBER: P1011047

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	368.5	368.7	368.9	369.2	369.4	369.5	369.5	369.5	369.5	369.5	369.5
115°	417.7	418.3	419.0	419.6	420.3	420.6	420.4	419.9	419.5	419.0	418.6
117.5°	467.8	468.0	468.2	468.5	468.7	468.8	468.6	468.1	467.7	467.2	466.8
120°	514.0	515.3	516.6	517.9	519.2	519.9	519.4	518.3	517.2	516.1	515.0
122.5°	562.1	563.0	563.9	564.8	565.7	566.1	565.9	565.4	565.0	564.5	564.1
125°	611.3	611.9	612.6	613.2	613.9	614.2	614.0	613.5	613.1	612.6	612.2
127.5°	656.5	657.8	659.1	660.4	661.7	662.4	662.2	661.7	661.3	660.8	660.4
130°	701.7	703.4	705.2	706.9	708.6	709.5	709.2	708.5	707.9	707.2	706.6
132.5°	746.9	748.6	750.4	752.1	753.8	754.7	754.5	754.1	753.6	753.2	752.8
135°	793.1	794.4	795.7	797.0	798.3	799.0	798.9	798.7	798.4	798.2	798.0
137.5°	835.3	836.4	837.5	838.6	839.7	840.2	840.5	841.2	841.9	842.5	843.2
140°	879.5	880.6	881.7	882.8	883.9	884.5	884.6	884.8	885.0	885.2	885.4
142.5°	919.8	920.9	922.0	923.1	924.2	924.8	925.0	925.4	925.9	926.3	926.7
145°	962.1	962.5	963.0	963.4	963.9	964.1	964.4	965.1	965.7	966.4	967.0
147.5°	998.5	999.4	1000.2	1001.1	1002.0	1002.4	1002.7	1003.4	1004.0	1004.7	1005.3
150°	1036.8	1037.2	1037.7	1038.1	1038.6	1038.8	1039.0	1039.4	1039.9	1040.3	1040.7
152.5°	1068.2	1068.9	1069.5	1070.2	1070.9	1071.2	1071.3	1071.5	1071.8	1072.0	1072.2
155°	1101.6	1101.6	1101.6	1101.6	1101.6	1101.6	1101.7	1101.9	1102.2	1102.4	1102.6
157.5°	1130.1	1129.9	1129.7	1129.5	1129.3	1129.2	1129.3	1129.5	1129.7	1129.9	1130.1
160°	1156.7	1156.3	1155.8	1155.4	1154.9	1154.7	1154.7	1154.7	1154.7	1154.7	1154.7
162.5°	1180.3	1179.6	1179.0	1178.3	1177.6	1177.3	1177.4	1177.6	1177.9	1178.1	1178.3
165°	1199.9	1199.3	1198.6	1198.0	1197.3	1197.0	1197.0	1197.0	1197.0	1197.0	1197.0
167.5°	1216.6	1215.7	1214.9	1214.0	1213.1	1212.7	1212.8	1213.0	1213.3	1213.5	1213.7
170°	1230.4	1229.5	1228.7	1227.8	1226.9	1226.5	1226.5	1226.5	1226.5	1226.5	1226.5
172.5°	1241.2	1240.3	1239.5	1238.6	1237.7	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3
175°	1248.1	1247.2	1246.3	1245.4	1244.5	1244.1	1244.1	1244.1	1244.1	1244.1	1244.1
177.5°	1252.0	1251.1	1250.3	1249.4	1248.5	1248.1	1248.1	1248.1	1248.1	1248.1	1248.1
180°	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0

TEST NUMBER: P1011047

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3
2.5°	1462.2	1464.9	1474.4	1481.1	1494.5	1493.2	1493.2	1491.8	1487.8	1494.5	1498.6
5°	1564.5	1587.4	1590.0	1619.6	1621.0	1633.1	1641.2	1634.4	1650.6	1649.2	1637.1
7.5°	1690.9	1721.9	1736.7	1764.9	1797.2	1789.1	1820.1	1825.5	1822.8	1836.2	1845.6
10°	1829.5	1883.3	1921.0	1973.4	1986.9	1995.0	2015.1	2032.6	2067.6	2040.7	2058.2
12.5°	1988.2	2027.2	2077.0	2160.4	2202.1	2229.0	2238.4	2250.5	2274.8	2260.0	2261.3
15°	2121.4	2173.9	2258.6	2362.2	2374.3	2407.9	2399.9	2472.5	2507.5	2455.0	2484.6
17.5°	2260.0	2329.9	2430.8	2520.9	2572.1	2594.9	2616.4	2686.4	2683.7	2675.6	2682.4
20°	2348.7	2463.1	2588.2	2707.9	2722.7	2740.2	2798.0	2827.6	2822.3	2845.1	2859.9
22.5°	2473.9	2594.9	2728.1	2807.5	2841.1	2861.3	2907.0	2925.8	2933.9	2939.3	2929.9
25°	2578.8	2707.9	2806.1	2876.1	2896.2	2907.0	2921.8	2927.2	2923.2	2913.7	2921.8
27.5°	2650.1	2753.7	2820.9	2853.2	2842.4	2825.0	2796.7	2777.9	2736.2	2716.0	2740.2
30°	2679.7	2725.4	2745.6	2691.8	2638.0	2594.9	2541.1	2441.6	2363.5	2386.4	2355.5
32.5°	2632.6	2603.0	2506.1	2367.6	2325.9	2255.9	2103.9	1986.9	1990.9	1929.0	1954.6
35°	2494.0	2359.5	2176.6	1966.7	1911.6	1873.9	1707.1	1681.5	1627.7	1569.9	1586.0
37.5°	2249.2	2052.8	1830.8	1676.1	1594.1	1512.0	1417.9	1361.4	1329.1	1304.9	1323.7
40°	1950.6	1711.1	1528.2	1389.6	1319.7	1267.2	1202.6	1146.1	1109.8	1105.8	1112.5
42.5°	1657.3	1455.5	1287.4	1155.5	1132.7	1070.8	1029.1	984.7	973.9	956.4	965.9
45°	1403.1	1238.9	1100.4	992.8	965.9	949.7	898.6	870.4	858.2	847.5	863.6
47.5°	1218.8	1046.6	945.7	881.1	854.2	827.3	799.1	780.2	770.8	772.2	770.8
50°	1041.2	914.7	826.0	776.2	760.0	741.2	718.3	706.2	702.2	690.1	699.5
52.5°	895.9	804.4	742.6	695.5	683.4	669.9	651.1	644.4	634.9	632.3	632.3
55°	778.9	707.6	657.8	626.9	612.1	601.3	590.5	582.5	575.8	575.8	575.8
57.5°	687.4	625.5	589.2	562.3	556.9	546.2	534.1	534.1	524.6	523.3	527.3
60°	609.4	554.2	526.0	503.1	495.0	492.3	480.2	480.2	477.6	470.8	476.2
62.5°	530.0	489.7	465.4	448.0	439.9	439.9	430.5	423.7	423.7	425.1	422.4
65°	457.4	427.8	406.3	392.8	388.8	383.4	382.0	376.7	372.6	374.0	372.6
67.5°	392.8	369.9	355.1	344.4	337.6	335.0	330.9	330.9	328.2	329.6	322.9
70°	335.0	312.1	300.0	289.2	286.5	286.5	281.2	282.5	279.8	283.8	281.2
72.5°	275.8	258.3	248.9	244.8	242.1	240.8	238.1	235.4	234.1	236.8	235.4
75°	223.3	208.5	201.8	199.1	196.4	196.4	195.1	193.7	192.4	192.4	192.4
77.5°	173.5	164.1	156.0	158.7	154.7	156.0	152.0	152.0	153.4	152.0	152.0
80°	127.8	121.1	121.1	118.4	113.0	115.7	115.7	111.7	110.3	113.0	109.0
82.5°	84.7	83.4	80.7	79.4	76.7	78.0	76.7	75.3	74.0	76.7	74.0
85°	49.8	49.8	48.4	45.7	48.4	47.1	45.7	45.7	44.4	44.4	44.4
87.5°	25.6	22.9	22.9	21.5	22.9	20.2	21.5	20.2	18.8	20.2	18.8
90°	24.5	25.3	26.2	27.1	27.5	27.7	28.2	28.6	29.1	29.5	29.1
92.5°	41.9	42.6	43.2	43.9	44.2	44.0	43.6	43.1	42.7	42.3	42.7
95°	73.6	74.5	75.4	76.3	76.7	76.7	76.7	76.7	76.7	76.7	76.7
97.5°	107.2	108.3	109.4	110.5	111.0	110.9	110.7	110.5	110.3	110.1	110.3
100°	145.1	145.8	146.4	147.1	147.4	147.6	148.1	148.5	149.0	149.4	149.0
102.5°	188.4	189.0	189.7	190.4	190.7	190.6	190.4	190.1	189.9	189.7	189.9
105°	231.9	231.9	231.9	231.9	231.9	232.1	232.6	233.0	233.5	233.9	233.5
107.5°	277.8	278.4	279.1	279.8	280.1	280.0	279.8	279.5	279.3	279.1	279.3
110°	324.2	325.1	326.0	326.9	327.3	327.1	326.6	326.2	325.7	325.3	325.7

TEST NUMBER: P1011047

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	370.6	371.7	372.8	373.9	374.4	374.4	374.4	374.4	374.4	374.4	374.4
115°	418.8	419.0	419.3	419.5	419.6	419.5	419.3	419.0	418.8	418.6	418.8
117.5°	466.8	466.8	466.8	466.8	466.8	466.5	465.8	465.2	464.5	463.9	464.5
120°	514.8	514.6	514.3	514.1	514.0	513.8	513.3	512.9	512.4	512.0	512.4
122.5°	563.4	562.8	562.1	561.4	561.1	560.8	560.1	559.5	558.8	558.2	558.8
125°	611.3	610.5	609.6	608.7	608.3	607.9	607.0	606.1	605.3	604.4	605.3
127.5°	659.1	657.8	656.5	655.2	654.5	654.1	653.2	652.3	651.5	650.6	651.5
130°	705.7	704.9	704.0	703.1	702.7	701.9	700.4	698.9	697.3	695.8	697.3
132.5°	751.7	750.6	749.5	748.4	747.9	747.3	746.2	745.1	744.0	742.9	744.0
135°	797.1	796.3	795.4	794.5	794.1	793.9	793.4	793.0	792.5	792.1	792.5
137.5°	842.1	841.0	839.9	838.8	838.3	838.0	837.3	836.6	836.0	835.3	836.0
140°	885.2	885.0	884.8	884.6	884.5	883.7	882.2	880.7	879.1	877.6	879.1
142.5°	926.5	926.3	926.0	925.8	925.7	925.2	924.1	923.0	921.9	920.8	921.9
145°	966.8	966.6	966.3	966.1	966.0	965.6	964.7	963.8	963.0	962.1	963.0
147.5°	1005.3	1005.3	1005.3	1005.3	1005.3	1004.6	1003.3	1002.0	1000.7	999.4	1000.7
150°	1040.7	1040.7	1040.7	1040.7	1040.7	1040.0	1038.7	1037.4	1036.1	1034.8	1036.1
152.5°	1072.6	1073.0	1073.5	1073.9	1074.1	1073.6	1072.5	1071.4	1070.3	1069.2	1070.3
155°	1103.5	1104.4	1105.3	1106.2	1106.6	1105.8	1104.3	1102.8	1101.2	1099.7	1101.2
157.5°	1131.0	1131.9	1132.8	1133.7	1134.1	1133.4	1132.1	1130.8	1129.5	1128.2	1129.5
160°	1155.8	1156.9	1158.0	1159.1	1159.6	1159.2	1158.3	1157.4	1156.6	1155.7	1156.6
162.5°	1179.4	1180.5	1181.6	1182.7	1183.2	1182.4	1180.9	1179.4	1177.8	1176.3	1177.8
165°	1198.3	1199.6	1200.9	1202.2	1202.9	1202.1	1200.6	1199.1	1197.5	1196.0	1197.5
167.5°	1215.0	1216.3	1217.6	1218.9	1219.6	1218.9	1217.6	1216.3	1215.0	1213.7	1215.0
170°	1228.0	1229.5	1231.0	1232.5	1233.3	1232.5	1231.0	1229.5	1228.0	1226.5	1228.0
172.5°	1238.6	1239.9	1241.2	1242.5	1243.2	1242.4	1240.9	1239.4	1237.8	1236.3	1237.8
175°	1245.4	1246.7	1248.0	1249.3	1250.0	1249.2	1247.7	1246.2	1244.7	1243.2	1244.7
177.5°	1249.4	1250.7	1252.0	1253.3	1254.0	1253.2	1251.7	1250.2	1248.6	1247.1	1248.6
180°	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0

TEST NUMBER: P1011047

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3
2.5°	1487.8	1491.8	1481.1	1478.4	1478.4	1483.8	1479.7	1443.4	1450.1	1442.1	1439.4
5°	1651.9	1643.9	1633.1	1627.7	1621.0	1602.2	1600.8	1559.1	1551.0	1524.1	1512.0
7.5°	1832.2	1825.5	1793.2	1789.1	1786.4	1769.0	1724.6	1680.2	1647.9	1616.9	1587.4
10°	2038.0	2017.8	2003.0	1973.4	1958.6	1934.4	1876.6	1834.9	1779.7	1732.6	1670.8
12.5°	2285.5	2262.7	2212.9	2191.4	2172.5	2105.3	2047.4	2000.3	1892.7	1860.4	1783.8
15°	2467.1	2418.7	2413.3	2366.2	2363.5	2289.6	2179.2	2128.1	2044.7	1926.3	1847.0
17.5°	2663.5	2620.5	2586.9	2530.4	2522.3	2452.3	2371.6	2246.5	2155.0	2042.0	1941.1
20°	2807.5	2784.6	2726.8	2703.9	2656.8	2597.6	2514.2	2359.5	2247.9	2134.9	2011.1
22.5°	2921.8	2898.9	2853.2	2822.3	2795.4	2718.7	2619.1	2487.3	2333.9	2186.0	2058.2
25°	2920.5	2913.7	2894.9	2880.1	2859.9	2803.4	2720.0	2593.6	2422.7	2260.0	2082.4
27.5°	2755.0	2773.8	2806.1	2822.3	2818.2	2810.2	2763.1	2656.8	2503.4	2309.7	2110.6
30°	2410.6	2479.2	2539.8	2620.5	2644.7	2703.9	2730.8	2670.3	2547.8	2367.6	2147.0
32.5°	1999.0	2098.5	2230.4	2274.8	2351.4	2465.8	2593.6	2616.4	2539.8	2401.2	2169.8
35°	1639.8	1721.9	1824.1	1894.1	1962.7	2148.3	2309.7	2449.6	2475.2	2383.7	2164.5
37.5°	1357.3	1415.2	1505.3	1564.5	1627.7	1786.4	2012.4	2194.0	2321.8	2324.5	2149.7
40°	1152.9	1178.4	1256.4	1299.5	1360.0	1497.2	1699.0	1935.8	2122.8	2208.8	2110.6
42.5°	976.6	1010.3	1074.8	1107.1	1146.1	1265.8	1399.0	1623.7	1855.1	2039.3	2038.0
45°	871.7	895.9	925.5	952.4	996.8	1068.1	1220.1	1388.3	1610.2	1818.7	1900.8
47.5°	778.9	801.7	831.3	839.4	869.0	936.3	1029.1	1175.7	1382.9	1590.0	1744.7
50°	700.9	719.7	739.9	754.7	768.1	823.3	893.2	1017.0	1182.4	1382.9	1575.2
52.5°	640.3	653.8	671.3	679.3	691.4	731.8	785.6	877.1	1012.9	1195.9	1382.9
55°	583.8	593.2	604.0	617.5	622.8	652.4	694.1	772.2	873.0	1037.2	1214.7
57.5°	531.4	535.4	542.1	550.2	556.9	582.5	618.8	671.3	760.0	886.5	1054.6
60°	472.2	482.9	487.0	495.0	499.1	519.3	547.5	591.9	660.5	769.5	895.9
62.5°	422.4	429.1	435.8	439.9	449.3	456.0	478.9	519.3	575.8	656.5	770.8
65°	378.0	380.7	384.7	388.8	391.5	399.5	421.1	448.0	491.0	562.3	651.1
67.5°	326.9	329.6	335.0	336.3	339.0	349.8	361.9	384.7	421.1	474.9	547.5
70°	277.1	281.2	283.8	286.5	290.6	294.6	308.1	326.9	355.1	392.8	449.3
72.5°	234.1	238.1	238.1	240.8	239.4	244.8	258.3	271.7	290.6	321.5	371.3
75°	191.0	191.0	193.7	195.1	196.4	201.8	207.2	217.9	232.7	256.9	287.9
77.5°	150.7	149.3	152.0	152.0	152.0	156.0	161.4	166.8	176.2	193.7	217.9
80°	110.3	110.3	113.0	114.3	111.7	113.0	115.7	121.1	127.8	139.9	153.4
82.5°	72.6	78.0	76.7	78.0	76.7	79.4	80.7	82.1	84.7	90.1	99.5
85°	44.4	44.4	44.4	45.7	44.4	45.7	45.7	45.7	47.1	49.8	53.8
87.5°	18.8	18.8	18.8	20.2	18.8	18.8	20.2	18.8	20.2	20.2	21.5
90°	28.6	28.2	27.7	27.5	27.1	26.2	25.3	24.5	23.6	20.8	17.9
92.5°	43.1	43.6	44.0	44.2	43.9	43.2	42.6	41.9	41.3	40.0	38.7
95°	76.7	76.7	76.7	76.7	76.3	75.4	74.5	73.6	72.7	71.0	69.2
97.5°	110.5	110.7	110.9	111.0	110.5	109.4	108.3	107.2	106.1	104.8	103.5
100°	148.5	148.1	147.6	147.4	147.1	146.4	145.8	145.1	144.5	143.4	142.3
102.5°	190.1	190.4	190.6	190.7	190.4	189.7	189.0	188.4	187.7	186.2	184.6
105°	233.0	232.6	232.1	231.9	231.9	231.9	231.9	231.9	231.9	229.9	228.0
107.5°	279.5	279.8	280.0	280.1	279.8	279.1	278.4	277.8	277.1	276.2	275.4
110°	326.2	326.6	327.1	327.3	326.9	326.0	325.1	324.2	323.3	322.9	322.5

TEST NUMBER: P1011047

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	374.4	374.4	374.4	374.4	373.9	372.8	371.7	370.6	369.5	369.5	369.5
115°	419.0	419.3	419.5	419.6	419.5	419.3	419.0	418.8	418.6	419.0	419.5
117.5°	465.2	465.8	466.5	466.8	466.8	466.8	466.8	466.8	466.8	467.2	467.7
120°	512.9	513.3	513.8	514.0	514.1	514.3	514.6	514.8	515.0	516.1	517.2
122.5°	559.5	560.1	560.8	561.1	561.4	562.1	562.8	563.4	564.1	564.5	565.0
125°	606.1	607.0	607.9	608.3	608.7	609.6	610.5	611.3	612.2	612.6	613.1
127.5°	652.3	653.2	654.1	654.5	655.2	656.5	657.8	659.1	660.4	660.8	661.3
130°	698.9	700.4	701.9	702.7	703.1	704.0	704.9	705.7	706.6	707.2	707.9
132.5°	745.1	746.2	747.3	747.9	748.4	749.5	750.6	751.7	752.8	753.2	753.6
135°	793.0	793.4	793.9	794.1	794.5	795.4	796.3	797.1	798.0	798.2	798.4
137.5°	836.6	837.3	838.0	838.3	838.8	839.9	841.0	842.1	843.2	842.5	841.9
140°	880.7	882.2	883.7	884.5	884.6	884.8	885.0	885.2	885.4	885.2	885.0
142.5°	923.0	924.1	925.2	925.7	925.8	926.0	926.3	926.5	926.7	926.3	925.9
145°	963.8	964.7	965.6	966.0	966.1	966.3	966.6	966.8	967.0	966.4	965.7
147.5°	1002.0	1003.3	1004.6	1005.3	1005.3	1005.3	1005.3	1005.3	1005.3	1004.7	1004.0
150°	1037.4	1038.7	1040.0	1040.7	1040.7	1040.7	1040.7	1040.7	1040.7	1040.3	1039.9
152.5°	1071.4	1072.5	1073.6	1074.1	1073.9	1073.5	1073.0	1072.6	1072.2	1072.0	1071.8
155°	1102.8	1104.3	1105.8	1106.6	1106.2	1105.3	1104.4	1103.5	1102.6	1102.4	1102.2
157.5°	1130.8	1132.1	1133.4	1134.1	1133.7	1132.8	1131.9	1131.0	1130.1	1129.9	1129.7
160°	1157.4	1158.3	1159.2	1159.6	1159.1	1158.0	1156.9	1155.8	1154.7	1154.7	1154.7
162.5°	1179.4	1180.9	1182.4	1183.2	1182.7	1181.6	1180.5	1179.4	1178.3	1178.1	1177.9
165°	1199.1	1200.6	1202.1	1202.9	1202.2	1200.9	1199.6	1198.3	1197.0	1197.0	1197.0
167.5°	1216.3	1217.6	1218.9	1219.6	1218.9	1217.6	1216.3	1215.0	1213.7	1213.5	1213.3
170°	1229.5	1231.0	1232.5	1233.3	1232.5	1231.0	1229.5	1228.0	1226.5	1226.5	1226.5
172.5°	1239.4	1240.9	1242.4	1243.2	1242.5	1241.2	1239.9	1238.6	1237.3	1237.3	1237.3
175°	1246.2	1247.7	1249.2	1250.0	1249.3	1248.0	1246.7	1245.4	1244.1	1244.1	1244.1
177.5°	1250.2	1251.7	1253.2	1254.0	1253.3	1252.0	1250.7	1249.4	1248.1	1248.1	1248.1
180°	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0

TEST NUMBER: P1011047

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3
2.5°	1425.9	1421.9	1421.9	1419.2	1411.1	1396.3	1395.0	1397.7	1389.6	1381.5	1369.4
5°	1495.9	1470.3	1462.2	1454.2	1438.0	1411.1	1400.4	1391.0	1376.2	1358.7	1339.8
7.5°	1555.1	1518.7	1508.0	1493.2	1460.9	1423.2	1399.0	1378.8	1358.7	1334.5	1311.6
10°	1629.1	1576.6	1551.0	1529.5	1485.1	1432.7	1396.3	1366.7	1334.5	1304.9	1275.3
12.5°	1712.5	1627.7	1619.6	1567.2	1516.1	1438.0	1393.6	1350.6	1307.5	1271.2	1240.3
15°	1782.4	1689.6	1656.0	1621.0	1522.8	1425.9	1382.9	1334.5	1284.7	1245.7	1199.9
17.5°	1826.8	1750.1	1678.8	1631.7	1529.5	1443.4	1360.0	1304.9	1252.4	1198.6	1160.9
20°	1880.6	1769.0	1707.1	1643.9	1543.0	1430.0	1346.6	1278.0	1213.4	1165.0	1119.2
22.5°	1934.4	1783.8	1732.6	1664.0	1545.7	1416.5	1322.3	1253.7	1179.8	1131.3	1081.6
25°	1929.0	1805.3	1720.5	1662.7	1518.7	1404.4	1294.1	1213.4	1144.8	1082.9	1033.1
27.5°	1933.1	1781.1	1695.0	1627.7	1499.9	1386.9	1264.5	1179.8	1108.5	1043.9	991.4
30°	1934.4	1744.7	1669.4	1588.7	1464.9	1345.2	1230.9	1144.8	1069.4	999.5	952.4
32.5°	1930.4	1715.2	1621.0	1548.3	1409.8	1304.9	1191.9	1100.4	1023.7	959.1	914.7
35°	1921.0	1680.2	1571.2	1479.7	1353.3	1247.0	1155.5	1061.4	979.3	920.1	869.0
37.5°	1895.4	1642.5	1518.7	1428.6	1287.4	1179.8	1099.0	1021.0	941.7	871.7	828.7
40°	1876.6	1591.4	1466.3	1368.1	1216.1	1111.1	1043.9	969.9	891.9	828.7	787.0
42.5°	1833.5	1543.0	1412.5	1295.4	1146.1	1038.5	975.3	916.1	848.8	787.0	749.3
45°	1763.6	1490.5	1346.6	1228.2	1069.4	967.2	909.4	860.9	801.7	742.6	704.9
47.5°	1665.4	1415.2	1276.6	1158.2	994.1	890.5	832.7	796.4	749.3	699.5	667.2
50°	1559.1	1333.1	1205.3	1088.3	921.5	820.6	764.1	730.5	699.5	653.8	622.8
52.5°	1420.5	1245.7	1123.3	1011.6	843.5	746.6	696.8	672.6	640.3	608.0	581.1
55°	1286.0	1132.7	1031.8	925.5	766.8	676.6	628.2	602.7	583.8	556.9	535.4
57.5°	1130.0	1027.7	934.9	838.1	695.5	613.4	567.7	536.7	524.6	512.5	492.3
60°	986.0	908.0	832.7	752.0	621.5	547.5	503.1	478.9	466.8	458.7	445.3
62.5°	854.2	793.7	729.1	664.5	546.2	478.9	445.3	421.1	410.3	408.9	396.8
65°	727.8	684.7	632.3	569.0	476.2	417.0	384.7	369.9	357.8	357.8	348.4
67.5°	601.3	571.7	530.0	485.6	413.0	357.8	328.2	314.8	308.1	308.1	301.3
70°	500.4	480.2	442.6	403.6	340.3	298.6	275.8	263.7	259.6	261.0	255.6
72.5°	406.3	384.7	353.8	325.5	278.5	247.5	231.4	217.9	211.2	212.5	211.2
75°	314.8	304.0	277.1	255.6	217.9	196.4	181.6	174.9	169.5	170.8	168.2
77.5°	236.8	220.6	205.8	191.0	168.2	150.7	138.6	131.8	127.8	127.8	127.8
80°	161.4	158.7	146.6	138.6	119.7	106.3	96.9	95.5	91.5	91.5	91.5
82.5°	104.9	98.2	91.5	86.1	75.3	67.3	63.2	60.5	59.2	57.8	60.5
85°	57.8	53.8	51.1	45.7	41.7	37.7	33.6	32.3	30.9	32.3	30.9
87.5°	22.9	18.8	18.8	17.5	16.1	14.8	14.8	12.1	12.1	10.8	10.8
90°	15.1	12.2	10.8	9.7	7.5	5.4	3.2	1.0	3.2	5.4	7.5
92.5°	37.4	36.1	35.4	34.7	33.4	32.1	30.8	29.5	30.8	32.1	33.4
95°	67.5	65.8	64.9	64.1	62.6	61.1	59.5	58.0	59.5	61.1	62.6
97.5°	102.2	100.9	100.2	99.7	98.6	97.5	96.4	95.3	96.4	97.5	98.6
100°	141.2	140.1	139.5	138.9	137.6	136.3	135.0	133.7	135.0	136.3	137.6
102.5°	183.1	181.6	180.8	180.5	179.8	179.2	178.5	177.9	178.5	179.2	179.8
105°	226.0	224.1	223.1	222.9	222.4	222.0	221.5	221.1	221.5	222.0	222.4
107.5°	274.5	273.6	273.2	273.1	272.9	272.6	272.4	272.2	272.4	272.6	272.9
110°	322.0	321.6	321.4	321.2	320.7	320.3	319.8	319.4	319.8	320.3	320.7

TEST NUMBER: P1011047

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	369.5	369.5	369.5	369.4	369.2	368.9	368.7	368.5	368.7	368.9	369.2
115°	419.9	420.4	420.6	420.3	419.6	419.0	418.3	417.7	418.3	419.0	419.6
117.5°	468.1	468.6	468.8	468.7	468.5	468.2	468.0	467.8	468.0	468.2	468.5
120°	518.3	519.4	519.9	519.2	517.9	516.6	515.3	514.0	515.3	516.6	517.9
122.5°	565.4	565.9	566.1	565.7	564.8	563.9	563.0	562.1	563.0	563.9	564.8
125°	613.5	614.0	614.2	613.9	613.2	612.6	611.9	611.3	611.9	612.6	613.2
127.5°	661.7	662.2	662.4	661.7	660.4	659.1	657.8	656.5	657.8	659.1	660.4
130°	708.5	709.2	709.5	708.6	706.9	705.2	703.4	701.7	703.4	705.2	706.9
132.5°	754.1	754.5	754.7	753.8	752.1	750.4	748.6	746.9	748.6	750.4	752.1
135°	798.7	798.9	799.0	798.3	797.0	795.7	794.4	793.1	794.4	795.7	797.0
137.5°	841.2	840.5	840.2	839.7	838.6	837.5	836.4	835.3	836.4	837.5	838.6
140°	884.8	884.6	884.5	883.9	882.8	881.7	880.6	879.5	880.6	881.7	882.8
142.5°	925.4	925.0	924.8	924.2	923.1	922.0	920.9	919.8	920.9	922.0	923.1
145°	965.1	964.4	964.1	963.9	963.4	963.0	962.5	962.1	962.5	963.0	963.4
147.5°	1003.4	1002.7	1002.4	1002.0	1001.1	1000.2	999.4	998.5	999.4	1000.2	1001.1
150°	1039.4	1039.0	1038.8	1038.6	1038.1	1037.7	1037.2	1036.8	1037.2	1037.7	1038.1
152.5°	1071.5	1071.3	1071.2	1070.9	1070.2	1069.5	1068.9	1068.2	1068.9	1069.5	1070.2
155°	1101.9	1101.7	1101.6	1101.6	1101.6	1101.6	1101.6	1101.6	1101.6	1101.6	1101.6
157.5°	1129.5	1129.3	1129.2	1129.3	1129.5	1129.7	1129.9	1130.1	1129.9	1129.7	1129.5
160°	1154.7	1154.7	1154.7	1154.9	1155.4	1155.8	1156.3	1156.7	1156.3	1155.8	1155.4
162.5°	1177.6	1177.4	1177.3	1177.6	1178.3	1179.0	1179.6	1180.3	1179.6	1179.0	1178.3
165°	1197.0	1197.0	1197.0	1197.3	1198.0	1198.6	1199.3	1199.9	1199.3	1198.6	1198.0
167.5°	1213.0	1212.8	1212.7	1213.1	1214.0	1214.9	1215.7	1216.6	1215.7	1214.9	1214.0
170°	1226.5	1226.5	1226.5	1226.9	1227.8	1228.7	1229.5	1230.4	1229.5	1228.7	1227.8
172.5°	1237.3	1237.3	1237.3	1237.7	1238.6	1239.5	1240.3	1241.2	1240.3	1239.5	1238.6
175°	1244.1	1244.1	1244.1	1244.5	1245.4	1246.3	1247.2	1248.1	1247.2	1246.3	1245.4
177.5°	1248.1	1248.1	1248.1	1248.5	1249.4	1250.3	1251.1	1252.0	1251.1	1250.3	1249.4
180°	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0

TEST NUMBER: P1011047

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3
2.5°	1366.7	1365.4	1368.1	1360.0	1346.6	1339.8	1321.0	1317.0	1315.6	1317.0	1318.3
5°	1329.1	1327.7	1323.7	1310.2	1294.1	1282.0	1259.1	1257.8	1249.7	1241.6	1245.7
7.5°	1292.8	1287.4	1279.3	1261.8	1240.3	1226.8	1208.0	1194.6	1183.8	1177.1	1171.7
10°	1256.4	1248.4	1240.3	1217.4	1190.5	1170.3	1147.5	1136.7	1124.6	1119.2	1113.8
12.5°	1209.3	1201.3	1186.5	1159.6	1143.4	1117.9	1095.0	1084.2	1077.5	1066.8	1060.0
15°	1171.7	1155.5	1147.5	1119.2	1085.6	1082.9	1041.2	1038.5	1025.1	1025.1	1014.3
17.5°	1128.6	1116.5	1101.7	1073.5	1049.3	1025.1	1003.5	995.5	983.4	980.7	975.3
20°	1086.9	1070.8	1065.4	1037.2	1011.6	982.0	959.1	951.1	945.7	940.3	944.3
22.5°	1043.9	1030.4	1017.0	991.4	972.6	943.0	929.5	921.5	913.4	910.7	912.1
25°	1002.2	990.1	976.6	951.1	930.9	906.7	894.6	890.5	886.5	886.5	885.2
27.5°	961.8	949.7	937.6	914.7	894.6	877.1	867.7	863.6	859.6	862.3	865.0
30°	920.1	909.4	898.6	878.4	862.3	846.1	840.8	838.1	836.7	843.5	843.5
32.5°	882.5	873.0	865.0	846.1	830.0	816.5	812.5	813.9	815.2	819.2	821.9
35°	843.5	836.7	828.7	812.5	799.1	787.0	788.3	788.3	791.0	797.7	803.1
37.5°	808.5	799.1	792.3	778.9	768.1	757.4	761.4	765.4	768.1	776.2	778.9
40°	766.8	762.7	757.4	743.9	734.5	733.1	734.5	737.2	742.6	746.6	750.6
42.5°	733.1	727.8	721.0	710.3	702.2	703.5	704.9	707.6	710.3	717.0	721.0
45°	695.5	691.4	686.1	676.6	669.9	671.3	672.6	672.6	675.3	683.4	686.1
47.5°	653.8	655.1	648.4	639.0	634.9	634.9	634.9	637.6	644.4	647.0	648.4
50°	613.4	610.7	609.4	600.0	597.3	595.9	597.3	598.6	608.0	606.7	610.7
52.5°	570.4	570.4	569.0	563.6	559.6	559.6	556.9	563.6	566.3	569.0	573.1
55°	528.7	524.6	523.3	520.6	515.2	513.9	516.6	524.6	527.3	530.0	534.1
57.5°	482.9	482.9	480.2	476.2	476.2	476.2	476.2	481.6	485.6	488.3	496.4
60°	441.2	435.8	431.8	431.8	431.8	430.5	438.5	438.5	446.6	448.0	450.6
62.5°	391.5	388.8	386.1	387.4	386.1	388.8	391.5	396.8	398.2	402.2	406.3
65°	344.4	344.4	341.7	349.8	344.4	344.4	351.1	351.1	353.8	357.8	363.2
67.5°	298.6	300.0	297.3	297.3	300.0	301.3	302.7	308.1	309.4	314.8	321.5
70°	251.6	254.2	255.6	252.9	255.6	258.3	261.0	262.3	267.7	270.4	274.4
72.5°	209.9	212.5	208.5	209.9	211.2	213.9	215.2	217.9	220.6	228.7	231.4
75°	168.2	166.8	165.5	170.8	168.2	173.5	174.9	174.9	177.6	184.3	187.0
77.5°	129.1	129.1	130.5	127.8	131.8	130.5	131.8	135.9	139.9	139.9	150.7
80°	90.1	92.8	92.8	92.8	94.2	95.5	92.8	99.5	100.9	100.9	104.9
82.5°	57.8	59.2	57.8	60.5	60.5	63.2	61.9	63.2	65.9	68.6	70.0
85°	30.9	30.9	33.6	33.6	32.3	33.6	32.3	33.6	36.3	36.3	37.7
87.5°	10.8	10.8	10.8	10.8	12.1	10.8	12.1	12.1	10.8	10.8	14.8
90°	9.7	10.8	12.2	15.1	17.9	20.8	23.6	24.5	25.3	26.2	27.1
92.5°	34.7	35.4	36.1	37.4	38.7	40.0	41.3	41.9	42.6	43.2	43.9
95°	64.1	64.9	65.8	67.5	69.2	71.0	72.7	73.6	74.5	75.4	76.3
97.5°	99.7	100.2	100.9	102.2	103.5	104.8	106.1	107.2	108.3	109.4	110.5
100°	138.9	139.5	140.1	141.2	142.3	143.4	144.5	145.1	145.8	146.4	147.1
102.5°	180.5	180.8	181.6	183.1	184.6	186.2	187.7	188.4	189.0	189.7	190.4
105°	222.9	223.1	224.1	226.0	228.0	229.9	231.9	231.9	231.9	231.9	231.9
107.5°	273.1	273.2	273.6	274.5	275.4	276.2	277.1	277.8	278.4	279.1	279.8
110°	321.2	321.4	321.6	322.0	322.5	322.9	323.3	324.2	325.1	326.0	326.9

TEST NUMBER: P1011047

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	369.4	369.5	369.5	369.5	369.5	369.5	369.5	370.6	371.7	372.8	373.9
115°	420.3	420.6	420.4	419.9	419.5	419.0	418.6	418.8	419.0	419.3	419.5
117.5°	468.7	468.8	468.6	468.1	467.7	467.2	466.8	466.8	466.8	466.8	466.8
120°	519.2	519.9	519.4	518.3	517.2	516.1	515.0	514.8	514.6	514.3	514.1
122.5°	565.7	566.1	565.9	565.4	565.0	564.5	564.1	563.4	562.8	562.1	561.4
125°	613.9	614.2	614.0	613.5	613.1	612.6	612.2	611.3	610.5	609.6	608.7
127.5°	661.7	662.4	662.2	661.7	661.3	660.8	660.4	659.1	657.8	656.5	655.2
130°	708.6	709.5	709.2	708.5	707.9	707.2	706.6	705.7	704.9	704.0	703.1
132.5°	753.8	754.7	754.5	754.1	753.6	753.2	752.8	751.7	750.6	749.5	748.4
135°	798.3	799.0	798.9	798.7	798.4	798.2	798.0	797.1	796.3	795.4	794.5
137.5°	839.7	840.2	840.5	841.2	841.9	842.5	843.2	842.1	841.0	839.9	838.8
140°	883.9	884.5	884.6	884.8	885.0	885.2	885.4	885.2	885.0	884.8	884.6
142.5°	924.2	924.8	925.0	925.4	925.9	926.3	926.7	926.5	926.3	926.0	925.8
145°	963.9	964.1	964.4	965.1	965.7	966.4	967.0	966.8	966.6	966.3	966.1
147.5°	1002.0	1002.4	1002.7	1003.4	1004.0	1004.7	1005.3	1005.3	1005.3	1005.3	1005.3
150°	1038.6	1038.8	1039.0	1039.4	1039.9	1040.3	1040.7	1040.7	1040.7	1040.7	1040.7
152.5°	1070.9	1071.2	1071.3	1071.5	1071.8	1072.0	1072.2	1072.6	1073.0	1073.5	1073.9
155°	1101.6	1101.6	1101.7	1101.9	1102.2	1102.4	1102.6	1103.5	1104.4	1105.3	1106.2
157.5°	1129.3	1129.2	1129.3	1129.5	1129.7	1129.9	1130.1	1131.0	1131.9	1132.8	1133.7
160°	1154.9	1154.7	1154.7	1154.7	1154.7	1154.7	1154.7	1155.8	1156.9	1158.0	1159.1
162.5°	1177.6	1177.3	1177.4	1177.6	1177.9	1178.1	1178.3	1179.4	1180.5	1181.6	1182.7
165°	1197.3	1197.0	1197.0	1197.0	1197.0	1197.0	1197.0	1198.3	1199.6	1200.9	1202.2
167.5°	1213.1	1212.7	1212.8	1213.0	1213.3	1213.5	1213.7	1215.0	1216.3	1217.6	1218.9
170°	1226.9	1226.5	1226.5	1226.5	1226.5	1226.5	1226.5	1228.0	1229.5	1231.0	1232.5
172.5°	1237.7	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1238.6	1239.9	1241.2	1242.5
175°	1244.5	1244.1	1244.1	1244.1	1244.1	1244.1	1244.1	1245.4	1246.7	1248.0	1249.3
177.5°	1248.5	1248.1	1248.1	1248.1	1248.1	1248.1	1248.1	1249.4	1250.7	1252.0	1253.3
180°	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0

TEST NUMBER: P1011047

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3
2.5°	1317.0	1318.3	1312.9	1308.9	1319.7	1312.9	1312.9	1314.3	1311.6	1315.6	1314.3
5°	1243.0	1244.3	1234.9	1237.6	1232.2	1230.9	1229.5	1237.6	1236.3	1234.9	1237.6
7.5°	1170.3	1170.3	1166.3	1163.6	1163.6	1159.6	1165.0	1163.6	1166.3	1166.3	1170.3
10°	1109.8	1112.5	1105.8	1099.0	1097.7	1099.0	1099.0	1100.4	1101.7	1111.1	1109.8
12.5°	1060.0	1056.0	1054.6	1050.6	1043.9	1041.2	1038.5	1053.3	1049.3	1049.3	1049.3
15°	1004.9	1014.3	1012.9	1000.8	998.2	1003.5	1000.8	1000.8	1014.3	1012.9	1011.6
17.5°	975.3	972.6	969.9	963.2	964.5	963.2	964.5	964.5	972.6	972.6	972.6
20°	941.7	936.3	936.3	933.6	933.6	929.5	934.9	936.3	941.7	941.7	943.0
22.5°	912.1	908.0	908.0	906.7	909.4	904.0	909.4	910.7	910.7	914.7	914.7
25°	886.5	883.8	883.8	886.5	886.5	886.5	886.5	891.9	887.8	889.2	887.8
27.5°	863.6	865.0	866.3	867.7	866.3	867.7	869.0	871.7	873.0	871.7	869.0
30°	842.1	846.1	847.5	847.5	850.2	851.5	852.9	852.9	854.2	850.2	852.9
32.5°	826.0	826.0	828.7	830.0	832.7	834.0	834.0	836.7	835.4	831.3	832.7
35°	803.1	803.1	808.5	811.2	815.2	813.9	815.2	815.2	816.5	813.9	809.8
37.5°	780.2	782.9	782.9	788.3	789.6	791.0	789.6	792.3	791.0	788.3	787.0
40°	753.3	752.0	753.3	757.4	758.7	758.7	758.7	761.4	761.4	761.4	760.0
42.5°	719.7	723.7	722.4	726.4	725.1	725.1	727.8	730.5	731.8	727.8	729.1
45°	687.4	687.4	690.1	690.1	691.4	691.4	696.8	694.1	696.8	694.1	695.5
47.5°	652.4	653.8	653.8	655.1	657.8	660.5	657.8	659.2	659.2	660.5	657.8
50°	613.4	613.4	616.1	620.1	625.5	622.8	621.5	626.9	622.8	622.8	620.1
52.5°	573.1	577.1	578.4	582.5	586.5	587.9	589.2	586.5	587.9	583.8	585.2
55°	534.1	535.4	540.8	544.8	548.8	548.8	547.5	548.8	550.2	544.8	544.8
57.5°	495.0	499.1	504.5	504.5	509.8	509.8	508.5	508.5	509.8	505.8	504.5
60°	453.3	457.4	464.1	464.1	472.2	473.5	470.8	468.1	468.1	464.1	465.4
62.5°	408.9	413.0	417.0	423.7	429.1	426.4	431.8	426.4	427.8	419.7	419.7
65°	369.9	371.3	378.0	384.7	384.7	387.4	384.7	386.1	382.0	382.0	376.7
67.5°	324.2	324.2	330.9	337.6	344.4	344.4	344.4	340.3	340.3	336.3	336.3
70°	283.8	282.5	289.2	293.3	297.3	298.6	295.9	294.6	291.9	287.9	286.5
72.5°	234.1	236.8	243.5	246.2	252.9	251.6	258.3	250.2	250.2	243.5	242.1
75°	189.7	192.4	199.1	203.1	207.2	207.2	211.2	207.2	201.8	199.1	197.7
77.5°	150.7	149.3	154.7	161.4	162.8	161.4	164.1	162.8	157.4	157.4	154.7
80°	107.6	111.7	117.0	115.7	121.1	119.7	119.7	117.0	117.0	113.0	115.7
82.5°	71.3	75.3	76.7	75.3	76.7	79.4	80.7	79.4	79.4	76.7	78.0
85°	37.7	37.7	40.4	41.7	40.4	40.4	41.7	45.7	43.0	40.4	43.0
87.5°	12.1	10.8	10.8	12.1	10.8	10.8	12.1	12.1	13.5	13.5	13.5
90°	27.5	27.7	28.2	28.6	29.1	29.5	29.1	28.6	28.2	27.7	27.5
92.5°	44.2	44.0	43.6	43.1	42.7	42.3	42.7	43.1	43.6	44.0	44.2
95°	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7
97.5°	111.0	110.9	110.7	110.5	110.3	110.1	110.3	110.5	110.7	110.9	111.0
100°	147.4	147.6	148.1	148.5	149.0	149.4	149.0	148.5	148.1	147.6	147.4
102.5°	190.7	190.6	190.4	190.1	189.9	189.7	189.9	190.1	190.4	190.6	190.7
105°	231.9	232.1	232.6	233.0	233.5	233.9	233.5	233.0	232.6	232.1	231.9
107.5°	280.1	280.0	279.8	279.5	279.3	279.1	279.3	279.5	279.8	280.0	280.1
110°	327.3	327.1	326.6	326.2	325.7	325.3	325.7	326.2	326.6	327.1	327.3

TEST NUMBER: P1011047

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	374.4	374.4	374.4	374.4	374.4	374.4	374.4	374.4	374.4	374.4	374.4
115°	419.6	419.5	419.3	419.0	418.8	418.6	418.8	419.0	419.3	419.5	419.6
117.5°	466.8	466.5	465.8	465.2	464.5	463.9	464.5	465.2	465.8	466.5	466.8
120°	514.0	513.8	513.3	512.9	512.4	512.0	512.4	512.9	513.3	513.8	514.0
122.5°	561.1	560.8	560.1	559.5	558.8	558.2	558.8	559.5	560.1	560.8	561.1
125°	608.3	607.9	607.0	606.1	605.3	604.4	605.3	606.1	607.0	607.9	608.3
127.5°	654.5	654.1	653.2	652.3	651.5	650.6	651.5	652.3	653.2	654.1	654.5
130°	702.7	701.9	700.4	698.9	697.3	695.8	697.3	698.9	700.4	701.9	702.7
132.5°	747.9	747.3	746.2	745.1	744.0	742.9	744.0	745.1	746.2	747.3	747.9
135°	794.1	793.9	793.4	793.0	792.5	792.1	792.5	793.0	793.4	793.9	794.1
137.5°	838.3	838.0	837.3	836.6	836.0	835.3	836.0	836.6	837.3	838.0	838.3
140°	884.5	883.7	882.2	880.7	879.1	877.6	879.1	880.7	882.2	883.7	884.5
142.5°	925.7	925.2	924.1	923.0	921.9	920.8	921.9	923.0	924.1	925.2	925.7
145°	966.0	965.6	964.7	963.8	963.0	962.1	963.0	963.8	964.7	965.6	966.0
147.5°	1005.3	1004.6	1003.3	1002.0	1000.7	999.4	1000.7	1002.0	1003.3	1004.6	1005.3
150°	1040.7	1040.0	1038.7	1037.4	1036.1	1034.8	1036.1	1037.4	1038.7	1040.0	1040.7
152.5°	1074.1	1073.6	1072.5	1071.4	1070.3	1069.2	1070.3	1071.4	1072.5	1073.6	1074.1
155°	1106.6	1105.8	1104.3	1102.8	1101.2	1099.7	1101.2	1102.8	1104.3	1105.8	1106.6
157.5°	1134.1	1133.4	1132.1	1130.8	1129.5	1128.2	1129.5	1130.8	1132.1	1133.4	1134.1
160°	1159.6	1159.2	1158.3	1157.4	1156.6	1155.7	1156.6	1157.4	1158.3	1159.2	1159.6
162.5°	1183.2	1182.4	1180.9	1179.4	1177.8	1176.3	1177.8	1179.4	1180.9	1182.4	1183.2
165°	1202.9	1202.1	1200.6	1199.1	1197.5	1196.0	1197.5	1199.1	1200.6	1202.1	1202.9
167.5°	1219.6	1218.9	1217.6	1216.3	1215.0	1213.7	1215.0	1216.3	1217.6	1218.9	1219.6
170°	1233.3	1232.5	1231.0	1229.5	1228.0	1226.5	1228.0	1229.5	1231.0	1232.5	1233.3
172.5°	1243.2	1242.4	1240.9	1239.4	1237.8	1236.3	1237.8	1239.4	1240.9	1242.4	1243.2
175°	1250.0	1249.2	1247.7	1246.2	1244.7	1243.2	1244.7	1246.2	1247.7	1249.2	1250.0
177.5°	1254.0	1253.2	1251.7	1250.2	1248.6	1247.1	1248.6	1250.2	1251.7	1253.2	1254.0
180°	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0

TEST NUMBER: P1011047

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3
2.5°	1318.3	1321.0	1322.3	1317.0	1312.9	1319.7	1329.1	1335.8	1341.2	1347.9	1351.9
5°	1240.3	1249.7	1249.7	1252.4	1256.4	1263.2	1280.6	1292.8	1303.5	1311.6	1318.3
7.5°	1174.4	1181.1	1185.1	1191.9	1198.6	1208.0	1228.2	1245.7	1261.8	1271.2	1282.0
10°	1115.2	1120.6	1127.3	1131.3	1143.4	1156.9	1182.4	1197.2	1216.1	1230.9	1244.3
12.5°	1058.7	1077.5	1081.6	1080.2	1091.0	1105.8	1131.3	1154.2	1174.4	1189.2	1204.0
15°	1018.3	1025.1	1033.1	1031.8	1054.6	1058.7	1080.2	1107.1	1134.0	1143.4	1156.9
17.5°	973.9	984.7	992.8	996.8	1003.5	1018.3	1038.5	1058.7	1093.7	1095.0	1130.0
20°	939.0	949.7	955.1	960.5	964.5	982.0	999.5	1022.4	1050.6	1065.4	1084.2
22.5°	916.1	921.5	925.5	929.5	934.9	944.3	965.9	991.4	1010.3	1026.4	1038.5
25°	889.2	894.6	899.9	902.6	906.7	912.1	928.2	948.4	975.3	986.0	998.2
27.5°	870.4	870.4	873.0	873.0	878.4	883.8	895.9	914.7	936.3	949.7	965.9
30°	850.2	848.8	850.2	848.8	847.5	855.6	866.3	882.5	897.3	913.4	924.2
32.5°	830.0	828.7	828.7	830.0	824.6	828.7	834.0	848.8	865.0	873.0	885.2
35°	808.5	805.8	805.8	805.8	803.1	800.4	805.8	819.2	830.0	840.8	850.2
37.5°	787.0	782.9	782.9	780.2	777.5	773.5	773.5	784.3	799.1	803.1	815.2
40°	757.4	757.4	754.7	753.3	750.6	747.9	743.9	753.3	766.8	770.8	780.2
42.5°	727.8	723.7	722.4	722.4	722.4	718.3	715.7	722.4	730.5	737.2	742.6
45°	694.1	691.4	692.8	691.4	688.8	687.4	686.1	688.8	698.2	700.9	707.6
47.5°	657.8	656.5	656.5	655.1	653.8	655.1	649.7	656.5	659.2	661.8	667.2
50°	620.1	618.8	617.5	616.1	616.1	617.5	616.1	616.1	621.5	624.2	629.6
52.5°	582.5	578.4	578.4	577.1	577.1	574.4	577.1	578.4	581.1	583.8	586.5
55°	542.1	542.1	538.1	538.1	535.4	535.4	536.7	535.4	540.8	543.5	543.5
57.5°	503.1	497.7	499.1	496.4	493.7	492.3	492.3	495.0	497.7	497.7	500.4
60°	461.4	456.0	454.7	449.3	452.0	448.0	449.3	449.3	454.7	452.0	454.7
62.5°	419.7	413.0	408.9	406.3	406.3	407.6	404.9	403.6	406.3	408.9	414.3
65°	375.3	371.3	367.2	363.2	363.2	361.9	364.6	360.5	359.2	360.5	363.2
67.5°	329.6	325.5	321.5	317.5	318.8	314.8	312.1	316.1	313.4	314.8	317.5
70°	285.2	282.5	274.4	271.7	270.4	271.7	270.4	267.7	271.7	270.4	271.7
72.5°	240.8	238.1	234.1	227.3	227.3	226.0	224.7	224.7	223.3	223.3	223.3
75°	197.7	192.4	188.3	187.0	184.3	182.9	181.6	178.9	180.3	181.6	178.9
77.5°	153.4	146.6	145.3	145.3	141.2	141.2	142.6	141.2	139.9	139.9	139.9
80°	113.0	107.6	107.6	104.9	102.2	102.2	102.2	102.2	100.9	99.5	100.9
82.5°	72.6	71.3	70.0	70.0	72.6	67.3	70.0	68.6	67.3	67.3	65.9
85°	40.4	41.7	40.4	41.7	39.0	40.4	40.4	40.4	39.0	40.4	37.7
87.5°	14.8	14.8	14.8	16.1	16.1	16.1	16.1	16.1	17.5	16.1	16.1
90°	27.1	26.2	25.3	24.5	23.6	20.8	17.9	15.1	12.2	10.8	9.7
92.5°	43.9	43.2	42.6	41.9	41.3	40.0	38.7	37.4	36.1	35.4	34.7
95°	76.3	75.4	74.5	73.6	72.7	71.0	69.2	67.5	65.8	64.9	64.1
97.5°	110.5	109.4	108.3	107.2	106.1	104.8	103.5	102.2	100.9	100.2	99.7
100°	147.1	146.4	145.8	145.1	144.5	143.4	142.3	141.2	140.1	139.5	138.9
102.5°	190.4	189.7	189.0	188.4	187.7	186.2	184.6	183.1	181.6	180.8	180.5
105°	231.9	231.9	231.9	231.9	231.9	229.9	228.0	226.0	224.1	223.1	222.9
107.5°	279.8	279.1	278.4	277.8	277.1	276.2	275.4	274.5	273.6	273.2	273.1
110°	326.9	326.0	325.1	324.2	323.3	322.9	322.5	322.0	321.6	321.4	321.2

TEST NUMBER: P1011047

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	373.9	372.8	371.7	370.6	369.5	369.5	369.5	369.5	369.5	369.5	369.4
115°	419.5	419.3	419.0	418.8	418.6	419.0	419.5	419.9	420.4	420.6	420.3
117.5°	466.8	466.8	466.8	466.8	466.8	467.2	467.7	468.1	468.6	468.8	468.7
120°	514.1	514.3	514.6	514.8	515.0	516.1	517.2	518.3	519.4	519.9	519.2
122.5°	561.4	562.1	562.8	563.4	564.1	564.5	565.0	565.4	565.9	566.1	565.7
125°	608.7	609.6	610.5	611.3	612.2	612.6	613.1	613.5	614.0	614.2	613.9
127.5°	655.2	656.5	657.8	659.1	660.4	660.8	661.3	661.7	662.2	662.4	661.7
130°	703.1	704.0	704.9	705.7	706.6	707.2	707.9	708.5	709.2	709.5	708.6
132.5°	748.4	749.5	750.6	751.7	752.8	753.2	753.6	754.1	754.5	754.7	753.8
135°	794.5	795.4	796.3	797.1	798.0	798.2	798.4	798.7	798.9	799.0	798.3
137.5°	838.8	839.9	841.0	842.1	843.2	842.5	841.9	841.2	840.5	840.2	839.7
140°	884.6	884.8	885.0	885.2	885.4	885.2	885.0	884.8	884.6	884.5	883.9
142.5°	925.8	926.0	926.3	926.5	926.7	926.3	925.9	925.4	925.0	924.8	924.2
145°	966.1	966.3	966.6	966.8	967.0	966.4	965.7	965.1	964.4	964.1	963.9
147.5°	1005.3	1005.3	1005.3	1005.3	1005.3	1004.7	1004.0	1003.4	1002.7	1002.4	1002.0
150°	1040.7	1040.7	1040.7	1040.7	1040.7	1040.3	1039.9	1039.4	1039.0	1038.8	1038.6
152.5°	1073.9	1073.5	1073.0	1072.6	1072.2	1072.0	1071.8	1071.5	1071.3	1071.2	1070.9
155°	1106.2	1105.3	1104.4	1103.5	1102.6	1102.4	1102.2	1101.9	1101.7	1101.6	1101.6
157.5°	1133.7	1132.8	1131.9	1131.0	1130.1	1129.9	1129.7	1129.5	1129.3	1129.2	1129.3
160°	1159.1	1158.0	1156.9	1155.8	1154.7	1154.7	1154.7	1154.7	1154.7	1154.7	1154.9
162.5°	1182.7	1181.6	1180.5	1179.4	1178.3	1178.1	1177.9	1177.6	1177.4	1177.3	1177.6
165°	1202.2	1200.9	1199.6	1198.3	1197.0	1197.0	1197.0	1197.0	1197.0	1197.0	1197.3
167.5°	1218.9	1217.6	1216.3	1215.0	1213.7	1213.5	1213.3	1213.0	1212.8	1212.7	1213.1
170°	1232.5	1231.0	1229.5	1228.0	1226.5	1226.5	1226.5	1226.5	1226.5	1226.5	1226.9
172.5°	1242.5	1241.2	1239.9	1238.6	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.7
175°	1249.3	1248.0	1246.7	1245.4	1244.1	1244.1	1244.1	1244.1	1244.1	1244.1	1244.5
177.5°	1253.3	1252.0	1250.7	1249.4	1248.1	1248.1	1248.1	1248.1	1248.1	1248.1	1248.5
180°	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0	1251.0

TEST NUMBER: P1011047

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1388.3	1388.3	1388.3	1388.3
2.5°	1358.7	1362.7	1376.2	1392.3
5°	1331.8	1342.5	1361.4	1386.9
7.5°	1302.2	1318.3	1345.2	1377.5
10°	1268.5	1291.4	1325.0	1365.4
12.5°	1232.2	1261.8	1304.9	1346.6
15°	1209.3	1238.9	1278.0	1323.7
17.5°	1165.0	1199.9	1240.3	1304.9
20°	1119.2	1158.2	1210.7	1275.3
22.5°	1084.2	1125.9	1175.7	1244.3
25°	1042.5	1085.6	1139.4	1210.7
27.5°	998.2	1041.2	1101.7	1177.1
30°	964.5	1006.2	1064.1	1144.8
32.5°	924.2	964.5	1025.1	1109.8
35°	878.4	924.2	982.0	1068.1
37.5°	843.5	885.2	945.7	1027.7
40°	805.8	842.1	901.3	982.0
42.5°	765.4	805.8	856.9	937.6
45°	727.8	757.4	809.8	886.5
47.5°	687.4	721.0	761.4	820.6
50°	644.4	672.6	717.0	757.4
52.5°	602.7	625.5	663.2	694.1
55°	558.3	581.1	609.4	628.2
57.5°	516.6	532.7	551.5	563.6
60°	465.4	481.6	493.7	505.8
62.5°	419.7	431.8	438.5	445.3
65°	372.6	379.4	383.4	388.8
67.5°	321.5	328.2	329.6	337.6
70°	274.4	275.8	278.5	282.5
72.5°	230.0	232.7	231.4	234.1
75°	184.3	187.0	184.3	187.0
77.5°	139.9	142.6	142.6	146.6
80°	100.9	102.2	103.6	103.6
82.5°	65.9	70.0	67.3	68.6
85°	37.7	39.0	39.0	40.4
87.5°	17.5	18.8	17.5	20.2
90°	7.5	5.4	3.2	1.0
92.5°	33.4	32.1	30.8	29.5
95°	62.6	61.1	59.5	58.0
97.5°	98.6	97.5	96.4	95.3
100°	137.6	136.3	135.0	133.7
102.5°	179.8	179.2	178.5	177.9
105°	222.4	222.0	221.5	221.1
107.5°	272.9	272.6	272.4	272.2
110°	320.7	320.3	319.8	319.4

TEST NUMBER: P1011047

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	369.2	368.9	368.7	368.5
115°	419.6	419.0	418.3	417.7
117.5°	468.5	468.2	468.0	467.8
120°	517.9	516.6	515.3	514.0
122.5°	564.8	563.9	563.0	562.1
125°	613.2	612.6	611.9	611.3
127.5°	660.4	659.1	657.8	656.5
130°	706.9	705.2	703.4	701.7
132.5°	752.1	750.4	748.6	746.9
135°	797.0	795.7	794.4	793.1
137.5°	838.6	837.5	836.4	835.3
140°	882.8	881.7	880.6	879.5
142.5°	923.1	922.0	920.9	919.8
145°	963.4	963.0	962.5	962.1
147.5°	1001.1	1000.2	999.4	998.5
150°	1038.1	1037.7	1037.2	1036.8
152.5°	1070.2	1069.5	1068.9	1068.2
155°	1101.6	1101.6	1101.6	1101.6
157.5°	1129.5	1129.7	1129.9	1130.1
160°	1155.4	1155.8	1156.3	1156.7
162.5°	1178.3	1179.0	1179.6	1180.3
165°	1198.0	1198.6	1199.3	1199.9
167.5°	1214.0	1214.9	1215.7	1216.6
170°	1227.8	1228.7	1229.5	1230.4
172.5°	1238.6	1239.5	1240.3	1241.2
175°	1245.4	1246.3	1247.2	1248.1
177.5°	1249.4	1250.3	1251.1	1252.0
180°	1251.0	1251.0	1251.0	1251.0

(END OF REPORT)