

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011053

Luminaire Tested: S123DIP-B1000D1025UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011053
REPORT IS A COMBINATION OF REPORTS P989068 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D1025UB40-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7541.0 lumens
Efficiency: N/A
Efficacy: 100.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011053

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1011053

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60
1	99	94	90	87	91	88	84	81	75	72	70	63	62	60	53	52	50
2	90	82	76	71	83	76	71	66	66	62	58	56	53	50	46	44	42
3	82	72	65	59	76	67	61	56	58	53	49	49	45	42	41	38	36
4	75	64	56	50	69	60	53	47	51	46	42	44	40	36	37	34	31
5	69	57	49	43	64	53	46	40	46	40	36	39	35	31	33	30	27
6	63	51	43	37	59	48	40	35	41	36	31	36	31	28	30	27	24
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19
9	51	38	31	26	47	36	29	24	31	26	22	27	23	20	23	20	17
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16841	16841	16841
5°	16884	16260	16236
10°	16733	15710	15549
15°	16500	15138	14799
20°	16234	14502	14058
25°	15889	13832	13264
30°	15511	13138	12430
35°	15115	12429	11601
40°	14701	11685	10784
45°	14245	10959	9933
50°	13783	10151	9078
55°	13187	9310	8211
60°	12575	8380	7288
65°	12000	7375	6326
70°	11173	6261	5204
75°	9978	4958	4041
80°	8616	3484	2858
85°	6724	1874	1432

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14245 cd/sqm

TEST NUMBER: P1011053

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.5	2.0
10°-20°	416.5	5.5
20°-30°	615.1	8.2
30°-40°	718.4	9.5
40°-50°	722.2	9.6
50°-60°	634.4	8.4
60°-70°	472.5	6.3
70°-80°	268.9	3.6
80°-90°	79.1	1.0
90°-100°	80.5	1.1
100°-110°	243.7	3.2
110°-120°	415.0	5.5
120°-130°	545.9	7.2
130°-140°	613.6	8.1
140°-150°	603.2	8.0
150°-160°	507.9	6.7
160°-170°	338.1	4.5
170°-180°	118.4	1.6
0°-30°	1179.1	15.6
0°-40°	1897.5	25.2
0°-60°	3254.2	43.2
0°-90°	4074.6	54.0
90°-120°	739.2	9.8
90°-150°	2502.0	33.2
90°-180°	3466.0	46.0
0°-180°	7541.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1565	1565	1565	1565	1565	
5°	1566	1559	1544	1558	1555	149
15°	1491	1485	1468	1478	1470	420
25°	1353	1345	1328	1329	1325	623
35°	1170	1162	1145	1137	1130	732
45°	959	954	936	920	914	741
55°	728	726	709	694	688	652
65°	496	490	476	466	461	490
75°	262	257	253	246	242	280
85°	70	67	67	65	65	75
90°	1	11	24	28	30	9
95°	58	65	73	77	77	64
105°	221	223	232	232	234	237
115°	418	421	419	420	419	413
125°	611	614	612	608	604	545
135°	793	799	798	794	792	611
145°	962	964	967	966	962	601
155°	1102	1102	1103	1107	1100	507
165°	1200	1197	1197	1203	1196	338
175°	1248	1244	1244	1250	1243	119
180°	1251	1251	1251	1251	1251	



TEST NUMBER: P1011053

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1564.6	1564.6	1564.6	1564.6	1564.6
2.5°	1571.3	1566.0	1551.2	1564.6	1563.3
5°	1566.0	1559.2	1544.4	1557.9	1555.2
7.5°	1553.9	1547.1	1532.3	1544.4	1543.1
10°	1537.7	1531.0	1513.5	1525.6	1522.9
12.5°	1516.2	1510.8	1494.7	1502.7	1501.4
15°	1490.6	1485.2	1467.8	1478.5	1470.4
17.5°	1462.4	1455.6	1438.2	1446.2	1443.5
20°	1430.1	1422.0	1404.5	1409.9	1405.9
22.5°	1393.8	1385.7	1368.2	1372.2	1366.9
25°	1353.4	1345.3	1327.8	1329.2	1325.1
27.5°	1311.7	1303.6	1284.8	1286.1	1282.1
30°	1266.0	1259.2	1240.4	1240.4	1231.0
32.5°	1220.2	1210.8	1197.3	1187.9	1183.9
35°	1170.4	1162.4	1144.9	1136.8	1130.1
37.5°	1120.7	1109.9	1092.4	1083.0	1079.0
40°	1068.2	1060.1	1041.3	1030.5	1025.1
42.5°	1015.7	1006.3	987.5	976.7	971.3
45°	959.2	953.8	936.3	920.2	913.5
47.5°	904.1	896.0	879.8	863.7	858.3
50°	847.6	840.8	823.3	808.5	800.5
52.5°	788.4	784.3	765.5	753.4	745.3
55°	727.8	726.5	709.0	694.2	687.5
57.5°	671.3	665.9	652.5	639.0	631.0
60°	609.4	608.1	591.9	579.8	573.1
62.5°	554.3	550.2	534.1	522.0	518.0
65°	496.4	489.7	476.2	465.5	461.4
67.5°	434.5	429.2	418.4	409.0	403.6
70°	379.4	371.3	363.2	353.8	347.1
72.5°	321.5	316.2	306.7	298.7	296.0
75°	262.3	257.0	252.9	246.2	242.2
77.5°	209.9	207.2	201.8	196.4	196.4
80°	158.7	154.7	152.0	150.7	150.7
82.5°	109.0	109.0	109.0	106.3	104.9
85°	70.0	67.3	67.3	64.6	64.6
87.5°	35.0	30.9	29.6	28.3	28.3
90°	1.0	10.8	23.6	27.5	29.5
92.5°	29.5	35.4	41.3	44.2	42.3
95°	58.0	64.9	72.7	76.7	76.7
97.5°	95.3	100.2	106.1	111.0	110.1
100°	133.7	139.5	144.5	147.4	149.4
102.5°	177.9	180.8	187.7	190.7	189.7
105°	221.1	223.1	231.9	231.9	233.9
107.5°	272.2	273.2	277.1	280.1	279.1
110°	319.4	321.4	323.3	327.3	325.3

TEST NUMBER: P1011053

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	368.5	369.5	369.5	374.4	374.4
115°	417.7	420.6	418.6	419.6	418.6
117.5°	467.8	468.8	466.8	466.8	463.9
120°	514.0	519.9	515.0	514.0	512.0
122.5°	562.1	566.1	564.1	561.1	558.2
125°	611.3	614.2	612.2	608.3	604.4
127.5°	656.5	662.4	660.4	654.5	650.6
130°	701.7	709.5	706.6	702.7	695.8
132.5°	746.9	754.7	752.8	747.9	742.9
135°	793.1	799.0	798.0	794.1	792.1
137.5°	835.3	840.2	843.2	838.3	835.3
140°	879.5	884.5	885.4	884.5	877.6
142.5°	919.8	924.8	926.7	925.7	920.8
145°	962.1	964.1	967.0	966.0	962.1
147.5°	998.5	1002.4	1005.3	1005.3	999.4
150°	1036.8	1038.8	1040.7	1040.7	1034.8
152.5°	1068.2	1071.2	1072.2	1074.1	1069.2
155°	1101.6	1101.6	1102.6	1106.6	1099.7
157.5°	1130.1	1129.2	1130.1	1134.1	1128.2
160°	1156.7	1154.7	1154.7	1159.6	1155.7
162.5°	1180.3	1177.3	1178.3	1183.2	1176.3
165°	1199.9	1197.0	1197.0	1202.9	1196.0
167.5°	1216.6	1212.7	1213.7	1219.6	1213.7
170°	1230.4	1226.5	1226.5	1233.3	1226.5
172.5°	1241.2	1237.3	1237.3	1243.2	1236.3
175°	1248.1	1244.1	1244.1	1250.0	1243.2
177.5°	1252.0	1248.1	1248.1	1254.0	1247.1
180°	1251.0	1251.0	1251.0	1251.0	1251.0

(END OF REPORT)