

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010745

Luminaire Tested: S123DIP-B775D585UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010745
REPORT IS A COMBINATION OF REPORTS P990414 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D585UB2750-4F0-XX-W2A-D_3000K
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5594.0 lumens
Efficiency: N/A
Efficacy: 109.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010745

CATALOG NUMBER: S123DIP-B775D585UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010745

CATALOG NUMBER: S123DIP-B775D585UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	97	93	88	84	90	86	82	79	73	70	68	61	59	57	50	49	48
2	88	80	74	68	81	74	69	64	63	59	55	53	50	47	44	41	39
3	80	70	62	56	74	65	58	53	55	50	46	47	43	39	38	35	33
4	73	62	54	47	67	57	50	44	49	43	39	41	37	33	34	31	28
5	67	55	46	40	62	51	44	38	44	38	33	37	32	29	31	27	24
6	62	49	41	35	57	46	38	33	39	33	29	33	29	25	28	24	21
7	57	44	36	30	53	41	34	29	36	30	25	30	26	22	25	22	19
8	53	40	32	27	49	38	30	25	32	27	22	28	23	20	23	20	17
9	49	37	29	24	46	34	27	23	30	24	20	25	21	18	21	18	15
10	46	34	26	21	43	32	25	20	27	22	18	24	19	16	20	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10399	10399	10399
5°	10428	10094	10086
10°	10330	9820	9746
15°	10194	9519	9385
20°	9999	9182	8997
25°	9760	8803	8596
30°	9516	8460	8193
35°	9243	8101	7865
40°	8980	7771	7518
45°	8691	7453	7232
50°	8404	7136	6922
55°	8085	6814	6637
60°	7775	6482	6345
65°	7455	6129	6002
70°	6973	5733	5650
75°	6364	5281	5285
80°	5657	4825	4870
85°	4956	4456	4573

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8691 cd/sqm

TEST NUMBER: P1010745

CATALOG NUMBER: S123DIP-B775D585UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.6	1.6
10°-20°	261.3	4.7
20°-30°	390.7	7.0
30°-40°	466.5	8.3
40°-50°	488.1	8.7
50°-60°	458.0	8.2
60°-70°	382.6	6.8
70°-80°	273.6	4.9
80°-90°	164.3	2.9
90°-100°	129.4	2.3
100°-110°	206.4	3.7
110°-120°	371.6	6.6
120°-130°	436.7	7.8
130°-140°	448.8	8.0
140°-150°	410.3	7.3
150°-160°	328.8	5.9
160°-170°	212.2	3.8
170°-180°	73.1	1.3
0°-30°	743.6	13.3
0°-40°	1210.1	21.6
0°-60°	2156.2	38.5
0°-90°	2976.7	53.2
90°-120°	707.4	12.6
90°-150°	2003.2	35.8
90°-180°	2617.0	46.8
0°-180°	5594.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	966	966	966	966	966	
5°	967	965	959	967	966	92
15°	921	924	923	934	932	259
25°	831	842	845	859	859	383
35°	716	732	746	762	766	448
45°	585	610	637	657	665	451
55°	446	481	519	547	556	400
65°	308	349	396	427	438	305
75°	167	217	269	304	317	179
85°	52	104	160	196	206	53
90°	14	72	133	171	182	12
95°	46	64	122	158	169	51
105°	179	210	204	132	143	189
115°	325	341	384	415	426	321
125°	454	458	491	514	523	406
135°	563	565	579	600	603	433
145°	648	651	652	662	666	406
155°	713	712	712	715	712	328
165°	752	750	749	754	750	212
175°	769	766	767	771	766	73
180°	769	769	769	769	769	

TEST NUMBER: P1010745

CATALOG NUMBER: S123DIP-B775D585UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	966.1	966.1	966.1	966.1	966.1
2.5°	971.4	968.2	959.8	968.2	967.2
5°	967.2	965.1	958.8	967.2	966.1
7.5°	959.8	959.8	953.5	964.0	963.0
10°	949.3	951.4	946.1	956.7	954.6
12.5°	936.7	939.8	936.7	946.1	944.0
15°	920.9	924.0	923.0	933.5	932.5
17.5°	901.9	908.3	907.2	916.7	914.6
20°	880.9	887.2	889.3	898.8	899.8
22.5°	858.8	865.1	868.3	880.9	879.8
25°	831.4	842.0	845.1	858.8	858.8
27.5°	805.1	816.7	823.0	834.6	835.6
30°	776.7	790.4	798.8	811.4	811.4
32.5°	745.1	760.9	772.5	786.2	789.3
35°	715.7	732.5	746.2	762.0	766.2
37.5°	684.1	703.0	718.8	736.7	739.9
40°	652.5	671.5	692.5	710.4	714.6
42.5°	617.8	642.0	664.1	684.1	690.4
45°	585.2	610.4	636.7	656.7	665.1
47.5°	550.4	578.8	608.3	630.4	636.7
50°	516.8	546.2	578.8	603.1	610.4
52.5°	481.0	512.5	549.4	574.6	584.1
55°	446.2	481.0	518.9	547.3	555.7
57.5°	412.6	448.3	489.4	517.8	527.3
60°	376.8	414.7	457.8	487.3	498.9
62.5°	343.1	382.0	428.3	457.8	468.3
65°	308.4	349.4	395.7	427.3	437.8
67.5°	273.6	316.8	363.1	397.8	406.2
70°	236.8	282.1	332.6	366.3	376.8
72.5°	203.1	248.4	301.0	335.7	346.3
75°	167.3	216.8	269.4	304.2	316.8
77.5°	136.8	186.3	238.9	275.7	285.2
80°	104.2	155.8	210.5	246.3	256.8
82.5°	75.8	128.4	184.2	220.0	230.5
85°	51.6	104.2	160.0	195.8	206.3
87.5°	31.6	84.2	137.9	173.7	184.2
90°	14.3	71.6	132.6	170.7	182.3
92.5°	25.7	67.6	125.4	164.1	174.1
95°	46.5	64.0	121.9	158.5	169.0
97.5°	73.9	95.8	116.2	152.4	163.4
100°	106.1	151.2	110.5	145.5	156.6
102.5°	142.7	179.7	127.5	138.1	149.8
105°	178.7	210.3	204.1	132.4	143.1
107.5°	216.0	243.3	294.9	235.3	169.9
110°	253.2	276.8	325.2	333.6	260.3



TEST NUMBER: P1010745

CATALOG NUMBER: S123DIP-B775D585UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	289.8	308.5	354.8	386.3	394.6
115°	324.8	340.8	383.9	414.8	425.6
117.5°	360.3	372.7	411.3	441.1	450.1
120°	391.7	402.2	438.6	467.4	474.8
122.5°	424.9	431.0	465.9	491.9	499.9
125°	453.6	458.2	491.0	514.2	522.7
127.5°	483.3	486.8	516.0	538.8	544.9
130°	510.8	514.2	537.6	559.9	565.1
132.5°	536.0	540.5	558.1	579.2	584.9
135°	562.8	565.3	579.0	599.8	603.2
137.5°	585.7	589.3	597.7	617.5	621.5
140°	607.6	611.0	615.8	633.9	638.0
142.5°	628.7	631.0	632.8	648.2	651.7
145°	648.1	651.0	652.2	661.7	665.9
147.5°	665.9	668.8	669.9	674.2	675.6
150°	683.1	684.8	685.9	687.1	687.4
152.5°	698.5	699.1	699.6	701.9	699.1
155°	712.8	711.6	712.2	715.1	711.6
157.5°	724.2	724.2	723.6	727.1	722.5
160°	734.5	733.9	733.4	736.8	732.8
162.5°	744.2	742.5	741.9	745.9	742.5
165°	751.6	749.9	749.4	753.9	749.9
167.5°	757.9	755.6	755.6	760.2	755.6
170°	763.1	760.8	760.8	765.4	760.8
172.5°	766.5	763.6	764.2	768.8	763.6
175°	769.4	766.5	767.1	771.1	766.5
177.5°	770.5	767.6	768.2	772.8	767.1
180°	769.4	769.4	769.4	769.4	769.4

(END OF REPORT)