

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011063

Luminaire Tested: S123DIP-B1000D1025UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011063
REPORT IS A COMBINATION OF REPORTS P989078 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D1025UB50-4F0-XX-W2A-F4
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7478.2 lumens
Efficiency: N/A
Efficacy: 99.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011063

CATALOG NUMBER: S123DIP-B1000D1025UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1011063

CATALOG NUMBER: S123DIP-B1000D1025UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	98	94	90	86	91	87	84	81	74	72	70	63	61	59	52	50	49
2	90	82	76	71	83	76	71	66	65	61	58	55	52	49	45	43	42
3	82	72	65	59	75	67	60	55	57	52	48	48	45	42	40	38	35
4	75	64	56	50	69	59	52	47	51	46	41	43	39	36	36	33	30
5	69	57	49	43	63	53	46	40	46	40	36	39	34	31	32	29	26
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	29	26	23
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	27	23	21
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	19
9	50	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17
10	47	35	28	23	44	33	26	22	29	23	20	25	20	17	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16283	16283	16283
5°	16323	15721	15697
10°	16178	15189	15033
15°	15953	14635	14309
20°	15696	14022	13592
25°	15362	13373	12824
30°	14997	12702	12018
35°	14614	12016	11216
40°	14214	11298	10428
45°	13773	10596	9603
50°	13326	9815	8776
55°	12751	9001	7939
60°	12158	8103	7047
65°	11603	7132	6116
70°	10802	6054	5032
75°	9647	4793	3906
80°	8333	3369	2763
85°	6493	1810	1383

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13773 cd/sqm

TEST NUMBER: P1011063

CATALOG NUMBER: S123DIP-B1000D1025UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	142.6	1.9
10°-20°	402.7	5.4
20°-30°	594.7	8.0
30°-40°	694.6	9.3
40°-50°	698.3	9.3
50°-60°	613.4	8.2
60°-70°	456.8	6.1
70°-80°	260.0	3.5
80°-90°	76.5	1.0
90°-100°	266.7	3.6
100°-110°	745.5	10.0
110°-120°	726.9	9.7
120°-130°	578.8	7.7
130°-140°	456.9	6.1
140°-150°	340.9	4.6
150°-160°	237.8	3.2
160°-170°	139.7	1.9
170°-180°	45.4	0.6
0°-30°	1140.0	15.2
0°-40°	1834.6	24.5
0°-60°	3146.3	42.1
0°-90°	3939.6	52.7
90°-120°	1739.1	23.3
90°-150°	3115.7	41.7
90°-180°	3539.0	47.3
0°-180°	7478.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1513	1513	1513	1513	1513	
5°	1514	1508	1493	1506	1504	144
15°	1441	1436	1419	1430	1422	406
25°	1308	1301	1284	1285	1281	603
35°	1132	1124	1107	1099	1093	708
45°	927	922	905	890	883	716
55°	704	702	686	671	665	630
65°	480	474	460	450	446	474
75°	254	248	244	238	234	271
85°	68	65	65	62	62	73
90°	2	11	24	27	28	7
95°	32	105	563	164	110	34
105°	110	163	764	1336	1208	117
115°	195	243	584	1281	1470	193
125°	271	320	545	988	1159	241
135°	317	379	538	814	940	245
145°	362	415	531	667	734	227
155°	411	444	514	584	609	189
165°	449	462	492	522	531	127
175°	468	469	472	479	478	44
180°	469	469	469	469	469	

TEST NUMBER: P1011063

CATALOG NUMBER: S123DIP-B1000D1025UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1512.7	1512.7	1512.7	1512.7	1512.7
2.5°	1519.2	1514.0	1499.7	1512.7	1511.4
5°	1514.0	1507.5	1493.2	1506.2	1503.6
7.5°	1502.3	1495.8	1481.5	1493.2	1491.9
10°	1486.7	1480.2	1463.3	1475.0	1472.4
12.5°	1465.9	1460.7	1445.1	1452.9	1451.6
15°	1441.2	1436.0	1419.1	1429.5	1421.7
17.5°	1413.9	1407.4	1390.5	1398.3	1395.7
20°	1382.7	1374.9	1358.0	1363.2	1359.3
22.5°	1347.6	1339.7	1322.8	1326.7	1321.5
25°	1308.5	1300.7	1283.8	1285.1	1281.2
27.5°	1268.2	1260.4	1242.2	1243.5	1239.6
30°	1224.0	1217.5	1199.3	1199.3	1190.2
32.5°	1179.8	1170.7	1157.6	1148.5	1144.6
35°	1131.6	1123.8	1106.9	1099.1	1092.6
37.5°	1083.5	1073.1	1056.2	1047.1	1043.2
40°	1032.8	1025.0	1006.8	996.4	991.2
42.5°	982.0	972.9	954.7	944.3	939.1
45°	927.4	922.2	905.3	889.7	883.2
47.5°	874.1	866.3	850.7	835.1	829.9
50°	819.5	813.0	796.0	781.7	773.9
52.5°	762.2	758.3	740.1	728.4	720.6
55°	703.7	702.4	685.5	671.2	664.7
57.5°	649.1	643.9	630.9	617.8	610.0
60°	589.2	587.9	572.3	560.6	554.1
62.5°	535.9	532.0	516.4	504.7	500.8
65°	480.0	473.5	460.5	450.1	446.1
67.5°	420.1	414.9	404.5	395.4	390.2
70°	366.8	359.0	351.2	342.1	335.6
72.5°	310.9	305.7	296.6	288.8	286.2
75°	253.6	248.4	244.5	238.0	234.1
77.5°	202.9	200.3	195.1	189.9	189.9
80°	153.5	149.6	147.0	145.7	145.7
82.5°	105.4	105.4	105.4	102.8	101.5
85°	67.6	65.0	65.0	62.4	62.4
87.5°	33.8	29.9	28.6	27.3	27.3
90°	1.9	11.4	23.8	26.6	27.6
92.5°	14.3	57.0	176.7	60.4	50.4
95°	32.3	105.0	563.4	164.4	110.2
97.5°	51.3	120.2	866.5	413.2	226.1
100°	70.3	132.6	899.7	864.6	595.7
102.5°	90.3	146.8	838.0	1157.6	943.4
105°	110.2	163.0	763.9	1335.8	1208.5
107.5°	131.1	182.0	698.3	1414.2	1381.4
110°	153.9	201.4	644.2	1416.6	1480.2

TEST NUMBER: P1011063

CATALOG NUMBER: S123DIP-B1000D1025UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	174.8	221.8	608.0	1362.9	1500.2
115°	194.8	242.8	584.3	1281.2	1469.8
117.5°	214.7	262.7	568.1	1193.8	1403.3
120°	235.6	282.6	557.7	1111.1	1315.9
122.5°	253.7	301.6	551.0	1046.0	1234.1
125°	270.8	319.7	545.3	988.1	1159.1
127.5°	284.1	336.8	542.5	940.6	1094.5
130°	296.4	352.0	539.6	896.9	1041.3
132.5°	305.9	365.8	538.7	856.0	989.0
135°	317.3	378.6	537.7	813.8	939.6
137.5°	327.8	389.0	535.8	773.8	887.4
140°	338.2	398.5	534.9	734.9	832.3
142.5°	349.6	407.1	533.0	699.3	781.0
145°	362.0	414.7	531.1	667.4	734.4
147.5°	374.3	422.8	528.2	642.8	694.5
150°	386.7	429.4	524.4	620.8	660.3
152.5°	399.0	436.6	519.7	601.8	631.8
155°	411.4	443.6	514.0	584.3	609.0
157.5°	420.9	449.8	509.2	567.2	587.1
160°	432.3	455.0	503.5	551.5	566.2
162.5°	440.8	458.9	497.8	536.8	547.2
165°	449.4	462.2	492.1	522.0	531.1
167.5°	456.0	465.0	486.4	509.2	514.9
170°	461.7	466.4	480.7	497.8	500.7
172.5°	465.5	467.9	476.0	487.8	487.4
175°	468.4	468.8	472.2	478.8	477.9
177.5°	470.3	469.3	469.3	473.1	471.2
180°	469.3	469.3	469.3	469.3	469.3

(END OF REPORT)