

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010746

Luminaire Tested: S123DIP-B775D585UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010746
REPORT IS A COMBINATION OF REPORTS P990415 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D585UB2750-4F0-XX-W2A-D_3500K
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5618.0 lumens
Efficiency: N/A
Efficacy: 109.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010746

CATALOG NUMBER: S123DIP-B775D585UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1010746

CATALOG NUMBER: S123DIP-B775D585UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	97	93	88	84	90	86	82	79	73	70	68	61	59	57	50	49	48
2	88	80	74	68	81	74	69	64	63	59	55	53	50	47	44	41	39
3	80	70	62	56	74	65	58	53	55	50	46	47	43	39	38	35	33
4	73	62	54	47	67	57	50	44	49	43	39	41	37	33	34	31	28
5	67	55	46	40	62	51	44	38	44	38	33	37	32	29	31	27	24
6	62	49	41	35	57	46	38	33	39	33	29	33	29	25	28	24	21
7	57	44	36	30	53	41	34	29	36	30	25	30	26	22	25	22	19
8	53	40	32	27	49	38	30	25	32	27	22	28	23	20	23	20	17
9	49	37	29	24	46	34	27	23	30	24	20	25	21	18	21	18	15
10	46	34	26	21	43	32	25	20	27	22	18	24	19	16	20	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10444	10444	10444
5°	10473	10138	10130
10°	10375	9863	9788
15°	10238	9560	9426
20°	10043	9222	9036
25°	9803	8842	8633
30°	9558	8496	8228
35°	9281	8135	7899
40°	9019	7805	7550
45°	8728	7485	7263
50°	8440	7167	6951
55°	8121	6842	6666
60°	7808	6510	6371
65°	7487	6155	6028
70°	7003	5758	5674
75°	6394	5305	5309
80°	5679	4846	4891
85°	4976	4475	4593

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8728 cd/sqm

TEST NUMBER: P1010746

CATALOG NUMBER: S123DIP-B775D585UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.0	1.6
10°-20°	262.4	4.7
20°-30°	392.4	7.0
30°-40°	468.5	8.3
40°-50°	490.2	8.7
50°-60°	460.0	8.2
60°-70°	384.2	6.8
70°-80°	274.7	4.9
80°-90°	165.0	2.9
90°-100°	130.0	2.3
100°-110°	207.3	3.7
110°-120°	373.2	6.6
120°-130°	438.6	7.8
130°-140°	450.7	8.0
140°-150°	412.1	7.3
150°-160°	330.2	5.9
160°-170°	213.1	3.8
170°-180°	73.4	1.3
0°-30°	746.8	13.3
0°-40°	1215.3	21.6
0°-60°	2165.5	38.5
0°-90°	2989.5	53.2
90°-120°	710.4	12.6
90°-150°	2011.8	35.8
90°-180°	2629.0	46.8
0°-180°	5618.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	970	970	970	970	970	
5°	971	969	963	971	970	92
15°	925	928	927	938	936	261
25°	835	846	849	862	862	385
35°	719	736	749	765	770	449
45°	588	613	640	660	668	453
55°	448	483	521	550	558	401
65°	310	351	397	429	440	306
75°	168	218	271	306	318	180
85°	52	105	161	197	207	53
90°	14	72	133	172	183	12
95°	47	64	122	159	170	51
105°	180	211	205	133	144	190
115°	326	342	386	417	427	322
125°	456	460	493	516	525	407
135°	565	568	582	602	606	435
145°	651	654	655	665	669	407
155°	716	715	715	718	715	330
165°	755	753	752	757	753	213
175°	773	770	770	774	770	74
180°	773	773	773	773	773	

TEST NUMBER: P1010746

CATALOG NUMBER: S123DIP-B775D585UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	970.3	970.3	970.3	970.3	970.3
2.5°	975.6	972.4	964.0	972.4	971.4
5°	971.4	969.3	962.9	971.4	970.3
7.5°	964.0	964.0	957.6	968.2	967.1
10°	953.4	955.5	950.2	960.8	958.7
12.5°	940.7	943.9	940.7	950.2	948.1
15°	924.9	928.0	927.0	937.5	936.5
17.5°	905.8	912.2	911.1	920.6	918.5
20°	884.7	891.0	893.1	902.7	903.7
22.5°	862.5	868.8	872.0	884.7	883.6
25°	835.0	845.6	848.8	862.5	862.5
27.5°	808.6	820.2	826.6	838.2	839.2
30°	780.1	793.8	802.2	814.9	814.9
32.5°	748.3	764.2	775.8	789.6	792.7
35°	718.7	735.7	749.4	765.3	769.5
37.5°	687.0	706.1	721.9	739.9	743.1
40°	655.3	674.4	695.5	713.5	717.7
42.5°	620.4	644.8	667.0	687.0	693.4
45°	587.7	613.0	639.5	659.6	668.0
47.5°	552.8	581.3	610.9	633.1	639.5
50°	519.0	548.6	581.3	605.7	613.0
52.5°	483.0	514.8	551.7	577.1	586.6
55°	448.2	483.0	521.1	549.6	558.1
57.5°	414.3	450.3	491.5	520.0	529.5
60°	378.4	416.5	459.8	489.4	501.0
62.5°	344.6	383.7	430.2	459.8	470.4
65°	309.7	350.9	397.4	429.1	439.7
67.5°	274.8	318.2	364.7	399.5	408.0
70°	237.8	283.3	334.0	367.8	378.4
72.5°	204.0	249.4	302.3	337.2	347.7
75°	168.1	217.7	270.6	305.5	318.2
77.5°	137.4	187.1	239.9	276.9	286.4
80°	104.6	156.4	211.4	247.3	257.9
82.5°	76.1	129.0	185.0	220.9	231.5
85°	51.8	104.6	160.7	196.6	207.2
87.5°	31.7	84.6	138.5	174.4	185.0
90°	14.3	71.8	133.2	171.5	183.1
92.5°	25.9	67.9	125.9	164.8	174.9
95°	46.6	64.3	122.4	159.2	169.8
97.5°	74.3	96.2	116.7	153.0	164.1
100°	106.5	151.8	110.9	146.1	157.3
102.5°	143.4	180.5	128.1	138.7	150.5
105°	179.6	211.2	205.0	133.0	143.7
107.5°	216.9	244.3	296.2	236.4	170.7
110°	254.3	278.0	326.5	335.0	261.5



TEST NUMBER: P1010746

CATALOG NUMBER: S123DIP-B775D585UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	291.0	309.8	356.3	387.9	396.3
115°	326.2	342.3	385.5	416.6	427.3
117.5°	361.8	374.2	413.1	443.0	452.0
120°	393.4	403.9	440.5	469.4	476.8
122.5°	426.7	432.8	467.9	494.1	502.0
125°	455.5	460.1	493.0	516.4	524.9
127.5°	485.4	488.9	518.1	541.1	547.3
130°	512.9	516.4	539.9	562.2	567.5
132.5°	538.2	542.8	560.5	581.8	587.4
135°	565.2	567.7	581.6	602.3	605.9
137.5°	588.2	591.8	600.3	620.1	624.2
140°	610.1	613.6	618.4	636.6	640.8
142.5°	631.4	633.7	635.4	650.9	654.4
145°	650.9	653.8	655.0	664.6	668.8
147.5°	668.7	671.6	672.8	677.1	678.4
150°	686.0	687.7	688.8	690.0	690.4
152.5°	701.5	702.0	702.6	704.9	702.0
155°	715.8	714.7	715.2	718.1	714.7
157.5°	727.3	727.3	726.7	730.2	725.6
160°	737.6	737.0	736.5	739.9	735.9
162.5°	747.4	745.7	745.1	749.1	745.7
165°	754.8	753.1	752.5	757.1	753.1
167.5°	761.2	758.9	758.9	763.5	758.9
170°	766.3	764.0	764.0	768.6	764.0
172.5°	769.8	766.9	767.5	772.1	766.9
175°	772.6	769.8	770.3	774.4	769.8
177.5°	773.8	770.9	771.5	776.1	770.3
180°	772.6	772.6	772.6	772.6	772.6

(END OF REPORT)