

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010748

Luminaire Tested: S123DIP-B775D585UB2750-4F0-XX-W2A-D_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010748
REPORT IS A COMBINATION OF REPORTS P990417 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D585UB2750-4F0-XX-W2A-D_5000K
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5379.0 lumens
Efficiency: N/A
Efficacy: 104.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010748

CATALOG NUMBER: S123DIP-B775D585UB2750-4F0-XX-W2A-D_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010748

CATALOG NUMBER: S123DIP-B775D585UB2750-4F0-XX-W2A-D_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	97	93	88	84	90	86	82	79	73	70	68	61	59	57	50	49	48
2	88	80	74	68	81	74	69	64	63	59	55	53	50	47	44	41	39
3	80	70	62	56	74	65	58	53	55	50	46	47	43	39	38	35	33
4	73	62	54	47	67	57	50	44	49	43	39	41	37	33	34	31	28
5	67	55	46	40	62	51	44	38	44	38	33	37	32	29	31	27	24
6	62	49	41	35	57	46	38	33	39	33	29	33	29	25	28	24	21
7	57	44	36	30	53	41	34	29	36	30	25	30	26	22	25	22	19
8	53	40	32	27	49	38	30	25	32	27	22	28	23	20	23	20	17
9	49	37	29	24	46	34	27	23	30	24	20	25	21	18	21	18	15
10	46	34	26	21	43	32	25	20	27	22	18	24	19	16	20	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10002	10002	10002
5°	10030	9709	9701
10°	9936	9446	9374
15°	9804	9155	9027
20°	9618	8832	8654
25°	9388	8467	8268
30°	9152	8137	7880
35°	8889	7791	7564
40°	8637	7475	7231
45°	8358	7168	6956
50°	8082	6864	6658
55°	7777	6552	6384
60°	7478	6234	6102
65°	7170	5895	5773
70°	6708	5515	5434
75°	6121	5079	5083
80°	5440	4642	4684
85°	4764	4286	4397

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8358 cd/sqm

TEST NUMBER: P1010748

CATALOG NUMBER: S123DIP-B775D585UB2750-4F0-XX-W2A-D_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.2	1.6
10°-20°	251.3	4.7
20°-30°	375.8	7.0
30°-40°	448.7	8.3
40°-50°	469.4	8.7
50°-60°	440.5	8.2
60°-70°	368.0	6.8
70°-80°	263.1	4.9
80°-90°	158.0	2.9
90°-100°	124.4	2.3
100°-110°	198.4	3.7
110°-120°	357.3	6.6
120°-130°	419.8	7.8
130°-140°	431.4	8.0
140°-150°	394.4	7.3
150°-160°	316.1	5.9
160°-170°	204.0	3.8
170°-180°	70.3	1.3
0°-30°	715.2	13.3
0°-40°	1163.9	21.6
0°-60°	2073.9	38.6
0°-90°	2863.0	53.2
90°-120°	680.1	12.6
90°-150°	1925.7	35.8
90°-180°	2516.0	46.8
0°-180°	5379.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	929	929	929	929	929	
5°	930	928	922	930	929	88
15°	886	889	888	898	897	250
25°	800	810	813	826	826	369
35°	688	704	718	733	737	430
45°	563	587	612	632	640	434
55°	429	463	499	526	534	384
65°	297	336	381	411	421	293
75°	161	208	259	292	305	172
85°	50	100	154	188	198	51
90°	14	69	128	164	175	11
95°	45	62	117	152	163	49
105°	172	202	196	127	138	182
115°	312	328	369	399	409	309
125°	436	440	472	494	502	390
135°	541	543	557	576	580	417
145°	623	626	627	636	640	390
155°	685	684	685	687	684	316
165°	722	721	720	725	721	204
175°	740	737	737	741	737	70
180°	740	740	740	740	740	

TEST NUMBER: P1010748

CATALOG NUMBER: S123DIP-B775D585UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	929.2	929.2	929.2	929.2	929.2
2.5°	934.3	931.3	923.2	931.3	930.3
5°	930.3	928.2	922.2	930.3	929.2
7.5°	923.2	923.2	917.1	927.2	926.2
10°	913.1	915.1	910.0	920.1	918.1
12.5°	900.9	903.9	900.9	910.0	908.0
15°	885.7	888.8	887.7	897.9	896.9
17.5°	867.5	873.6	872.6	881.7	879.6
20°	847.3	853.3	855.4	864.5	865.5
22.5°	826.0	832.1	835.1	847.3	846.2
25°	799.7	809.8	812.8	826.0	826.0
27.5°	774.4	785.5	791.6	802.7	803.7
30°	747.0	760.2	768.3	780.4	780.4
32.5°	716.7	731.9	743.0	756.2	759.2
35°	688.3	704.5	717.7	732.9	736.9
37.5°	658.0	676.2	691.4	708.6	711.6
40°	627.6	645.8	666.1	683.3	687.3
42.5°	594.2	617.5	638.7	658.0	664.0
45°	562.8	587.1	612.4	631.6	639.7
47.5°	529.4	556.7	585.1	606.3	612.4
50°	497.0	525.4	556.7	580.0	587.1
52.5°	462.6	493.0	528.4	552.7	561.8
55°	429.2	462.6	499.0	526.4	534.5
57.5°	396.8	431.2	470.7	498.0	507.1
60°	362.4	398.8	440.3	468.7	479.8
62.5°	330.0	367.4	412.0	440.3	450.5
65°	296.6	336.1	380.6	411.0	421.1
67.5°	263.2	304.7	349.2	382.6	390.7
70°	227.8	271.3	319.9	352.3	362.4
72.5°	195.4	238.9	289.5	322.9	333.0
75°	160.9	208.5	259.1	292.5	304.7
77.5°	131.6	179.2	229.8	265.2	274.3
80°	100.2	149.8	202.5	236.9	247.0
82.5°	72.9	123.5	177.1	211.6	221.7
85°	49.6	100.2	153.9	188.3	198.4
87.5°	30.4	81.0	132.6	167.0	177.1
90°	13.7	68.8	127.6	164.2	175.4
92.5°	24.7	65.0	120.6	157.8	167.5
95°	44.6	61.6	117.2	152.5	162.6
97.5°	71.1	92.2	111.7	146.5	157.1
100°	102.0	145.3	106.2	139.9	150.6
102.5°	137.2	172.7	122.7	132.8	144.1
105°	171.8	202.2	196.2	127.4	137.6
107.5°	207.6	233.8	283.5	226.3	163.4
110°	243.5	266.0	312.6	320.8	250.3



TEST NUMBER: P1010748

CATALOG NUMBER: S123DIP-B775D585UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	278.6	296.6	341.1	371.4	379.4
115°	312.2	327.6	369.0	398.8	409.1
117.5°	346.3	358.2	395.4	424.1	432.7
120°	376.5	386.6	421.6	449.3	456.4
122.5°	408.4	414.3	447.9	472.9	480.5
125°	435.9	440.3	471.9	494.2	502.4
127.5°	464.5	467.9	496.0	517.9	523.9
130°	490.9	494.3	516.8	538.2	543.2
132.5°	515.2	519.6	536.4	556.8	562.3
135°	541.0	543.3	556.6	576.5	579.9
137.5°	563.0	566.4	574.6	593.5	597.5
140°	583.9	587.2	591.9	609.3	613.3
142.5°	604.3	606.6	608.2	623.1	626.4
145°	623.0	625.8	626.9	636.1	640.1
147.5°	640.1	642.8	643.9	648.0	649.4
150°	656.6	658.2	659.3	660.4	660.8
152.5°	671.4	672.0	672.5	674.7	672.0
155°	685.1	684.0	684.6	687.3	684.0
157.5°	696.1	696.1	695.6	698.9	694.5
160°	706.0	705.5	704.9	708.2	704.4
162.5°	715.4	713.7	713.2	717.0	713.7
165°	722.5	720.9	720.3	724.7	720.9
167.5°	728.5	726.3	726.3	730.7	726.3
170°	733.5	731.3	731.3	735.7	731.3
172.5°	736.8	734.0	734.6	739.0	734.0
175°	739.5	736.8	737.3	741.2	736.8
177.5°	740.6	737.9	738.4	742.8	737.3
180°	739.5	739.5	739.5	739.5	739.5

(END OF REPORT)