

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010751

Luminaire Tested: S123DIP-B775D585UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010751
REPORT IS A COMBINATION OF REPORTS P990420 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D585UB2750-4F0-XX-W2A-F_3500K
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5557.0 lumens
Efficiency: N/A
Efficacy: 108.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010751

CATALOG NUMBER: S123DIP-B775D585UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1010751

CATALOG NUMBER: S123DIP-B775D585UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	88	88	88	75	75	75	63	63	63
1	99	95	91	87	92	89	85	82	77	74	72	66	64	62	56	54	53
2	91	83	77	71	84	77	72	67	67	63	59	58	55	52	49	47	45
3	83	73	65	59	77	68	62	56	59	54	50	51	47	44	43	41	38
4	76	65	56	50	70	60	53	48	53	47	43	45	41	38	39	35	33
5	69	58	49	43	64	54	47	41	47	41	37	41	36	33	35	31	29
6	64	52	43	37	59	48	41	36	43	37	32	37	32	29	32	28	25
7	59	47	39	33	55	44	37	31	39	33	28	34	29	25	29	25	22
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	25	21	18
10	48	36	28	23	45	34	27	22	30	24	20	26	22	18	23	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13235	13235	13235
5°	13268	12778	12759
10°	13150	12346	12219
15°	12967	11895	11631
20°	12757	11396	11047
25°	12486	10870	10424
30°	12190	10325	9768
35°	11879	9767	9117
40°	11552	9183	8475
45°	11195	8612	7806
50°	10832	7977	7134
55°	10364	7316	6452
60°	9882	6586	5728
65°	9430	5797	4971
70°	8779	4922	4090
75°	7844	3897	3175
80°	6775	2739	2245
85°	5283	1473	1124

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11195 cd/sqm

TEST NUMBER: P1010751

CATALOG NUMBER: S123DIP-B775D585UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.9	2.1
10°-20°	327.3	5.9
20°-30°	483.4	8.7
30°-40°	564.6	10.2
40°-50°	567.5	10.2
50°-60°	498.6	9.0
60°-70°	371.3	6.7
70°-80°	211.3	3.8
80°-90°	61.6	1.1
90°-100°	27.2	0.5
100°-110°	131.7	2.4
110°-120°	322.8	5.8
120°-130°	409.8	7.4
130°-140°	437.8	7.9
140°-150°	409.4	7.4
150°-160°	330.2	5.9
160°-170°	213.1	3.8
170°-180°	73.4	1.3
0°-30°	926.6	16.7
0°-40°	1491.2	26.8
0°-60°	2557.3	46.0
0°-90°	3201.6	57.6
90°-120°	481.8	8.7
90°-150°	1738.7	31.3
90°-180°	2355.0	42.4
0°-180°	5557.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1230	1230	1230	1230	1230	
5°	1231	1225	1214	1224	1222	117
15°	1171	1167	1153	1162	1156	330
25°	1064	1057	1044	1044	1041	490
35°	920	913	900	893	888	575
45°	754	750	736	723	718	582
55°	572	571	557	546	540	512
65°	390	385	374	366	363	385
75°	206	202	199	194	190	220
85°	55	53	53	51	51	59
90°	1	6	14	16	17	6
95°	35	12	18	22	22	42
105°	171	177	126	24	25	181
115°	321	324	330	335	338	317
125°	452	457	459	460	462	404
135°	563	567	569	571	569	434
145°	650	654	655	656	656	407
155°	716	715	715	718	715	330
165°	755	753	752	757	753	213
175°	773	770	770	774	770	74
180°	773	773	773	773	773	

TEST NUMBER: P1010751

CATALOG NUMBER: S123DIP-B775D585UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1229.6	1229.6	1229.6	1229.6	1229.6
2.5°	1234.8	1230.6	1219.0	1229.6	1228.5
5°	1230.6	1225.3	1213.7	1224.3	1222.2
7.5°	1221.1	1215.8	1204.2	1213.7	1212.6
10°	1208.4	1203.1	1189.4	1198.9	1196.8
12.5°	1191.5	1187.3	1174.6	1180.9	1179.9
15°	1171.4	1167.2	1153.4	1161.9	1155.6
17.5°	1149.2	1143.9	1130.2	1136.5	1134.4
20°	1123.8	1117.5	1103.7	1108.0	1104.8
22.5°	1095.3	1088.9	1075.2	1078.4	1074.1
25°	1063.6	1057.2	1043.5	1044.5	1041.4
27.5°	1030.8	1024.5	1009.7	1010.7	1007.5
30°	994.9	989.6	974.8	974.8	967.4
32.5°	958.9	951.5	940.9	933.5	930.4
35°	919.8	913.4	899.7	893.4	888.1
37.5°	880.7	872.2	858.5	851.1	847.9
40°	839.4	833.1	818.3	809.8	805.6
42.5°	798.2	790.8	776.0	767.5	763.3
45°	753.8	749.6	735.8	723.1	717.9
47.5°	710.5	704.1	691.4	678.7	674.5
50°	666.1	660.8	647.0	635.4	629.1
52.5°	619.5	616.4	601.6	592.0	585.7
55°	572.0	570.9	557.2	545.5	540.2
57.5°	527.6	523.3	512.8	502.2	495.8
60°	478.9	477.9	465.2	455.7	450.4
62.5°	435.6	432.4	419.7	410.2	407.0
65°	390.1	384.8	374.3	365.8	362.6
67.5°	341.5	337.3	328.8	321.4	317.2
70°	298.1	291.8	285.5	278.1	272.8
72.5°	252.7	248.4	241.0	234.7	232.6
75°	206.2	201.9	198.8	193.5	190.3
77.5°	164.9	162.8	158.6	154.4	154.4
80°	124.8	121.6	119.5	118.4	118.4
82.5°	85.6	85.6	85.6	83.5	82.5
85°	55.0	52.9	52.9	50.7	50.7
87.5°	27.5	24.3	23.3	22.2	22.2
90°	0.6	6.3	13.8	16.1	17.2
92.5°	13.2	9.8	14.9	18.9	19.5
95°	35.0	11.5	17.8	21.8	21.8
97.5°	63.7	47.6	18.4	23.0	23.5
100°	97.0	108.5	18.9	23.5	24.1
102.5°	134.9	142.4	42.5	23.5	24.7
105°	171.1	177.4	125.7	24.1	25.3
107.5°	209.5	214.7	223.3	134.9	59.7
110°	248.0	252.6	258.9	239.9	157.9

TEST NUMBER: P1010751

CATALOG NUMBER: S123DIP-B775D585UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	284.7	288.7	295.0	300.2	299.1
115°	320.9	324.3	329.5	335.2	337.5
117.5°	356.5	360.5	363.4	368.0	368.5
120°	389.2	394.4	396.1	400.7	400.7
122.5°	422.5	426.5	428.8	431.7	432.2
125°	452.3	456.9	459.2	460.4	461.5
127.5°	482.2	486.8	489.6	491.4	490.2
130°	509.7	514.3	516.6	518.9	517.8
132.5°	536.1	540.7	542.5	544.8	543.0
135°	563.1	566.6	568.9	570.6	568.9
137.5°	586.1	590.7	591.8	594.7	593.5
140°	609.0	612.5	614.2	616.5	615.4
142.5°	630.3	633.7	635.4	637.2	635.4
145°	649.8	653.8	655.0	656.1	656.1
147.5°	668.7	671.6	672.8	673.9	671.0
150°	686.0	687.7	688.8	690.0	688.3
152.5°	701.5	702.0	702.6	704.9	702.0
155°	715.8	714.7	715.2	718.1	714.7
157.5°	727.3	727.3	726.7	730.2	725.6
160°	737.6	737.0	736.5	739.9	735.9
162.5°	747.4	745.7	745.1	749.1	745.7
165°	754.8	753.1	752.5	757.1	753.1
167.5°	761.2	758.9	758.9	763.5	758.9
170°	766.3	764.0	764.0	768.6	764.0
172.5°	769.8	766.9	767.5	772.1	766.9
175°	772.6	769.8	770.3	774.4	769.8
177.5°	773.8	770.9	771.5	776.1	770.3
180°	772.6	772.6	772.6	772.6	772.6

(END OF REPORT)