

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010758

Luminaire Tested: S123DIP-B775D805UB2750-4F0-XX-W2A-A_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010758
REPORT IS A COMBINATION OF REPORTS P990472 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D805UB2750-4F0-XX-W2A-A_5000K
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6167.0 lumens
Efficiency: N/A
Efficacy: 108.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010758

CATALOG NUMBER: S123DIP-B775D805UB2750-4F0-XX-W2A-A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010758

CATALOG NUMBER: S123DIP-B775D805UB2750-4F0-XX-W2A-A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	57	57	57
1	98	94	90	87	91	87	84	81	74	72	70	62	60	59	51	50	49	49	49	44
2	90	82	76	71	83	76	71	67	65	61	58	55	52	50	45	43	42	42	42	37
3	82	73	66	60	76	68	61	56	58	53	49	49	45	42	40	38	36	36	36	32
4	75	64	57	51	69	60	53	48	51	46	42	43	40	36	36	33	31	31	31	27
5	69	58	50	44	64	54	46	41	46	41	36	39	35	32	33	29	27	27	27	24
6	64	52	44	38	59	48	41	36	42	36	32	35	31	28	30	26	24	24	24	21
7	59	47	39	33	54	44	37	31	38	32	28	32	28	25	27	24	21	21	21	19
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	25	22	19	19	19	17
9	51	39	31	26	47	36	30	25	32	26	22	27	23	20	23	20	17	17	17	15
10	48	35	28	24	44	33	27	22	29	24	20	25	21	18	21	18	16	16	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11241	11241	11241	11241
5°	11248	12953	11282	9666
10°	11177	15673	11189	8442
15°	11023	18588	11113	7598
20°	10889	21401	10913	6992
25°	10693	21940	10716	6675
30°	10552	18127	10552	6468
35°	10377	12123	10311	6284
40°	10166	8751	10041	6004
45°	9904	6932	9619	5655
50°	9264	5887	8936	5313
55°	8563	5173	8215	4931
60°	7851	4504	7435	4530
65°	7071	3856	6728	3995
70°	6258	3201	5840	3369
75°	5352	2414	5006	2599
80°	4229	1612	3898	1709
85°	2920	740	2334	674

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 18129 cd/sqm

TEST NUMBER: P1010758

CATALOG NUMBER: S123DIP-B775D805UB2750-4F0-XX-W2A-A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.7	1.7
10°-20°	329.9	5.3
20°-30°	555.1	9.0
30°-40°	627.3	10.2
40°-50°	561.8	9.1
50°-60°	453.5	7.4
60°-70°	316.0	5.1
70°-80°	165.9	2.7
80°-90°	41.7	0.7
90°-100°	34.9	0.6
100°-110°	168.5	2.7
110°-120°	412.9	6.7
120°-130°	524.2	8.5
130°-140°	560.0	9.1
140°-150°	523.6	8.5
150°-160°	422.4	6.8
160°-170°	272.6	4.4
170°-180°	93.9	1.5
0°-30°	987.7	16.0
0°-40°	1615.0	26.2
0°-60°	2630.3	42.7
0°-90°	3154.0	51.1
90°-120°	616.3	10.0
90°-150°	2224.1	36.1
90°-180°	3013.0	48.9
0°-180°	6167.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1044	1044	1044	1044	1044	
5°	1043	1241	1046	926	1043	99
15°	996	1847	1004	755	996	281
25°	911	2192	913	667	911	420
35°	804	1181	798	612	804	503
45°	667	638	648	520	667	510
55°	473	433	453	413	473	423
65°	292	281	278	291	292	291
75°	141	145	132	156	141	151
85°	30	33	24	30	30	35
90°	1	22	1	22	1	5
95°	45	28	45	28	45	54
105°	219	32	219	32	219	232
115°	410	432	410	432	410	405
125°	579	590	579	590	579	517
135°	720	728	720	728	720	555
145°	831	839	831	839	831	520
155°	916	914	916	914	916	422
165°	966	963	966	963	966	273
175°	988	985	988	985	988	94
180°	988	988	988	988	988	

TEST NUMBER: P1010758

CATALOG NUMBER: S123DIP-B775D805UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	1047.4	1055.5	1059.5	1065.6	1071.7	1080.8	1083.8	1088.9	1086.8	1090.9	1092.9
5°	1043.3	1057.5	1069.6	1084.8	1099.0	1109.1	1119.2	1135.4	1147.6	1149.6	1158.7
7.5°	1036.2	1056.5	1077.7	1099.0	1126.3	1142.5	1160.7	1183.0	1201.2	1230.5	1241.7
10°	1027.1	1055.5	1085.8	1115.2	1152.6	1177.9	1200.2	1237.6	1275.1	1305.4	1333.8
12.5°	1013.0	1048.4	1087.9	1131.4	1179.9	1209.3	1239.7	1289.2	1345.9	1392.5	1422.8
15°	995.8	1040.3	1090.9	1137.4	1191.1	1245.7	1278.1	1333.8	1414.7	1458.2	1536.2
17.5°	981.6	1027.1	1077.7	1150.6	1223.5	1278.1	1301.4	1403.6	1459.2	1532.1	1620.2
20°	959.3	1017.0	1081.8	1154.6	1248.8	1282.2	1329.7	1432.9	1501.8	1596.9	1705.2
22.5°	936.1	997.8	1075.7	1151.6	1256.9	1292.3	1357.0	1439.0	1548.3	1642.4	1761.8
25°	910.8	977.6	1056.5	1146.6	1249.8	1301.4	1362.1	1463.3	1581.7	1700.1	1810.4
27.5°	885.5	958.3	1040.3	1130.4	1230.5	1291.3	1352.0	1457.2	1609.0	1737.5	1878.2
30°	861.2	934.0	1016.0	1108.1	1213.3	1272.0	1329.7	1461.3	1630.3	1775.0	1916.7
32.5°	834.9	909.8	995.8	1072.7	1178.9	1241.7	1306.4	1461.3	1643.4	1797.2	1926.8
35°	803.5	880.4	954.3	1031.2	1136.4	1206.3	1279.1	1451.2	1655.6	1804.3	1884.3
37.5°	773.1	840.9	904.7	979.6	1089.9	1164.8	1248.8	1439.0	1649.5	1774.0	1796.2
40°	738.7	806.5	858.1	928.0	1044.3	1131.4	1216.4	1422.8	1623.2	1702.1	1637.4
42.5°	705.3	759.0	803.5	871.3	997.8	1082.8	1174.9	1393.5	1571.6	1587.8	1442.0
45°	666.9	705.3	744.8	821.7	947.2	1034.2	1136.4	1351.0	1488.6	1442.0	1257.9
47.5°	617.3	651.7	695.2	766.1	893.6	983.6	1080.8	1296.3	1368.2	1271.0	1069.6
50°	569.7	599.1	639.6	708.4	836.9	924.9	1028.2	1210.3	1245.7	1092.9	921.9
52.5°	522.2	544.4	583.9	652.7	781.2	866.2	960.4	1122.3	1102.0	938.1	786.3
55°	472.6	491.8	529.3	597.1	716.5	797.4	887.5	1014.0	961.4	805.5	684.1
57.5°	424.0	444.3	482.7	539.4	651.7	730.6	802.5	901.7	822.7	698.3	591.0
60°	380.5	397.7	427.0	482.7	584.9	648.7	714.4	782.2	716.5	596.0	514.1
62.5°	335.0	351.2	378.5	429.1	517.1	573.8	626.4	682.1	609.2	521.2	448.3
65°	292.5	305.6	330.9	377.5	449.3	495.9	538.4	576.8	518.1	437.2	382.5
67.5°	254.0	265.1	286.4	327.9	388.6	422.0	456.4	488.8	439.2	374.4	327.9
70°	212.5	221.6	240.8	271.2	319.8	354.2	379.5	403.8	359.2	307.6	276.3
72.5°	176.1	185.2	197.3	228.7	262.1	283.3	310.7	323.8	298.5	256.0	224.7
75°	140.7	147.7	158.9	179.1	210.5	224.7	241.9	252.0	228.7	200.4	181.1
77.5°	110.3	113.3	121.4	135.6	156.9	173.0	186.2	192.3	176.1	157.9	141.7
80°	77.9	82.0	88.0	100.2	116.4	121.4	129.5	136.6	126.5	110.3	100.2
82.5°	51.6	56.7	59.7	64.8	74.9	81.0	83.0	89.1	79.9	73.9	69.8
85°	30.4	32.4	33.4	36.4	41.5	44.5	47.6	48.6	46.6	45.5	41.5
87.5°	15.2	15.2	15.2	17.2	18.2	20.2	21.3	21.3	21.3	20.2	19.2
90°	0.7	2.3	4.0	5.6	7.3	8.1	9.2	11.3	13.4	15.5	17.6
92.5°	16.9	15.9	14.9	14.0	13.0	12.5	13.2	14.7	16.2	17.6	19.1
95°	44.8	38.1	31.4	24.7	18.0	14.7	15.6	17.4	19.2	21.0	22.8
97.5°	81.5	76.9	72.3	67.8	63.2	60.9	56.7	48.4	40.1	31.8	23.5
100°	124.1	127.4	130.6	133.9	137.2	138.8	126.1	100.6	75.1	49.7	24.2
102.5°	172.6	174.7	176.8	178.9	181.0	182.1	167.9	139.5	111.1	82.7	54.3
105°	218.8	220.6	222.4	224.2	226.0	226.9	219.6	204.9	190.2	175.5	160.8
107.5°	268.0	269.5	270.9	272.4	273.9	274.6	275.8	278.3	280.7	283.2	285.6
110°	317.2	318.5	319.8	321.1	322.4	323.1	324.0	325.8	327.6	329.4	331.2

TEST NUMBER: P1010758

CATALOG NUMBER: S123DIP-B775D805UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	364.2	365.3	366.5	367.6	368.7	369.3	370.2	372.0	373.8	375.6	377.4
115°	410.5	411.5	412.5	413.4	414.4	414.9	415.6	417.1	418.6	420.0	421.5
117.5°	456.0	457.1	458.3	459.4	460.5	461.1	461.5	462.3	463.2	464.0	464.8
120°	497.8	499.3	500.7	502.2	503.7	504.4	504.7	505.2	505.7	506.2	506.7
122.5°	540.4	541.6	542.7	543.9	545.0	545.6	545.9	546.6	547.2	547.9	548.5
125°	578.6	579.9	581.2	582.5	583.8	584.5	584.8	585.5	586.1	586.8	587.4
127.5°	616.8	618.1	619.4	620.7	622.0	622.7	623.1	623.9	624.7	625.5	626.3
130°	652.0	653.3	654.6	655.9	657.2	657.9	658.2	658.9	659.5	660.2	660.8
132.5°	685.8	687.1	688.4	689.7	691.0	691.7	691.9	692.4	692.9	693.4	693.9
135°	720.3	721.3	722.3	723.2	724.2	724.7	725.0	725.7	726.4	727.0	727.7
137.5°	749.7	751.0	752.3	753.6	754.9	755.6	755.8	756.1	756.4	756.7	757.0
140°	779.1	780.1	781.1	782.0	783.0	783.5	783.7	784.2	784.7	785.2	785.7
142.5°	806.2	807.2	808.2	809.1	810.1	810.6	810.8	811.3	811.8	812.3	812.8
145°	831.2	832.3	833.5	834.6	835.7	836.3	836.5	836.8	837.1	837.5	837.8
147.5°	855.4	856.2	857.0	857.9	858.7	859.1	859.3	859.6	859.9	860.3	860.6
150°	877.5	878.0	878.5	879.0	879.5	879.7	879.9	880.2	880.5	880.8	881.1
152.5°	897.3	897.5	897.6	897.8	897.9	898.0	898.1	898.3	898.4	898.6	898.8
155°	915.6	915.3	915.0	914.7	914.4	914.2	914.3	914.4	914.6	914.7	914.9
157.5°	930.3	930.3	930.3	930.3	930.3	930.3	930.2	930.1	929.9	929.8	929.6
160°	943.5	943.3	943.2	943.0	942.9	942.8	942.7	942.6	942.4	942.3	942.1
162.5°	956.0	955.5	955.0	954.5	954.0	953.8	953.7	953.6	953.4	953.3	953.1
165°	965.6	965.1	964.6	964.1	963.6	963.4	963.3	963.1	963.0	962.8	962.6
167.5°	973.7	973.0	972.4	971.7	971.0	970.7	970.7	970.7	970.7	970.7	970.7
170°	980.3	979.6	979.0	978.3	977.6	977.3	977.3	977.3	977.3	977.3	977.3
172.5°	984.7	983.9	983.1	982.2	981.4	981.0	981.1	981.2	981.4	981.5	981.7
175°	988.3	987.5	986.7	985.9	985.1	984.7	984.8	984.9	985.1	985.2	985.4
177.5°	989.8	989.0	988.2	987.3	986.5	986.1	986.2	986.4	986.5	986.7	986.9
180°	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3

TEST NUMBER: P1010758

CATALOG NUMBER: S123DIP-B775D805UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	1100.0	1102.0	1109.1	1114.2	1124.3	1123.3	1123.3	1122.3	1119.2	1124.3	1127.3
5°	1176.9	1194.1	1196.1	1218.4	1219.4	1228.5	1234.6	1229.5	1241.7	1240.7	1231.6
7.5°	1272.0	1295.3	1306.4	1327.7	1352.0	1345.9	1369.2	1373.2	1371.2	1381.3	1388.4
10°	1376.3	1416.7	1445.1	1484.5	1494.7	1500.7	1515.9	1529.1	1555.4	1535.1	1548.3
12.5°	1495.7	1525.0	1562.5	1625.2	1656.6	1676.8	1683.9	1693.0	1711.2	1700.1	1701.1
15°	1595.9	1635.3	1699.1	1777.0	1786.1	1811.4	1805.3	1860.0	1886.3	1846.8	1869.1
17.5°	1700.1	1752.7	1828.6	1896.4	1934.9	1952.1	1968.3	2020.9	2018.9	2012.8	2017.9
20°	1766.9	1852.9	1947.0	2037.1	2048.2	2061.4	2104.9	2127.1	2123.1	2140.3	2151.4
22.5°	1861.0	1952.1	2052.3	2112.0	2137.3	2152.4	2186.8	2201.0	2207.1	2211.1	2204.1
25°	1939.9	2037.1	2111.0	2163.6	2178.8	2186.8	2198.0	2202.0	2199.0	2191.9	2198.0
27.5°	1993.6	2071.5	2122.1	2146.4	2138.3	2125.1	2103.9	2089.7	2058.3	2043.2	2061.4
30°	2015.8	2050.2	2065.4	2024.9	1984.5	1952.1	1911.6	1836.7	1778.0	1795.2	1771.9
32.5°	1980.4	1958.1	1885.3	1781.1	1749.7	1697.1	1582.7	1494.7	1497.7	1451.2	1470.4
35°	1876.2	1775.0	1637.4	1479.5	1438.0	1409.7	1284.2	1265.0	1224.5	1181.0	1193.1
37.5°	1692.0	1544.3	1377.3	1260.9	1199.2	1137.4	1066.6	1024.1	999.8	981.6	995.8
40°	1467.3	1287.2	1149.6	1045.4	992.7	953.3	904.7	862.2	834.9	831.8	836.9
42.5°	1246.7	1094.9	968.4	869.3	852.1	805.5	774.2	740.8	732.7	719.5	726.6
45°	1055.5	932.0	827.8	746.8	726.6	714.4	676.0	654.7	645.6	637.5	649.7
47.5°	916.8	787.3	711.4	662.8	642.6	622.4	601.1	586.9	579.9	580.9	579.9
50°	783.3	688.1	621.3	583.9	571.8	557.6	540.4	531.3	528.2	519.1	526.2
52.5°	674.0	605.2	558.6	523.2	514.1	504.0	489.8	484.7	477.6	475.6	475.6
55°	585.9	532.3	494.8	471.6	460.4	452.3	444.3	438.2	433.1	433.1	433.1
57.5°	517.1	470.6	443.2	423.0	419.0	410.9	401.7	401.7	394.7	393.7	396.7
60°	458.4	416.9	395.7	378.5	372.4	370.4	361.3	361.3	359.2	354.2	358.2
62.5°	398.7	368.4	350.1	337.0	330.9	330.9	323.8	318.8	318.8	319.8	317.8
65°	344.1	321.8	305.6	295.5	292.5	288.4	287.4	283.3	280.3	281.3	280.3
67.5°	295.5	278.3	267.2	259.1	254.0	252.0	248.9	248.9	246.9	247.9	242.9
70°	252.0	234.8	225.7	217.6	215.5	215.5	211.5	212.5	210.5	213.5	211.5
72.5°	207.5	194.3	187.2	184.2	182.2	181.1	179.1	177.1	176.1	178.1	177.1
75°	168.0	156.9	151.8	149.8	147.7	147.7	146.7	145.7	144.7	144.7	144.7
77.5°	130.5	123.5	117.4	119.4	116.4	117.4	114.4	114.4	115.4	114.4	114.4
80°	96.1	91.1	91.1	89.1	85.0	87.0	87.0	84.0	83.0	85.0	82.0
82.5°	63.8	62.7	60.7	59.7	57.7	58.7	57.7	56.7	55.7	57.7	55.7
85°	37.4	37.4	36.4	34.4	36.4	35.4	34.4	34.4	33.4	33.4	33.4
87.5°	19.2	17.2	17.2	16.2	17.2	15.2	16.2	15.2	14.2	15.2	14.2
90°	18.3	18.9	19.6	20.3	20.6	20.8	21.1	21.4	21.7	22.0	21.7
92.5°	20.2	21.4	22.5	23.6	24.2	24.3	24.5	24.6	24.8	25.0	24.8
95°	23.9	25.1	26.2	27.3	27.9	27.9	27.9	27.9	27.9	27.9	27.9
97.5°	24.8	26.1	27.4	28.7	29.4	29.5	29.6	29.8	29.9	30.1	29.9
100°	25.5	26.8	28.1	29.4	30.1	30.2	30.3	30.5	30.6	30.8	30.6
102.5°	48.9	43.5	38.2	32.8	30.1	30.3	30.6	30.9	31.3	31.6	31.3
105°	131.9	103.0	74.1	45.2	30.8	31.0	31.3	31.6	32.0	32.3	32.0
107.5°	260.5	235.4	210.3	185.2	172.6	161.9	140.5	119.2	97.8	76.4	97.8
110°	325.8	320.4	315.0	309.6	306.9	295.2	271.9	248.6	225.2	201.9	225.2

TEST NUMBER: P1010758

CATALOG NUMBER: S123DIP-B775D805UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	378.9	380.3	381.8	383.3	384.0	383.8	383.5	383.2	382.9	382.6	382.9
115°	423.1	424.7	426.4	428.0	428.8	429.1	429.8	430.5	431.1	431.8	431.1
117.5°	466.1	467.4	468.7	470.0	470.7	470.8	470.9	471.1	471.2	471.4	471.2
120°	508.0	509.3	510.6	511.9	512.5	512.5	512.5	512.5	512.5	512.5	512.5
122.5°	549.3	550.1	551.0	551.8	552.2	552.3	552.4	552.6	552.7	552.9	552.7
125°	587.7	588.1	588.4	588.7	588.9	589.1	589.4	589.7	590.1	590.4	590.1
127.5°	626.8	627.3	627.8	628.3	628.5	628.3	628.0	627.7	627.4	627.1	627.4
130°	661.5	662.1	662.8	663.5	663.8	663.6	663.3	663.0	662.6	662.3	662.6
132.5°	694.5	695.2	695.8	696.5	696.8	696.6	696.1	695.6	695.1	694.6	695.1
135°	728.2	728.7	729.2	729.7	729.9	729.7	729.2	728.7	728.2	727.7	728.2
137.5°	757.8	758.6	759.5	760.3	760.7	760.5	760.2	759.9	759.5	759.2	759.5
140°	786.3	787.0	787.6	788.3	788.6	788.4	788.1	787.8	787.4	787.1	787.4
142.5°	813.3	813.8	814.3	814.8	815.0	814.8	814.3	813.8	813.3	812.8	813.3
145°	838.1	838.5	838.8	839.1	839.3	839.3	839.3	839.3	839.3	839.3	839.3
147.5°	860.9	861.2	861.5	861.8	862.0	861.6	860.8	860.0	859.2	858.4	859.2
150°	881.4	881.8	882.1	882.4	882.6	882.4	881.9	881.4	880.9	880.4	880.9
152.5°	899.4	900.1	900.7	901.4	901.7	901.3	900.5	899.6	898.8	898.0	898.8
155°	915.7	916.5	917.4	918.2	918.6	918.1	917.1	916.2	915.2	914.2	915.2
157.5°	930.6	931.6	932.5	933.5	934.0	933.3	932.0	930.7	929.4	928.1	929.4
160°	943.1	944.1	945.0	946.0	946.5	945.9	944.8	943.6	942.5	941.3	942.5
162.5°	954.2	955.4	956.5	957.6	958.2	957.7	956.7	955.8	954.8	953.8	954.8
165°	963.9	965.2	966.5	967.8	968.5	967.9	966.8	965.7	964.5	963.4	964.5
167.5°	972.0	973.3	974.6	975.9	976.6	975.9	974.6	973.3	972.0	970.7	972.0
170°	978.6	979.9	981.2	982.5	983.2	982.5	981.2	979.9	978.6	977.3	978.6
172.5°	983.0	984.3	985.6	986.9	987.6	986.9	985.4	983.9	982.5	981.0	982.5
175°	986.5	987.7	988.8	989.9	990.5	989.9	988.6	987.3	986.0	984.7	986.0
177.5°	988.2	989.5	990.8	992.1	992.7	991.9	990.3	988.6	987.0	985.4	987.0
180°	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3

TEST NUMBER: P1010758

CATALOG NUMBER: S123DIP-B775D805UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	1119.2	1122.3	1114.2	1112.1	1112.1	1116.2	1113.2	1085.8	1090.9	1084.8	1082.8
5°	1242.7	1236.6	1228.5	1224.5	1219.4	1205.2	1204.2	1172.9	1166.8	1146.6	1137.4
7.5°	1378.3	1373.2	1348.9	1345.9	1343.9	1330.7	1297.3	1263.9	1239.7	1216.4	1194.1
10°	1533.1	1517.9	1506.8	1484.5	1473.4	1455.2	1411.7	1380.3	1338.8	1303.4	1256.9
12.5°	1719.3	1702.1	1664.7	1648.5	1634.3	1583.7	1540.2	1504.8	1423.8	1399.5	1341.9
15°	1855.9	1819.5	1815.5	1780.0	1778.0	1722.4	1639.4	1600.9	1538.2	1449.1	1389.4
17.5°	2003.7	1971.3	1946.0	1903.5	1897.4	1844.8	1784.1	1690.0	1621.2	1536.2	1460.3
20°	2112.0	2094.8	2051.2	2034.0	1998.6	1954.1	1891.4	1775.0	1691.0	1606.0	1512.9
22.5°	2198.0	2180.8	2146.4	2123.1	2102.9	2045.2	1970.3	1871.1	1755.8	1644.4	1548.3
25°	2197.0	2191.9	2177.7	2166.6	2151.4	2108.9	2046.2	1951.1	1822.5	1700.1	1566.5
27.5°	2072.5	2086.7	2111.0	2123.1	2120.1	2114.0	2078.6	1998.6	1883.3	1737.5	1587.8
30°	1813.4	1865.0	1910.6	1971.3	1989.5	2034.0	2054.3	2008.7	1916.7	1781.1	1615.1
32.5°	1503.8	1578.7	1677.8	1711.2	1768.9	1854.9	1951.1	1968.3	1910.6	1806.4	1632.3
35°	1233.6	1295.3	1372.2	1424.8	1476.5	1616.1	1737.5	1842.8	1862.0	1793.2	1628.2
37.5°	1021.1	1064.6	1132.4	1176.9	1224.5	1343.9	1513.9	1650.5	1746.6	1748.7	1617.1
40°	867.3	886.5	945.2	977.6	1023.1	1126.3	1278.1	1456.2	1596.9	1661.6	1587.8
42.5°	734.7	760.0	808.6	832.8	862.2	952.3	1052.4	1221.4	1395.5	1534.1	1533.1
45°	655.8	674.0	696.2	716.5	749.9	803.5	917.8	1044.3	1211.3	1368.2	1429.9
47.5°	585.9	603.1	625.4	631.5	653.7	704.3	774.2	884.5	1040.3	1196.1	1312.5
50°	527.2	541.4	556.6	567.7	577.8	619.3	671.9	765.0	889.5	1040.3	1185.0
52.5°	481.7	491.8	505.0	511.0	520.1	550.5	591.0	659.8	762.0	899.6	1040.3
55°	439.2	446.3	454.4	464.5	468.5	490.8	522.2	580.9	656.8	780.2	913.8
57.5°	399.7	402.8	407.8	413.9	419.0	438.2	465.5	505.0	571.8	666.9	793.4
60°	355.2	363.3	366.3	372.4	375.4	390.6	411.9	445.3	496.9	578.8	674.0
62.5°	317.8	322.8	327.9	330.9	338.0	343.1	360.3	390.6	433.1	493.8	579.9
65°	284.4	286.4	289.4	292.5	294.5	300.6	316.7	337.0	369.4	423.0	489.8
67.5°	245.9	247.9	252.0	253.0	255.0	263.1	272.2	289.4	316.7	357.2	411.9
70°	208.5	211.5	213.5	215.5	218.6	221.6	231.7	245.9	267.2	295.5	338.0
72.5°	176.1	179.1	179.1	181.1	180.1	184.2	194.3	204.4	218.6	241.9	279.3
75°	143.7	143.7	145.7	146.7	147.7	151.8	155.8	163.9	175.1	193.3	216.6
77.5°	113.3	112.3	114.4	114.4	114.4	117.4	121.4	125.5	132.6	145.7	163.9
80°	83.0	83.0	85.0	86.0	84.0	85.0	87.0	91.1	96.1	105.2	115.4
82.5°	54.6	58.7	57.7	58.7	57.7	59.7	60.7	61.7	63.8	67.8	74.9
85°	33.4	33.4	33.4	34.4	33.4	34.4	34.4	34.4	35.4	37.4	40.5
87.5°	14.2	14.2	14.2	15.2	14.2	14.2	15.2	14.2	15.2	15.2	16.2
90°	21.4	21.1	20.8	20.6	20.3	19.6	18.9	18.3	17.6	15.5	13.4
92.5°	24.6	24.5	24.3	24.2	23.6	22.5	21.4	20.2	19.1	17.6	16.2
95°	27.9	27.9	27.9	27.9	27.3	26.2	25.1	23.9	22.8	21.0	19.2
97.5°	29.8	29.6	29.5	29.4	28.7	27.4	26.1	24.8	23.5	31.8	40.1
100°	30.5	30.3	30.2	30.1	29.4	28.1	26.8	25.5	24.2	49.7	75.1
102.5°	30.9	30.6	30.3	30.1	32.8	38.2	43.5	48.9	54.3	82.7	111.1
105°	31.6	31.3	31.0	30.8	45.2	74.1	103.0	131.9	160.8	175.5	190.2
107.5°	119.2	140.5	161.9	172.6	185.2	210.3	235.4	260.5	285.6	283.2	280.7
110°	248.6	271.9	295.2	306.9	309.6	315.0	320.4	325.8	331.2	329.4	327.6

TEST NUMBER: P1010758

CATALOG NUMBER: S123DIP-B775D805UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	383.2	383.5	383.8	384.0	383.3	381.8	380.3	378.9	377.4	375.6	373.8
115°	430.5	429.8	429.1	428.8	428.0	426.4	424.7	423.1	421.5	420.0	418.6
117.5°	471.1	470.9	470.8	470.7	470.0	468.7	467.4	466.1	464.8	464.0	463.2
120°	512.5	512.5	512.5	512.5	511.9	510.6	509.3	508.0	506.7	506.2	505.7
122.5°	552.6	552.4	552.3	552.2	551.8	551.0	550.1	549.3	548.5	547.9	547.2
125°	589.7	589.4	589.1	588.9	588.7	588.4	588.1	587.7	587.4	586.8	586.1
127.5°	627.7	628.0	628.3	628.5	628.3	627.8	627.3	626.8	626.3	625.5	624.7
130°	663.0	663.3	663.6	663.8	663.5	662.8	662.1	661.5	660.8	660.2	659.5
132.5°	695.6	696.1	696.6	696.8	696.5	695.8	695.2	694.5	693.9	693.4	692.9
135°	728.7	729.2	729.7	729.9	729.7	729.2	728.7	728.2	727.7	727.0	726.4
137.5°	759.9	760.2	760.5	760.7	760.3	759.5	758.6	757.8	757.0	756.7	756.4
140°	787.8	788.1	788.4	788.6	788.3	787.6	787.0	786.3	785.7	785.2	784.7
142.5°	813.8	814.3	814.8	815.0	814.8	814.3	813.8	813.3	812.8	812.3	811.8
145°	839.3	839.3	839.3	839.3	839.1	838.8	838.5	838.1	837.8	837.5	837.1
147.5°	860.0	860.8	861.6	862.0	861.8	861.5	861.2	860.9	860.6	860.3	859.9
150°	881.4	881.9	882.4	882.6	882.4	882.1	881.8	881.4	881.1	880.8	880.5
152.5°	899.6	900.5	901.3	901.7	901.4	900.7	900.1	899.4	898.8	898.6	898.4
155°	916.2	917.1	918.1	918.6	918.2	917.4	916.5	915.7	914.9	914.7	914.6
157.5°	930.7	932.0	933.3	934.0	933.5	932.5	931.6	930.6	929.6	929.8	929.9
160°	943.6	944.8	945.9	946.5	946.0	945.0	944.1	943.1	942.1	942.3	942.4
162.5°	955.8	956.7	957.7	958.2	957.6	956.5	955.4	954.2	953.1	953.3	953.4
165°	965.7	966.8	967.9	968.5	967.8	966.5	965.2	963.9	962.6	962.8	963.0
167.5°	973.3	974.6	975.9	976.6	975.9	974.6	973.3	972.0	970.7	970.7	970.7
170°	979.9	981.2	982.5	983.2	982.5	981.2	979.9	978.6	977.3	977.3	977.3
172.5°	983.9	985.4	986.9	987.6	986.9	985.6	984.3	983.0	981.7	981.5	981.4
175°	987.3	988.6	989.9	990.5	989.9	988.8	987.7	986.5	985.4	985.2	985.1
177.5°	988.6	990.3	991.9	992.7	992.1	990.8	989.5	988.2	986.9	986.7	986.5
180°	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3

TEST NUMBER: P1010758

CATALOG NUMBER: S123DIP-B775D805UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	1072.7	1069.6	1069.6	1067.6	1061.5	1050.4	1049.4	1051.4	1045.4	1039.3	1030.2
5°	1125.3	1106.1	1100.0	1093.9	1081.8	1061.5	1053.5	1046.4	1035.2	1022.1	1007.9
7.5°	1169.8	1142.5	1134.4	1123.3	1099.0	1070.7	1052.4	1037.3	1022.1	1003.9	986.7
10°	1225.5	1186.0	1166.8	1150.6	1117.2	1077.7	1050.4	1028.2	1003.9	981.6	959.3
12.5°	1288.2	1224.5	1218.4	1178.9	1140.5	1081.8	1048.4	1016.0	983.6	956.3	933.0
15°	1340.8	1271.0	1245.7	1219.4	1145.5	1072.7	1040.3	1003.9	966.4	937.1	902.7
17.5°	1374.2	1316.6	1262.9	1227.5	1150.6	1085.8	1023.1	981.6	942.1	901.7	873.3
20°	1414.7	1330.7	1284.2	1236.6	1160.7	1075.7	1013.0	961.4	912.8	876.4	842.0
22.5°	1455.2	1341.9	1303.4	1251.8	1162.7	1065.6	994.8	943.1	887.5	851.1	813.6
25°	1451.2	1358.1	1294.3	1250.8	1142.5	1056.5	973.5	912.8	861.2	814.6	777.2
27.5°	1454.2	1339.8	1275.1	1224.5	1128.3	1043.3	951.2	887.5	833.9	785.3	745.8
30°	1455.2	1312.5	1255.8	1195.1	1102.0	1012.0	925.9	861.2	804.5	751.9	716.5
32.5°	1452.2	1290.3	1219.4	1164.8	1060.5	981.6	896.6	827.8	770.1	721.5	688.1
35°	1445.1	1263.9	1182.0	1113.2	1018.0	938.1	869.3	798.4	736.7	692.2	653.7
37.5°	1425.9	1235.6	1142.5	1074.7	968.4	887.5	826.8	768.1	708.4	655.8	623.4
40°	1411.7	1197.2	1103.0	1029.2	914.8	835.9	785.3	729.6	670.9	623.4	592.0
42.5°	1379.3	1160.7	1062.6	974.5	862.2	781.2	733.7	689.1	638.5	592.0	563.7
45°	1326.7	1121.3	1013.0	923.9	804.5	727.6	684.1	647.7	603.1	558.6	530.3
47.5°	1252.8	1064.6	960.4	871.3	747.8	669.9	626.4	599.1	563.7	526.2	501.9
50°	1172.9	1002.9	906.7	818.7	693.2	617.3	574.8	549.5	526.2	491.8	468.5
52.5°	1068.6	937.1	845.0	761.0	634.5	561.6	524.2	506.0	481.7	457.4	437.2
55°	967.4	852.1	776.2	696.2	576.8	509.0	472.6	453.4	439.2	419.0	402.8
57.5°	850.0	773.1	703.3	630.5	523.2	461.5	427.0	403.8	394.7	385.6	370.4
60°	741.8	683.1	626.4	565.7	467.5	411.9	378.5	360.3	351.2	345.1	335.0
62.5°	642.6	597.1	548.5	499.9	410.9	360.3	335.0	316.7	308.6	307.6	298.5
65°	547.5	515.1	475.6	428.1	358.2	313.7	289.4	278.3	269.2	269.2	262.1
67.5°	452.3	430.1	398.7	365.3	310.7	269.2	246.9	236.8	231.7	231.7	226.7
70°	376.4	361.3	332.9	303.6	256.0	224.7	207.5	198.3	195.3	196.3	192.3
72.5°	305.6	289.4	266.1	244.9	209.5	186.2	174.1	163.9	158.9	159.9	158.9
75°	236.8	228.7	208.5	192.3	163.9	147.7	136.6	131.6	127.5	128.5	126.5
77.5°	178.1	166.0	154.8	143.7	126.5	113.3	104.2	99.2	96.1	96.1	96.1
80°	121.4	119.4	110.3	104.2	90.1	79.9	72.9	71.8	68.8	68.8	68.8
82.5°	78.9	73.9	68.8	64.8	56.7	50.6	47.6	45.5	44.5	43.5	45.5
85°	43.5	40.5	38.5	34.4	31.4	28.3	25.3	24.3	23.3	24.3	23.3
87.5°	17.2	14.2	14.2	13.2	12.1	11.1	11.1	9.1	9.1	8.1	8.1
90°	11.3	9.2	8.1	7.3	5.6	4.0	2.3	0.7	2.3	4.0	5.6
92.5°	14.7	13.2	12.5	13.0	14.0	14.9	15.9	16.9	15.9	14.9	14.0
95°	17.4	15.6	14.7	18.0	24.7	31.4	38.1	44.8	38.1	31.4	24.7
97.5°	48.4	56.7	60.9	63.2	67.8	72.3	76.9	81.5	76.9	72.3	67.8
100°	100.6	126.1	138.8	137.2	133.9	130.6	127.4	124.1	127.4	130.6	133.9
102.5°	139.5	167.9	182.1	181.0	178.9	176.8	174.7	172.6	174.7	176.8	178.9
105°	204.9	219.6	226.9	226.0	224.2	222.4	220.6	218.8	220.6	222.4	224.2
107.5°	278.3	275.8	274.6	273.9	272.4	270.9	269.5	268.0	269.5	270.9	272.4
110°	325.8	324.0	323.1	322.4	321.1	319.8	318.5	317.2	318.5	319.8	321.1

TEST NUMBER: P1010758

CATALOG NUMBER: S123DIP-B775D805UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	372.0	370.2	369.3	368.7	367.6	366.5	365.3	364.2	365.3	366.5	367.6
115°	417.1	415.6	414.9	414.4	413.4	412.5	411.5	410.5	411.5	412.5	413.4
117.5°	462.3	461.5	461.1	460.5	459.4	458.3	457.1	456.0	457.1	458.3	459.4
120°	505.2	504.7	504.4	503.7	502.2	500.7	499.3	497.8	499.3	500.7	502.2
122.5°	546.6	545.9	545.6	545.0	543.9	542.7	541.6	540.4	541.6	542.7	543.9
125°	585.5	584.8	584.5	583.8	582.5	581.2	579.9	578.6	579.9	581.2	582.5
127.5°	623.9	623.1	622.7	622.0	620.7	619.4	618.1	616.8	618.1	619.4	620.7
130°	658.9	658.2	657.9	657.2	655.9	654.6	653.3	652.0	653.3	654.6	655.9
132.5°	692.4	691.9	691.7	691.0	689.7	688.4	687.1	685.8	687.1	688.4	689.7
135°	725.7	725.0	724.7	724.2	723.2	722.3	721.3	720.3	721.3	722.3	723.2
137.5°	756.1	755.8	755.6	754.9	753.6	752.3	751.0	749.7	751.0	752.3	753.6
140°	784.2	783.7	783.5	783.0	782.0	781.1	780.1	779.1	780.1	781.1	782.0
142.5°	811.3	810.8	810.6	810.1	809.1	808.2	807.2	806.2	807.2	808.2	809.1
145°	836.8	836.5	836.3	835.7	834.6	833.5	832.3	831.2	832.3	833.5	834.6
147.5°	859.6	859.3	859.1	858.7	857.9	857.0	856.2	855.4	856.2	857.0	857.9
150°	880.2	879.9	879.7	879.5	879.0	878.5	878.0	877.5	878.0	878.5	879.0
152.5°	898.3	898.1	898.0	897.9	897.8	897.6	897.5	897.3	897.5	897.6	897.8
155°	914.4	914.3	914.2	914.4	914.7	915.0	915.3	915.6	915.3	915.0	914.7
157.5°	930.1	930.2	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
160°	942.6	942.7	942.8	942.9	943.0	943.2	943.3	943.5	943.3	943.2	943.0
162.5°	953.6	953.7	953.8	954.0	954.5	955.0	955.5	956.0	955.5	955.0	954.5
165°	963.1	963.3	963.4	963.6	964.1	964.6	965.1	965.6	965.1	964.6	964.1
167.5°	970.7	970.7	970.7	971.0	971.7	972.4	973.0	973.7	973.0	972.4	971.7
170°	977.3	977.3	977.3	977.6	978.3	979.0	979.6	980.3	979.6	979.0	978.3
172.5°	981.2	981.1	981.0	981.4	982.2	983.1	983.9	984.7	983.9	983.1	982.2
175°	984.9	984.8	984.7	985.1	985.9	986.7	987.5	988.3	987.5	986.7	985.9
177.5°	986.4	986.2	986.1	986.5	987.3	988.2	989.0	989.8	989.0	988.2	987.3
180°	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3

TEST NUMBER: P1010758

CATALOG NUMBER: S123DIP-B775D805UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	1028.2	1027.1	1029.2	1023.1	1013.0	1007.9	993.7	990.7	989.7	990.7	991.7
5°	999.8	998.8	995.8	985.7	973.5	964.4	947.2	946.2	940.1	934.0	937.1
7.5°	972.5	968.4	962.4	949.2	933.0	922.9	908.7	898.6	890.5	885.5	881.4
10°	945.2	939.1	933.0	915.8	895.6	880.4	863.2	855.1	846.0	842.0	837.9
12.5°	909.8	903.7	892.6	872.3	860.2	840.9	823.7	815.6	810.6	802.5	797.4
15°	881.4	869.3	863.2	842.0	816.7	814.6	783.3	781.2	771.1	771.1	763.0
17.5°	849.0	839.9	828.8	807.5	789.3	771.1	754.9	748.9	739.7	737.7	733.7
20°	817.7	805.5	801.5	780.2	761.0	738.7	721.5	715.5	711.4	707.4	710.4
22.5°	785.3	775.2	765.0	745.8	731.6	709.4	699.3	693.2	687.1	685.1	686.1
25°	753.9	744.8	734.7	715.5	700.3	682.1	673.0	669.9	666.9	666.9	665.9
27.5°	723.6	714.4	705.3	688.1	673.0	659.8	652.7	649.7	646.6	648.7	650.7
30°	692.2	684.1	676.0	660.8	648.7	636.5	632.5	630.5	629.4	634.5	634.5
32.5°	663.8	656.8	650.7	636.5	624.4	614.3	611.2	612.2	613.2	616.3	618.3
35°	634.5	629.4	623.4	611.2	601.1	592.0	593.0	593.0	595.0	600.1	604.1
37.5°	608.2	601.1	596.0	585.9	577.8	569.7	572.8	575.8	577.8	583.9	585.9
40°	576.8	573.8	569.7	559.6	552.5	551.5	552.5	554.6	558.6	561.6	564.7
42.5°	551.5	547.5	542.4	534.3	528.2	529.3	530.3	532.3	534.3	539.4	542.4
45°	523.2	520.1	516.1	509.0	504.0	505.0	506.0	506.0	508.0	514.1	516.1
47.5°	491.8	492.8	487.8	480.7	477.6	477.6	477.6	479.7	484.7	486.8	487.8
50°	461.5	459.4	458.4	451.3	449.3	448.3	449.3	450.3	457.4	456.4	459.4
52.5°	429.1	429.1	428.1	424.0	421.0	421.0	419.0	424.0	426.0	428.1	431.1
55°	397.7	394.7	393.7	391.6	387.6	386.6	388.6	394.7	396.7	398.7	401.7
57.5°	363.3	363.3	361.3	358.2	358.2	358.2	358.2	362.3	365.3	367.3	373.4
60°	331.9	327.9	324.8	324.8	324.8	323.8	329.9	329.9	336.0	337.0	339.0
62.5°	294.5	292.5	290.4	291.4	290.4	292.5	294.5	298.5	299.5	302.6	305.6
65°	259.1	259.1	257.0	263.1	259.1	259.1	264.1	264.1	266.1	269.2	273.2
67.5°	224.7	225.7	223.6	223.6	225.7	226.7	227.7	231.7	232.8	236.8	241.9
70°	189.2	191.3	192.3	190.2	192.3	194.3	196.3	197.3	201.4	203.4	206.4
72.5°	157.9	159.9	156.9	157.9	158.9	160.9	161.9	163.9	166.0	172.0	174.1
75°	126.5	125.5	124.5	128.5	126.5	130.5	131.6	131.6	133.6	138.6	140.7
77.5°	97.1	97.1	98.2	96.1	99.2	98.2	99.2	102.2	105.2	105.2	113.3
80°	67.8	69.8	69.8	69.8	70.8	71.8	69.8	74.9	75.9	75.9	78.9
82.5°	43.5	44.5	43.5	45.5	45.5	47.6	46.6	47.6	49.6	51.6	52.6
85°	23.3	23.3	25.3	25.3	24.3	25.3	24.3	25.3	27.3	27.3	28.3
87.5°	8.1	8.1	8.1	8.1	9.1	8.1	9.1	9.1	8.1	8.1	11.1
90°	7.3	8.1	9.2	11.3	13.4	15.5	17.6	18.3	18.9	19.6	20.3
92.5°	13.0	12.5	13.2	14.7	16.2	17.6	19.1	20.2	21.4	22.5	23.6
95°	18.0	14.7	15.6	17.4	19.2	21.0	22.8	23.9	25.1	26.2	27.3
97.5°	63.2	60.9	56.7	48.4	40.1	31.8	23.5	24.8	26.1	27.4	28.7
100°	137.2	138.8	126.1	100.6	75.1	49.7	24.2	25.5	26.8	28.1	29.4
102.5°	181.0	182.1	167.9	139.5	111.1	82.7	54.3	48.9	43.5	38.2	32.8
105°	226.0	226.9	219.6	204.9	190.2	175.5	160.8	131.9	103.0	74.1	45.2
107.5°	273.9	274.6	275.8	278.3	280.7	283.2	285.6	260.5	235.4	210.3	185.2
110°	322.4	323.1	324.0	325.8	327.6	329.4	331.2	325.8	320.4	315.0	309.6

TEST NUMBER: P1010758

CATALOG NUMBER: S123DIP-B775D805UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	368.7	369.3	370.2	372.0	373.8	375.6	377.4	378.9	380.3	381.8	383.3
115°	414.4	414.9	415.6	417.1	418.6	420.0	421.5	423.1	424.7	426.4	428.0
117.5°	460.5	461.1	461.5	462.3	463.2	464.0	464.8	466.1	467.4	468.7	470.0
120°	503.7	504.4	504.7	505.2	505.7	506.2	506.7	508.0	509.3	510.6	511.9
122.5°	545.0	545.6	545.9	546.6	547.2	547.9	548.5	549.3	550.1	551.0	551.8
125°	583.8	584.5	584.8	585.5	586.1	586.8	587.4	587.7	588.1	588.4	588.7
127.5°	622.0	622.7	623.1	623.9	624.7	625.5	626.3	626.8	627.3	627.8	628.3
130°	657.2	657.9	658.2	658.9	659.5	660.2	660.8	661.5	662.1	662.8	663.5
132.5°	691.0	691.7	691.9	692.4	692.9	693.4	693.9	694.5	695.2	695.8	696.5
135°	724.2	724.7	725.0	725.7	726.4	727.0	727.7	728.2	728.7	729.2	729.7
137.5°	754.9	755.6	755.8	756.1	756.4	756.7	757.0	757.8	758.6	759.5	760.3
140°	783.0	783.5	783.7	784.2	784.7	785.2	785.7	786.3	787.0	787.6	788.3
142.5°	810.1	810.6	810.8	811.3	811.8	812.3	812.8	813.3	813.8	814.3	814.8
145°	835.7	836.3	836.5	836.8	837.1	837.5	837.8	838.1	838.5	838.8	839.1
147.5°	858.7	859.1	859.3	859.6	859.9	860.3	860.6	860.9	861.2	861.5	861.8
150°	879.5	879.7	879.9	880.2	880.5	880.8	881.1	881.4	881.8	882.1	882.4
152.5°	897.9	898.0	898.1	898.3	898.4	898.6	898.8	899.4	900.1	900.7	901.4
155°	914.4	914.2	914.3	914.4	914.6	914.7	914.9	915.7	916.5	917.4	918.2
157.5°	930.3	930.3	930.2	930.1	929.9	929.8	929.6	930.6	931.6	932.5	933.5
160°	942.9	942.8	942.7	942.6	942.4	942.3	942.1	943.1	944.1	945.0	946.0
162.5°	954.0	953.8	953.7	953.6	953.4	953.3	953.1	954.2	955.4	956.5	957.6
165°	963.6	963.4	963.3	963.1	963.0	962.8	962.6	963.9	965.2	966.5	967.8
167.5°	971.0	970.7	970.7	970.7	970.7	970.7	970.7	972.0	973.3	974.6	975.9
170°	977.6	977.3	977.3	977.3	977.3	977.3	977.3	978.6	979.9	981.2	982.5
172.5°	981.4	981.0	981.1	981.2	981.4	981.5	981.7	983.0	984.3	985.6	986.9
175°	985.1	984.7	984.8	984.9	985.1	985.2	985.4	986.5	987.7	988.8	989.9
177.5°	986.5	986.1	986.2	986.4	986.5	986.7	986.9	988.2	989.5	990.8	992.1
180°	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3

TEST NUMBER: P1010758

CATALOG NUMBER: S123DIP-B775D805UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	990.7	991.7	987.7	984.6	992.7	987.7	987.7	988.7	986.7	989.7	988.7
5°	935.1	936.1	929.0	931.0	927.0	925.9	924.9	931.0	930.0	929.0	931.0
7.5°	880.4	880.4	877.4	875.3	875.3	872.3	876.4	875.3	877.4	877.4	880.4
10°	834.9	836.9	831.8	826.8	825.8	826.8	826.8	827.8	828.8	835.9	834.9
12.5°	797.4	794.4	793.4	790.3	785.3	783.3	781.2	792.4	789.3	789.3	789.3
15°	755.9	763.0	762.0	752.9	750.9	754.9	752.9	752.9	763.0	762.0	761.0
17.5°	733.7	731.6	729.6	724.6	725.6	724.6	725.6	725.6	731.6	731.6	731.6
20°	708.4	704.3	704.3	702.3	702.3	699.3	703.3	704.3	708.4	708.4	709.4
22.5°	686.1	683.1	683.1	682.1	684.1	680.0	684.1	685.1	685.1	688.1	688.1
25°	666.9	664.9	664.9	666.9	666.9	666.9	666.9	670.9	667.9	668.9	667.9
27.5°	649.7	650.7	651.7	652.7	651.7	652.7	653.7	655.8	656.8	655.8	653.7
30°	633.5	636.5	637.5	637.5	639.6	640.6	641.6	641.6	642.6	639.6	641.6
32.5°	621.3	621.3	623.4	624.4	626.4	627.4	627.4	629.4	628.4	625.4	626.4
35°	604.1	604.1	608.2	610.2	613.2	612.2	613.2	613.2	614.3	612.2	609.2
37.5°	586.9	589.0	589.0	593.0	594.0	595.0	594.0	596.0	595.0	593.0	592.0
40°	566.7	565.7	566.7	569.7	570.7	570.7	570.7	572.8	572.8	572.8	571.8
42.5°	541.4	544.4	543.4	546.5	545.4	545.4	547.5	549.5	550.5	547.5	548.5
45°	517.1	517.1	519.1	519.1	520.1	520.1	524.2	522.2	524.2	522.2	523.2
47.5°	490.8	491.8	491.8	492.8	494.8	496.9	494.8	495.9	495.9	496.9	494.8
50°	461.5	461.5	463.5	466.5	470.6	468.5	467.5	471.6	468.5	468.5	466.5
52.5°	431.1	434.1	435.1	438.2	441.2	442.2	443.2	441.2	442.2	439.2	440.2
55°	401.7	402.8	406.8	409.8	412.9	412.9	411.9	412.9	413.9	409.8	409.8
57.5°	372.4	375.4	379.5	379.5	383.5	383.5	382.5	382.5	383.5	380.5	379.5
60°	341.0	344.1	349.1	349.1	355.2	356.2	354.2	352.2	352.2	349.1	350.1
62.5°	307.6	310.7	313.7	318.8	322.8	320.8	324.8	320.8	321.8	315.7	315.7
65°	278.3	279.3	284.4	289.4	289.4	291.4	289.4	290.4	287.4	287.4	283.3
67.5°	243.9	243.9	248.9	254.0	259.1	259.1	259.1	256.0	256.0	253.0	253.0
70°	213.5	212.5	217.6	220.6	223.6	224.7	222.6	221.6	219.6	216.6	215.5
72.5°	176.1	178.1	183.2	185.2	190.2	189.2	194.3	188.2	188.2	183.2	182.2
75°	142.7	144.7	149.8	152.8	155.8	155.8	158.9	155.8	151.8	149.8	148.8
77.5°	113.3	112.3	116.4	121.4	122.4	121.4	123.5	122.4	118.4	118.4	116.4
80°	81.0	84.0	88.0	87.0	91.1	90.1	90.1	88.0	88.0	85.0	87.0
82.5°	53.6	56.7	57.7	56.7	57.7	59.7	60.7	59.7	59.7	57.7	58.7
85°	28.3	28.3	30.4	31.4	30.4	30.4	31.4	34.4	32.4	30.4	32.4
87.5°	9.1	8.1	8.1	9.1	8.1	8.1	9.1	9.1	10.1	10.1	10.1
90°	20.6	20.8	21.1	21.4	21.7	22.0	21.7	21.4	21.1	20.8	20.6
92.5°	24.2	24.3	24.5	24.6	24.8	25.0	24.8	24.6	24.5	24.3	24.2
95°	27.9	27.9	27.9	27.9	27.9	27.9	27.9	27.9	27.9	27.9	27.9
97.5°	29.4	29.5	29.6	29.8	29.9	30.1	29.9	29.8	29.6	29.5	29.4
100°	30.1	30.2	30.3	30.5	30.6	30.8	30.6	30.5	30.3	30.2	30.1
102.5°	30.1	30.3	30.6	30.9	31.3	31.6	31.3	30.9	30.6	30.3	30.1
105°	30.8	31.0	31.3	31.6	32.0	32.3	32.0	31.6	31.3	31.0	30.8
107.5°	172.6	161.9	140.5	119.2	97.8	76.4	97.8	119.2	140.5	161.9	172.6
110°	306.9	295.2	271.9	248.6	225.2	201.9	225.2	248.6	271.9	295.2	306.9

TEST NUMBER: P1010758

CATALOG NUMBER: S123DIP-B775D805UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	384.0	383.8	383.5	383.2	382.9	382.6	382.9	383.2	383.5	383.8	384.0
115°	428.8	429.1	429.8	430.5	431.1	431.8	431.1	430.5	429.8	429.1	428.8
117.5°	470.7	470.8	470.9	471.1	471.2	471.4	471.2	471.1	470.9	470.8	470.7
120°	512.5	512.5	512.5	512.5	512.5	512.5	512.5	512.5	512.5	512.5	512.5
122.5°	552.2	552.3	552.4	552.6	552.7	552.9	552.7	552.6	552.4	552.3	552.2
125°	588.9	589.1	589.4	589.7	590.1	590.4	590.1	589.7	589.4	589.1	588.9
127.5°	628.5	628.3	628.0	627.7	627.4	627.1	627.4	627.7	628.0	628.3	628.5
130°	663.8	663.6	663.3	663.0	662.6	662.3	662.6	663.0	663.3	663.6	663.8
132.5°	696.8	696.6	696.1	695.6	695.1	694.6	695.1	695.6	696.1	696.6	696.8
135°	729.9	729.7	729.2	728.7	728.2	727.7	728.2	728.7	729.2	729.7	729.9
137.5°	760.7	760.5	760.2	759.9	759.5	759.2	759.5	759.9	760.2	760.5	760.7
140°	788.6	788.4	788.1	787.8	787.4	787.1	787.4	787.8	788.1	788.4	788.6
142.5°	815.0	814.8	814.3	813.8	813.3	812.8	813.3	813.8	814.3	814.8	815.0
145°	839.3	839.3	839.3	839.3	839.3	839.3	839.3	839.3	839.3	839.3	839.3
147.5°	862.0	861.6	860.8	860.0	859.2	858.4	859.2	860.0	860.8	861.6	862.0
150°	882.6	882.4	881.9	881.4	880.9	880.4	880.9	881.4	881.9	882.4	882.6
152.5°	901.7	901.3	900.5	899.6	898.8	898.0	898.8	899.6	900.5	901.3	901.7
155°	918.6	918.1	917.1	916.2	915.2	914.2	915.2	916.2	917.1	918.1	918.6
157.5°	934.0	933.3	932.0	930.7	929.4	928.1	929.4	930.7	932.0	933.3	934.0
160°	946.5	945.9	944.8	943.6	942.5	941.3	942.5	943.6	944.8	945.9	946.5
162.5°	958.2	957.7	956.7	955.8	954.8	953.8	954.8	955.8	956.7	957.7	958.2
165°	968.5	967.9	966.8	965.7	964.5	963.4	964.5	965.7	966.8	967.9	968.5
167.5°	976.6	975.9	974.6	973.3	972.0	970.7	972.0	973.3	974.6	975.9	976.6
170°	983.2	982.5	981.2	979.9	978.6	977.3	978.6	979.9	981.2	982.5	983.2
172.5°	987.6	986.9	985.4	983.9	982.5	981.0	982.5	983.9	985.4	986.9	987.6
175°	990.5	989.9	988.6	987.3	986.0	984.7	986.0	987.3	988.6	989.9	990.5
177.5°	992.7	991.9	990.3	988.6	987.0	985.4	987.0	988.6	990.3	991.9	992.7
180°	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3

TEST NUMBER: P1010758

CATALOG NUMBER: S123DIP-B775D805UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	991.7	993.7	994.8	990.7	987.7	992.7	999.8	1004.9	1008.9	1014.0	1017.0
5°	933.0	940.1	940.1	942.1	945.2	950.2	963.4	972.5	980.6	986.7	991.7
7.5°	883.4	888.5	891.5	896.6	901.7	908.7	923.9	937.1	949.2	956.3	964.4
10°	838.9	843.0	848.0	851.1	860.2	870.3	889.5	900.6	914.8	925.9	936.1
12.5°	796.4	810.6	813.6	812.6	820.7	831.8	851.1	868.3	883.4	894.6	905.7
15°	766.1	771.1	777.2	776.2	793.4	796.4	812.6	832.8	853.1	860.2	870.3
17.5°	732.7	740.8	746.8	749.9	754.9	766.1	781.2	796.4	822.7	823.7	850.0
20°	706.3	714.4	718.5	722.5	725.6	738.7	751.9	769.1	790.3	801.5	815.6
22.5°	689.1	693.2	696.2	699.3	703.3	710.4	726.6	745.8	760.0	772.1	781.2
25°	668.9	673.0	677.0	679.0	682.1	686.1	698.3	713.4	733.7	741.8	750.9
27.5°	654.7	654.7	656.8	656.8	660.8	664.9	674.0	688.1	704.3	714.4	726.6
30°	639.6	638.5	639.6	638.5	637.5	643.6	651.7	663.8	675.0	687.1	695.2
32.5°	624.4	623.4	623.4	624.4	620.3	623.4	627.4	638.5	650.7	656.8	665.9
35°	608.2	606.2	606.2	606.2	604.1	602.1	606.2	616.3	624.4	632.5	639.6
37.5°	592.0	589.0	589.0	586.9	584.9	581.9	581.9	590.0	601.1	604.1	613.2
40°	569.7	569.7	567.7	566.7	564.7	562.7	559.6	566.7	576.8	579.9	586.9
42.5°	547.5	544.4	543.4	543.4	543.4	540.4	538.4	543.4	549.5	554.6	558.6
45°	522.2	520.1	521.2	520.1	518.1	517.1	516.1	518.1	525.2	527.2	532.3
47.5°	494.8	493.8	493.8	492.8	491.8	492.8	488.8	493.8	495.9	497.9	501.9
50°	466.5	465.5	464.5	463.5	463.5	464.5	463.5	463.5	467.5	469.6	473.6
52.5°	438.2	435.1	435.1	434.1	434.1	432.1	434.1	435.1	437.2	439.2	441.2
55°	407.8	407.8	404.8	404.8	402.8	402.8	403.8	402.8	406.8	408.8	408.8
57.5°	378.5	374.4	375.4	373.4	371.4	370.4	370.4	372.4	374.4	374.4	376.4
60°	347.1	343.1	342.0	338.0	340.0	337.0	338.0	338.0	342.0	340.0	342.0
62.5°	315.7	310.7	307.6	305.6	305.6	306.6	304.6	303.6	305.6	307.6	311.7
65°	282.3	279.3	276.3	273.2	273.2	272.2	274.2	271.2	270.2	271.2	273.2
67.5°	247.9	244.9	241.9	238.8	239.8	236.8	234.8	237.8	235.8	236.8	238.8
70°	214.5	212.5	206.4	204.4	203.4	204.4	203.4	201.4	204.4	203.4	204.4
72.5°	181.1	179.1	176.1	171.0	171.0	170.0	169.0	169.0	168.0	168.0	168.0
75°	148.8	144.7	141.7	140.7	138.6	137.6	136.6	134.6	135.6	136.6	134.6
77.5°	115.4	110.3	109.3	109.3	106.3	106.3	107.3	106.3	105.2	105.2	105.2
80°	85.0	81.0	81.0	78.9	76.9	76.9	76.9	76.9	75.9	74.9	75.9
82.5°	54.6	53.6	52.6	52.6	54.6	50.6	52.6	51.6	50.6	50.6	49.6
85°	30.4	31.4	30.4	31.4	29.3	30.4	30.4	30.4	29.3	30.4	28.3
87.5°	11.1	11.1	11.1	12.1	12.1	12.1	12.1	12.1	13.2	12.1	12.1
90°	20.3	19.6	18.9	18.3	17.6	15.5	13.4	11.3	9.2	8.1	7.3
92.5°	23.6	22.5	21.4	20.2	19.1	17.6	16.2	14.7	13.2	12.5	13.0
95°	27.3	26.2	25.1	23.9	22.8	21.0	19.2	17.4	15.6	14.7	18.0
97.5°	28.7	27.4	26.1	24.8	23.5	31.8	40.1	48.4	56.7	60.9	63.2
100°	29.4	28.1	26.8	25.5	24.2	49.7	75.1	100.6	126.1	138.8	137.2
102.5°	32.8	38.2	43.5	48.9	54.3	82.7	111.1	139.5	167.9	182.1	181.0
105°	45.2	74.1	103.0	131.9	160.8	175.5	190.2	204.9	219.6	226.9	226.0
107.5°	185.2	210.3	235.4	260.5	285.6	283.2	280.7	278.3	275.8	274.6	273.9
110°	309.6	315.0	320.4	325.8	331.2	329.4	327.6	325.8	324.0	323.1	322.4

TEST NUMBER: P1010758

CATALOG NUMBER: S123DIP-B775D805UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	383.3	381.8	380.3	378.9	377.4	375.6	373.8	372.0	370.2	369.3	368.7
115°	428.0	426.4	424.7	423.1	421.5	420.0	418.6	417.1	415.6	414.9	414.4
117.5°	470.0	468.7	467.4	466.1	464.8	464.0	463.2	462.3	461.5	461.1	460.5
120°	511.9	510.6	509.3	508.0	506.7	506.2	505.7	505.2	504.7	504.4	503.7
122.5°	551.8	551.0	550.1	549.3	548.5	547.9	547.2	546.6	545.9	545.6	545.0
125°	588.7	588.4	588.1	587.7	587.4	586.8	586.1	585.5	584.8	584.5	583.8
127.5°	628.3	627.8	627.3	626.8	626.3	625.5	624.7	623.9	623.1	622.7	622.0
130°	663.5	662.8	662.1	661.5	660.8	660.2	659.5	658.9	658.2	657.9	657.2
132.5°	696.5	695.8	695.2	694.5	693.9	693.4	692.9	692.4	691.9	691.7	691.0
135°	729.7	729.2	728.7	728.2	727.7	727.0	726.4	725.7	725.0	724.7	724.2
137.5°	760.3	759.5	758.6	757.8	757.0	756.7	756.4	756.1	755.8	755.6	754.9
140°	788.3	787.6	787.0	786.3	785.7	785.2	784.7	784.2	783.7	783.5	783.0
142.5°	814.8	814.3	813.8	813.3	812.8	812.3	811.8	811.3	810.8	810.6	810.1
145°	839.1	838.8	838.5	838.1	837.8	837.5	837.1	836.8	836.5	836.3	835.7
147.5°	861.8	861.5	861.2	860.9	860.6	860.3	859.9	859.6	859.3	859.1	858.7
150°	882.4	882.1	881.8	881.4	881.1	880.8	880.5	880.2	879.9	879.7	879.5
152.5°	901.4	900.7	900.1	899.4	898.8	898.6	898.4	898.3	898.1	898.0	897.9
155°	918.2	917.4	916.5	915.7	914.9	914.7	914.6	914.4	914.3	914.2	914.4
157.5°	933.5	932.5	931.6	930.6	929.6	929.8	929.9	930.1	930.2	930.3	930.3
160°	946.0	945.0	944.1	943.1	942.1	942.3	942.4	942.6	942.7	942.8	942.9
162.5°	957.6	956.5	955.4	954.2	953.1	953.3	953.4	953.6	953.7	953.8	954.0
165°	967.8	966.5	965.2	963.9	962.6	962.8	963.0	963.1	963.3	963.4	963.6
167.5°	975.9	974.6	973.3	972.0	970.7	970.7	970.7	970.7	970.7	970.7	971.0
170°	982.5	981.2	979.9	978.6	977.3	977.3	977.3	977.3	977.3	977.3	977.6
172.5°	986.9	985.6	984.3	983.0	981.7	981.5	981.4	981.2	981.1	981.0	981.4
175°	989.9	988.8	987.7	986.5	985.4	985.2	985.1	984.9	984.8	984.7	985.1
177.5°	992.1	990.8	989.5	988.2	986.9	986.7	986.5	986.4	986.2	986.1	986.5
180°	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3

TEST NUMBER: P1010758

CATALOG NUMBER: S123DIP-B775D805UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1044.3	1044.3	1044.3	1044.3
2.5°	1022.1	1025.1	1035.2	1047.4
5°	1001.8	1009.9	1024.1	1043.3
7.5°	979.6	991.7	1012.0	1036.2
10°	954.3	971.5	996.8	1027.1
12.5°	927.0	949.2	981.6	1013.0
15°	909.8	932.0	961.4	995.8
17.5°	876.4	902.7	933.0	981.6
20°	842.0	871.3	910.8	959.3
22.5°	815.6	847.0	884.5	936.1
25°	784.3	816.7	857.1	910.8
27.5°	750.9	783.3	828.8	885.5
30°	725.6	756.9	800.5	861.2
32.5°	695.2	725.6	771.1	834.9
35°	660.8	695.2	738.7	803.5
37.5°	634.5	665.9	711.4	773.1
40°	606.2	633.5	678.0	738.7
42.5°	575.8	606.2	644.6	705.3
45°	547.5	569.7	609.2	666.9
47.5°	517.1	542.4	572.8	617.3
50°	484.7	506.0	539.4	569.7
52.5°	453.4	470.6	498.9	522.2
55°	420.0	437.2	458.4	472.6
57.5°	388.6	400.7	414.9	424.0
60°	350.1	362.3	371.4	380.5
62.5°	315.7	324.8	329.9	335.0
65°	280.3	285.4	288.4	292.5
67.5°	241.9	246.9	247.9	254.0
70°	206.4	207.5	209.5	212.5
72.5°	173.0	175.1	174.1	176.1
75°	138.6	140.7	138.6	140.7
77.5°	105.2	107.3	107.3	110.3
80°	75.9	76.9	77.9	77.9
82.5°	49.6	52.6	50.6	51.6
85°	28.3	29.3	29.3	30.4
87.5°	13.2	14.2	13.2	15.2
90°	5.6	4.0	2.3	0.7
92.5°	14.0	14.9	15.9	16.9
95°	24.7	31.4	38.1	44.8
97.5°	67.8	72.3	76.9	81.5
100°	133.9	130.6	127.4	124.1
102.5°	178.9	176.8	174.7	172.6
105°	224.2	222.4	220.6	218.8
107.5°	272.4	270.9	269.5	268.0
110°	321.1	319.8	318.5	317.2



TEST NUMBER: P1010758

CATALOG NUMBER: S123DIP-B775D805UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	367.6	366.5	365.3	364.2
115°	413.4	412.5	411.5	410.5
117.5°	459.4	458.3	457.1	456.0
120°	502.2	500.7	499.3	497.8
122.5°	543.9	542.7	541.6	540.4
125°	582.5	581.2	579.9	578.6
127.5°	620.7	619.4	618.1	616.8
130°	655.9	654.6	653.3	652.0
132.5°	689.7	688.4	687.1	685.8
135°	723.2	722.3	721.3	720.3
137.5°	753.6	752.3	751.0	749.7
140°	782.0	781.1	780.1	779.1
142.5°	809.1	808.2	807.2	806.2
145°	834.6	833.5	832.3	831.2
147.5°	857.9	857.0	856.2	855.4
150°	879.0	878.5	878.0	877.5
152.5°	897.8	897.6	897.5	897.3
155°	914.7	915.0	915.3	915.6
157.5°	930.3	930.3	930.3	930.3
160°	943.0	943.2	943.3	943.5
162.5°	954.5	955.0	955.5	956.0
165°	964.1	964.6	965.1	965.6
167.5°	971.7	972.4	973.0	973.7
170°	978.3	979.0	979.6	980.3
172.5°	982.2	983.1	983.9	984.7
175°	985.9	986.7	987.5	988.3
177.5°	987.3	988.2	989.0	989.8
180°	988.3	988.3	988.3	988.3

(END OF REPORT)