

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010774

Luminaire Tested: S123RDIP-B1000D1025UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010774
REPORT IS A COMBINATION OF REPORTS P992730 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1000D1025UB2750-4F0-XX-W2A-F_2700K
Description: Define 3 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7759.0 lumens
Efficiency: N/A
Efficacy: 103.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010774

CATALOG NUMBER: S123RDIP-B1000D1025UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1010774

CATALOG NUMBER: S123RDIP-B1000D1025UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82		68	68	68		54
1	98	94	90	86	90	86	83	80	73	70	68		60	59	57		49
2	89	82	76	71	82	76	71	66	64	60	57		53	51	48		43
3	82	72	65	60	75	67	61	56	57	52	48		47	44	41		39
4	75	64	56	51	69	59	53	47	51	45	41		42	38	35		35
5	69	57	49	43	63	53	46	41	45	40	36		38	34	31		31
6	63	51	44	38	58	48	41	36	41	35	31		35	30	27		28
7	59	47	39	33	54	43	36	31	37	32	28		31	27	24		26
8	54	42	35	29	50	39	33	28	34	29	25		29	25	22		24
9	51	39	31	26	47	36	29	25	31	26	22		27	22	19		22
10	47	36	28	24	44	33	27	22	29	24	20		25	21	18		21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17800	17800	17800
5°	17829	17170	17124
10°	17689	16525	16199
15°	17460	15727	15186
20°	17158	14859	14055
25°	16848	13958	12981
30°	16449	12998	11714
35°	16039	12056	10560
40°	15652	11032	9284
45°	15159	10031	8138
50°	14612	8963	6950
55°	14046	7819	5863
60°	13505	6646	4759
65°	12807	5442	3714
70°	11927	4115	2654
75°	10662	2788	2104
80°	9099	1937	1475
85°	6829	1047	774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15159 cd/sqm

TEST NUMBER: P1010774

CATALOG NUMBER: S123RDIP-B1000D1025UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.5	2.0
10°-20°	432.5	5.6
20°-30°	622.7	8.0
30°-40°	701.2	9.0
40°-50°	670.7	8.6
50°-60°	549.1	7.1
60°-70°	370.2	4.8
70°-80°	185.7	2.4
80°-90°	51.2	0.7
90°-100°	46.5	0.6
100°-110°	224.8	2.9
110°-120°	551.0	7.1
120°-130°	699.5	9.0
130°-140°	747.2	9.6
140°-150°	698.7	9.0
150°-160°	563.6	7.3
160°-170°	363.7	4.7
170°-180°	125.3	1.6
0°-30°	1210.6	15.6
0°-40°	1911.8	24.6
0°-60°	3131.6	40.4
0°-90°	3738.6	48.2
90°-120°	822.3	10.6
90°-150°	2967.7	38.2
90°-180°	4020.0	51.8
0°-180°	7759.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1654	1654	1654	1654	1654	
5°	1654	1647	1631	1643	1640	157
15°	1577	1562	1525	1518	1509	444
25°	1435	1402	1340	1312	1297	660
35°	1242	1194	1110	1053	1029	777
45°	1021	960	857	781	748	788
55°	775	710	596	518	491	695
65°	530	456	351	286	271	524
75°	280	216	142	129	126	299
85°	71	42	38	35	35	78
90°	1	11	24	27	29	8
95°	60	20	30	37	37	71
105°	292	303	215	41	43	310
115°	548	554	562	572	576	541
125°	772	780	784	786	788	690
135°	961	967	971	974	971	740
145°	1109	1116	1118	1120	1120	694
155°	1222	1220	1221	1226	1220	563
165°	1288	1286	1284	1292	1286	364
175°	1319	1314	1315	1322	1314	126
180°	1319	1319	1319	1319	1319	

TEST NUMBER: P1010774

CATALOG NUMBER: S123RDIP-B1000D1025UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1653.7	1653.7	1653.7	1653.7	1653.7
2.5°	1660.4	1655.0	1638.9	1653.7	1651.0
5°	1653.7	1647.0	1630.9	1643.0	1640.3
7.5°	1641.6	1634.9	1614.8	1622.9	1618.8
10°	1625.5	1616.1	1592.0	1593.3	1586.6
12.5°	1602.7	1592.0	1561.2	1559.8	1551.8
15°	1577.3	1562.5	1524.9	1518.2	1508.8
17.5°	1546.4	1530.3	1483.4	1470.0	1456.5
20°	1511.5	1490.1	1439.1	1421.7	1405.6
22.5°	1472.6	1447.2	1392.2	1369.4	1354.6
25°	1435.1	1401.6	1339.9	1311.7	1296.9
27.5°	1389.5	1353.3	1286.2	1248.7	1225.9
30°	1342.5	1302.3	1227.2	1181.6	1160.1
32.5°	1295.6	1248.7	1168.2	1117.2	1094.4
35°	1242.0	1193.7	1110.5	1052.8	1028.7
37.5°	1188.3	1136.0	1048.8	984.4	954.9
40°	1137.3	1078.3	983.1	913.4	882.5
42.5°	1079.7	1020.7	921.4	843.6	816.8
45°	1020.7	960.3	857.0	780.6	748.4
47.5°	963.0	895.9	794.0	710.8	682.7
50°	898.6	835.6	726.9	643.8	612.9
52.5°	840.9	771.2	663.9	576.7	549.9
55°	775.2	709.5	595.5	517.7	490.9
57.5°	716.2	645.1	529.8	456.0	433.2
60°	654.5	580.7	469.4	397.0	374.2
62.5°	592.8	519.0	407.7	340.7	316.5
65°	529.8	456.0	351.4	285.7	270.9
67.5°	466.7	391.6	289.7	240.1	224.0
70°	405.0	332.6	238.7	191.8	177.0
72.5°	343.3	272.3	189.1	152.9	148.9
75°	280.3	215.9	142.2	128.8	126.1
77.5°	222.6	163.6	111.3	103.3	100.6
80°	167.6	112.7	84.5	80.5	77.8
82.5°	115.3	69.7	60.4	56.3	56.3
85°	71.1	41.6	37.6	34.9	34.9
87.5°	32.2	17.4	17.4	16.1	14.8
90°	1.0	10.8	23.5	27.4	29.4
92.5°	22.5	16.7	25.5	32.3	33.3
95°	59.8	19.6	30.4	37.2	37.2
97.5°	108.8	81.3	31.4	39.2	40.2
100°	165.6	185.2	32.3	40.2	41.2
102.5°	230.2	243.0	72.5	40.2	42.1
105°	292.0	302.7	214.6	41.2	43.1
107.5°	357.6	366.4	381.1	230.2	101.9
110°	423.3	431.1	441.9	409.5	269.4

TEST NUMBER: P1010774

CATALOG NUMBER: S123RDIP-B1000D1025UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	486.0	492.8	503.6	512.4	510.5
115°	547.7	553.6	562.4	572.2	576.1
117.5°	608.4	615.3	620.2	628.0	629.0
120°	664.3	673.1	676.0	683.9	683.9
122.5°	721.1	728.0	731.9	736.8	737.8
125°	772.1	779.9	783.8	785.8	787.7
127.5°	823.0	830.8	835.7	838.7	836.7
130°	870.0	877.9	881.8	885.7	883.7
132.5°	915.1	922.9	925.9	929.8	926.9
135°	961.2	967.0	970.9	973.9	970.9
137.5°	1000.3	1008.2	1010.1	1015.0	1013.1
140°	1039.5	1045.4	1048.3	1052.3	1050.3
142.5°	1075.8	1081.7	1084.6	1087.5	1084.6
145°	1109.1	1116.0	1117.9	1119.9	1119.9
147.5°	1141.4	1146.3	1148.3	1150.2	1145.3
150°	1170.8	1173.8	1175.7	1177.7	1174.7
152.5°	1197.3	1198.3	1199.2	1203.2	1198.3
155°	1221.8	1219.8	1220.8	1225.7	1219.8
157.5°	1241.4	1241.4	1240.4	1246.3	1238.4
160°	1259.0	1258.0	1257.0	1262.9	1256.1
162.5°	1275.7	1272.7	1271.7	1278.6	1272.7
165°	1288.4	1285.5	1284.5	1292.3	1285.5
167.5°	1299.2	1295.3	1295.3	1303.1	1295.3
170°	1308.0	1304.1	1304.1	1311.9	1304.1
172.5°	1313.9	1309.0	1309.9	1317.8	1309.0
175°	1318.8	1313.9	1314.8	1321.7	1313.9
177.5°	1320.7	1315.8	1316.8	1324.6	1314.8
180°	1318.8	1318.8	1318.8	1318.8	1318.8

(END OF REPORT)