

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011098

Luminaire Tested: S123DIP-B1000D1195UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011098
REPORT IS A COMBINATION OF REPORTS P989128 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D1195UB40-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8147.0 lumens
Efficiency: N/A
Efficacy: 99.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011098

CATALOG NUMBER: S123DIP-B1000D1195UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1011098

CATALOG NUMBER: S123DIP-B1000D1195UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	89	86	90	86	83	80	73	71	68	61	59	57	50	48	47
2	89	81	75	70	82	75	70	65	64	60	57	53	50	48	44	42	40
3	81	72	64	58	75	66	60	55	56	51	47	47	44	41	39	36	34
4	74	63	55	49	68	59	52	46	50	45	40	42	38	35	34	32	29
5	68	56	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25
6	63	51	42	37	58	47	40	35	40	35	30	34	30	26	28	25	22
7	58	46	38	32	53	43	35	30	37	31	27	31	27	23	26	22	20
8	54	41	34	28	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	18	16
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16841	16841	16841
5°	16884	16260	16236
10°	16733	15710	15549
15°	16500	15138	14799
20°	16234	14502	14058
25°	15889	13832	13264
30°	15511	13138	12430
35°	15115	12429	11601
40°	14701	11685	10784
45°	14245	10959	9933
50°	13783	10151	9078
55°	13187	9310	8211
60°	12575	8380	7288
65°	12000	7375	6326
70°	11173	6261	5204
75°	9978	4958	4041
80°	8616	3484	2858
85°	6724	1874	1432

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14245 cd/sqm

TEST NUMBER: P1011098

CATALOG NUMBER: S123DIP-B1000D1195UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.5	1.8
10°-20°	416.5	5.1
20°-30°	615.1	7.6
30°-40°	718.4	8.8
40°-50°	722.2	8.9
50°-60°	634.4	7.8
60°-70°	472.5	5.8
70°-80°	268.9	3.3
80°-90°	79.6	1.0
90°-100°	94.6	1.2
100°-110°	286.3	3.5
110°-120°	487.4	6.0
120°-130°	641.3	7.9
130°-140°	720.8	8.8
140°-150°	708.6	8.7
150°-160°	596.6	7.3
160°-170°	397.2	4.9
170°-180°	139.1	1.7
0°-30°	1179.1	14.5
0°-40°	1897.5	23.3
0°-60°	3254.2	39.9
0°-90°	4075.1	50.0
90°-120°	868.4	10.7
90°-150°	2939.0	36.1
90°-180°	4072.0	50.0
0°-180°	8147.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1565	1565	1565	1565	1565	
5°	1566	1559	1544	1558	1555	149
15°	1491	1485	1468	1478	1470	420
25°	1353	1345	1328	1329	1325	623
35°	1170	1162	1145	1137	1130	732
45°	959	954	936	920	914	741
55°	728	726	709	694	688	652
65°	496	490	476	466	461	490
75°	262	257	253	246	242	280
85°	70	67	67	65	65	75
90°	1	13	28	32	35	10
95°	68	76	85	90	90	75
105°	260	262	272	272	275	278
115°	491	494	492	493	492	486
125°	718	722	719	715	710	640
135°	932	938	937	933	930	718
145°	1130	1132	1136	1135	1130	706
155°	1294	1294	1295	1300	1292	596
165°	1410	1406	1406	1413	1405	398
175°	1466	1462	1462	1468	1460	139
180°	1470	1470	1470	1470	1470	

TEST NUMBER: P1011098

CATALOG NUMBER: S123DIP-B1000D1195UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1564.6	1564.6	1564.6	1564.6	1564.6
2.5°	1571.3	1566.0	1551.2	1564.6	1563.3
5°	1566.0	1559.2	1544.4	1557.9	1555.2
7.5°	1553.9	1547.1	1532.3	1544.4	1543.1
10°	1537.7	1531.0	1513.5	1525.6	1522.9
12.5°	1516.2	1510.8	1494.7	1502.7	1501.4
15°	1490.6	1485.2	1467.8	1478.5	1470.4
17.5°	1462.4	1455.6	1438.2	1446.2	1443.5
20°	1430.1	1422.0	1404.5	1409.9	1405.9
22.5°	1393.8	1385.7	1368.2	1372.2	1366.9
25°	1353.4	1345.3	1327.8	1329.2	1325.1
27.5°	1311.7	1303.6	1284.8	1286.1	1282.1
30°	1266.0	1259.2	1240.4	1240.4	1231.0
32.5°	1220.2	1210.8	1197.3	1187.9	1183.9
35°	1170.4	1162.4	1144.9	1136.8	1130.1
37.5°	1120.7	1109.9	1092.4	1083.0	1079.0
40°	1068.2	1060.1	1041.3	1030.5	1025.1
42.5°	1015.7	1006.3	987.5	976.7	971.3
45°	959.2	953.8	936.3	920.2	913.5
47.5°	904.1	896.0	879.8	863.7	858.3
50°	847.6	840.8	823.3	808.5	800.5
52.5°	788.4	784.3	765.5	753.4	745.3
55°	727.8	726.5	709.0	694.2	687.5
57.5°	671.3	665.9	652.5	639.0	631.0
60°	609.4	608.1	591.9	579.8	573.1
62.5°	554.3	550.2	534.1	522.0	518.0
65°	496.4	489.7	476.2	465.5	461.4
67.5°	434.5	429.2	418.4	409.0	403.6
70°	379.4	371.3	363.2	353.8	347.1
72.5°	321.5	316.2	306.7	298.7	296.0
75°	262.3	257.0	252.9	246.2	242.2
77.5°	209.9	207.2	201.8	196.4	196.4
80°	158.7	154.7	152.0	150.7	150.7
82.5°	109.0	109.0	109.0	106.3	104.9
85°	70.0	67.3	67.3	64.6	64.6
87.5°	35.0	30.9	29.6	28.3	28.3
90°	1.2	12.7	27.7	32.3	34.6
92.5°	34.6	41.6	48.5	51.9	49.6
95°	68.1	76.2	85.4	90.0	90.0
97.5°	112.0	117.7	124.7	130.4	129.3
100°	157.0	163.9	169.7	173.2	175.5
102.5°	208.9	212.4	220.5	224.0	222.8
105°	259.7	262.1	272.4	272.4	274.7
107.5°	319.8	320.9	325.5	329.0	327.9
110°	375.2	377.5	379.8	384.4	382.1



TEST NUMBER: P1011098

CATALOG NUMBER: S123DIP-B1000D1195UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	432.9	434.1	434.1	439.8	439.8
115°	490.6	494.1	491.8	492.9	491.8
117.5°	549.5	550.7	548.3	548.3	544.9
120°	603.8	610.7	604.9	603.8	601.4
122.5°	660.3	664.9	662.6	659.2	655.7
125°	718.0	721.5	719.2	714.6	710.0
127.5°	771.1	778.1	775.8	768.8	764.2
130°	824.2	833.5	830.0	825.4	817.3
132.5°	877.4	886.6	884.3	878.5	872.7
135°	931.6	938.5	937.4	932.8	930.5
137.5°	981.2	987.0	990.5	984.7	981.2
140°	1033.2	1039.0	1040.1	1039.0	1030.9
142.5°	1080.5	1086.3	1088.6	1087.5	1081.7
145°	1130.2	1132.5	1135.9	1134.8	1130.2
147.5°	1172.9	1177.5	1181.0	1181.0	1174.0
150°	1217.9	1220.2	1222.5	1222.5	1215.6
152.5°	1254.8	1258.3	1259.5	1261.8	1256.0
155°	1294.1	1294.1	1295.2	1299.9	1291.8
157.5°	1327.6	1326.4	1327.6	1332.2	1325.3
160°	1358.7	1356.4	1356.4	1362.2	1357.6
162.5°	1386.4	1383.0	1384.1	1389.9	1381.8
165°	1409.5	1406.1	1406.1	1413.0	1404.9
167.5°	1429.2	1424.5	1425.7	1432.6	1425.7
170°	1445.3	1440.7	1440.7	1448.8	1440.7
172.5°	1458.0	1453.4	1453.4	1460.3	1452.2
175°	1466.1	1461.5	1461.5	1468.4	1460.3
177.5°	1470.7	1466.1	1466.1	1473.0	1464.9
180°	1469.6	1469.6	1469.6	1469.6	1469.6

(END OF REPORT)