

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011116

Luminaire Tested: S123DIP-B1000D365UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011116
REPORT IS A COMBINATION OF REPORTS P989146 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D365UB27-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5304.0 lumens
Efficiency: N/A
Efficacy: 94.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011116

CATALOG NUMBER: S123DIP-B1000D365UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1011116

CATALOG NUMBER: S123DIP-B1000D365UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	108	108	108	108	98	98	98	89	89	89	81	81	81
1	104	99	95	91	99	95	91	88	86	83	81	78	76	74	71	69	68
2	94	87	80	75	90	83	77	72	75	71	67	69	65	62	63	60	57
3	86	76	68	62	82	73	66	60	67	61	56	61	56	52	55	52	49
4	79	67	59	53	75	65	57	51	59	53	48	54	49	45	49	45	42
5	73	60	52	45	69	58	50	44	53	47	42	49	43	39	45	40	37
6	67	54	46	40	64	52	44	38	48	41	36	44	39	34	41	36	32
7	62	49	41	35	59	47	39	34	44	37	32	40	35	30	37	32	29
8	58	45	37	31	55	43	36	30	40	33	29	37	31	27	34	29	26
9	54	41	33	28	51	40	32	27	37	30	26	34	28	25	31	27	23
10	50	38	30	25	48	36	29	25	34	28	23	31	26	22	29	25	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16792	16792	16792
5°	16833	16212	16188
10°	16684	15663	15503
15°	16451	15092	14756
20°	16186	14460	14016
25°	15842	13791	13225
30°	15465	13098	12392
35°	15071	12392	11566
40°	14657	11650	10753
45°	14204	10928	9903
50°	13742	10122	9050
55°	13149	9282	8186
60°	12537	8356	7267
65°	11966	7354	6308
70°	11140	6244	5189
75°	9951	4944	4027
80°	8594	3475	2849
85°	6705	1869	1427

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14204 cd/sqm

TEST NUMBER: P1011116

CATALOG NUMBER: S123DIP-B1000D365UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.1	2.8
10°-20°	415.3	7.8
20°-30°	613.3	11.6
30°-40°	716.3	13.5
40°-50°	720.1	13.6
50°-60°	632.6	11.9
60°-70°	471.1	8.9
70°-80°	268.1	5.1
80°-90°	77.2	1.5
90°-100°	28.9	0.5
100°-110°	87.4	1.6
110°-120°	148.8	2.8
120°-130°	195.8	3.7
130°-140°	220.0	4.1
140°-150°	216.3	4.1
150°-160°	182.1	3.4
160°-170°	121.2	2.3
170°-180°	42.5	0.8
0°-30°	1175.6	22.2
0°-40°	1891.9	35.7
0°-60°	3244.6	61.2
0°-90°	4061.0	76.6
90°-120°	265.1	5.0
90°-150°	897.2	16.9
90°-180°	1243.0	23.4
0°-180°	5304.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1560	1560	1560	1560	1560	
5°	1561	1555	1540	1553	1551	148
15°	1486	1481	1463	1474	1466	419
25°	1349	1341	1324	1325	1321	622
35°	1167	1159	1142	1134	1127	730
45°	956	951	934	918	911	738
55°	726	724	707	692	685	650
65°	495	488	475	464	460	488
75°	262	256	252	246	241	279
85°	70	67	67	64	64	75
90°	0	4	8	10	11	6
95°	21	23	26	28	28	23
105°	79	80	83	83	84	85
115°	150	151	150	150	150	148
125°	219	220	220	218	217	195
135°	284	286	286	285	284	219
145°	345	346	347	346	345	216
155°	395	395	395	397	394	182
165°	430	429	429	431	429	121
175°	448	446	446	448	446	43
180°	449	449	449	449	449	

TEST NUMBER: P1011116

CATALOG NUMBER: S123DIP-B1000D365UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1560.0	1560.0	1560.0	1560.0	1560.0
2.5°	1566.7	1561.3	1546.6	1560.0	1558.7
5°	1561.3	1554.6	1539.9	1553.3	1550.6
7.5°	1549.3	1542.6	1527.8	1539.9	1538.5
10°	1533.2	1526.5	1509.0	1521.1	1518.4
12.5°	1511.7	1506.3	1490.3	1498.3	1497.0
15°	1486.2	1480.9	1463.4	1474.2	1466.1
17.5°	1458.1	1451.4	1433.9	1442.0	1439.3
20°	1425.9	1417.8	1400.4	1405.7	1401.7
22.5°	1389.7	1381.6	1364.2	1368.2	1362.8
25°	1349.4	1341.4	1323.9	1325.3	1321.2
27.5°	1307.8	1299.8	1281.0	1282.3	1278.3
30°	1262.2	1255.5	1236.7	1236.7	1227.3
32.5°	1216.6	1207.2	1193.8	1184.4	1180.4
35°	1167.0	1158.9	1141.5	1133.5	1126.7
37.5°	1117.4	1106.6	1089.2	1079.8	1075.8
40°	1065.0	1057.0	1038.2	1027.5	1022.1
42.5°	1012.7	1003.3	984.6	973.8	968.5
45°	956.4	951.0	933.6	917.5	910.8
47.5°	901.4	893.3	877.3	861.2	855.8
50°	845.1	838.4	820.9	806.2	798.1
52.5°	786.0	782.0	763.2	751.2	743.1
55°	725.7	724.3	706.9	692.1	685.4
57.5°	669.3	664.0	650.6	637.1	629.1
60°	607.6	606.3	590.2	578.1	571.4
62.5°	552.6	548.6	532.5	520.4	516.4
65°	495.0	488.3	474.8	464.1	460.1
67.5°	433.3	427.9	417.2	407.8	402.4
70°	378.3	370.2	362.2	352.8	346.1
72.5°	320.6	315.2	305.8	297.8	295.1
75°	261.6	256.2	252.2	245.5	241.4
77.5°	209.3	206.6	201.2	195.8	195.8
80°	158.3	154.3	151.6	150.2	150.2
82.5°	108.7	108.7	108.7	106.0	104.6
85°	69.8	67.1	67.1	64.4	64.4
87.5°	34.9	30.9	29.5	28.2	28.2
90°	0.4	3.9	8.5	9.9	10.6
92.5°	10.6	12.7	14.8	15.9	15.2
95°	20.8	23.3	26.1	27.5	27.5
97.5°	34.2	35.9	38.1	39.8	39.5
100°	47.9	50.0	51.8	52.9	53.6
102.5°	63.8	64.8	67.3	68.4	68.0
105°	79.3	80.0	83.2	83.2	83.9
107.5°	97.6	98.0	99.4	100.4	100.1
110°	114.5	115.2	115.9	117.4	116.6

TEST NUMBER: P1011116

CATALOG NUMBER: S123DIP-B1000D365UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	132.2	132.5	132.5	134.3	134.3
115°	149.8	150.8	150.1	150.5	150.1
117.5°	167.7	168.1	167.4	167.4	166.3
120°	184.3	186.4	184.7	184.3	183.6
122.5°	201.6	203.0	202.3	201.2	200.2
125°	219.2	220.3	219.6	218.1	216.7
127.5°	235.4	237.5	236.8	234.7	233.3
130°	251.6	254.4	253.4	252.0	249.5
132.5°	267.8	270.7	269.9	268.2	266.4
135°	284.4	286.5	286.2	284.8	284.0
137.5°	299.6	301.3	302.4	300.6	299.6
140°	315.4	317.2	317.5	317.2	314.7
142.5°	329.9	331.6	332.3	332.0	330.2
145°	345.0	345.7	346.8	346.4	345.0
147.5°	358.1	359.5	360.5	360.5	358.4
150°	371.8	372.5	373.2	373.2	371.1
152.5°	383.1	384.1	384.5	385.2	383.4
155°	395.1	395.1	395.4	396.8	394.4
157.5°	405.3	404.9	405.3	406.7	404.6
160°	414.8	414.1	414.1	415.8	414.4
162.5°	423.2	422.2	422.5	424.3	421.8
165°	430.3	429.2	429.2	431.4	428.9
167.5°	436.3	434.9	435.2	437.3	435.2
170°	441.2	439.8	439.8	442.3	439.8
172.5°	445.1	443.7	443.7	445.8	443.3
175°	447.6	446.2	446.2	448.3	445.8
177.5°	449.0	447.6	447.6	449.7	447.2
180°	448.6	448.6	448.6	448.6	448.6

(END OF REPORT)