

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010787

Luminaire Tested: S123RDIP-B1000D1195UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010787
REPORT IS A COMBINATION OF REPORTS P992773 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1000D1195UB2750-4F0-XX-W2A-F_4000K
Description: Define 3 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8487.0 lumens
Efficiency: N/A
Efficacy: 103.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010787

CATALOG NUMBER: S123RDIP-B1000D1195UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010787

CATALOG NUMBER: S123RDIP-B1000D1195UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	97	93	89	85	88	85	82	79	71	68	66	57	56	55	45	44	43
2	88	81	75	70	81	75	69	65	62	59	55	51	48	46	40	39	37
3	81	72	64	59	74	66	60	55	55	51	47	45	42	39	36	34	32
4	74	63	56	50	68	58	52	47	49	44	40	40	37	34	32	30	28
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	29	26	24
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	21
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19
8	54	42	34	29	49	39	32	27	33	28	24	27	23	21	22	19	17
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	21	18	16
10	47	35	28	23	43	33	26	22	28	23	19	23	19	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17853	17853	17853
5°	17882	17221	17174
10°	17741	16574	16247
15°	17511	15773	15231
20°	17209	14903	14096
25°	16897	13998	13021
30°	16498	13036	11749
35°	16086	12091	10591
40°	15699	11064	9311
45°	15203	10060	8161
50°	14655	8990	6971
55°	14088	7842	5880
60°	13544	6666	4773
65°	12843	5458	3725
70°	11962	4127	2663
75°	10693	2795	2109
80°	9126	1941	1479
85°	6849	1050	776

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15203 cd/sqm

TEST NUMBER: P1010787

CATALOG NUMBER: S123RDIP-B1000D1195UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.9	1.8
10°-20°	433.7	5.1
20°-30°	624.5	7.4
30°-40°	703.3	8.3
40°-50°	672.7	7.9
50°-60°	550.7	6.5
60°-70°	371.3	4.4
70°-80°	186.2	2.2
80°-90°	51.8	0.6
90°-100°	54.8	0.6
100°-110°	264.9	3.1
110°-120°	649.2	7.6
120°-130°	824.1	9.7
130°-140°	880.4	10.4
140°-150°	823.3	9.7
150°-160°	664.0	7.8
160°-170°	428.5	5.0
170°-180°	147.7	1.7
0°-30°	1214.2	14.3
0°-40°	1917.4	22.6
0°-60°	3140.8	37.0
0°-90°	3750.1	44.2
90°-120°	968.9	11.4
90°-150°	3496.7	41.2
90°-180°	4737.0	55.8
0°-180°	8487.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1659	1659	1659	1659	1659	
5°	1659	1652	1636	1648	1645	157
15°	1582	1567	1529	1523	1513	446
25°	1439	1406	1344	1316	1301	662
35°	1246	1197	1114	1056	1032	780
45°	1024	963	860	783	751	790
55°	778	712	597	519	492	697
65°	531	457	352	286	272	526
75°	281	217	143	129	126	300
85°	71	42	38	35	35	78
90°	1	13	28	32	35	8
95°	70	23	36	44	44	84
105°	344	357	253	48	51	365
115°	645	652	663	674	679	637
125°	910	919	924	926	928	813
135°	1132	1139	1144	1148	1144	872
145°	1307	1315	1317	1320	1320	818
155°	1440	1437	1438	1444	1437	663
165°	1518	1515	1513	1523	1515	429
175°	1554	1548	1549	1557	1548	148
180°	1554	1554	1554	1554	1554	

TEST NUMBER: P1010787

CATALOG NUMBER: S123RDIP-B1000D1195UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1658.6	1658.6	1658.6	1658.6	1658.6
2.5°	1665.3	1659.9	1643.8	1658.6	1655.9
5°	1658.6	1651.8	1635.7	1647.8	1645.1
7.5°	1646.5	1639.7	1619.6	1627.6	1623.6
10°	1630.3	1620.9	1596.7	1598.0	1591.3
12.5°	1607.5	1596.7	1565.8	1564.4	1556.3
15°	1581.9	1567.1	1529.4	1522.7	1513.3
17.5°	1551.0	1534.8	1487.7	1474.3	1460.8
20°	1516.0	1494.5	1443.3	1425.9	1409.7
22.5°	1477.0	1451.4	1396.3	1373.4	1358.6
25°	1439.3	1405.7	1343.8	1315.6	1300.8
27.5°	1393.6	1357.3	1290.0	1252.3	1229.5
30°	1346.5	1306.1	1230.8	1185.1	1163.6
32.5°	1299.4	1252.3	1171.6	1120.5	1097.6
35°	1245.6	1197.2	1113.8	1055.9	1031.7
37.5°	1191.8	1139.3	1051.9	987.3	957.7
40°	1140.7	1081.5	986.0	916.0	885.1
42.5°	1082.8	1023.7	924.1	846.1	819.2
45°	1023.7	963.1	859.5	782.9	750.6
47.5°	965.8	898.6	796.3	712.9	684.7
50°	901.2	838.0	729.1	645.7	614.7
52.5°	843.4	773.5	665.8	578.4	551.5
55°	777.5	711.6	597.2	519.2	492.3
57.5°	718.3	647.0	531.3	457.4	434.5
60°	656.4	582.4	470.8	398.2	375.3
62.5°	594.6	520.6	408.9	341.7	317.5
65°	531.3	457.4	352.4	286.5	271.7
67.5°	468.1	392.8	290.6	240.8	224.6
70°	406.2	333.6	239.4	192.4	177.6
72.5°	344.4	273.1	189.7	153.3	149.3
75°	281.1	216.6	142.6	129.1	126.4
77.5°	223.3	164.1	111.6	103.6	100.9
80°	168.1	113.0	84.7	80.7	78.0
82.5°	115.7	69.9	60.5	56.5	56.5
85°	71.3	41.7	37.7	35.0	35.0
87.5°	32.3	17.5	17.5	16.1	14.8
90°	1.2	12.7	27.7	32.3	34.6
92.5°	26.6	19.6	30.0	38.1	39.2
95°	70.4	23.1	35.8	43.9	43.9
97.5°	128.1	95.8	36.9	46.2	47.3
100°	195.1	218.2	38.1	47.3	48.5
102.5°	271.3	286.3	85.4	47.3	49.6
105°	344.0	356.7	252.8	48.5	50.8
107.5°	421.4	431.7	449.1	271.3	120.1
110°	498.7	507.9	520.6	482.5	317.5

TEST NUMBER: P1010787

CATALOG NUMBER: S123RDIP-B1000D1195UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	572.6	580.7	593.4	603.7	601.4
115°	645.3	652.2	662.6	674.2	678.8
117.5°	716.9	725.0	730.7	740.0	741.1
120°	782.7	793.1	796.5	805.8	805.8
122.5°	849.6	857.7	862.3	868.1	869.3
125°	909.7	918.9	923.5	925.8	928.1
127.5°	969.7	978.9	984.7	988.2	985.8
130°	1025.1	1034.3	1038.9	1043.6	1041.3
132.5°	1078.2	1087.4	1090.9	1095.5	1092.0
135°	1132.5	1139.4	1144.0	1147.5	1144.0
137.5°	1178.6	1187.9	1190.2	1195.9	1193.6
140°	1224.8	1231.7	1235.2	1239.8	1237.5
142.5°	1267.5	1274.4	1277.9	1281.4	1277.9
145°	1306.8	1314.8	1317.2	1319.5	1319.5
147.5°	1344.9	1350.6	1352.9	1355.2	1349.5
150°	1379.5	1383.0	1385.3	1387.6	1384.1
152.5°	1410.7	1411.8	1413.0	1417.6	1411.8
155°	1439.5	1437.2	1438.4	1444.1	1437.2
157.5°	1462.6	1462.6	1461.5	1468.4	1459.1
160°	1483.4	1482.2	1481.1	1488.0	1479.9
162.5°	1503.0	1499.5	1498.4	1506.5	1499.5
165°	1518.0	1514.6	1513.4	1522.6	1514.6
167.5°	1530.7	1526.1	1526.1	1535.3	1526.1
170°	1541.1	1536.5	1536.5	1545.7	1536.5
172.5°	1548.0	1542.3	1543.4	1552.6	1542.3
175°	1553.8	1548.0	1549.2	1557.3	1548.0
177.5°	1556.1	1550.3	1551.5	1560.7	1549.2
180°	1553.8	1553.8	1553.8	1553.8	1553.8

(END OF REPORT)