

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011117

Luminaire Tested: S123DIP-B1000D365UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011117
REPORT IS A COMBINATION OF REPORTS P989147 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D365UB27-4F0-XX-W2A-F4
Description: Define 3 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5374.1 lumens
Efficiency: N/A
Efficacy: 95.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011117

CATALOG NUMBER: S123DIP-B1000D365UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1011117

CATALOG NUMBER: S123DIP-B1000D365UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	108	108	108	108	98	98	98	88	88	88	80	80	80
1	103	99	95	91	98	94	91	87	86	83	80	78	75	73	70	69	67
2	94	86	80	74	89	82	77	72	75	70	66	68	65	61	62	59	56
3	86	76	68	62	81	73	66	60	66	60	56	60	56	52	55	51	48
4	79	67	59	53	75	64	57	51	59	53	48	54	49	44	49	45	41
5	72	60	52	45	69	58	50	44	53	46	41	48	43	39	44	40	36
6	67	54	46	39	63	52	44	38	48	41	36	44	38	34	40	35	32
7	62	49	41	35	59	47	39	34	43	37	32	40	34	30	37	32	28
8	58	45	37	31	55	43	35	30	40	33	29	37	31	27	34	29	25
9	54	41	33	28	51	39	32	27	36	30	26	34	28	24	31	26	23
10	50	38	30	25	48	36	29	24	34	28	23	31	26	22	29	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16792	16792	16792
5°	16833	16212	16188
10°	16684	15663	15503
15°	16451	15092	14756
20°	16186	14460	14016
25°	15842	13791	13225
30°	15465	13098	12392
35°	15071	12392	11566
40°	14657	11650	10753
45°	14204	10928	9903
50°	13742	10122	9050
55°	13149	9282	8186
60°	12537	8356	7267
65°	11966	7354	6308
70°	11140	6244	5189
75°	9951	4944	4027
80°	8594	3475	2849
85°	6705	1869	1427

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14204 cd/sqm

TEST NUMBER: P1011117

CATALOG NUMBER: S123DIP-B1000D365UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.1	2.7
10°-20°	415.3	7.7
20°-30°	613.3	11.4
30°-40°	716.3	13.3
40°-50°	720.1	13.4
50°-60°	632.6	11.8
60°-70°	471.1	8.8
70°-80°	268.1	5.0
80°-90°	77.2	1.4
90°-100°	99.0	1.8
100°-110°	276.6	5.1
110°-120°	269.7	5.0
120°-130°	214.8	4.0
130°-140°	169.5	3.2
140°-150°	126.5	2.4
150°-160°	88.2	1.6
160°-170°	51.8	1.0
170°-180°	16.9	0.3
0°-30°	1175.6	21.9
0°-40°	1891.9	35.2
0°-60°	3244.6	60.4
0°-90°	4061.0	75.6
90°-120°	645.3	12.0
90°-150°	1156.1	21.5
90°-180°	1313.0	24.4
0°-180°	5374.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1560	1560	1560	1560	1560	
5°	1561	1555	1540	1553	1551	148
15°	1486	1481	1463	1474	1466	419
25°	1349	1341	1324	1325	1321	622
35°	1167	1159	1142	1134	1127	730
45°	956	951	934	918	911	738
55°	726	724	707	692	685	650
65°	495	488	475	464	460	488
75°	262	256	252	246	241	279
85°	70	67	67	64	64	75
90°	1	4	9	10	10	6
95°	12	39	209	61	41	13
105°	41	60	283	496	448	43
115°	72	90	217	475	545	72
125°	100	119	202	367	430	89
135°	118	140	200	302	349	91
145°	134	154	197	248	272	84
155°	153	165	191	217	226	70
165°	167	172	183	194	197	47
175°	174	174	175	178	177	17
180°	174	174	174	174	174	

TEST NUMBER: P1011117

CATALOG NUMBER: S123DIP-B1000D365UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1560.0	1560.0	1560.0	1560.0	1560.0
2.5°	1566.7	1561.3	1546.6	1560.0	1558.7
5°	1561.3	1554.6	1539.9	1553.3	1550.6
7.5°	1549.3	1542.6	1527.8	1539.9	1538.5
10°	1533.2	1526.5	1509.0	1521.1	1518.4
12.5°	1511.7	1506.3	1490.3	1498.3	1497.0
15°	1486.2	1480.9	1463.4	1474.2	1466.1
17.5°	1458.1	1451.4	1433.9	1442.0	1439.3
20°	1425.9	1417.8	1400.4	1405.7	1401.7
22.5°	1389.7	1381.6	1364.2	1368.2	1362.8
25°	1349.4	1341.4	1323.9	1325.3	1321.2
27.5°	1307.8	1299.8	1281.0	1282.3	1278.3
30°	1262.2	1255.5	1236.7	1236.7	1227.3
32.5°	1216.6	1207.2	1193.8	1184.4	1180.4
35°	1167.0	1158.9	1141.5	1133.5	1126.7
37.5°	1117.4	1106.6	1089.2	1079.8	1075.8
40°	1065.0	1057.0	1038.2	1027.5	1022.1
42.5°	1012.7	1003.3	984.6	973.8	968.5
45°	956.4	951.0	933.6	917.5	910.8
47.5°	901.4	893.3	877.3	861.2	855.8
50°	845.1	838.4	820.9	806.2	798.1
52.5°	786.0	782.0	763.2	751.2	743.1
55°	725.7	724.3	706.9	692.1	685.4
57.5°	669.3	664.0	650.6	637.1	629.1
60°	607.6	606.3	590.2	578.1	571.4
62.5°	552.6	548.6	532.5	520.4	516.4
65°	495.0	488.3	474.8	464.1	460.1
67.5°	433.3	427.9	417.2	407.8	402.4
70°	378.3	370.2	362.2	352.8	346.1
72.5°	320.6	315.2	305.8	297.8	295.1
75°	261.6	256.2	252.2	245.5	241.4
77.5°	209.3	206.6	201.2	195.8	195.8
80°	158.3	154.3	151.6	150.2	150.2
82.5°	108.7	108.7	108.7	106.0	104.6
85°	69.8	67.1	67.1	64.4	64.4
87.5°	34.9	30.9	29.5	28.2	28.2
90°	0.7	4.2	8.8	9.8	10.2
92.5°	5.3	21.2	65.6	22.4	18.7
95°	12.0	39.0	209.1	61.0	40.9
97.5°	19.0	44.6	321.5	153.4	83.9
100°	26.1	49.2	333.9	320.8	221.0
102.5°	33.5	54.4	310.9	429.6	350.1
105°	40.9	60.4	283.4	495.7	448.4
107.5°	48.7	67.5	259.1	524.8	512.6
110°	57.1	74.8	239.0	525.6	549.3



TEST NUMBER: P1011117

CATALOG NUMBER: S123DIP-B1000D365UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	64.9	82.4	225.6	505.8	556.7
115°	72.3	90.0	216.8	475.4	545.4
117.5°	79.7	97.5	210.8	443.0	520.7
120°	87.4	104.9	206.9	412.3	488.3
122.5°	94.1	112.0	204.5	388.2	458.0
125°	100.5	118.6	202.4	366.6	430.1
127.5°	105.4	125.0	201.3	349.0	406.1
130°	110.0	130.6	200.2	332.8	386.4
132.5°	113.5	135.7	199.9	317.6	367.0
135°	117.8	140.4	199.5	302.0	348.7
137.5°	121.6	144.4	198.8	287.2	329.3
140°	125.5	147.9	198.5	272.7	308.8
142.5°	129.7	151.0	197.8	259.4	289.8
145°	134.3	153.9	197.1	247.7	272.5
147.5°	138.9	156.9	196.0	238.5	257.7
150°	143.5	159.4	194.6	230.4	245.0
152.5°	148.1	162.0	192.8	223.4	234.4
155°	152.7	164.6	190.7	216.8	226.0
157.5°	156.2	167.0	189.0	210.4	217.9
160°	160.4	168.8	186.8	204.6	210.1
162.5°	163.6	170.3	184.7	199.1	203.1
165°	166.8	171.5	182.6	193.7	197.1
167.5°	169.2	172.6	180.5	189.0	191.1
170°	171.3	173.1	178.4	184.8	185.8
172.5°	172.7	173.6	176.6	181.0	180.9
175°	173.8	174.0	175.2	177.7	177.3
177.5°	174.5	174.2	174.2	175.6	174.9
180°	174.2	174.2	174.2	174.2	174.2

(END OF REPORT)