

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010794

Luminaire Tested: S123RDIP-B1000D365UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010794
REPORT IS A COMBINATION OF REPORTS P992810 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1000D365UB2750-4F0-XX-W2A-F_2700K
Description: Define 3 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5183.0 lumens
Efficiency: N/A
Efficacy: 92.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010794

CATALOG NUMBER: S123RDIP-B1000D365UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1010794

CATALOG NUMBER: S123RDIP-B1000D365UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	76	76	76
1	103	99	95	92	98	94	91	88	85	82	80	76	74	72	68	67	66
2	94	87	81	76	89	83	77	73	75	71	67	67	64	61	61	58	56
3	86	77	70	64	82	73	67	61	66	61	57	60	56	52	54	51	48
4	79	68	60	54	75	65	58	52	59	54	49	54	49	45	49	45	42
5	73	61	53	47	69	59	51	46	53	47	43	49	44	40	44	40	37
6	68	55	47	41	64	53	45	40	48	42	37	44	39	35	40	36	33
7	63	50	42	36	59	48	41	35	44	38	33	40	35	31	37	32	29
8	58	46	38	33	55	44	37	32	40	34	30	37	32	28	34	30	26
9	55	42	34	29	52	40	33	28	37	31	27	34	29	25	31	27	24
10	51	39	31	26	49	37	30	26	34	29	24	32	27	23	29	25	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17800	17800	17800
5°	17829	17170	17124
10°	17689	16525	16199
15°	17460	15727	15186
20°	17158	14859	14055
25°	16848	13958	12981
30°	16449	12998	11714
35°	16039	12056	10560
40°	15652	11032	9284
45°	15159	10031	8138
50°	14612	8963	6950
55°	14046	7819	5863
60°	13505	6646	4759
65°	12807	5442	3714
70°	11927	4115	2654
75°	10662	2788	2104
80°	9099	1937	1475
85°	6829	1047	774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15159 cd/sqm

TEST NUMBER: P1010794

CATALOG NUMBER: S123RDIP-B1000D365UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.5	3.0
10°-20°	432.5	8.3
20°-30°	622.7	12.0
30°-40°	701.2	13.5
40°-50°	670.7	12.9
50°-60°	549.1	10.6
60°-70°	370.2	7.1
70°-80°	185.7	3.6
80°-90°	49.5	1.0
90°-100°	16.7	0.3
100°-110°	80.9	1.6
110°-120°	198.2	3.8
120°-130°	251.6	4.9
130°-140°	268.8	5.2
140°-150°	251.3	4.8
150°-160°	202.7	3.9
160°-170°	130.8	2.5
170°-180°	45.1	0.9
0°-30°	1210.6	23.4
0°-40°	1911.8	36.9
0°-60°	3131.6	60.4
0°-90°	3737.0	72.1
90°-120°	295.8	5.7
90°-150°	1067.4	20.6
90°-180°	1446.0	27.9
0°-180°	5183.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1654	1654	1654	1654	1654	
5°	1654	1647	1631	1643	1640	157
15°	1577	1562	1525	1518	1509	444
25°	1435	1402	1340	1312	1297	660
35°	1242	1194	1110	1053	1029	777
45°	1021	960	857	781	748	788
55°	775	710	596	518	491	695
65°	530	456	351	286	271	524
75°	280	216	142	129	126	299
85°	71	42	38	35	35	78
90°	0	4	8	10	11	6
95°	22	7	11	13	13	26
105°	105	109	77	15	16	111
115°	197	199	202	206	207	195
125°	278	280	282	283	283	248
135°	346	348	349	350	349	266
145°	399	401	402	403	403	250
155°	439	439	439	441	439	202
165°	463	462	462	465	462	131
175°	474	473	473	475	473	45
180°	474	474	474	474	474	

TEST NUMBER: P1010794

CATALOG NUMBER: S123RDIP-B1000D365UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1653.7	1653.7	1653.7	1653.7	1653.7
2.5°	1660.4	1655.0	1638.9	1653.7	1651.0
5°	1653.7	1647.0	1630.9	1643.0	1640.3
7.5°	1641.6	1634.9	1614.8	1622.9	1618.8
10°	1625.5	1616.1	1592.0	1593.3	1586.6
12.5°	1602.7	1592.0	1561.2	1559.8	1551.8
15°	1577.3	1562.5	1524.9	1518.2	1508.8
17.5°	1546.4	1530.3	1483.4	1470.0	1456.5
20°	1511.5	1490.1	1439.1	1421.7	1405.6
22.5°	1472.6	1447.2	1392.2	1369.4	1354.6
25°	1435.1	1401.6	1339.9	1311.7	1296.9
27.5°	1389.5	1353.3	1286.2	1248.7	1225.9
30°	1342.5	1302.3	1227.2	1181.6	1160.1
32.5°	1295.6	1248.7	1168.2	1117.2	1094.4
35°	1242.0	1193.7	1110.5	1052.8	1028.7
37.5°	1188.3	1136.0	1048.8	984.4	954.9
40°	1137.3	1078.3	983.1	913.4	882.5
42.5°	1079.7	1020.7	921.4	843.6	816.8
45°	1020.7	960.3	857.0	780.6	748.4
47.5°	963.0	895.9	794.0	710.8	682.7
50°	898.6	835.6	726.9	643.8	612.9
52.5°	840.9	771.2	663.9	576.7	549.9
55°	775.2	709.5	595.5	517.7	490.9
57.5°	716.2	645.1	529.8	456.0	433.2
60°	654.5	580.7	469.4	397.0	374.2
62.5°	592.8	519.0	407.7	340.7	316.5
65°	529.8	456.0	351.4	285.7	270.9
67.5°	466.7	391.6	289.7	240.1	224.0
70°	405.0	332.6	238.7	191.8	177.0
72.5°	343.3	272.3	189.1	152.9	148.9
75°	280.3	215.9	142.2	128.8	126.1
77.5°	222.6	163.6	111.3	103.3	100.6
80°	167.6	112.7	84.5	80.5	77.8
82.5°	115.3	69.7	60.4	56.3	56.3
85°	71.1	41.6	37.6	34.9	34.9
87.5°	32.2	17.4	17.4	16.1	14.8
90°	0.4	3.9	8.5	9.9	10.6
92.5°	8.1	6.0	9.2	11.6	12.0
95°	21.5	7.0	10.9	13.4	13.4
97.5°	39.1	29.2	11.3	14.1	14.4
100°	59.6	66.6	11.6	14.4	14.8
102.5°	82.8	87.4	26.1	14.4	15.2
105°	105.0	108.9	77.2	14.8	15.5
107.5°	128.6	131.8	137.1	82.8	36.7
110°	152.2	155.1	158.9	147.3	96.9

TEST NUMBER: P1010794

CATALOG NUMBER: S123RDIP-B1000D365UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	174.8	177.3	181.1	184.3	183.6
115°	197.0	199.1	202.3	205.8	207.2
117.5°	218.8	221.3	223.1	225.9	226.2
120°	238.9	242.1	243.2	246.0	246.0
122.5°	259.4	261.8	263.2	265.0	265.4
125°	277.7	280.5	281.9	282.6	283.3
127.5°	296.0	298.8	300.6	301.7	301.0
130°	312.9	315.8	317.2	318.6	317.9
132.5°	329.1	332.0	333.0	334.4	333.4
135°	345.7	347.8	349.2	350.3	349.2
137.5°	359.8	362.6	363.3	365.1	364.4
140°	373.9	376.0	377.1	378.5	377.8
142.5°	386.9	389.1	390.1	391.2	390.1
145°	398.9	401.4	402.1	402.8	402.8
147.5°	410.6	412.3	413.0	413.7	412.0
150°	421.1	422.2	422.9	423.6	422.5
152.5°	430.6	431.0	431.3	432.8	431.0
155°	439.4	438.7	439.1	440.9	438.7
157.5°	446.5	446.5	446.1	448.3	445.4
160°	452.8	452.5	452.1	454.2	451.8
162.5°	458.8	457.8	457.4	459.9	457.8
165°	463.4	462.4	462.0	464.8	462.4
167.5°	467.3	465.9	465.9	468.7	465.9
170°	470.5	469.0	469.0	471.9	469.0
172.5°	472.6	470.8	471.2	474.0	470.8
175°	474.3	472.6	472.9	475.4	472.6
177.5°	475.0	473.3	473.6	476.5	472.9
180°	474.3	474.3	474.3	474.3	474.3

(END OF REPORT)