

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011125

Luminaire Tested: S123DIP-B1000D365UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011125
REPORT IS A COMBINATION OF REPORTS P989170 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D365UB30-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5350.0 lumens
Efficiency: N/A
Efficacy: 95.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011125

CATALOG NUMBER: S123DIP-B1000D365UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1011125

CATALOG NUMBER: S123DIP-B1000D365UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	108	108	108	108	98	98	98	89	89	89	81	81	81
1	104	99	95	91	99	95	91	88	86	83	81	78	76	74	71	69	68
2	94	87	80	75	90	83	77	72	75	71	67	69	65	62	63	60	57
3	86	76	68	62	82	73	66	60	67	61	56	61	56	52	55	52	49
4	79	67	59	53	75	65	57	51	59	53	48	54	49	45	49	45	42
5	73	60	52	45	69	58	50	44	53	47	42	49	43	39	45	40	37
6	67	54	46	40	64	52	44	38	48	41	36	44	39	34	40	36	32
7	62	49	41	35	59	47	39	34	44	37	32	40	35	30	37	32	29
8	58	45	37	31	55	43	36	30	40	33	29	37	31	27	34	29	26
9	54	41	33	28	51	40	32	27	37	30	26	34	28	25	31	27	23
10	50	38	30	25	48	36	29	25	34	28	23	31	26	22	29	25	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16937	16937	16937
5°	16979	16352	16328
10°	16828	15798	15636
15°	16593	15222	14883
20°	16326	14585	14137
25°	15978	13910	13339
30°	15598	13212	12499
35°	15200	12498	11666
40°	14784	11751	10845
45°	14325	11021	9988
50°	13859	10209	9129
55°	13262	9362	8257
60°	12647	8428	7329
65°	12067	7417	6363
70°	11235	6297	5234
75°	10035	4987	4062
80°	8665	3505	2873
85°	6762	1882	1438

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14325 cd/sqm

TEST NUMBER: P1011125

CATALOG NUMBER: S123DIP-B1000D365UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.3	2.8
10°-20°	418.8	7.8
20°-30°	618.6	11.6
30°-40°	722.5	13.5
40°-50°	726.3	13.6
50°-60°	638.0	11.9
60°-70°	475.2	8.9
70°-80°	270.4	5.1
80°-90°	77.8	1.5
90°-100°	29.1	0.5
100°-110°	88.2	1.6
110°-120°	150.1	2.8
120°-130°	197.5	3.7
130°-140°	222.0	4.1
140°-150°	218.2	4.1
150°-160°	183.7	3.4
160°-170°	122.3	2.3
170°-180°	42.8	0.8
0°-30°	1185.8	22.2
0°-40°	1908.2	35.7
0°-60°	3272.5	61.2
0°-90°	4095.9	76.6
90°-120°	267.5	5.0
90°-150°	905.2	16.9
90°-180°	1254.0	23.4
0°-180°	5350.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1574	1574	1574	1574	1574	
5°	1575	1568	1553	1567	1564	149
15°	1499	1494	1476	1487	1479	423
25°	1361	1353	1335	1337	1333	627
35°	1177	1169	1151	1143	1136	736
45°	965	959	942	925	919	745
55°	732	731	713	698	691	656
65°	499	492	479	468	464	493
75°	264	258	254	248	244	282
85°	70	68	68	65	65	75
90°	0	4	8	10	11	6
95°	21	24	26	28	28	23
105°	80	81	84	84	85	86
115°	151	152	152	152	152	150
125°	221	222	222	220	219	197
135°	287	289	289	287	287	221
145°	348	349	350	350	348	217
155°	398	398	399	400	398	183
165°	434	433	433	435	433	122
175°	452	450	450	452	450	43
180°	453	453	453	453	453	

TEST NUMBER: P1011125

CATALOG NUMBER: S123DIP-B1000D365UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1573.5	1573.5	1573.5	1573.5	1573.5
2.5°	1580.2	1574.8	1559.9	1573.5	1572.1
5°	1574.8	1568.0	1553.2	1566.7	1564.0
7.5°	1562.6	1555.9	1541.0	1553.2	1551.8
10°	1546.4	1539.6	1522.0	1534.2	1531.5
12.5°	1524.7	1519.3	1503.1	1511.2	1509.9
15°	1499.0	1493.6	1476.0	1486.9	1478.7
17.5°	1470.6	1463.9	1446.3	1454.4	1451.7
20°	1438.2	1430.0	1412.5	1417.9	1413.8
22.5°	1401.6	1393.5	1375.9	1380.0	1374.6
25°	1361.0	1352.9	1335.3	1336.7	1332.6
27.5°	1319.1	1311.0	1292.0	1293.4	1289.3
30°	1273.1	1266.3	1247.4	1247.4	1237.9
32.5°	1227.1	1217.6	1204.1	1194.6	1190.6
35°	1177.0	1168.9	1151.3	1143.2	1136.5
37.5°	1127.0	1116.2	1098.6	1089.1	1085.0
40°	1074.2	1066.1	1047.2	1036.3	1030.9
42.5°	1021.5	1012.0	993.0	982.2	976.8
45°	964.6	959.2	941.6	925.4	918.6
47.5°	909.2	901.0	884.8	868.6	863.2
50°	852.3	845.6	828.0	813.1	805.0
52.5°	792.8	788.8	769.8	757.6	749.5
55°	731.9	730.6	713.0	698.1	691.3
57.5°	675.1	669.7	656.2	642.6	634.5
60°	612.9	611.5	595.3	583.1	576.3
62.5°	557.4	553.3	537.1	524.9	520.9
65°	499.2	492.5	478.9	468.1	464.1
67.5°	437.0	431.6	420.8	411.3	405.9
70°	381.5	373.4	365.3	355.8	349.1
72.5°	323.3	317.9	308.5	300.3	297.6
75°	263.8	258.4	254.4	247.6	243.5
77.5°	211.1	208.4	202.9	197.5	197.5
80°	159.6	155.6	152.9	151.5	151.5
82.5°	109.6	109.6	109.6	106.9	105.5
85°	70.4	67.6	67.6	64.9	64.9
87.5°	35.2	31.1	29.8	28.4	28.4
90°	0.4	3.9	8.5	10.0	10.7
92.5°	10.7	12.8	14.9	16.0	15.3
95°	21.0	23.5	26.3	27.7	27.7
97.5°	34.5	36.3	38.4	40.2	39.8
100°	48.4	50.5	52.3	53.3	54.0
102.5°	64.4	65.4	67.9	69.0	68.6
105°	80.0	80.7	83.9	83.9	84.6
107.5°	98.5	98.8	100.3	101.3	101.0
110°	115.5	116.3	117.0	118.4	117.7

TEST NUMBER: P1011125

CATALOG NUMBER: S123DIP-B1000D365UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	133.3	133.7	133.7	135.5	135.5
115°	151.1	152.2	151.5	151.8	151.5
117.5°	169.2	169.6	168.9	168.9	167.8
120°	185.9	188.1	186.3	185.9	185.2
122.5°	203.4	204.8	204.1	203.0	201.9
125°	221.1	222.2	221.5	220.1	218.7
127.5°	237.5	239.6	238.9	236.8	235.4
130°	253.8	256.7	255.6	254.2	251.7
132.5°	270.2	273.0	272.3	270.6	268.8
135°	286.9	289.0	288.7	287.3	286.6
137.5°	302.2	304.0	305.0	303.3	302.2
140°	318.2	320.0	320.3	320.0	317.5
142.5°	332.8	334.6	335.3	334.9	333.1
145°	348.1	348.8	349.8	349.5	348.1
147.5°	361.2	362.6	363.7	363.7	361.6
150°	375.1	375.8	376.5	376.5	374.4
152.5°	386.5	387.5	387.9	388.6	386.8
155°	398.5	398.5	398.9	400.3	397.8
157.5°	408.9	408.5	408.9	410.3	408.1
160°	418.5	417.7	417.7	419.5	418.1
162.5°	427.0	425.9	426.3	428.1	425.6
165°	434.1	433.0	433.0	435.2	432.7
167.5°	440.1	438.7	439.1	441.2	439.1
170°	445.1	443.7	443.7	446.2	443.7
172.5°	449.0	447.6	447.6	449.7	447.3
175°	451.5	450.1	450.1	452.2	449.7
177.5°	452.9	451.5	451.5	453.7	451.2
180°	452.6	452.6	452.6	452.6	452.6

(END OF REPORT)