

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010807

Luminaire Tested: S123RDIP-B1000D585UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010807
REPORT IS A COMBINATION OF REPORTS P992853 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1000D585UB2750-4F0-XX-W2A-F_4000K
Description: Define 3 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6080.0 lumens
Efficiency: N/A
Efficacy: 97.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010807

CATALOG NUMBER: S123RDIP-B1000D585UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010807

CATALOG NUMBER: S123RDIP-B1000D585UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	67	67	67
1	101	97	93	89	94	91	87	84	79	77	75	69	67	66	60	58	57	57	57	53
2	92	85	79	74	86	80	74	70	70	66	63	61	58	56	53	51	49	49	49	45
3	84	75	68	62	79	70	64	59	62	57	53	54	51	47	47	44	42	42	42	38
4	77	67	59	53	72	63	56	50	56	50	46	49	44	41	43	39	37	37	37	33
5	71	60	51	45	66	56	49	44	50	44	40	44	39	36	39	35	32	32	32	29
6	66	54	46	40	61	51	43	38	45	39	35	40	35	32	35	31	28	28	28	26
7	61	49	41	35	57	46	39	34	41	35	31	36	32	28	32	28	25	25	25	23
8	57	44	37	31	53	42	35	30	38	32	28	33	29	25	30	26	23	23	23	21
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	27	24	21	21	21	19
10	49	37	30	25	46	35	29	24	32	26	23	29	24	21	25	22	19	19	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17853	17853	17853
5°	17882	17221	17174
10°	17741	16574	16247
15°	17511	15773	15231
20°	17209	14903	14096
25°	16897	13998	13021
30°	16498	13036	11749
35°	16086	12091	10591
40°	15699	11064	9311
45°	15203	10060	8161
50°	14655	8990	6971
55°	14088	7842	5880
60°	13544	6666	4773
65°	12843	5458	3725
70°	11962	4127	2663
75°	10693	2795	2109
80°	9126	1941	1479
85°	6849	1050	776

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15203 cd/sqm

TEST NUMBER: P1010807

CATALOG NUMBER: S123RDIP-B1000D585UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.9	2.6
10°-20°	433.7	7.1
20°-30°	624.5	10.3
30°-40°	703.3	11.6
40°-50°	672.7	11.1
50°-60°	550.7	9.1
60°-70°	371.3	6.1
70°-80°	186.2	3.1
80°-90°	50.2	0.8
90°-100°	27.0	0.4
100°-110°	130.4	2.1
110°-120°	319.5	5.3
120°-130°	405.6	6.7
130°-140°	433.3	7.1
140°-150°	405.2	6.7
150°-160°	326.8	5.4
160°-170°	210.9	3.5
170°-180°	72.7	1.2
0°-30°	1214.2	20.0
0°-40°	1917.4	31.5
0°-60°	3140.8	51.7
0°-90°	3748.5	61.7
90°-120°	476.9	7.8
90°-150°	1721.0	28.3
90°-180°	2331.0	38.3
0°-180°	6080.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1659	1659	1659	1659	1659	
5°	1659	1652	1636	1648	1645	157
15°	1582	1567	1529	1523	1513	446
25°	1439	1406	1344	1316	1301	662
35°	1246	1197	1114	1056	1032	780
45°	1024	963	860	783	751	790
55°	778	712	597	519	492	697
65°	531	457	352	286	272	526
75°	281	217	143	129	126	300
85°	71	42	38	35	35	78
90°	1	6	14	16	17	6
95°	35	11	18	22	22	41
105°	169	176	124	24	25	180
115°	318	321	326	332	334	314
125°	448	452	454	456	457	400
135°	557	561	563	565	563	429
145°	643	647	648	649	649	403
155°	708	707	708	711	707	326
165°	747	746	745	749	746	211
175°	765	762	762	766	762	73
180°	765	765	765	765	765	

TEST NUMBER: P1010807

CATALOG NUMBER: S123RDIP-B1000D585UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1658.6	1658.6	1658.6	1658.6	1658.6
2.5°	1665.3	1659.9	1643.8	1658.6	1655.9
5°	1658.6	1651.8	1635.7	1647.8	1645.1
7.5°	1646.5	1639.7	1619.6	1627.6	1623.6
10°	1630.3	1620.9	1596.7	1598.0	1591.3
12.5°	1607.5	1596.7	1565.8	1564.4	1556.3
15°	1581.9	1567.1	1529.4	1522.7	1513.3
17.5°	1551.0	1534.8	1487.7	1474.3	1460.8
20°	1516.0	1494.5	1443.3	1425.9	1409.7
22.5°	1477.0	1451.4	1396.3	1373.4	1358.6
25°	1439.3	1405.7	1343.8	1315.6	1300.8
27.5°	1393.6	1357.3	1290.0	1252.3	1229.5
30°	1346.5	1306.1	1230.8	1185.1	1163.6
32.5°	1299.4	1252.3	1171.6	1120.5	1097.6
35°	1245.6	1197.2	1113.8	1055.9	1031.7
37.5°	1191.8	1139.3	1051.9	987.3	957.7
40°	1140.7	1081.5	986.0	916.0	885.1
42.5°	1082.8	1023.7	924.1	846.1	819.2
45°	1023.7	963.1	859.5	782.9	750.6
47.5°	965.8	898.6	796.3	712.9	684.7
50°	901.2	838.0	729.1	645.7	614.7
52.5°	843.4	773.5	665.8	578.4	551.5
55°	777.5	711.6	597.2	519.2	492.3
57.5°	718.3	647.0	531.3	457.4	434.5
60°	656.4	582.4	470.8	398.2	375.3
62.5°	594.6	520.6	408.9	341.7	317.5
65°	531.3	457.4	352.4	286.5	271.7
67.5°	468.1	392.8	290.6	240.8	224.6
70°	406.2	333.6	239.4	192.4	177.6
72.5°	344.4	273.1	189.7	153.3	149.3
75°	281.1	216.6	142.6	129.1	126.4
77.5°	223.3	164.1	111.6	103.6	100.9
80°	168.1	113.0	84.7	80.7	78.0
82.5°	115.7	69.9	60.5	56.5	56.5
85°	71.3	41.7	37.7	35.0	35.0
87.5°	32.3	17.5	17.5	16.1	14.8
90°	0.6	6.2	13.6	15.9	17.0
92.5°	13.1	9.7	14.8	18.7	19.3
95°	34.7	11.4	17.6	21.6	21.6
97.5°	63.1	47.2	18.2	22.7	23.3
100°	96.0	107.4	18.7	23.3	23.9
102.5°	133.5	140.9	42.0	23.3	24.4
105°	169.3	175.6	124.4	23.9	25.0
107.5°	207.4	212.5	221.0	133.5	59.1
110°	245.5	250.0	256.2	237.5	156.2



TEST NUMBER: P1010807

CATALOG NUMBER: S123RDIP-B1000D585UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	281.8	285.8	292.0	297.2	296.0
115°	317.6	321.0	326.1	331.8	334.1
117.5°	352.8	356.8	359.7	364.2	364.8
120°	385.2	390.3	392.0	396.6	396.6
122.5°	418.2	422.2	424.4	427.3	427.8
125°	447.7	452.3	454.5	455.7	456.8
127.5°	477.3	481.8	484.7	486.4	485.2
130°	504.5	509.1	511.4	513.6	512.5
132.5°	530.7	535.2	536.9	539.2	537.5
135°	557.4	560.8	563.1	564.8	563.1
137.5°	580.1	584.7	585.8	588.6	587.5
140°	602.8	606.2	608.0	610.2	609.1
142.5°	623.9	627.3	629.0	630.7	629.0
145°	643.2	647.2	648.3	649.4	649.4
147.5°	661.9	664.8	665.9	667.0	664.2
150°	679.0	680.7	681.8	683.0	681.2
152.5°	694.3	694.9	695.5	697.7	694.9
155°	708.5	707.4	708.0	710.8	707.4
157.5°	719.9	719.9	719.3	722.7	718.2
160°	730.1	729.5	729.0	732.4	728.4
162.5°	739.8	738.1	737.5	741.5	738.1
165°	747.2	745.5	744.9	749.4	745.5
167.5°	753.4	751.1	751.1	755.7	751.1
170°	758.5	756.2	756.2	760.8	756.2
172.5°	761.9	759.1	759.7	764.2	759.1
175°	764.8	761.9	762.5	766.5	761.9
177.5°	765.9	763.1	763.6	768.2	762.5
180°	764.8	764.8	764.8	764.8	764.8

(END OF REPORT)