

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010816

Luminaire Tested: S123RDIP-B1000D805UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010816
REPORT IS A COMBINATION OF REPORTS P992892 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1000D805UB2750-4F0-XX-W2A-F_3500K
Description: Define 3 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6934.0 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010816

CATALOG NUMBER: S123RDIP-B1000D805UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1010816

CATALOG NUMBER: S123RDIP-B1000D805UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	55		
1	99	95	91	88	92	88	85	82	76	74	71	64	63	61	54	53	52	47		
2	91	83	77	72	84	78	72	68	67	63	60	57	54	52	48	46	44	40		
3	83	74	66	61	77	69	62	57	59	55	51	51	47	44	43	40	38	34		
4	76	65	58	52	70	61	54	49	53	48	43	45	41	38	38	35	33	29		
5	70	58	50	44	65	55	47	42	48	42	38	41	37	33	35	32	29	26		
6	64	53	45	39	60	49	42	37	43	37	33	37	33	29	32	28	26	23		
7	60	48	40	34	55	45	38	32	39	33	29	34	29	26	29	26	23	20		
8	55	43	36	30	51	41	34	29	36	30	26	31	27	23	27	23	21	18		
9	52	40	32	27	48	37	31	26	33	27	23	29	24	21	25	21	19	17		
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	23	20	17	15		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18034	18034	18034
5°	18063	17396	17349
10°	17922	16742	16411
15°	17688	15933	15385
20°	17384	15054	14239
25°	17069	14140	13153
30°	16664	13168	11868
35°	16249	12214	10698
40°	15859	11177	9406
45°	15356	10163	8244
50°	14804	9081	7042
55°	14231	7922	5939
60°	13683	6734	4821
65°	12974	5514	3763
70°	12086	4170	2690
75°	10803	2823	2130
80°	9218	1962	1494
85°	6916	1058	782

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15356 cd/sqm

TEST NUMBER: P1010816

CATALOG NUMBER: S123RDIP-B1000D805UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.5	2.3
10°-20°	438.1	6.3
20°-30°	630.8	9.1
30°-40°	710.4	10.2
40°-50°	679.5	9.8
50°-60°	556.3	8.0
60°-70°	375.0	5.4
70°-80°	188.1	2.7
80°-90°	51.2	0.7
90°-100°	36.4	0.5
100°-110°	176.0	2.5
110°-120°	431.3	6.2
120°-130°	547.5	7.9
130°-140°	584.9	8.4
140°-150°	546.9	7.9
150°-160°	441.1	6.4
160°-170°	284.7	4.1
170°-180°	98.1	1.4
0°-30°	1226.5	17.7
0°-40°	1936.9	27.9
0°-60°	3172.7	45.8
0°-90°	3787.1	54.6
90°-120°	643.7	9.3
90°-150°	2323.0	33.5
90°-180°	3147.0	45.4
0°-180°	6934.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1675	1675	1675	1675	1675	
5°	1675	1669	1652	1664	1662	159
15°	1598	1583	1545	1538	1529	450
25°	1454	1420	1357	1329	1314	669
35°	1258	1209	1125	1067	1042	788
45°	1034	973	868	791	758	798
55°	785	719	603	524	497	704
65°	537	462	356	289	274	531
75°	284	219	144	130	128	303
85°	72	42	38	35	35	79
90°	1	8	18	22	23	7
95°	47	15	24	29	29	56
105°	228	237	168	32	34	242
115°	429	433	440	448	451	423
125°	604	610	614	615	617	540
135°	752	757	760	762	760	579
145°	868	874	875	877	877	544
155°	956	955	956	959	955	441
165°	1008	1006	1005	1012	1006	285
175°	1032	1028	1029	1035	1028	98
180°	1032	1032	1032	1032	1032	

TEST NUMBER: P1010816

CATALOG NUMBER: S123RDIP-B1000D805UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1675.4	1675.4	1675.4	1675.4	1675.4
2.5°	1682.2	1676.7	1660.4	1675.4	1672.7
5°	1675.4	1668.6	1652.3	1664.5	1661.8
7.5°	1663.2	1656.4	1636.0	1644.1	1640.1
10°	1646.9	1637.3	1612.9	1614.2	1607.4
12.5°	1623.8	1612.9	1581.6	1580.3	1572.1
15°	1597.9	1583.0	1544.9	1538.2	1528.6
17.5°	1566.7	1550.4	1502.8	1489.2	1475.6
20°	1531.4	1509.6	1458.0	1440.3	1424.0
22.5°	1492.0	1466.1	1410.4	1387.3	1372.4
25°	1453.9	1419.9	1357.4	1328.9	1314.0
27.5°	1407.7	1371.0	1303.1	1265.0	1241.9
30°	1360.1	1319.4	1243.3	1197.1	1175.4
32.5°	1312.6	1265.0	1183.5	1131.9	1108.8
35°	1258.2	1209.3	1125.1	1066.7	1042.2
37.5°	1203.9	1150.9	1062.6	997.4	967.5
40°	1152.3	1092.5	996.0	925.3	894.1
42.5°	1093.8	1034.0	933.5	854.7	827.5
45°	1034.0	972.9	868.3	790.8	758.2
47.5°	975.6	907.7	804.4	720.2	691.6
50°	910.4	846.5	736.5	652.2	621.0
52.5°	852.0	781.3	672.6	584.3	557.1
55°	785.4	718.8	603.3	524.5	497.3
57.5°	725.6	653.6	536.7	462.0	438.9
60°	663.1	588.4	475.6	402.2	379.1
62.5°	600.6	525.9	413.1	345.1	320.7
65°	536.7	462.0	356.0	289.4	274.5
67.5°	472.9	396.8	293.5	243.2	226.9
70°	410.4	337.0	241.9	194.3	179.4
72.5°	347.9	275.8	191.6	154.9	150.8
75°	284.0	218.8	144.0	130.4	127.7
77.5°	225.6	165.8	112.8	104.6	101.9
80°	169.8	114.1	85.6	81.5	78.8
82.5°	116.9	70.7	61.1	57.1	57.1
85°	72.0	42.1	38.0	35.3	35.3
87.5°	32.6	17.7	17.7	16.3	14.9
90°	0.8	8.4	18.4	21.5	23.0
92.5°	17.6	13.0	19.9	25.3	26.1
95°	46.8	15.3	23.8	29.1	29.1
97.5°	85.1	63.7	24.5	30.7	31.4
100°	129.6	144.9	25.3	31.4	32.2
102.5°	180.2	190.2	56.8	31.4	33.0
105°	228.5	237.0	168.0	32.2	33.7
107.5°	279.9	286.8	298.3	180.2	79.8
110°	331.3	337.4	345.9	320.6	210.9



TEST NUMBER: P1010816

CATALOG NUMBER: S123RDIP-B1000D805UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	380.4	385.8	394.2	401.1	399.6
115°	428.7	433.3	440.2	447.9	450.9
117.5°	476.3	481.6	485.5	491.6	492.4
120°	520.0	526.9	529.2	535.3	535.3
122.5°	564.4	569.8	572.9	576.7	577.5
125°	604.3	610.5	613.5	615.1	616.6
127.5°	644.2	650.3	654.2	656.5	654.9
130°	681.0	687.2	690.2	693.3	691.8
132.5°	716.3	722.4	724.7	727.8	725.5
135°	752.3	756.9	760.0	762.3	760.0
137.5°	783.0	789.2	790.7	794.5	793.0
140°	813.7	818.3	820.6	823.7	822.1
142.5°	842.1	846.7	849.0	851.3	849.0
145°	868.1	873.5	875.0	876.6	876.6
147.5°	893.5	897.3	898.8	900.4	896.5
150°	916.5	918.8	920.3	921.8	919.5
152.5°	937.2	937.9	938.7	941.8	937.9
155°	956.3	954.8	955.6	959.4	954.8
157.5°	971.7	971.7	970.9	975.5	969.4
160°	985.5	984.7	983.9	988.5	983.2
162.5°	998.5	996.2	995.5	1000.8	996.2
165°	1008.5	1006.2	1005.4	1011.6	1006.2
167.5°	1016.9	1013.9	1013.9	1020.0	1013.9
170°	1023.8	1020.8	1020.8	1026.9	1020.8
172.5°	1028.4	1024.6	1025.4	1031.5	1024.6
175°	1032.3	1028.4	1029.2	1034.6	1028.4
177.5°	1033.8	1030.0	1030.7	1036.9	1029.2
180°	1032.3	1032.3	1032.3	1032.3	1032.3

(END OF REPORT)