

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010826

Luminaire Tested: S123RDIP-B1165D1025UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010826
REPORT IS A COMBINATION OF REPORTS P992932 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1165D1025UB2750-4F0-XX-W2A-F_3500K
Description: Define 3 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8482.0 lumens
Efficiency: N/A
Efficacy: 94.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010826

CATALOG NUMBER: S123RDIP-B1165D1025UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1010826

CATALOG NUMBER: S123RDIP-B1165D1025UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	84	84	84	71	71	71	58	58	58
1	99	94	91	87	91	87	84	81	75	72	70	63	61	60	52	51	50
2	90	83	77	72	83	77	72	67	66	62	59	55	53	50	46	44	42
3	82	73	66	60	76	68	62	57	58	54	50	49	46	43	41	39	36
4	75	65	57	51	70	60	54	48	52	47	43	44	40	37	37	34	32
5	69	58	50	44	64	54	47	42	47	41	37	40	36	32	33	30	28
6	64	52	44	38	59	49	42	36	42	37	32	36	32	28	30	27	25
7	59	47	39	34	55	44	37	32	38	33	29	33	29	25	28	24	22
8	55	43	35	30	51	40	33	28	35	29	26	30	26	23	26	22	20
9	51	39	32	27	48	37	30	25	32	27	23	28	23	20	24	20	18
10	48	36	29	24	44	34	27	23	30	24	21	26	21	19	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20997	20997	20997
5°	21031	20254	20200
10°	20866	19492	19109
15°	20595	18551	17913
20°	20240	17528	16578
25°	19873	16464	15314
30°	19404	15332	13818
35°	18919	14221	12457
40°	18464	13014	10952
45°	17881	11834	9599
50°	17237	10573	8199
55°	16568	9223	6915
60°	15932	7839	5613
65°	15106	6420	4382
70°	14071	4854	3131
75°	12580	3287	2481
80°	10738	2285	1741
85°	8059	1234	911

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17881 cd/sqm

TEST NUMBER: P1010826

CATALOG NUMBER: S123RDIP-B1165D1025UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.4	2.2
10°-20°	510.1	6.0
20°-30°	734.5	8.7
30°-40°	827.2	9.8
40°-50°	791.2	9.3
50°-60°	647.7	7.6
60°-70°	436.7	5.1
70°-80°	219.0	2.6
80°-90°	59.9	0.7
90°-100°	47.1	0.6
100°-110°	227.8	2.7
110°-120°	558.1	6.6
120°-130°	708.5	8.4
130°-140°	756.9	8.9
140°-150°	707.8	8.3
150°-160°	570.9	6.7
160°-170°	368.4	4.3
170°-180°	127.0	1.5
0°-30°	1428.0	16.8
0°-40°	2255.2	26.6
0°-60°	3694.0	43.6
0°-90°	4409.7	52.0
90°-120°	833.0	9.8
90°-150°	3006.1	35.4
90°-180°	4072.0	48.0
0°-180°	8482.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1951	1951	1951	1951	1951	
5°	1951	1943	1924	1938	1935	185
15°	1860	1843	1799	1791	1780	524
25°	1693	1653	1580	1547	1530	779
35°	1465	1408	1310	1242	1214	917
45°	1204	1133	1011	921	883	929
55°	914	837	702	611	579	820
65°	625	538	414	337	320	618
75°	331	255	168	152	149	352
85°	84	49	44	41	41	92
90°	1	11	24	28	30	9
95°	60	20	31	38	38	72
105°	296	307	217	42	44	314
115°	555	561	570	580	584	548
125°	782	790	794	796	798	699
135°	974	980	984	986	984	750
145°	1123	1130	1132	1134	1134	703
155°	1238	1236	1237	1242	1236	570
165°	1305	1302	1301	1309	1302	369
175°	1336	1331	1332	1339	1331	127
180°	1336	1336	1336	1336	1336	

TEST NUMBER: P1010826

CATALOG NUMBER: S123RDIP-B1165D1025UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1950.7	1950.7	1950.7	1950.7	1950.7
2.5°	1958.6	1952.3	1933.3	1950.7	1947.5
5°	1950.7	1942.8	1923.8	1938.1	1934.9
7.5°	1936.5	1928.6	1904.8	1914.3	1909.6
10°	1917.5	1906.4	1877.9	1879.5	1871.6
12.5°	1890.6	1877.9	1841.5	1840.0	1830.5
15°	1860.5	1843.1	1798.8	1790.9	1779.8
17.5°	1824.1	1805.2	1749.8	1734.0	1718.1
20°	1783.0	1757.7	1697.6	1677.0	1658.0
22.5°	1737.1	1707.1	1642.2	1615.3	1597.9
25°	1692.8	1653.3	1580.5	1547.3	1529.9
27.5°	1639.0	1596.3	1517.2	1472.9	1446.0
30°	1583.7	1536.2	1447.6	1393.8	1368.5
32.5°	1528.3	1472.9	1378.0	1317.9	1291.0
35°	1465.0	1408.1	1310.0	1241.9	1213.5
37.5°	1401.7	1340.0	1237.2	1161.2	1126.4
40°	1341.6	1272.0	1159.7	1077.4	1041.0
42.5°	1273.6	1204.0	1086.9	995.1	963.5
45°	1204.0	1132.8	1011.0	920.8	882.8
47.5°	1135.9	1056.8	936.6	838.5	805.3
50°	1060.0	985.6	857.5	759.4	723.0
52.5°	992.0	909.7	783.1	680.3	648.7
55°	914.4	836.9	702.4	610.7	579.0
57.5°	844.8	761.0	624.9	537.9	511.0
60°	772.1	685.0	553.7	468.3	441.4
62.5°	699.3	612.3	481.0	401.8	373.4
65°	624.9	537.9	414.5	337.0	319.6
67.5°	550.6	462.0	341.7	283.2	264.2
70°	477.8	392.4	281.6	226.2	208.8
72.5°	405.0	321.2	223.1	180.4	175.6
75°	330.7	254.7	167.7	151.9	148.7
77.5°	262.6	193.0	131.3	121.8	118.7
80°	197.8	132.9	99.7	94.9	91.8
82.5°	136.1	82.3	71.2	66.4	66.4
85°	83.9	49.0	44.3	41.1	41.1
87.5°	38.0	20.6	20.6	19.0	17.4
90°	1.0	10.9	23.8	27.8	29.8
92.5°	22.8	16.9	25.8	32.8	33.7
95°	60.5	19.8	30.8	37.7	37.7
97.5°	110.2	82.4	31.8	39.7	40.7
100°	167.7	187.6	32.8	40.7	41.7
102.5°	233.2	246.1	73.4	40.7	42.7
105°	295.7	306.7	217.3	41.7	43.7
107.5°	362.2	371.2	386.1	233.2	103.2
110°	428.7	436.7	447.6	414.8	272.9

TEST NUMBER: P1010826

CATALOG NUMBER: S123RDIP-B1165D1025UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	492.2	499.2	510.1	519.0	517.1
115°	554.8	560.7	569.7	579.6	583.5
117.5°	616.3	623.2	628.2	636.1	637.1
120°	672.9	681.8	684.8	692.7	692.7
122.5°	730.4	737.4	741.3	746.3	747.3
125°	782.0	790.0	793.9	795.9	797.9
127.5°	833.6	841.6	846.5	849.5	847.5
130°	881.3	889.2	893.2	897.2	895.2
132.5°	926.9	934.9	937.8	941.8	938.8
135°	973.6	979.5	983.5	986.5	983.5
137.5°	1013.3	1021.2	1023.2	1028.2	1026.2
140°	1053.0	1058.9	1061.9	1065.9	1063.9
142.5°	1089.7	1095.6	1098.6	1101.6	1098.6
145°	1123.4	1130.4	1132.4	1134.3	1134.3
147.5°	1156.2	1161.1	1163.1	1165.1	1160.2
150°	1186.0	1188.9	1190.9	1192.9	1189.9
152.5°	1212.7	1213.7	1214.7	1218.7	1213.7
155°	1237.6	1235.6	1236.6	1241.5	1235.6
157.5°	1257.4	1257.4	1256.4	1262.4	1254.4
160°	1275.3	1274.3	1273.3	1279.2	1272.3
162.5°	1292.1	1289.2	1288.2	1295.1	1289.2
165°	1305.0	1302.1	1301.1	1309.0	1302.1
167.5°	1316.0	1312.0	1312.0	1319.9	1312.0
170°	1324.9	1320.9	1320.9	1328.9	1320.9
172.5°	1330.8	1325.9	1326.9	1334.8	1325.9
175°	1335.8	1330.8	1331.8	1338.8	1330.8
177.5°	1337.8	1332.8	1333.8	1341.8	1331.8
180°	1335.8	1335.8	1335.8	1335.8	1335.8

(END OF REPORT)