

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011151

Luminaire Tested: S123DIP-B1000D365UB50-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011151
REPORT IS A COMBINATION OF REPORTS P989196 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D365UB50-4F0-XX-W2A-F
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5341.0 lumens
Efficiency: N/A
Efficacy: 95.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011151

CATALOG NUMBER: S123DIP-B1000D365UB50-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1011151

CATALOG NUMBER: S123DIP-B1000D365UB50-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	78	78	78
1	103	98	94	91	98	94	90	87	85	82	79	76	74	72	69	67	66
2	94	86	80	74	89	82	76	71	74	70	66	67	64	60	61	58	55
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	54	50	47
4	78	67	59	52	74	64	56	51	58	52	47	53	48	44	48	44	41
5	72	60	51	45	68	57	49	44	52	46	41	48	42	38	43	39	35
6	66	54	45	39	63	52	44	38	47	41	36	43	38	33	39	35	31
7	62	49	40	35	58	47	39	34	43	36	32	39	34	30	36	31	28
8	57	44	36	31	54	43	35	30	39	33	28	36	30	27	33	28	25
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22
10	50	37	30	25	48	36	29	24	33	27	23	31	25	22	28	24	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16283	16283	16283
5°	16323	15721	15697
10°	16178	15189	15033
15°	15953	14635	14309
20°	15696	14022	13592
25°	15362	13373	12824
30°	14997	12702	12018
35°	14614	12016	11216
40°	14214	11298	10428
45°	13773	10596	9603
50°	13326	9815	8776
55°	12751	9001	7939
60°	12158	8103	7047
65°	11603	7132	6116
70°	10802	6054	5032
75°	9647	4793	3906
80°	8333	3369	2763
85°	6493	1810	1383

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13773 cd/sqm

TEST NUMBER: P1011151

CATALOG NUMBER: S123DIP-B1000D365UB50-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	142.6	2.7
10°-20°	402.7	7.5
20°-30°	594.7	11.1
30°-40°	694.6	13.0
40°-50°	698.3	13.1
50°-60°	613.4	11.5
60°-70°	456.8	8.6
70°-80°	260.0	4.9
80°-90°	74.8	1.4
90°-100°	16.2	0.3
100°-110°	78.5	1.5
110°-120°	192.3	3.6
120°-130°	244.1	4.6
130°-140°	260.8	4.9
140°-150°	243.8	4.6
150°-160°	196.7	3.7
160°-170°	126.9	2.4
170°-180°	43.7	0.8
0°-30°	1140.0	21.3
0°-40°	1834.6	34.3
0°-60°	3146.3	58.9
0°-90°	3937.9	73.7
90°-120°	287.0	5.4
90°-150°	1035.7	19.4
90°-180°	1403.0	26.3
0°-180°	5341.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1513	1513	1513	1513	1513	
5°	1514	1508	1493	1506	1504	144
15°	1441	1436	1419	1430	1422	406
25°	1308	1301	1284	1285	1281	603
35°	1132	1124	1107	1099	1093	708
45°	927	922	905	890	883	716
55°	704	702	686	671	665	630
65°	480	474	460	450	446	474
75°	254	248	244	238	234	271
85°	68	65	65	62	62	73
90°	0	4	8	10	10	6
95°	21	7	11	13	13	25
105°	102	106	75	14	15	108
115°	191	193	196	200	201	189
125°	269	272	274	274	275	241
135°	335	338	339	340	339	258
145°	387	390	390	391	391	242
155°	426	426	426	428	426	196
165°	450	449	448	451	449	127
175°	460	458	459	461	458	44
180°	460	460	460	460	460	

TEST NUMBER: P1011151

CATALOG NUMBER: S123DIP-B1000D365UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1512.7	1512.7	1512.7	1512.7	1512.7
2.5°	1519.2	1514.0	1499.7	1512.7	1511.4
5°	1514.0	1507.5	1493.2	1506.2	1503.6
7.5°	1502.3	1495.8	1481.5	1493.2	1491.9
10°	1486.7	1480.2	1463.3	1475.0	1472.4
12.5°	1465.9	1460.7	1445.1	1452.9	1451.6
15°	1441.2	1436.0	1419.1	1429.5	1421.7
17.5°	1413.9	1407.4	1390.5	1398.3	1395.7
20°	1382.7	1374.9	1358.0	1363.2	1359.3
22.5°	1347.6	1339.7	1322.8	1326.7	1321.5
25°	1308.5	1300.7	1283.8	1285.1	1281.2
27.5°	1268.2	1260.4	1242.2	1243.5	1239.6
30°	1224.0	1217.5	1199.3	1199.3	1190.2
32.5°	1179.8	1170.7	1157.6	1148.5	1144.6
35°	1131.6	1123.8	1106.9	1099.1	1092.6
37.5°	1083.5	1073.1	1056.2	1047.1	1043.2
40°	1032.8	1025.0	1006.8	996.4	991.2
42.5°	982.0	972.9	954.7	944.3	939.1
45°	927.4	922.2	905.3	889.7	883.2
47.5°	874.1	866.3	850.7	835.1	829.9
50°	819.5	813.0	796.0	781.7	773.9
52.5°	762.2	758.3	740.1	728.4	720.6
55°	703.7	702.4	685.5	671.2	664.7
57.5°	649.1	643.9	630.9	617.8	610.0
60°	589.2	587.9	572.3	560.6	554.1
62.5°	535.9	532.0	516.4	504.7	500.8
65°	480.0	473.5	460.5	450.1	446.1
67.5°	420.1	414.9	404.5	395.4	390.2
70°	366.8	359.0	351.2	342.1	335.6
72.5°	310.9	305.7	296.6	288.8	286.2
75°	253.6	248.4	244.5	238.0	234.1
77.5°	202.9	200.3	195.1	189.9	189.9
80°	153.5	149.6	147.0	145.7	145.7
82.5°	105.4	105.4	105.4	102.8	101.5
85°	67.6	65.0	65.0	62.4	62.4
87.5°	33.8	29.9	28.6	27.3	27.3
90°	0.3	3.8	8.2	9.6	10.3
92.5°	7.9	5.8	8.9	11.3	11.6
95°	20.9	6.8	10.6	13.0	13.0
97.5°	38.0	28.4	10.9	13.7	14.0
100°	57.8	64.6	11.3	14.0	14.4
102.5°	80.4	84.8	25.3	14.0	14.7
105°	101.9	105.7	74.9	14.4	15.0
107.5°	124.8	127.9	133.0	80.4	35.6
110°	147.7	150.4	154.2	142.9	94.0

TEST NUMBER: P1011151

CATALOG NUMBER: S123DIP-B1000D365UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	169.6	172.0	175.8	178.8	178.1
115°	191.1	193.2	196.3	199.7	201.1
117.5°	212.3	214.7	216.4	219.2	219.5
120°	231.8	234.9	235.9	238.7	238.7
122.5°	251.7	254.1	255.4	257.1	257.5
125°	269.4	272.2	273.5	274.2	274.9
127.5°	287.2	290.0	291.7	292.7	292.0
130°	303.6	306.4	307.7	309.1	308.4
132.5°	319.4	322.1	323.1	324.5	323.5
135°	335.4	337.5	338.9	339.9	338.9
137.5°	349.1	351.8	352.5	354.2	353.6
140°	362.8	364.8	365.9	367.2	366.6
142.5°	375.4	377.5	378.5	379.5	378.5
145°	387.1	389.5	390.1	390.8	390.8
147.5°	398.4	400.1	400.7	401.4	399.7
150°	408.6	409.6	410.3	411.0	410.0
152.5°	417.8	418.2	418.5	419.9	418.2
155°	426.4	425.7	426.0	427.8	425.7
157.5°	433.2	433.2	432.9	434.9	432.2
160°	439.4	439.0	438.7	440.7	438.4
162.5°	445.2	444.2	443.8	446.2	444.2
165°	449.6	448.6	448.3	451.0	448.6
167.5°	453.4	452.0	452.0	454.8	452.0
170°	456.5	455.1	455.1	457.8	455.1
172.5°	458.5	456.8	457.2	459.9	456.8
175°	460.2	458.5	458.9	461.3	458.5
177.5°	460.9	459.2	459.6	462.3	458.9
180°	460.2	460.2	460.2	460.2	460.2

(END OF REPORT)