

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011155

Luminaire Tested: S123DIP-B1000D585UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011155
REPORT IS A COMBINATION OF REPORTS P989201 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D585UB27-4F0-XX-W2A-A4
Description: Define 3 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6285.0 lumens
Efficiency: N/A
Efficacy: 101.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011155

CATALOG NUMBER: S123DIP-B1000D585UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1011155

CATALOG NUMBER: S123DIP-B1000D585UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	105	105	105	105	93	93	93	81	81	81	71	71	71	67		
1	102	98	94	90	96	92	89	86	82	79	77	72	70	69	64	62	61	57		
2	93	86	80	74	87	81	76	71	72	68	64	64	61	58	56	54	52	48		
3	85	76	68	62	80	72	65	60	64	59	54	57	53	49	50	47	45	41		
4	78	67	59	53	73	64	56	51	57	51	47	51	46	43	45	42	39	36		
5	72	60	52	46	67	57	50	44	51	45	41	46	41	37	41	37	34	31		
6	66	54	46	40	62	51	44	38	46	40	36	42	37	33	37	33	30	27		
7	61	49	41	35	58	47	39	34	42	36	31	38	33	29	34	30	27	24		
8	57	45	37	31	54	42	35	30	38	32	28	35	30	26	31	27	24	22		
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	29	25	22	20		
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20	18		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14900	14900	14900	14900
5°	14910	17168	14954	12813
10°	14816	20775	14830	11189
15°	14611	24639	14729	10072
20°	14434	28367	14465	9268
25°	14172	29082	14204	8849
30°	13986	24027	13986	8574
35°	13754	16069	13667	8330
40°	13476	11600	13310	7959
45°	13128	9189	12750	7497
50°	12280	7803	11845	7043
55°	11350	6857	10888	6537
60°	10408	5971	9853	6005
65°	9372	5112	8918	5296
70°	8296	4243	7742	4465
75°	7091	3200	6634	3447
80°	5608	2137	5168	2264
85°	3861	982	3093	891

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 24030 cd/sqm

TEST NUMBER: P1011155

CATALOG NUMBER: S123DIP-B1000D585UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.1	2.2
10°-20°	437.3	7.0
20°-30°	735.8	11.7
30°-40°	831.5	13.2
40°-50°	744.7	11.8
50°-60°	601.2	9.6
60°-70°	418.9	6.7
70°-80°	219.9	3.5
80°-90°	54.3	0.9
90°-100°	151.9	2.4
100°-110°	444.7	7.1
110°-120°	434.2	6.9
120°-130°	345.8	5.5
130°-140°	272.8	4.3
140°-150°	203.5	3.2
150°-160°	141.9	2.3
160°-170°	83.4	1.3
170°-180°	27.1	0.4
0°-30°	1309.2	20.8
0°-40°	2140.6	34.1
0°-60°	3486.5	55.5
0°-90°	4179.5	66.5
90°-120°	1030.8	16.4
90°-150°	1853.0	29.5
90°-180°	2105.0	33.5
0°-180°	6285.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1384	1384	1384	1384	1384	
5°	1383	1644	1387	1227	1383	131
15°	1320	2448	1331	1001	1320	373
25°	1207	2905	1210	884	1207	557
35°	1065	1565	1058	812	1065	667
45°	884	845	858	690	884	676
55°	626	574	601	547	626	561
65°	388	373	369	386	388	386
75°	186	192	174	207	186	200
85°	40	44	32	40	40	46
90°	1	16	1	16	1	4
95°	19	66	19	66	19	20
105°	66	721	66	721	66	70
115°	116	876	116	876	116	115
125°	162	691	162	691	162	143
135°	189	560	189	560	189	146
145°	216	438	216	438	216	135
155°	245	363	245	363	245	113
165°	268	317	268	317	268	76
175°	279	285	279	285	279	27
180°	280	280	280	280	280	

TEST NUMBER: P1011155

CATALOG NUMBER: S123DIP-B1000D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3
2.5°	1388.3	1399.0	1404.4	1412.5	1420.5	1432.6	1436.6	1443.3	1440.6	1446.0	1448.7
5°	1382.9	1401.7	1417.8	1437.9	1456.7	1470.1	1483.5	1505.0	1521.1	1523.8	1535.9
7.5°	1373.6	1400.4	1428.6	1456.7	1492.9	1514.4	1538.5	1568.1	1592.2	1631.1	1645.9
10°	1361.5	1399.0	1439.3	1478.2	1527.8	1561.3	1590.9	1640.5	1690.1	1730.4	1767.9
12.5°	1342.7	1389.7	1442.0	1499.6	1564.0	1602.9	1643.2	1708.9	1784.0	1845.7	1886.0
15°	1319.9	1378.9	1446.0	1507.7	1578.8	1651.2	1694.1	1767.9	1875.2	1932.9	2036.2
17.5°	1301.1	1361.5	1428.6	1525.1	1621.7	1694.1	1725.0	1860.5	1934.2	2030.8	2147.5
20°	1271.6	1348.1	1433.9	1530.5	1655.2	1699.5	1762.6	1899.4	1990.6	2116.7	2260.2
22.5°	1240.8	1322.6	1425.9	1526.5	1666.0	1712.9	1798.8	1907.4	2052.3	2177.0	2335.3
25°	1207.2	1295.8	1400.4	1519.8	1656.6	1725.0	1805.5	1939.6	2096.6	2253.5	2399.7
27.5°	1173.7	1270.3	1378.9	1498.3	1631.1	1711.6	1792.1	1931.6	2132.8	2303.1	2489.6
30°	1141.5	1238.1	1346.7	1468.8	1608.3	1686.1	1762.6	1936.9	2160.9	2352.8	2540.5
32.5°	1106.6	1205.9	1319.9	1421.8	1562.7	1645.9	1731.7	1936.9	2178.4	2382.3	2554.0
35°	1065.0	1167.0	1264.9	1366.8	1506.4	1598.9	1695.5	1923.5	2194.5	2391.7	2497.6
37.5°	1024.8	1114.7	1199.2	1298.4	1444.6	1543.9	1655.2	1907.4	2186.4	2351.4	2380.9
40°	979.2	1069.1	1137.5	1230.0	1384.3	1499.6	1612.3	1886.0	2151.5	2256.2	2170.3
42.5°	934.9	1006.0	1065.0	1154.9	1322.6	1435.3	1557.3	1847.1	2083.1	2104.6	1911.4
45°	884.0	934.9	987.2	1089.2	1255.5	1370.9	1506.4	1790.7	1973.1	1911.4	1667.3
47.5°	818.2	863.8	921.5	1015.4	1184.4	1303.8	1432.6	1718.3	1813.5	1684.8	1417.8
50°	755.2	794.1	847.7	939.0	1109.3	1226.0	1362.8	1604.3	1651.2	1448.7	1222.0
52.5°	692.1	721.7	774.0	865.2	1035.5	1148.2	1273.0	1487.6	1460.7	1243.4	1042.2
55°	626.4	651.9	701.5	791.4	949.7	1057.0	1176.4	1344.0	1274.3	1067.7	906.8
57.5°	562.0	588.9	639.8	714.9	863.8	968.5	1063.7	1195.2	1090.5	925.5	783.4
60°	504.4	527.2	566.1	639.8	775.3	859.8	947.0	1036.9	949.7	790.1	681.4
62.5°	444.0	465.5	501.7	568.7	685.4	760.6	830.3	904.1	807.5	690.8	594.2
65°	387.7	405.1	438.6	500.3	595.6	657.3	713.6	764.6	686.8	579.5	507.0
67.5°	336.7	351.4	379.6	434.6	515.1	559.3	605.0	647.9	582.2	496.3	434.6
70°	281.7	293.8	319.2	359.5	423.9	469.5	503.0	535.2	476.2	407.8	366.2
72.5°	233.4	245.5	261.6	303.1	347.4	375.6	411.8	429.2	395.7	339.4	297.8
75°	186.4	195.8	210.6	237.4	279.0	297.8	320.6	334.0	303.1	265.6	240.1
77.5°	146.2	150.2	161.0	179.7	207.9	229.4	246.8	254.9	233.4	209.3	187.8
80°	103.3	108.7	116.7	132.8	154.3	161.0	171.7	181.1	167.7	146.2	132.8
82.5°	68.4	75.1	79.1	85.8	99.3	107.3	110.0	118.0	106.0	97.9	92.6
85°	40.2	42.9	44.3	48.3	55.0	59.0	63.0	64.4	61.7	60.4	55.0
87.5°	20.1	20.1	20.1	22.8	24.1	26.8	28.2	28.2	28.2	26.8	25.5
90°	1.1	2.3	3.4	5.1	6.2	6.8	7.4	9.1	10.8	12.5	14.2
92.5°	8.5	12.5	18.1	23.2	28.9	34.0	39.1	57.2	87.3	116.7	105.4
95°	19.3	21.0	27.2	36.8	51.6	62.6	73.7	121.8	206.2	299.2	336.0
97.5°	30.6	31.2	36.3	44.8	59.5	71.7	83.9	131.5	229.5	385.9	516.7
100°	41.9	42.5	46.5	54.4	68.0	79.0	90.1	129.8	213.6	362.6	536.6
102.5°	53.8	55.0	58.4	65.7	77.6	87.6	97.5	132.0	200.0	328.6	499.7
105°	65.7	67.4	70.8	77.6	88.4	97.2	106.0	136.6	194.9	302.0	455.5
107.5°	78.2	79.9	83.3	90.1	100.3	108.5	116.7	143.9	193.8	282.7	416.5
110°	91.8	93.5	96.3	102.6	112.2	120.2	128.1	153.5	196.6	272.5	384.2

TEST NUMBER: P1011155

CATALOG NUMBER: S123DIP-B1000D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	104.3	106.0	108.8	115.0	124.7	132.4	140.0	163.2	202.3	266.9	362.6
115°	116.2	118.4	121.8	127.5	137.1	144.8	152.4	173.9	208.5	266.3	348.5
117.5°	128.1	130.9	133.7	138.8	149.6	156.6	163.7	185.3	216.4	266.9	338.8
120°	140.5	142.2	145.1	150.7	161.5	168.6	175.6	196.0	225.5	269.1	332.6
122.5°	151.3	153.0	155.8	162.0	172.2	179.8	187.5	207.4	234.0	273.1	328.6
125°	161.5	162.6	166.0	172.2	183.0	190.6	198.3	218.1	243.1	277.1	325.2
127.5°	169.4	171.1	175.1	181.3	193.2	200.8	208.5	227.8	250.4	281.6	323.5
130°	176.8	178.5	183.6	190.4	202.3	210.0	217.6	236.3	257.8	286.1	321.8
132.5°	182.4	184.7	190.4	198.9	210.8	218.2	225.5	243.6	264.6	289.5	321.3
135°	189.2	191.5	197.7	206.2	218.1	225.8	233.4	251.0	270.3	292.9	320.7
137.5°	195.5	197.7	204.0	213.0	224.9	232.0	239.1	256.1	274.8	295.2	319.6
140°	201.7	204.5	210.2	219.3	230.6	237.7	244.8	261.2	278.2	297.5	319.0
142.5°	208.5	210.8	217.0	224.9	236.3	242.8	249.3	265.2	281.6	299.2	317.9
145°	215.9	217.6	222.7	231.2	240.8	247.3	253.8	268.6	283.9	299.7	316.7
147.5°	223.2	224.4	229.5	236.8	246.5	252.2	257.8	271.4	285.6	299.7	315.0
150°	230.6	231.2	235.7	243.1	251.0	256.1	261.2	274.2	286.1	299.7	312.8
152.5°	238.0	238.0	242.5	248.7	255.5	260.4	265.2	275.9	287.3	298.0	309.9
155°	245.3	245.3	248.7	254.4	260.6	264.6	268.6	278.2	287.3	296.9	306.5
157.5°	251.0	251.6	254.4	259.5	265.2	268.3	271.4	279.3	287.8	295.2	303.7
160°	257.8	257.8	260.1	264.6	268.6	271.4	274.2	281.0	287.8	294.1	300.3
162.5°	262.9	262.9	264.6	268.0	271.4	273.6	275.9	281.6	287.3	291.8	296.9
165°	268.0	267.4	268.6	271.4	273.7	275.6	277.6	282.2	286.1	289.5	293.5
167.5°	272.0	271.4	272.0	274.2	275.9	277.4	278.8	282.2	285.6	287.3	290.1
170°	275.4	274.2	274.8	276.5	277.6	278.2	278.8	281.6	283.9	285.0	286.7
172.5°	277.6	277.1	277.1	278.2	278.8	279.0	279.3	281.6	283.3	283.3	283.9
175°	279.3	278.8	278.2	279.3	279.3	279.6	279.9	281.0	282.2	281.6	281.6
177.5°	280.5	279.9	279.3	279.9	279.9	279.9	279.9	280.5	281.6	280.5	279.9
180°	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9

TEST NUMBER: P1011155

CATALOG NUMBER: S123DIP-B1000D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3
2.5°	1458.1	1460.7	1470.1	1476.8	1490.3	1488.9	1488.9	1487.6	1483.5	1490.3	1494.3
5°	1560.0	1582.8	1585.5	1615.0	1616.3	1628.4	1636.5	1629.8	1645.9	1644.5	1632.4
7.5°	1686.1	1716.9	1731.7	1759.9	1792.1	1784.0	1814.9	1820.2	1817.5	1831.0	1840.4
10°	1824.3	1877.9	1915.5	1967.8	1981.2	1989.2	2009.4	2026.8	2061.7	2034.8	2052.3
12.5°	1982.5	2021.4	2071.1	2154.2	2195.8	2222.6	2232.0	2244.1	2268.2	2253.5	2254.8
15°	2115.3	2167.6	2252.1	2355.4	2367.5	2401.0	2393.0	2465.4	2500.3	2448.0	2477.5
17.5°	2253.5	2323.2	2423.8	2513.7	2564.7	2587.5	2609.0	2678.7	2676.0	2668.0	2674.7
20°	2342.0	2456.0	2580.8	2700.2	2714.9	2732.4	2790.0	2819.5	2814.2	2837.0	2851.7
22.5°	2466.8	2587.5	2720.3	2799.4	2833.0	2853.1	2898.7	2917.5	2925.5	2930.9	2921.5
25°	2571.4	2700.2	2798.1	2867.8	2888.0	2898.7	2913.4	2918.8	2914.8	2905.4	2913.4
27.5°	2642.5	2745.8	2812.8	2845.0	2834.3	2816.9	2788.7	2769.9	2728.3	2708.2	2732.4
30°	2672.0	2717.6	2737.7	2684.1	2630.4	2587.5	2533.8	2434.6	2356.8	2379.6	2348.7
32.5°	2625.0	2595.5	2499.0	2360.8	2319.2	2249.5	2097.9	1981.2	1985.2	1923.5	1949.0
35°	2486.9	2352.8	2170.3	1961.1	1906.1	1868.5	1702.2	1676.7	1623.0	1565.4	1581.5
37.5°	2242.8	2046.9	1825.6	1671.3	1589.5	1507.7	1413.8	1357.5	1325.3	1301.1	1319.9
40°	1945.0	1706.2	1523.8	1385.6	1315.9	1263.6	1199.2	1142.8	1106.6	1102.6	1109.3
42.5°	1652.6	1451.4	1283.7	1152.2	1129.4	1067.7	1026.1	981.9	971.1	953.7	963.1
45°	1399.0	1235.4	1097.2	989.9	963.1	947.0	896.0	867.9	855.8	845.1	861.2
47.5°	1215.3	1043.6	943.0	878.6	851.8	824.9	796.8	778.0	768.6	769.9	768.6
50°	1038.2	912.1	823.6	774.0	757.9	739.1	716.3	704.2	700.2	688.1	697.5
52.5°	893.3	802.1	740.4	693.5	681.4	668.0	649.2	642.5	633.1	630.4	630.4
55°	776.6	705.6	655.9	625.1	610.3	599.6	588.9	580.8	574.1	574.1	574.1
57.5°	685.4	623.7	587.5	560.7	555.3	544.6	532.5	532.5	523.1	521.8	525.8
60°	607.6	552.6	524.5	501.7	493.6	490.9	478.9	478.9	476.2	469.5	474.8
62.5°	528.5	488.3	464.1	446.7	438.6	438.6	429.2	422.5	422.5	423.9	421.2
65°	456.1	426.6	405.1	391.7	387.7	382.3	380.9	375.6	371.6	372.9	371.6
67.5°	391.7	368.9	354.1	343.4	336.7	334.0	330.0	330.0	327.3	328.6	321.9
70°	334.0	311.2	299.1	288.4	285.7	285.7	280.3	281.7	279.0	283.0	280.3
72.5°	275.0	257.5	248.2	244.1	241.4	240.1	237.4	234.7	233.4	236.1	234.7
75°	222.7	207.9	201.2	198.5	195.8	195.8	194.5	193.2	191.8	191.8	191.8
77.5°	173.0	163.6	155.6	158.3	154.3	155.6	151.6	151.6	152.9	151.6	151.6
80°	127.4	120.7	120.7	118.0	112.7	115.4	115.4	111.3	110.0	112.7	108.7
82.5°	84.5	83.2	80.5	79.1	76.5	77.8	76.5	75.1	73.8	76.5	73.8
85°	49.6	49.6	48.3	45.6	48.3	46.9	45.6	45.6	44.3	44.3	44.3
87.5°	25.5	22.8	22.8	21.5	22.8	20.1	21.5	20.1	18.8	20.1	18.8
90°	13.6	14.2	14.7	15.3	15.8	16.4	15.9	16.4	17.0	16.4	17.0
92.5°	78.8	56.1	43.6	38.0	36.0	34.0	32.9	30.6	31.2	30.0	31.2
95°	272.5	204.0	138.3	108.2	98.0	87.8	77.1	72.0	68.0	65.7	68.0
97.5°	534.3	468.6	353.6	278.8	246.5	214.2	176.2	154.7	141.1	134.9	141.1
100°	648.2	668.0	622.1	555.8	515.6	475.4	418.2	376.8	354.7	355.3	354.7
102.5°	653.9	734.3	743.9	712.2	690.4	668.6	627.2	596.6	579.1	562.6	579.1
105°	618.2	736.6	793.2	804.0	796.6	789.3	763.2	741.7	723.6	720.7	723.6
107.5°	567.2	702.6	791.5	835.7	843.4	851.0	847.6	837.4	830.1	823.8	830.1
110°	519.6	649.3	753.6	825.0	844.8	864.6	880.5	885.0	883.9	882.8	883.9

TEST NUMBER: P1011155

CATALOG NUMBER: S123DIP-B1000D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	478.2	596.6	703.7	785.9	812.8	839.7	872.0	888.4	894.1	894.7	894.1
115°	446.5	551.3	649.9	733.2	764.0	794.9	837.4	862.4	873.7	876.5	873.7
117.5°	425.5	516.2	603.4	679.9	711.9	743.9	788.1	815.9	832.9	836.9	832.9
120°	409.7	489.5	566.0	634.0	662.6	691.3	736.0	767.7	781.3	784.7	781.3
122.5°	396.6	468.6	536.0	597.8	623.8	649.9	688.4	716.2	731.5	736.0	731.5
125°	385.9	450.4	512.2	566.6	589.2	611.9	648.2	673.1	687.3	691.3	687.3
127.5°	375.7	434.0	490.1	540.0	561.0	581.9	614.8	636.3	649.3	652.7	649.3
130°	367.7	418.7	469.7	515.6	534.8	554.1	584.2	604.6	616.5	621.0	616.5
132.5°	360.4	404.6	450.4	492.4	510.5	528.6	556.4	576.8	587.0	589.8	587.0
135°	354.1	392.1	432.3	469.1	485.2	501.4	529.2	546.2	556.4	560.4	556.4
137.5°	348.5	380.2	414.2	447.0	461.4	475.9	499.7	517.3	525.8	529.2	525.8
140°	343.4	370.0	398.9	426.1	438.2	450.4	472.0	487.8	496.9	496.3	496.9
142.5°	338.8	360.4	384.2	406.8	417.0	427.2	444.8	458.4	466.3	465.7	466.3
145°	334.9	353.0	371.7	389.8	398.0	406.3	420.4	432.3	436.9	438.0	436.9
147.5°	330.9	346.8	362.1	377.4	383.4	389.3	400.6	409.1	413.6	414.2	413.6
150°	326.9	340.0	353.0	364.9	370.3	375.7	384.2	390.4	393.8	393.8	393.8
152.5°	322.4	333.7	344.5	354.7	359.0	363.2	369.4	375.1	376.8	376.8	376.8
155°	317.9	327.5	336.6	345.1	348.5	351.9	357.0	361.5	362.6	363.2	362.6
157.5°	312.8	320.7	328.6	335.4	338.2	341.1	345.6	349.0	350.2	350.2	350.2
160°	307.7	315.0	321.3	326.9	328.9	330.9	334.9	338.3	338.3	337.7	338.3
162.5°	302.6	308.2	313.3	318.4	320.1	321.8	324.1	326.9	326.9	326.4	326.9
165°	298.0	302.6	306.0	309.9	311.4	312.8	315.0	317.3	316.7	316.7	316.7
167.5°	293.5	297.5	300.3	302.6	303.7	304.8	306.0	307.7	307.1	307.1	307.1
170°	289.5	292.4	294.1	296.3	296.9	297.5	298.0	299.2	298.6	298.6	298.6
172.5°	285.6	287.8	289.0	290.7	291.0	291.2	291.2	292.4	291.2	290.7	291.2
175°	282.7	283.9	284.4	285.6	285.6	285.6	285.6	286.1	285.6	285.0	285.6
177.5°	280.5	281.0	281.6	282.2	282.2	282.2	281.6	282.2	281.0	281.0	281.0
180°	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9

TEST NUMBER: P1011155

CATALOG NUMBER: S123DIP-B1000D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3
2.5°	1483.5	1487.6	1476.8	1474.2	1474.2	1479.5	1475.5	1439.3	1446.0	1437.9	1435.3
5°	1647.2	1639.1	1628.4	1623.0	1616.3	1597.6	1596.2	1554.6	1546.6	1519.8	1507.7
7.5°	1826.9	1820.2	1788.0	1784.0	1781.3	1763.9	1719.6	1675.4	1643.2	1612.3	1582.8
10°	2032.2	2012.0	1997.3	1967.8	1953.0	1928.9	1871.2	1829.6	1774.6	1727.7	1666.0
12.5°	2279.0	2256.2	2206.5	2185.1	2166.3	2099.2	2041.6	1994.6	1887.3	1855.1	1778.6
15°	2460.1	2411.8	2406.4	2359.5	2356.8	2283.0	2173.0	2122.0	2038.9	1920.8	1841.7
17.5°	2655.9	2613.0	2579.4	2523.1	2515.1	2445.3	2364.8	2240.1	2148.9	2036.2	1935.6
20°	2799.4	2776.6	2718.9	2696.1	2649.2	2590.2	2507.0	2352.8	2241.4	2128.7	2005.3
22.5°	2913.4	2890.6	2845.0	2814.2	2787.4	2710.9	2611.6	2480.2	2327.3	2179.7	2052.3
25°	2912.1	2905.4	2886.6	2871.9	2851.7	2795.4	2712.2	2586.1	2415.8	2253.5	2076.4
27.5°	2747.1	2765.9	2798.1	2814.2	2810.2	2802.1	2755.2	2649.2	2496.3	2303.1	2104.6
30°	2403.7	2472.1	2532.5	2613.0	2637.1	2696.1	2723.0	2662.6	2540.5	2360.8	2140.8
32.5°	1993.3	2092.5	2224.0	2268.2	2344.7	2458.7	2586.1	2609.0	2532.5	2394.3	2163.6
35°	1635.1	1716.9	1818.9	1888.6	1957.0	2142.2	2303.1	2442.6	2468.1	2376.9	2158.3
37.5°	1353.4	1411.1	1501.0	1560.0	1623.0	1781.3	2006.7	2187.8	2315.2	2317.9	2143.5
40°	1149.5	1175.0	1252.8	1295.8	1356.1	1492.9	1694.1	1930.2	2116.7	2202.5	2104.6
42.5°	973.8	1007.4	1071.7	1103.9	1142.8	1262.2	1395.0	1619.0	1849.7	2033.5	2032.2
45°	869.2	893.3	922.9	949.7	994.0	1065.0	1216.6	1384.3	1605.6	1813.5	1895.3
47.5°	776.6	799.5	829.0	837.0	866.5	933.6	1026.1	1172.4	1378.9	1585.5	1739.7
50°	698.9	717.6	737.7	752.5	765.9	820.9	890.7	1014.1	1179.1	1378.9	1570.7
52.5°	638.5	651.9	669.3	677.4	689.5	729.7	783.4	874.6	1010.0	1192.5	1378.9
55°	582.2	591.5	602.3	615.7	621.1	650.6	692.1	769.9	870.5	1034.2	1211.3
57.5°	529.8	533.9	540.6	548.6	555.3	580.8	617.0	669.3	757.9	884.0	1051.6
60°	470.8	481.5	485.6	493.6	497.6	517.8	545.9	590.2	658.6	767.3	893.3
62.5°	421.2	427.9	434.6	438.6	448.0	454.7	477.5	517.8	574.1	654.6	768.6
65°	376.9	379.6	383.6	387.7	390.3	398.4	419.8	446.7	489.6	560.7	649.2
67.5°	326.0	328.6	334.0	335.3	338.0	348.8	360.8	383.6	419.8	473.5	545.9
70°	276.3	280.3	283.0	285.7	289.7	293.8	307.2	326.0	354.1	391.7	448.0
72.5°	233.4	237.4	237.4	240.1	238.8	244.1	257.5	271.0	289.7	320.6	370.2
75°	190.5	190.5	193.2	194.5	195.8	201.2	206.6	217.3	232.1	256.2	287.1
77.5°	150.2	148.9	151.6	151.6	151.6	155.6	161.0	166.3	175.7	193.2	217.3
80°	110.0	110.0	112.7	114.0	111.3	112.7	115.4	120.7	127.4	139.5	152.9
82.5°	72.4	77.8	76.5	77.8	76.5	79.1	80.5	81.8	84.5	89.9	99.3
85°	44.3	44.3	44.3	45.6	44.3	45.6	45.6	45.6	46.9	49.6	53.7
87.5°	18.8	18.8	18.8	20.1	18.8	18.8	20.1	18.8	20.1	20.1	21.5
90°	16.4	15.9	16.4	15.8	15.3	14.7	14.2	13.6	14.2	12.5	10.8
92.5°	30.6	32.9	34.0	36.0	38.0	43.6	56.1	78.8	105.4	116.7	87.3
95°	72.0	77.1	87.8	98.0	108.2	138.3	204.0	272.5	336.0	299.2	206.2
97.5°	154.7	176.2	214.2	246.5	278.8	353.6	468.6	534.3	516.7	385.9	229.5
100°	376.8	418.2	475.4	515.6	555.8	622.1	668.0	648.2	536.6	362.6	213.6
102.5°	596.6	627.2	668.6	690.4	712.2	743.9	734.3	653.9	499.7	328.6	200.0
105°	741.7	763.2	789.3	796.6	804.0	793.2	736.6	618.2	455.5	302.0	194.9
107.5°	837.4	847.6	851.0	843.4	835.7	791.5	702.6	567.2	416.5	282.7	193.8
110°	885.0	880.5	864.6	844.8	825.0	753.6	649.3	519.6	384.2	272.5	196.6

TEST NUMBER: P1011155

CATALOG NUMBER: S123DIP-B1000D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	888.4	872.0	839.7	812.8	785.9	703.7	596.6	478.2	362.6	266.9	202.3
115°	862.4	837.4	794.9	764.0	733.2	649.9	551.3	446.5	348.5	266.3	208.5
117.5°	815.9	788.1	743.9	711.9	679.9	603.4	516.2	425.5	338.8	266.9	216.4
120°	767.7	736.0	691.3	662.6	634.0	566.0	489.5	409.7	332.6	269.1	225.5
122.5°	716.2	688.4	649.9	623.8	597.8	536.0	468.6	396.6	328.6	273.1	234.0
125°	673.1	648.2	611.9	589.2	566.6	512.2	450.4	385.9	325.2	277.1	243.1
127.5°	636.3	614.8	581.9	561.0	540.0	490.1	434.0	375.7	323.5	281.6	250.4
130°	604.6	584.2	554.1	534.8	515.6	469.7	418.7	367.7	321.8	286.1	257.8
132.5°	576.8	556.4	528.6	510.5	492.4	450.4	404.6	360.4	321.3	289.5	264.6
135°	546.2	529.2	501.4	485.2	469.1	432.3	392.1	354.1	320.7	292.9	270.3
137.5°	517.3	499.7	475.9	461.4	447.0	414.2	380.2	348.5	319.6	295.2	274.8
140°	487.8	472.0	450.4	438.2	426.1	398.9	370.0	343.4	319.0	297.5	278.2
142.5°	458.4	444.8	427.2	417.0	406.8	384.2	360.4	338.8	317.9	299.2	281.6
145°	432.3	420.4	406.3	398.0	389.8	371.7	353.0	334.9	316.7	299.7	283.9
147.5°	409.1	400.6	389.3	383.4	377.4	362.1	346.8	330.9	315.0	299.7	285.6
150°	390.4	384.2	375.7	370.3	364.9	353.0	340.0	326.9	312.8	299.7	286.1
152.5°	375.1	369.4	363.2	359.0	354.7	344.5	333.7	322.4	309.9	298.0	287.3
155°	361.5	357.0	351.9	348.5	345.1	336.6	327.5	317.9	306.5	296.9	287.3
157.5°	349.0	345.6	341.1	338.2	335.4	328.6	320.7	312.8	303.7	295.2	287.8
160°	338.3	334.9	330.9	328.9	326.9	321.3	315.0	307.7	300.3	294.1	287.8
162.5°	326.9	324.1	321.8	320.1	318.4	313.3	308.2	302.6	296.9	291.8	287.3
165°	317.3	315.0	312.8	311.4	309.9	306.0	302.6	298.0	293.5	289.5	286.1
167.5°	307.7	306.0	304.8	303.7	302.6	300.3	297.5	293.5	290.1	287.3	285.6
170°	299.2	298.0	297.5	296.9	296.3	294.1	292.4	289.5	286.7	285.0	283.9
172.5°	292.4	291.2	291.2	291.0	290.7	289.0	287.8	285.6	283.9	283.3	283.3
175°	286.1	285.6	285.6	285.6	285.6	284.4	283.9	282.7	281.6	281.6	282.2
177.5°	282.2	281.6	282.2	282.2	282.2	281.6	281.0	280.5	279.9	280.5	281.6
180°	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9

TEST NUMBER: P1011155

CATALOG NUMBER: S123DIP-B1000D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3
2.5°	1421.8	1417.8	1417.8	1415.1	1407.1	1392.3	1391.0	1393.7	1385.6	1377.6	1365.5
5°	1491.6	1466.1	1458.1	1450.0	1433.9	1407.1	1396.4	1387.0	1372.2	1354.8	1336.0
7.5°	1550.6	1514.4	1503.7	1488.9	1456.7	1419.2	1395.0	1374.9	1354.8	1330.6	1307.8
10°	1624.4	1572.1	1546.6	1525.1	1480.9	1428.6	1392.3	1362.8	1330.6	1301.1	1271.6
12.5°	1707.6	1623.0	1615.0	1562.7	1511.7	1433.9	1389.7	1346.7	1303.8	1267.6	1236.7
15°	1777.3	1684.8	1651.2	1616.3	1518.4	1421.8	1378.9	1330.6	1281.0	1242.1	1196.5
17.5°	1821.6	1745.1	1674.0	1627.1	1525.1	1439.3	1356.1	1301.1	1248.8	1195.2	1157.6
20°	1875.2	1763.9	1702.2	1639.1	1538.5	1425.9	1342.7	1274.3	1209.9	1161.6	1116.0
22.5°	1928.9	1778.6	1727.7	1659.3	1541.2	1412.5	1318.6	1250.2	1176.4	1128.1	1078.5
25°	1923.5	1800.1	1715.6	1657.9	1514.4	1400.4	1290.4	1209.9	1141.5	1079.8	1030.2
27.5°	1927.5	1776.0	1690.1	1623.0	1495.6	1382.9	1260.9	1176.4	1105.3	1040.9	988.6
30°	1928.9	1739.7	1664.6	1584.1	1460.7	1341.4	1227.3	1141.5	1066.4	996.6	949.7
32.5°	1924.9	1710.2	1616.3	1543.9	1405.7	1301.1	1188.4	1097.2	1020.8	956.4	912.1
35°	1915.5	1675.4	1566.7	1475.5	1349.4	1243.4	1152.2	1058.3	976.5	917.5	866.5
37.5°	1890.0	1637.8	1514.4	1424.5	1283.7	1176.4	1095.9	1018.1	939.0	869.2	826.3
40°	1871.2	1586.8	1462.1	1364.2	1212.6	1108.0	1040.9	967.1	889.3	826.3	784.7
42.5°	1828.3	1538.5	1408.4	1291.7	1142.8	1035.5	972.5	913.5	846.4	784.7	747.1
45°	1758.5	1486.2	1342.7	1224.7	1066.4	964.4	906.8	858.5	799.5	740.4	702.9
47.5°	1660.6	1411.1	1273.0	1154.9	991.3	888.0	830.3	794.1	747.1	697.5	665.3
50°	1554.6	1329.3	1201.9	1085.2	918.8	818.2	761.9	728.4	697.5	651.9	621.1
52.5°	1416.5	1242.1	1120.0	1008.7	841.0	744.5	694.8	670.7	638.5	606.3	579.5
55°	1282.3	1129.4	1028.8	922.9	764.6	674.7	626.4	600.9	582.2	555.3	533.9
57.5°	1126.7	1024.8	932.2	835.7	693.5	611.7	566.1	535.2	523.1	511.1	490.9
60°	983.2	905.4	830.3	749.8	619.7	545.9	501.7	477.5	465.5	457.4	444.0
62.5°	851.8	791.4	727.0	662.6	544.6	477.5	444.0	419.8	409.1	407.8	395.7
65°	725.7	682.8	630.4	567.4	474.8	415.8	383.6	368.9	356.8	356.8	347.4
67.5°	599.6	570.1	528.5	484.2	411.8	356.8	327.3	313.9	307.2	307.2	300.5
70°	499.0	478.9	441.3	402.4	339.4	297.8	275.0	262.9	258.9	260.2	254.9
72.5°	405.1	383.6	352.8	324.6	277.7	246.8	230.7	217.3	210.6	211.9	210.6
75°	313.9	303.1	276.3	254.9	217.3	195.8	181.1	174.4	169.0	170.4	167.7
77.5°	236.1	220.0	205.2	190.5	167.7	150.2	138.2	131.5	127.4	127.4	127.4
80°	161.0	158.3	146.2	138.2	119.4	106.0	96.6	95.2	91.2	91.2	91.2
82.5°	104.6	97.9	91.2	85.8	75.1	67.1	63.0	60.4	59.0	57.7	60.4
85°	57.7	53.7	51.0	45.6	41.6	37.6	33.5	32.2	30.9	32.2	30.9
87.5°	22.8	18.8	18.8	17.4	16.1	14.8	14.8	12.1	12.1	10.7	10.7
90°	9.1	7.4	6.8	6.2	5.1	3.4	2.3	1.1	2.3	3.4	5.1
92.5°	57.2	39.1	34.0	28.9	23.2	18.1	12.5	8.5	12.5	18.1	23.2
95°	121.8	73.7	62.6	51.6	36.8	27.2	21.0	19.3	21.0	27.2	36.8
97.5°	131.5	83.9	71.7	59.5	44.8	36.3	31.2	30.6	31.2	36.3	44.8
100°	129.8	90.1	79.0	68.0	54.4	46.5	42.5	41.9	42.5	46.5	54.4
102.5°	132.0	97.5	87.6	77.6	65.7	58.4	55.0	53.8	55.0	58.4	65.7
105°	136.6	106.0	97.2	88.4	77.6	70.8	67.4	65.7	67.4	70.8	77.6
107.5°	143.9	116.7	108.5	100.3	90.1	83.3	79.9	78.2	79.9	83.3	90.1
110°	153.5	128.1	120.2	112.2	102.6	96.3	93.5	91.8	93.5	96.3	102.6

TEST NUMBER: P1011155

CATALOG NUMBER: S123DIP-B1000D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	163.2	140.0	132.4	124.7	115.0	108.8	106.0	104.3	106.0	108.8	115.0
115°	173.9	152.4	144.8	137.1	127.5	121.8	118.4	116.2	118.4	121.8	127.5
117.5°	185.3	163.7	156.6	149.6	138.8	133.7	130.9	128.1	130.9	133.7	138.8
120°	196.0	175.6	168.6	161.5	150.7	145.1	142.2	140.5	142.2	145.1	150.7
122.5°	207.4	187.5	179.8	172.2	162.0	155.8	153.0	151.3	153.0	155.8	162.0
125°	218.1	198.3	190.6	183.0	172.2	166.0	162.6	161.5	162.6	166.0	172.2
127.5°	227.8	208.5	200.8	193.2	181.3	175.1	171.1	169.4	171.1	175.1	181.3
130°	236.3	217.6	210.0	202.3	190.4	183.6	178.5	176.8	178.5	183.6	190.4
132.5°	243.6	225.5	218.2	210.8	198.9	190.4	184.7	182.4	184.7	190.4	198.9
135°	251.0	233.4	225.8	218.1	206.2	197.7	191.5	189.2	191.5	197.7	206.2
137.5°	256.1	239.1	232.0	224.9	213.0	204.0	197.7	195.5	197.7	204.0	213.0
140°	261.2	244.8	237.7	230.6	219.3	210.2	204.5	201.7	204.5	210.2	219.3
142.5°	265.2	249.3	242.8	236.3	224.9	217.0	210.8	208.5	210.8	217.0	224.9
145°	268.6	253.8	247.3	240.8	231.2	222.7	217.6	215.9	217.6	222.7	231.2
147.5°	271.4	257.8	252.2	246.5	236.8	229.5	224.4	223.2	224.4	229.5	236.8
150°	274.2	261.2	256.1	251.0	243.1	235.7	231.2	230.6	231.2	235.7	243.1
152.5°	275.9	265.2	260.4	255.5	248.7	242.5	238.0	238.0	238.0	242.5	248.7
155°	278.2	268.6	264.6	260.6	254.4	248.7	245.3	245.3	245.3	248.7	254.4
157.5°	279.3	271.4	268.3	265.2	259.5	254.4	251.6	251.0	251.6	254.4	259.5
160°	281.0	274.2	271.4	268.6	264.6	260.1	257.8	257.8	257.8	260.1	264.6
162.5°	281.6	275.9	273.6	271.4	268.0	264.6	262.9	262.9	262.9	264.6	268.0
165°	282.2	277.6	275.6	273.7	271.4	268.6	267.4	268.0	267.4	268.6	271.4
167.5°	282.2	278.8	277.4	275.9	274.2	272.0	271.4	272.0	271.4	272.0	274.2
170°	281.6	278.8	278.2	277.6	276.5	274.8	274.2	275.4	274.2	274.8	276.5
172.5°	281.6	279.3	279.0	278.8	278.2	277.1	277.1	277.6	277.1	277.1	278.2
175°	281.0	279.9	279.6	279.3	279.3	278.2	278.8	279.3	278.8	278.2	279.3
177.5°	280.5	279.9	279.9	279.9	279.9	279.3	279.9	280.5	279.9	279.3	279.9
180°	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9

TEST NUMBER: P1011155

CATALOG NUMBER: S123DIP-B1000D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3
2.5°	1362.8	1361.5	1364.2	1356.1	1342.7	1336.0	1317.2	1313.2	1311.9	1313.2	1314.5
5°	1325.3	1323.9	1319.9	1306.5	1290.4	1278.3	1255.5	1254.2	1246.1	1238.1	1242.1
7.5°	1289.1	1283.7	1275.6	1258.2	1236.7	1223.3	1204.5	1191.1	1180.4	1173.7	1168.3
10°	1252.8	1244.8	1236.7	1213.9	1187.1	1167.0	1144.2	1133.5	1121.4	1116.0	1110.6
12.5°	1205.9	1197.8	1183.1	1156.3	1140.2	1114.7	1091.9	1081.1	1074.4	1063.7	1057.0
15°	1168.3	1152.2	1144.2	1116.0	1082.5	1079.8	1038.2	1035.5	1022.1	1022.1	1011.4
17.5°	1125.4	1113.3	1098.6	1070.4	1046.3	1022.1	1000.7	992.6	980.5	977.9	972.5
20°	1083.8	1067.7	1062.4	1034.2	1008.7	979.2	956.4	948.3	943.0	937.6	941.6
22.5°	1040.9	1027.5	1014.1	988.6	969.8	940.3	926.9	918.8	910.8	908.1	909.4
25°	999.3	987.2	973.8	948.3	928.2	904.1	892.0	888.0	884.0	884.0	882.6
27.5°	959.1	947.0	934.9	912.1	892.0	874.6	865.2	861.2	857.1	859.8	862.5
30°	917.5	906.8	896.0	875.9	859.8	843.7	838.4	835.7	834.3	841.0	841.0
32.5°	879.9	870.5	862.5	843.7	827.6	814.2	810.2	811.5	812.9	816.9	819.6
35°	841.0	834.3	826.3	810.2	796.8	784.7	786.0	786.0	788.7	795.4	800.8
37.5°	806.2	796.8	790.1	776.6	765.9	755.2	759.2	763.2	765.9	774.0	776.6
40°	764.6	760.6	755.2	741.8	732.4	731.0	732.4	735.1	740.4	744.5	748.5
42.5°	731.0	725.7	719.0	708.2	700.2	701.5	702.9	705.6	708.2	714.9	719.0
45°	693.5	689.5	684.1	674.7	668.0	669.3	670.7	670.7	673.4	681.4	684.1
47.5°	651.9	653.2	646.5	637.1	633.1	633.1	633.1	635.8	642.5	645.2	646.5
50°	611.7	609.0	607.6	598.2	595.6	594.2	595.6	596.9	606.3	605.0	609.0
52.5°	568.7	568.7	567.4	562.0	558.0	558.0	555.3	562.0	564.7	567.4	571.4
55°	527.2	523.1	521.8	519.1	513.7	512.4	515.1	523.1	525.8	528.5	532.5
57.5°	481.5	481.5	478.9	474.8	474.8	474.8	474.8	480.2	484.2	486.9	495.0
60°	440.0	434.6	430.6	430.6	430.6	429.2	437.3	437.3	445.3	446.7	449.4
62.5°	390.3	387.7	385.0	386.3	385.0	387.7	390.3	395.7	397.0	401.1	405.1
65°	343.4	343.4	340.7	348.8	343.4	343.4	350.1	350.1	352.8	356.8	362.2
67.5°	297.8	299.1	296.4	296.4	299.1	300.5	301.8	307.2	308.5	313.9	320.6
70°	250.8	253.5	254.9	252.2	254.9	257.5	260.2	261.6	266.9	269.6	273.6
72.5°	209.3	211.9	207.9	209.3	210.6	213.3	214.6	217.3	220.0	228.0	230.7
75°	167.7	166.3	165.0	170.4	167.7	173.0	174.4	174.4	177.1	183.8	186.4
77.5°	128.8	128.8	130.1	127.4	131.5	130.1	131.5	135.5	139.5	139.5	150.2
80°	89.9	92.6	92.6	92.6	93.9	95.2	92.6	99.3	100.6	100.6	104.6
82.5°	57.7	59.0	57.7	60.4	60.4	63.0	61.7	63.0	65.7	68.4	69.8
85°	30.9	30.9	33.5	33.5	32.2	33.5	32.2	33.5	36.2	36.2	37.6
87.5°	10.7	10.7	10.7	10.7	12.1	10.7	12.1	12.1	10.7	10.7	14.8
90°	6.2	6.8	7.4	9.1	10.8	12.5	14.2	13.6	14.2	14.7	15.3
92.5°	28.9	34.0	39.1	57.2	87.3	116.7	105.4	78.8	56.1	43.6	38.0
95°	51.6	62.6	73.7	121.8	206.2	299.2	336.0	272.5	204.0	138.3	108.2
97.5°	59.5	71.7	83.9	131.5	229.5	385.9	516.7	534.3	468.6	353.6	278.8
100°	68.0	79.0	90.1	129.8	213.6	362.6	536.6	648.2	668.0	622.1	555.8
102.5°	77.6	87.6	97.5	132.0	200.0	328.6	499.7	653.9	734.3	743.9	712.2
105°	88.4	97.2	106.0	136.6	194.9	302.0	455.5	618.2	736.6	793.2	804.0
107.5°	100.3	108.5	116.7	143.9	193.8	282.7	416.5	567.2	702.6	791.5	835.7
110°	112.2	120.2	128.1	153.5	196.6	272.5	384.2	519.6	649.3	753.6	825.0

TEST NUMBER: P1011155

CATALOG NUMBER: S123DIP-B1000D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	124.7	132.4	140.0	163.2	202.3	266.9	362.6	478.2	596.6	703.7	785.9
115°	137.1	144.8	152.4	173.9	208.5	266.3	348.5	446.5	551.3	649.9	733.2
117.5°	149.6	156.6	163.7	185.3	216.4	266.9	338.8	425.5	516.2	603.4	679.9
120°	161.5	168.6	175.6	196.0	225.5	269.1	332.6	409.7	489.5	566.0	634.0
122.5°	172.2	179.8	187.5	207.4	234.0	273.1	328.6	396.6	468.6	536.0	597.8
125°	183.0	190.6	198.3	218.1	243.1	277.1	325.2	385.9	450.4	512.2	566.6
127.5°	193.2	200.8	208.5	227.8	250.4	281.6	323.5	375.7	434.0	490.1	540.0
130°	202.3	210.0	217.6	236.3	257.8	286.1	321.8	367.7	418.7	469.7	515.6
132.5°	210.8	218.2	225.5	243.6	264.6	289.5	321.3	360.4	404.6	450.4	492.4
135°	218.1	225.8	233.4	251.0	270.3	292.9	320.7	354.1	392.1	432.3	469.1
137.5°	224.9	232.0	239.1	256.1	274.8	295.2	319.6	348.5	380.2	414.2	447.0
140°	230.6	237.7	244.8	261.2	278.2	297.5	319.0	343.4	370.0	398.9	426.1
142.5°	236.3	242.8	249.3	265.2	281.6	299.2	317.9	338.8	360.4	384.2	406.8
145°	240.8	247.3	253.8	268.6	283.9	299.7	316.7	334.9	353.0	371.7	389.8
147.5°	246.5	252.2	257.8	271.4	285.6	299.7	315.0	330.9	346.8	362.1	377.4
150°	251.0	256.1	261.2	274.2	286.1	299.7	312.8	326.9	340.0	353.0	364.9
152.5°	255.5	260.4	265.2	275.9	287.3	298.0	309.9	322.4	333.7	344.5	354.7
155°	260.6	264.6	268.6	278.2	287.3	296.9	306.5	317.9	327.5	336.6	345.1
157.5°	265.2	268.3	271.4	279.3	287.8	295.2	303.7	312.8	320.7	328.6	335.4
160°	268.6	271.4	274.2	281.0	287.8	294.1	300.3	307.7	315.0	321.3	326.9
162.5°	271.4	273.6	275.9	281.6	287.3	291.8	296.9	302.6	308.2	313.3	318.4
165°	273.7	275.6	277.6	282.2	286.1	289.5	293.5	298.0	302.6	306.0	309.9
167.5°	275.9	277.4	278.8	282.2	285.6	287.3	290.1	293.5	297.5	300.3	302.6
170°	277.6	278.2	278.8	281.6	283.9	285.0	286.7	289.5	292.4	294.1	296.3
172.5°	278.8	279.0	279.3	281.6	283.3	283.3	283.9	285.6	287.8	289.0	290.7
175°	279.3	279.6	279.9	281.0	282.2	281.6	281.6	282.7	283.9	284.4	285.6
177.5°	279.9	279.9	279.9	280.5	281.6	280.5	279.9	280.5	281.0	281.6	282.2
180°	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9

TEST NUMBER: P1011155

CATALOG NUMBER: S123DIP-B1000D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3
2.5°	1313.2	1314.5	1309.2	1305.1	1315.9	1309.2	1309.2	1310.5	1307.8	1311.9	1310.5
5°	1239.4	1240.8	1231.4	1234.1	1228.7	1227.3	1226.0	1234.1	1232.7	1231.4	1234.1
7.5°	1167.0	1167.0	1163.0	1160.3	1160.3	1156.3	1161.6	1160.3	1163.0	1163.0	1167.0
10°	1106.6	1109.3	1102.6	1095.9	1094.6	1095.9	1095.9	1097.2	1098.6	1108.0	1106.6
12.5°	1057.0	1053.0	1051.6	1047.6	1040.9	1038.2	1035.5	1050.3	1046.3	1046.3	1046.3
15°	1002.0	1011.4	1010.0	998.0	995.3	1000.7	998.0	998.0	1011.4	1010.0	1008.7
17.5°	972.5	969.8	967.1	960.4	961.8	960.4	961.8	961.8	969.8	969.8	969.8
20°	939.0	933.6	933.6	930.9	930.9	926.9	932.2	933.6	939.0	939.0	940.3
22.5°	909.4	905.4	905.4	904.1	906.8	901.4	906.8	908.1	908.1	912.1	912.1
25°	884.0	881.3	881.3	884.0	884.0	884.0	884.0	889.3	885.3	886.6	885.3
27.5°	861.2	862.5	863.8	865.2	863.8	865.2	866.5	869.2	870.5	869.2	866.5
30°	839.7	843.7	845.1	845.1	847.7	849.1	850.4	850.4	851.8	847.7	850.4
32.5°	823.6	823.6	826.3	827.6	830.3	831.6	831.6	834.3	833.0	829.0	830.3
35°	800.8	800.8	806.2	808.8	812.9	811.5	812.9	812.9	814.2	811.5	807.5
37.5°	778.0	780.7	780.7	786.0	787.4	788.7	787.4	790.1	788.7	786.0	784.7
40°	751.2	749.8	751.2	755.2	756.5	756.5	756.5	759.2	759.2	759.2	757.9
42.5°	717.6	721.7	720.3	724.3	723.0	723.0	725.7	728.4	729.7	725.7	727.0
45°	685.4	685.4	688.1	688.1	689.5	689.5	694.8	692.1	694.8	692.1	693.5
47.5°	650.6	651.9	651.9	653.2	655.9	658.6	655.9	657.3	657.3	658.6	655.9
50°	611.7	611.7	614.3	618.4	623.7	621.1	619.7	625.1	621.1	621.1	618.4
52.5°	571.4	575.4	576.8	580.8	584.8	586.2	587.5	584.8	586.2	582.2	583.5
55°	532.5	533.9	539.2	543.3	547.3	547.3	545.9	547.3	548.6	543.3	543.3
57.5°	493.6	497.6	503.0	503.0	508.4	508.4	507.0	507.0	508.4	504.4	503.0
60°	452.0	456.1	462.8	462.8	470.8	472.2	469.5	466.8	466.8	462.8	464.1
62.5°	407.8	411.8	415.8	422.5	427.9	425.2	430.6	425.2	426.6	418.5	418.5
65°	368.9	370.2	376.9	383.6	383.6	386.3	383.6	385.0	380.9	380.9	375.6
67.5°	323.3	323.3	330.0	336.7	343.4	343.4	343.4	339.4	339.4	335.3	335.3
70°	283.0	281.7	288.4	292.4	296.4	297.8	295.1	293.8	291.1	287.1	285.7
72.5°	233.4	236.1	242.8	245.5	252.2	250.8	257.5	249.5	249.5	242.8	241.4
75°	189.1	191.8	198.5	202.5	206.6	206.6	210.6	206.6	201.2	198.5	197.2
77.5°	150.2	148.9	154.3	161.0	162.3	161.0	163.6	162.3	156.9	156.9	154.3
80°	107.3	111.3	116.7	115.4	120.7	119.4	119.4	116.7	116.7	112.7	115.4
82.5°	71.1	75.1	76.5	75.1	76.5	79.1	80.5	79.1	79.1	76.5	77.8
85°	37.6	37.6	40.2	41.6	40.2	40.2	41.6	45.6	42.9	40.2	42.9
87.5°	12.1	10.7	10.7	12.1	10.7	10.7	12.1	12.1	13.4	13.4	13.4
90°	15.8	16.4	15.9	16.4	17.0	16.4	17.0	16.4	15.9	16.4	15.8
92.5°	36.0	34.0	32.9	30.6	31.2	30.0	31.2	30.6	32.9	34.0	36.0
95°	98.0	87.8	77.1	72.0	68.0	65.7	68.0	72.0	77.1	87.8	98.0
97.5°	246.5	214.2	176.2	154.7	141.1	134.9	141.1	154.7	176.2	214.2	246.5
100°	515.6	475.4	418.2	376.8	354.7	355.3	354.7	376.8	418.2	475.4	515.6
102.5°	690.4	668.6	627.2	596.6	579.1	562.6	579.1	596.6	627.2	668.6	690.4
105°	796.6	789.3	763.2	741.7	723.6	720.7	723.6	741.7	763.2	789.3	796.6
107.5°	843.4	851.0	847.6	837.4	830.1	823.8	830.1	837.4	847.6	851.0	843.4
110°	844.8	864.6	880.5	885.0	883.9	882.8	883.9	885.0	880.5	864.6	844.8

TEST NUMBER: P1011155

CATALOG NUMBER: S123DIP-B1000D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	812.8	839.7	872.0	888.4	894.1	894.7	894.1	888.4	872.0	839.7	812.8
115°	764.0	794.9	837.4	862.4	873.7	876.5	873.7	862.4	837.4	794.9	764.0
117.5°	711.9	743.9	788.1	815.9	832.9	836.9	832.9	815.9	788.1	743.9	711.9
120°	662.6	691.3	736.0	767.7	781.3	784.7	781.3	767.7	736.0	691.3	662.6
122.5°	623.8	649.9	688.4	716.2	731.5	736.0	731.5	716.2	688.4	649.9	623.8
125°	589.2	611.9	648.2	673.1	687.3	691.3	687.3	673.1	648.2	611.9	589.2
127.5°	561.0	581.9	614.8	636.3	649.3	652.7	649.3	636.3	614.8	581.9	561.0
130°	534.8	554.1	584.2	604.6	616.5	621.0	616.5	604.6	584.2	554.1	534.8
132.5°	510.5	528.6	556.4	576.8	587.0	589.8	587.0	576.8	556.4	528.6	510.5
135°	485.2	501.4	529.2	546.2	556.4	560.4	556.4	546.2	529.2	501.4	485.2
137.5°	461.4	475.9	499.7	517.3	525.8	529.2	525.8	517.3	499.7	475.9	461.4
140°	438.2	450.4	472.0	487.8	496.9	496.3	496.9	487.8	472.0	450.4	438.2
142.5°	417.0	427.2	444.8	458.4	466.3	465.7	466.3	458.4	444.8	427.2	417.0
145°	398.0	406.3	420.4	432.3	436.9	438.0	436.9	432.3	420.4	406.3	398.0
147.5°	383.4	389.3	400.6	409.1	413.6	414.2	413.6	409.1	400.6	389.3	383.4
150°	370.3	375.7	384.2	390.4	393.8	393.8	393.8	390.4	384.2	375.7	370.3
152.5°	359.0	363.2	369.4	375.1	376.8	376.8	376.8	375.1	369.4	363.2	359.0
155°	348.5	351.9	357.0	361.5	362.6	363.2	362.6	361.5	357.0	351.9	348.5
157.5°	338.2	341.1	345.6	349.0	350.2	350.2	350.2	349.0	345.6	341.1	338.2
160°	328.9	330.9	334.9	338.3	338.3	337.7	338.3	338.3	334.9	330.9	328.9
162.5°	320.1	321.8	324.1	326.9	326.9	326.4	326.9	326.9	324.1	321.8	320.1
165°	311.4	312.8	315.0	317.3	316.7	316.7	316.7	317.3	315.0	312.8	311.4
167.5°	303.7	304.8	306.0	307.7	307.1	307.1	307.1	307.7	306.0	304.8	303.7
170°	296.9	297.5	298.0	299.2	298.6	298.6	298.6	299.2	298.0	297.5	296.9
172.5°	291.0	291.2	291.2	292.4	291.2	290.7	291.2	292.4	291.2	291.2	291.0
175°	285.6	285.6	285.6	286.1	285.6	285.0	285.6	286.1	285.6	285.6	285.6
177.5°	282.2	282.2	281.6	282.2	281.0	281.0	281.0	282.2	281.6	282.2	282.2
180°	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9

TEST NUMBER: P1011155

CATALOG NUMBER: S123DIP-B1000D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3
2.5°	1314.5	1317.2	1318.6	1313.2	1309.2	1315.9	1325.3	1332.0	1337.3	1344.0	1348.1
5°	1236.7	1246.1	1246.1	1248.8	1252.8	1259.5	1277.0	1289.1	1299.8	1307.8	1314.5
7.5°	1171.0	1177.7	1181.7	1188.4	1195.2	1204.5	1224.7	1242.1	1258.2	1267.6	1278.3
10°	1112.0	1117.4	1124.1	1128.1	1140.2	1153.6	1179.1	1193.8	1212.6	1227.3	1240.8
12.5°	1055.7	1074.4	1078.5	1077.1	1087.8	1102.6	1128.1	1150.9	1171.0	1185.8	1200.5
15°	1015.4	1022.1	1030.2	1028.8	1051.6	1055.7	1077.1	1103.9	1130.8	1140.2	1153.6
17.5°	971.1	981.9	989.9	994.0	1000.7	1015.4	1035.5	1055.7	1090.5	1091.9	1126.7
20°	936.3	947.0	952.4	957.7	961.8	979.2	996.6	1019.4	1047.6	1062.4	1081.1
22.5°	913.5	918.8	922.9	926.9	932.2	941.6	963.1	988.6	1007.4	1023.5	1035.5
25°	886.6	892.0	897.4	900.1	904.1	909.4	925.5	945.7	972.5	983.2	995.3
27.5°	867.9	867.9	870.5	870.5	875.9	881.3	893.3	912.1	933.6	947.0	963.1
30°	847.7	846.4	847.7	846.4	845.1	853.1	863.8	879.9	894.7	910.8	921.5
32.5°	827.6	826.3	826.3	827.6	822.3	826.3	831.6	846.4	862.5	870.5	882.6
35°	806.2	803.5	803.5	803.5	800.8	798.1	803.5	816.9	827.6	838.4	847.7
37.5°	784.7	780.7	780.7	778.0	775.3	771.3	771.3	782.0	796.8	800.8	812.9
40°	755.2	755.2	752.5	751.2	748.5	745.8	741.8	751.2	764.6	768.6	778.0
42.5°	725.7	721.7	720.3	720.3	720.3	716.3	713.6	720.3	728.4	735.1	740.4
45°	692.1	689.5	690.8	689.5	686.8	685.4	684.1	686.8	696.2	698.9	705.6
47.5°	655.9	654.6	654.6	653.2	651.9	653.2	647.9	654.6	657.3	660.0	665.3
50°	618.4	617.0	615.7	614.3	614.3	615.7	614.3	614.3	619.7	622.4	627.8
52.5°	580.8	576.8	576.8	575.4	575.4	572.8	575.4	576.8	579.5	582.2	584.8
55°	540.6	540.6	536.5	536.5	533.9	533.9	535.2	533.9	539.2	541.9	541.9
57.5°	501.7	496.3	497.6	495.0	492.3	490.9	490.9	493.6	496.3	496.3	499.0
60°	460.1	454.7	453.4	448.0	450.7	446.7	448.0	448.0	453.4	450.7	453.4
62.5°	418.5	411.8	407.8	405.1	405.1	406.4	403.8	402.4	405.1	407.8	413.1
65°	374.2	370.2	366.2	362.2	362.2	360.8	363.5	359.5	358.1	359.5	362.2
67.5°	328.6	324.6	320.6	316.6	317.9	313.9	311.2	315.2	312.5	313.9	316.6
70°	284.4	281.7	273.6	271.0	269.6	271.0	269.6	266.9	271.0	269.6	271.0
72.5°	240.1	237.4	233.4	226.7	226.7	225.3	224.0	224.0	222.7	222.7	222.7
75°	197.2	191.8	187.8	186.4	183.8	182.4	181.1	178.4	179.7	181.1	178.4
77.5°	152.9	146.2	144.9	144.9	140.8	140.8	142.2	140.8	139.5	139.5	139.5
80°	112.7	107.3	107.3	104.6	101.9	101.9	101.9	101.9	100.6	99.3	100.6
82.5°	72.4	71.1	69.8	69.8	72.4	67.1	69.8	68.4	67.1	67.1	65.7
85°	40.2	41.6	40.2	41.6	38.9	40.2	40.2	40.2	38.9	40.2	37.6
87.5°	14.8	14.8	14.8	16.1	16.1	16.1	16.1	16.1	17.4	16.1	16.1
90°	15.3	14.7	14.2	13.6	14.2	12.5	10.8	9.1	7.4	6.8	6.2
92.5°	38.0	43.6	56.1	78.8	105.4	116.7	87.3	57.2	39.1	34.0	28.9
95°	108.2	138.3	204.0	272.5	336.0	299.2	206.2	121.8	73.7	62.6	51.6
97.5°	278.8	353.6	468.6	534.3	516.7	385.9	229.5	131.5	83.9	71.7	59.5
100°	555.8	622.1	668.0	648.2	536.6	362.6	213.6	129.8	90.1	79.0	68.0
102.5°	712.2	743.9	734.3	653.9	499.7	328.6	200.0	132.0	97.5	87.6	77.6
105°	804.0	793.2	736.6	618.2	455.5	302.0	194.9	136.6	106.0	97.2	88.4
107.5°	835.7	791.5	702.6	567.2	416.5	282.7	193.8	143.9	116.7	108.5	100.3
110°	825.0	753.6	649.3	519.6	384.2	272.5	196.6	153.5	128.1	120.2	112.2

TEST NUMBER: P1011155

CATALOG NUMBER: S123DIP-B1000D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	785.9	703.7	596.6	478.2	362.6	266.9	202.3	163.2	140.0	132.4	124.7
115°	733.2	649.9	551.3	446.5	348.5	266.3	208.5	173.9	152.4	144.8	137.1
117.5°	679.9	603.4	516.2	425.5	338.8	266.9	216.4	185.3	163.7	156.6	149.6
120°	634.0	566.0	489.5	409.7	332.6	269.1	225.5	196.0	175.6	168.6	161.5
122.5°	597.8	536.0	468.6	396.6	328.6	273.1	234.0	207.4	187.5	179.8	172.2
125°	566.6	512.2	450.4	385.9	325.2	277.1	243.1	218.1	198.3	190.6	183.0
127.5°	540.0	490.1	434.0	375.7	323.5	281.6	250.4	227.8	208.5	200.8	193.2
130°	515.6	469.7	418.7	367.7	321.8	286.1	257.8	236.3	217.6	210.0	202.3
132.5°	492.4	450.4	404.6	360.4	321.3	289.5	264.6	243.6	225.5	218.2	210.8
135°	469.1	432.3	392.1	354.1	320.7	292.9	270.3	251.0	233.4	225.8	218.1
137.5°	447.0	414.2	380.2	348.5	319.6	295.2	274.8	256.1	239.1	232.0	224.9
140°	426.1	398.9	370.0	343.4	319.0	297.5	278.2	261.2	244.8	237.7	230.6
142.5°	406.8	384.2	360.4	338.8	317.9	299.2	281.6	265.2	249.3	242.8	236.3
145°	389.8	371.7	353.0	334.9	316.7	299.7	283.9	268.6	253.8	247.3	240.8
147.5°	377.4	362.1	346.8	330.9	315.0	299.7	285.6	271.4	257.8	252.2	246.5
150°	364.9	353.0	340.0	326.9	312.8	299.7	286.1	274.2	261.2	256.1	251.0
152.5°	354.7	344.5	333.7	322.4	309.9	298.0	287.3	275.9	265.2	260.4	255.5
155°	345.1	336.6	327.5	317.9	306.5	296.9	287.3	278.2	268.6	264.6	260.6
157.5°	335.4	328.6	320.7	312.8	303.7	295.2	287.8	279.3	271.4	268.3	265.2
160°	326.9	321.3	315.0	307.7	300.3	294.1	287.8	281.0	274.2	271.4	268.6
162.5°	318.4	313.3	308.2	302.6	296.9	291.8	287.3	281.6	275.9	273.6	271.4
165°	309.9	306.0	302.6	298.0	293.5	289.5	286.1	282.2	277.6	275.6	273.7
167.5°	302.6	300.3	297.5	293.5	290.1	287.3	285.6	282.2	278.8	277.4	275.9
170°	296.3	294.1	292.4	289.5	286.7	285.0	283.9	281.6	278.8	278.2	277.6
172.5°	290.7	289.0	287.8	285.6	283.9	283.3	283.3	281.6	279.3	279.0	278.8
175°	285.6	284.4	283.9	282.7	281.6	281.6	282.2	281.0	279.9	279.6	279.3
177.5°	282.2	281.6	281.0	280.5	279.9	280.5	281.6	280.5	279.9	279.9	279.9
180°	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9

TEST NUMBER: P1011155

CATALOG NUMBER: S123DIP-B1000D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1384.3	1384.3	1384.3	1384.3
2.5°	1354.8	1358.8	1372.2	1388.3
5°	1327.9	1338.7	1357.5	1382.9
7.5°	1298.4	1314.5	1341.4	1373.6
10°	1264.9	1287.7	1321.2	1361.5
12.5°	1228.7	1258.2	1301.1	1342.7
15°	1205.9	1235.4	1274.3	1319.9
17.5°	1161.6	1196.5	1236.7	1301.1
20°	1116.0	1154.9	1207.2	1271.6
22.5°	1081.1	1122.7	1172.4	1240.8
25°	1039.6	1082.5	1136.1	1207.2
27.5°	995.3	1038.2	1098.6	1173.7
30°	961.8	1003.3	1061.0	1141.5
32.5°	921.5	961.8	1022.1	1106.6
35°	875.9	921.5	979.2	1065.0
37.5°	841.0	882.6	943.0	1024.8
40°	803.5	839.7	898.7	979.2
42.5°	763.2	803.5	854.4	934.9
45°	725.7	755.2	807.5	884.0
47.5°	685.4	719.0	759.2	818.2
50°	642.5	670.7	714.9	755.2
52.5°	600.9	623.7	661.3	692.1
55°	556.7	579.5	607.6	626.4
57.5°	515.1	531.2	550.0	562.0
60°	464.1	480.2	492.3	504.4
62.5°	418.5	430.6	437.3	444.0
65°	371.6	378.3	382.3	387.7
67.5°	320.6	327.3	328.6	336.7
70°	273.6	275.0	277.7	281.7
72.5°	229.4	232.1	230.7	233.4
75°	183.8	186.4	183.8	186.4
77.5°	139.5	142.2	142.2	146.2
80°	100.6	101.9	103.3	103.3
82.5°	65.7	69.8	67.1	68.4
85°	37.6	38.9	38.9	40.2
87.5°	17.4	18.8	17.4	20.1
90°	5.1	3.4	2.3	1.1
92.5°	23.2	18.1	12.5	8.5
95°	36.8	27.2	21.0	19.3
97.5°	44.8	36.3	31.2	30.6
100°	54.4	46.5	42.5	41.9
102.5°	65.7	58.4	55.0	53.8
105°	77.6	70.8	67.4	65.7
107.5°	90.1	83.3	79.9	78.2
110°	102.6	96.3	93.5	91.8



TEST NUMBER: P1011155

CATALOG NUMBER: S123DIP-B1000D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	115.0	108.8	106.0	104.3
115°	127.5	121.8	118.4	116.2
117.5°	138.8	133.7	130.9	128.1
120°	150.7	145.1	142.2	140.5
122.5°	162.0	155.8	153.0	151.3
125°	172.2	166.0	162.6	161.5
127.5°	181.3	175.1	171.1	169.4
130°	190.4	183.6	178.5	176.8
132.5°	198.9	190.4	184.7	182.4
135°	206.2	197.7	191.5	189.2
137.5°	213.0	204.0	197.7	195.5
140°	219.3	210.2	204.5	201.7
142.5°	224.9	217.0	210.8	208.5
145°	231.2	222.7	217.6	215.9
147.5°	236.8	229.5	224.4	223.2
150°	243.1	235.7	231.2	230.6
152.5°	248.7	242.5	238.0	238.0
155°	254.4	248.7	245.3	245.3
157.5°	259.5	254.4	251.6	251.0
160°	264.6	260.1	257.8	257.8
162.5°	268.0	264.6	262.9	262.9
165°	271.4	268.6	267.4	268.0
167.5°	274.2	272.0	271.4	272.0
170°	276.5	274.8	274.2	275.4
172.5°	278.2	277.1	277.1	277.6
175°	279.3	278.2	278.8	279.3
177.5°	279.9	279.3	279.9	280.5
180°	279.9	279.9	279.9	279.9

(END OF REPORT)