

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011159

Luminaire Tested: S123DIP-B1000D585UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011159
REPORT IS A COMBINATION OF REPORTS P989207 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D585UB27-4F0-XX-W2A-F4
Description: Define 3 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6171.9 lumens
Efficiency: N/A
Efficacy: 99.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011159

CATALOG NUMBER: S123DIP-B1000D585UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1011159

CATALOG NUMBER: S123DIP-B1000D585UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71
1	101	97	93	89	95	91	88	85	81	78	76	71	69	67	62	61	60
2	92	85	78	73	86	80	74	69	71	66	63	62	59	56	55	52	50
3	84	74	67	61	79	70	63	58	62	57	53	55	51	48	49	45	43
4	77	66	58	51	72	62	55	49	55	50	45	49	45	41	43	40	37
5	71	59	50	44	66	56	48	42	50	44	39	44	39	35	39	35	32
6	65	53	44	38	61	50	42	37	45	39	34	40	35	31	35	31	28
7	60	48	40	34	57	45	38	32	41	35	30	36	31	27	32	28	25
8	56	43	35	30	53	41	34	29	37	31	27	33	28	25	30	26	22
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	23	20
10	49	37	29	24	46	35	28	23	32	26	22	28	24	20	26	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16792	16792	16792
5°	16833	16212	16188
10°	16684	15663	15503
15°	16451	15092	14756
20°	16186	14460	14016
25°	15842	13791	13225
30°	15465	13098	12392
35°	15071	12392	11566
40°	14657	11650	10753
45°	14204	10928	9903
50°	13742	10122	9050
55°	13149	9282	8186
60°	12537	8356	7267
65°	11966	7354	6308
70°	11140	6244	5189
75°	9951	4944	4027
80°	8594	3475	2849
85°	6705	1869	1427

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14204 cd/sqm

TEST NUMBER: P1011159

CATALOG NUMBER: S123DIP-B1000D585UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.1	2.4
10°-20°	415.3	6.7
20°-30°	613.3	9.9
30°-40°	716.3	11.6
40°-50°	720.1	11.7
50°-60°	632.6	10.2
60°-70°	471.1	7.6
70°-80°	268.1	4.3
80°-90°	77.8	1.3
90°-100°	159.1	2.6
100°-110°	444.6	7.2
110°-120°	433.5	7.0
120°-130°	345.2	5.6
130°-140°	272.5	4.4
140°-150°	203.3	3.3
150°-160°	141.8	2.3
160°-170°	83.3	1.3
170°-180°	27.1	0.4
0°-30°	1175.6	19.0
0°-40°	1891.9	30.7
0°-60°	3244.6	52.6
0°-90°	4061.6	65.8
90°-120°	1037.2	16.8
90°-150°	1858.1	30.1
90°-180°	2110.0	34.2
0°-180°	6171.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1560	1560	1560	1560	1560	
5°	1561	1555	1540	1553	1551	148
15°	1486	1481	1463	1474	1466	419
25°	1349	1341	1324	1325	1321	622
35°	1167	1159	1142	1134	1127	730
45°	956	951	934	918	911	738
55°	726	724	707	692	685	650
65°	495	488	475	464	460	488
75°	262	256	252	246	241	279
85°	70	67	67	64	64	75
90°	1	7	14	16	16	6
95°	19	63	336	98	66	20
105°	66	97	456	797	721	70
115°	116	145	348	764	876	115
125°	162	191	325	589	691	143
135°	189	226	321	485	560	146
145°	216	247	317	398	438	135
155°	245	265	306	348	363	113
165°	268	276	294	311	317	76
175°	279	280	282	286	285	27
180°	280	280	280	280	280	

TEST NUMBER: P1011159

CATALOG NUMBER: S123DIP-B1000D585UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1560.0	1560.0	1560.0	1560.0	1560.0
2.5°	1566.7	1561.3	1546.6	1560.0	1558.7
5°	1561.3	1554.6	1539.9	1553.3	1550.6
7.5°	1549.3	1542.6	1527.8	1539.9	1538.5
10°	1533.2	1526.5	1509.0	1521.1	1518.4
12.5°	1511.7	1506.3	1490.3	1498.3	1497.0
15°	1486.2	1480.9	1463.4	1474.2	1466.1
17.5°	1458.1	1451.4	1433.9	1442.0	1439.3
20°	1425.9	1417.8	1400.4	1405.7	1401.7
22.5°	1389.7	1381.6	1364.2	1368.2	1362.8
25°	1349.4	1341.4	1323.9	1325.3	1321.2
27.5°	1307.8	1299.8	1281.0	1282.3	1278.3
30°	1262.2	1255.5	1236.7	1236.7	1227.3
32.5°	1216.6	1207.2	1193.8	1184.4	1180.4
35°	1167.0	1158.9	1141.5	1133.5	1126.7
37.5°	1117.4	1106.6	1089.2	1079.8	1075.8
40°	1065.0	1057.0	1038.2	1027.5	1022.1
42.5°	1012.7	1003.3	984.6	973.8	968.5
45°	956.4	951.0	933.6	917.5	910.8
47.5°	901.4	893.3	877.3	861.2	855.8
50°	845.1	838.4	820.9	806.2	798.1
52.5°	786.0	782.0	763.2	751.2	743.1
55°	725.7	724.3	706.9	692.1	685.4
57.5°	669.3	664.0	650.6	637.1	629.1
60°	607.6	606.3	590.2	578.1	571.4
62.5°	552.6	548.6	532.5	520.4	516.4
65°	495.0	488.3	474.8	464.1	460.1
67.5°	433.3	427.9	417.2	407.8	402.4
70°	378.3	370.2	362.2	352.8	346.1
72.5°	320.6	315.2	305.8	297.8	295.1
75°	261.6	256.2	252.2	245.5	241.4
77.5°	209.3	206.6	201.2	195.8	195.8
80°	158.3	154.3	151.6	150.2	150.2
82.5°	108.7	108.7	108.7	106.0	104.6
85°	69.8	67.1	67.1	64.4	64.4
87.5°	34.9	30.9	29.5	28.2	28.2
90°	1.1	6.8	14.2	15.8	16.4
92.5°	8.5	34.0	105.4	36.0	30.0
95°	19.3	62.6	336.0	98.0	65.7
97.5°	30.6	71.7	516.7	246.5	134.9
100°	41.9	79.0	536.6	515.6	355.3
102.5°	53.8	87.6	499.7	690.4	562.6
105°	65.7	97.2	455.5	796.6	720.7
107.5°	78.2	108.5	416.5	843.4	823.8
110°	91.8	120.2	384.2	844.8	882.8

TEST NUMBER: P1011159

CATALOG NUMBER: S123DIP-B1000D585UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	104.3	132.4	362.6	812.8	894.7
115°	116.2	144.8	348.5	764.0	876.5
117.5°	128.1	156.6	338.8	711.9	836.9
120°	140.5	168.6	332.6	662.6	784.7
122.5°	151.3	179.8	328.6	623.8	736.0
125°	161.5	190.6	325.2	589.2	691.3
127.5°	169.4	200.8	323.5	561.0	652.7
130°	176.8	210.0	321.8	534.8	621.0
132.5°	182.4	218.2	321.3	510.5	589.8
135°	189.2	225.8	320.7	485.2	560.4
137.5°	195.5	232.0	319.6	461.4	529.2
140°	201.7	237.7	319.0	438.2	496.3
142.5°	208.5	242.8	317.9	417.0	465.7
145°	215.9	247.3	316.7	398.0	438.0
147.5°	223.2	252.2	315.0	383.4	414.2
150°	230.6	256.1	312.8	370.3	393.8
152.5°	238.0	260.4	309.9	359.0	376.8
155°	245.3	264.6	306.5	348.5	363.2
157.5°	251.0	268.3	303.7	338.2	350.2
160°	257.8	271.4	300.3	328.9	337.7
162.5°	262.9	273.6	296.9	320.1	326.4
165°	268.0	275.6	293.5	311.4	316.7
167.5°	272.0	277.4	290.1	303.7	307.1
170°	275.4	278.2	286.7	296.9	298.6
172.5°	277.6	279.0	283.9	291.0	290.7
175°	279.3	279.6	281.6	285.6	285.0
177.5°	280.5	279.9	279.9	282.2	281.0
180°	279.9	279.9	279.9	279.9	279.9

(END OF REPORT)