

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010856

Luminaire Tested: S123RDIP-B1165D585UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010856
REPORT IS A COMBINATION OF REPORTS P993052 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1165D585UB2750-4F0-XX-W2A-F_3500K
Description: Define 3 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6764.0 lumens
Efficiency: N/A
Efficacy: 88.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010856

CATALOG NUMBER: S123RDIP-B1165D585UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1010856

CATALOG NUMBER: S123RDIP-B1165D585UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65		
1	102	97	94	90	95	92	88	85	81	79	76	72	70	68	63	61	60	56		
2	93	86	79	74	87	81	75	71	72	68	64	63	60	57	56	53	51	47		
3	85	76	68	62	80	71	65	60	64	59	54	56	52	49	50	47	44	41		
4	78	67	59	53	73	64	57	51	57	51	47	51	46	42	45	41	38	35		
5	72	60	52	46	67	57	50	44	51	45	41	46	41	37	40	37	34	31		
6	66	54	46	40	62	51	44	39	46	40	36	41	36	33	37	33	30	27		
7	62	49	41	36	58	47	39	34	42	36	32	38	33	29	34	30	27	24		
8	57	45	37	32	54	43	36	31	39	33	28	35	30	26	31	27	24	22		
9	53	41	34	28	50	39	32	27	35	30	26	32	27	24	29	25	22	20		
10	50	38	31	26	47	36	29	25	33	27	23	30	25	22	27	23	20	18		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20997	20997	20997
5°	21031	20254	20200
10°	20866	19492	19109
15°	20595	18551	17913
20°	20240	17528	16578
25°	19873	16464	15314
30°	19404	15332	13818
35°	18919	14221	12457
40°	18464	13014	10952
45°	17881	11834	9599
50°	17237	10573	8199
55°	16568	9223	6915
60°	15932	7839	5613
65°	15106	6420	4382
70°	14071	4854	3131
75°	12580	3287	2481
80°	10738	2285	1741
85°	8059	1234	911

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17881 cd/sqm

TEST NUMBER: P1010856

CATALOG NUMBER: S123RDIP-B1165D585UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.4	2.7
10°-20°	510.1	7.5
20°-30°	734.5	10.9
30°-40°	827.2	12.2
40°-50°	791.2	11.7
50°-60°	647.7	9.6
60°-70°	436.7	6.5
70°-80°	219.0	3.2
80°-90°	58.8	0.9
90°-100°	27.2	0.4
100°-110°	131.7	1.9
110°-120°	322.8	4.8
120°-130°	409.8	6.1
130°-140°	437.8	6.5
140°-150°	409.4	6.1
150°-160°	330.2	4.9
160°-170°	213.1	3.2
170°-180°	73.4	1.1
0°-30°	1428.0	21.1
0°-40°	2255.2	33.3
0°-60°	3694.0	54.6
0°-90°	4408.5	65.2
90°-120°	481.8	7.1
90°-150°	1738.7	25.7
90°-180°	2355.0	34.8
0°-180°	6764.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1951	1951	1951	1951	1951	
5°	1951	1943	1924	1938	1935	185
15°	1860	1843	1799	1791	1780	524
25°	1693	1653	1580	1547	1530	779
35°	1465	1408	1310	1242	1214	917
45°	1204	1133	1011	921	883	929
55°	914	837	702	611	579	820
65°	625	538	414	337	320	618
75°	331	255	168	152	149	352
85°	84	49	44	41	41	92
90°	1	6	14	16	17	7
95°	35	12	18	22	22	42
105°	171	177	126	24	25	181
115°	321	324	330	335	338	317
125°	452	457	459	460	462	404
135°	563	567	569	571	569	434
145°	650	654	655	656	656	407
155°	716	715	715	718	715	330
165°	755	753	752	757	753	213
175°	773	770	770	774	770	74
180°	773	773	773	773	773	

TEST NUMBER: P1010856

CATALOG NUMBER: S123RDIP-B1165D585UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1950.7	1950.7	1950.7	1950.7	1950.7
2.5°	1958.6	1952.3	1933.3	1950.7	1947.5
5°	1950.7	1942.8	1923.8	1938.1	1934.9
7.5°	1936.5	1928.6	1904.8	1914.3	1909.6
10°	1917.5	1906.4	1877.9	1879.5	1871.6
12.5°	1890.6	1877.9	1841.5	1840.0	1830.5
15°	1860.5	1843.1	1798.8	1790.9	1779.8
17.5°	1824.1	1805.2	1749.8	1734.0	1718.1
20°	1783.0	1757.7	1697.6	1677.0	1658.0
22.5°	1737.1	1707.1	1642.2	1615.3	1597.9
25°	1692.8	1653.3	1580.5	1547.3	1529.9
27.5°	1639.0	1596.3	1517.2	1472.9	1446.0
30°	1583.7	1536.2	1447.6	1393.8	1368.5
32.5°	1528.3	1472.9	1378.0	1317.9	1291.0
35°	1465.0	1408.1	1310.0	1241.9	1213.5
37.5°	1401.7	1340.0	1237.2	1161.2	1126.4
40°	1341.6	1272.0	1159.7	1077.4	1041.0
42.5°	1273.6	1204.0	1086.9	995.1	963.5
45°	1204.0	1132.8	1011.0	920.8	882.8
47.5°	1135.9	1056.8	936.6	838.5	805.3
50°	1060.0	985.6	857.5	759.4	723.0
52.5°	992.0	909.7	783.1	680.3	648.7
55°	914.4	836.9	702.4	610.7	579.0
57.5°	844.8	761.0	624.9	537.9	511.0
60°	772.1	685.0	553.7	468.3	441.4
62.5°	699.3	612.3	481.0	401.8	373.4
65°	624.9	537.9	414.5	337.0	319.6
67.5°	550.6	462.0	341.7	283.2	264.2
70°	477.8	392.4	281.6	226.2	208.8
72.5°	405.0	321.2	223.1	180.4	175.6
75°	330.7	254.7	167.7	151.9	148.7
77.5°	262.6	193.0	131.3	121.8	118.7
80°	197.8	132.9	99.7	94.9	91.8
82.5°	136.1	82.3	71.2	66.4	66.4
85°	83.9	49.0	44.3	41.1	41.1
87.5°	38.0	20.6	20.6	19.0	17.4
90°	0.6	6.3	13.8	16.1	17.2
92.5°	13.2	9.8	14.9	18.9	19.5
95°	35.0	11.5	17.8	21.8	21.8
97.5°	63.7	47.6	18.4	23.0	23.5
100°	97.0	108.5	18.9	23.5	24.1
102.5°	134.9	142.4	42.5	23.5	24.7
105°	171.1	177.4	125.7	24.1	25.3
107.5°	209.5	214.7	223.3	134.9	59.7
110°	248.0	252.6	258.9	239.9	157.9

TEST NUMBER: P1010856

CATALOG NUMBER: S123RDIP-B1165D585UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	284.7	288.7	295.0	300.2	299.1
115°	320.9	324.3	329.5	335.2	337.5
117.5°	356.5	360.5	363.4	368.0	368.5
120°	389.2	394.4	396.1	400.7	400.7
122.5°	422.5	426.5	428.8	431.7	432.2
125°	452.3	456.9	459.2	460.4	461.5
127.5°	482.2	486.8	489.6	491.4	490.2
130°	509.7	514.3	516.6	518.9	517.8
132.5°	536.1	540.7	542.5	544.8	543.0
135°	563.1	566.6	568.9	570.6	568.9
137.5°	586.1	590.7	591.8	594.7	593.5
140°	609.0	612.5	614.2	616.5	615.4
142.5°	630.3	633.7	635.4	637.2	635.4
145°	649.8	653.8	655.0	656.1	656.1
147.5°	668.7	671.6	672.8	673.9	671.0
150°	686.0	687.7	688.8	690.0	688.3
152.5°	701.5	702.0	702.6	704.9	702.0
155°	715.8	714.7	715.2	718.1	714.7
157.5°	727.3	727.3	726.7	730.2	725.6
160°	737.6	737.0	736.5	739.9	735.9
162.5°	747.4	745.7	745.1	749.1	745.7
165°	754.8	753.1	752.5	757.1	753.1
167.5°	761.2	758.9	758.9	763.5	758.9
170°	766.3	764.0	764.0	768.6	764.0
172.5°	769.8	766.9	767.5	772.1	766.9
175°	772.6	769.8	770.3	774.4	769.8
177.5°	773.8	770.9	771.5	776.1	770.3
180°	772.6	772.6	772.6	772.6	772.6

(END OF REPORT)