

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010864

Luminaire Tested: S123RDIP-B1165D805UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010864
REPORT IS A COMBINATION OF REPORTS P993090 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1165D805UB2750-4F0-XX-W2A-F_2700K
Description: Define 3 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7459.0 lumens
Efficiency: N/A
Efficacy: 90.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 82.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010864

CATALOG NUMBER: S123RDIP-B1165D805UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1010864

CATALOG NUMBER: S123RDIP-B1165D805UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	109	109	109	109		102	102	102	102		88	88	88		75	75	75		64	64	64
1	100	96	92	89		93	90	86	83		78	75	73		67	65	64		57	56	55
2	91	84	78	73		85	79	73	69		69	65	61		59	56	54		51	49	47
3	84	74	67	61		78	70	63	58		61	56	52		53	49	46		45	42	40
4	77	66	58	52		71	62	55	50		54	49	45		47	43	40		41	37	35
5	71	59	51	45		66	55	48	43		49	43	39		43	38	35		37	33	31
6	65	53	45	39		61	50	43	37		44	38	34		39	34	30		33	30	27
7	60	48	40	35		56	45	38	33		40	34	30		35	31	27		31	27	24
8	56	44	36	31		52	41	34	29		37	31	27		32	28	24		28	25	22
9	52	40	33	28		49	38	31	26		34	28	24		30	25	22		26	22	20
10	49	37	30	25		46	35	28	24		31	26	22		28	23	20		24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20730	20730	20730
5°	20764	19997	19943
10°	20601	19245	18866
15°	20334	18316	17686
20°	19983	17305	16368
25°	19621	16255	15119
30°	19156	15137	13642
35°	18679	14040	12298
40°	18230	12848	10813
45°	17654	11683	9477
50°	17017	10438	8094
55°	16358	9106	6828
60°	15727	7740	5542
65°	14915	6338	4325
70°	13891	4792	3092
75°	12420	3246	2449
80°	10597	2255	1718
85°	7953	1217	900

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17654 cd/sqm

TEST NUMBER: P1010864

CATALOG NUMBER: S123RDIP-B1165D805UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.0	2.4
10°-20°	503.7	6.8
20°-30°	725.2	9.7
30°-40°	816.6	10.9
40°-50°	781.2	10.5
50°-60°	639.4	8.6
60°-70°	431.1	5.8
70°-80°	216.2	2.9
80°-90°	58.6	0.8
90°-100°	35.9	0.5
100°-110°	173.7	2.3
110°-120°	425.7	5.7
120°-130°	540.4	7.2
130°-140°	577.3	7.7
140°-150°	539.8	7.2
150°-160°	435.4	5.8
160°-170°	281.0	3.8
170°-180°	96.8	1.3
0°-30°	1409.9	18.9
0°-40°	2226.5	29.8
0°-60°	3647.1	48.9
0°-90°	4353.0	58.4
90°-120°	635.3	8.5
90°-150°	2292.7	30.7
90°-180°	3106.0	41.6
0°-180°	7459.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1926	1926	1926	1926	1926	
5°	1926	1918	1899	1913	1910	183
15°	1837	1820	1776	1768	1757	518
25°	1671	1632	1560	1528	1510	769
35°	1446	1390	1293	1226	1198	905
45°	1189	1118	998	909	872	917
55°	903	826	694	603	572	810
65°	617	531	409	333	316	611
75°	326	252	166	150	147	348
85°	83	48	44	41	41	91
90°	1	8	18	21	23	8
95°	46	15	24	29	29	55
105°	226	234	166	32	33	239
115°	423	428	434	442	445	418
125°	596	602	606	607	609	533
135°	742	747	750	752	750	572
145°	857	862	864	865	865	536
155°	944	942	943	947	942	435
165°	995	993	992	998	993	281
175°	1019	1015	1016	1021	1015	97
180°	1019	1019	1019	1019	1019	

TEST NUMBER: P1010864

CATALOG NUMBER: S123RDIP-B1165D805UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1925.9	1925.9	1925.9	1925.9	1925.9
2.5°	1933.7	1927.5	1908.7	1925.9	1922.8
5°	1925.9	1918.1	1899.4	1913.4	1910.3
7.5°	1911.9	1904.1	1880.6	1890.0	1885.3
10°	1893.1	1882.2	1854.1	1855.6	1847.8
12.5°	1866.6	1854.1	1818.1	1816.6	1807.2
15°	1836.9	1819.7	1776.0	1768.2	1757.2
17.5°	1801.0	1782.2	1727.6	1711.9	1696.3
20°	1760.4	1735.4	1676.0	1655.7	1637.0
22.5°	1715.1	1685.4	1621.3	1594.8	1577.6
25°	1671.3	1632.3	1560.4	1527.6	1510.4
27.5°	1618.2	1576.0	1497.9	1454.2	1427.7
30°	1563.5	1516.7	1429.2	1376.1	1351.1
32.5°	1508.9	1454.2	1360.5	1301.1	1274.6
35°	1446.4	1390.2	1293.3	1226.2	1198.0
37.5°	1383.9	1323.0	1221.5	1146.5	1112.1
40°	1324.6	1255.8	1144.9	1063.7	1027.8
42.5°	1257.4	1188.7	1073.1	982.5	951.2
45°	1188.7	1118.4	998.1	909.1	871.6
47.5°	1121.5	1043.4	924.7	827.8	795.0
50°	1046.5	973.1	846.6	749.8	713.8
52.5°	979.4	898.1	773.2	671.7	640.4
55°	902.8	826.3	693.5	602.9	571.7
57.5°	834.1	751.3	617.0	531.1	504.5
60°	762.2	676.3	546.7	462.3	435.8
62.5°	690.4	604.5	474.8	396.7	368.6
65°	617.0	531.1	409.2	332.7	315.5
67.5°	543.6	456.1	337.4	279.6	260.9
70°	471.7	387.4	278.0	223.4	206.2
72.5°	399.9	317.1	220.2	178.1	173.4
75°	326.5	251.5	165.6	150.0	146.8
77.5°	259.3	190.6	129.6	120.3	117.1
80°	195.2	131.2	98.4	93.7	90.6
82.5°	134.3	81.2	70.3	65.6	65.6
85°	82.8	48.4	43.7	40.6	40.6
87.5°	37.5	20.3	20.3	18.7	17.2
90°	0.8	8.3	18.2	21.2	22.7
92.5°	17.4	12.9	19.7	25.0	25.7
95°	46.2	15.1	23.5	28.8	28.8
97.5°	84.0	62.8	24.2	30.3	31.0
100°	127.9	143.1	25.0	31.0	31.8
102.5°	177.9	187.7	56.0	31.0	32.5
105°	225.6	233.9	165.8	31.8	33.3
107.5°	276.3	283.1	294.4	177.9	78.7
110°	327.0	333.0	341.4	316.4	208.2

TEST NUMBER: P1010864

CATALOG NUMBER: S123RDIP-B1165D805UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	375.4	380.7	389.1	395.9	394.4
115°	423.1	427.7	434.5	442.0	445.1
117.5°	470.1	475.3	479.1	485.2	485.9
120°	513.2	520.0	522.3	528.3	528.3
122.5°	557.1	562.4	565.4	569.2	570.0
125°	596.5	602.5	605.5	607.1	608.6
127.5°	635.8	641.9	645.7	647.9	646.4
130°	672.2	678.2	681.2	684.3	682.7
132.5°	707.0	713.0	715.3	718.3	716.1
135°	742.5	747.1	750.1	752.4	750.1
137.5°	772.8	778.9	780.4	784.2	782.7
140°	803.1	807.6	809.9	812.9	811.4
142.5°	831.1	835.6	837.9	840.2	837.9
145°	856.8	862.1	863.7	865.2	865.2
147.5°	881.8	885.6	887.1	888.6	884.8
150°	904.5	906.8	908.3	909.8	907.6
152.5°	925.0	925.7	926.5	929.5	925.7
155°	943.9	942.4	943.1	946.9	942.4
157.5°	959.0	959.0	958.3	962.8	956.8
160°	972.6	971.9	971.1	975.7	970.4
162.5°	985.5	983.2	982.5	987.8	983.2
165°	995.4	993.1	992.3	998.4	993.1
167.5°	1003.7	1000.7	1000.7	1006.7	1000.7
170°	1010.5	1007.5	1007.5	1013.5	1007.5
172.5°	1015.0	1011.3	1012.0	1018.1	1011.3
175°	1018.8	1015.0	1015.8	1021.1	1015.0
177.5°	1020.3	1016.6	1017.3	1023.4	1015.8
180°	1018.8	1018.8	1018.8	1018.8	1018.8

(END OF REPORT)