

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010874

Luminaire Tested: S123RDIP-B340D1025UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010874
REPORT IS A COMBINATION OF REPORTS P993130 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B340D1025UB2750-4F0-XX-W2A-F_2700K
Description: Define 3 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5276.0 lumens
Efficiency: N/A
Efficacy: 127.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010874

CATALOG NUMBER: S123RDIP-B340D1025UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1010874

CATALOG NUMBER: S123RDIP-B340D1025UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32
1	92	88	84	81	82	78	75	73	60	58	57	44	43	41	29	28	27
2	84	77	71	66	74	69	64	60	53	50	47	39	37	35	25	24	23
3	77	68	61	55	68	60	55	50	47	43	40	34	32	30	22	21	20
4	70	60	52	47	62	54	47	42	42	37	34	30	28	25	20	19	17
5	64	53	46	40	57	48	41	36	37	33	29	27	24	22	18	16	15
6	59	48	40	34	52	43	36	31	33	29	25	25	22	19	17	15	13
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	14	12	11
9	47	35	28	23	42	32	26	21	25	21	17	19	16	13	13	11	10
10	44	32	25	21	39	29	23	19	23	19	16	17	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5970	5970	5970
5°	5979	5759	5743
10°	5933	5542	5433
15°	5856	5274	5093
20°	5754	4984	4714
25°	5650	4681	4354
30°	5517	4359	3929
35°	5379	4043	3541
40°	5249	3700	3114
45°	5084	3364	2729
50°	4901	3006	2331
55°	4711	2622	1966
60°	4529	2229	1596
65°	4296	1826	1246
70°	3999	1381	891
75°	3576	935	706
80°	3051	649	495
85°	2286	351	259

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5084 cd/sqm

TEST NUMBER: P1010874

CATALOG NUMBER: S123RDIP-B340D1025UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.1	1.0
10°-20°	145.0	2.7
20°-30°	208.8	4.0
30°-40°	235.2	4.5
40°-50°	225.0	4.3
50°-60°	184.1	3.5
60°-70°	124.2	2.4
70°-80°	62.3	1.2
80°-90°	18.9	0.4
90°-100°	46.5	0.9
100°-110°	224.8	4.3
110°-120°	551.0	10.4
120°-130°	699.5	13.3
130°-140°	747.2	14.2
140°-150°	698.7	13.2
150°-160°	563.6	10.7
160°-170°	363.7	6.9
170°-180°	125.3	2.4
0°-30°	406.0	7.7
0°-40°	641.2	12.2
0°-60°	1050.3	19.9
0°-90°	1255.6	23.8
90°-120°	822.3	15.6
90°-150°	2967.7	56.2
90°-180°	4020.0	76.2
0°-180°	5276.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	555	555	555	555	555	
5°	555	552	547	551	550	53
15°	529	524	511	509	506	149
25°	481	470	449	440	435	221
35°	416	400	372	353	345	261
45°	342	322	287	262	251	264
55°	260	238	200	174	165	233
65°	178	153	118	96	91	176
75°	94	72	48	43	42	100
85°	24	14	13	12	12	26
90°	1	11	24	27	29	5
95°	60	20	30	37	37	71
105°	292	303	215	41	43	310
115°	548	554	562	572	576	541
125°	772	780	784	786	788	690
135°	961	967	971	974	971	740
145°	1109	1116	1118	1120	1120	694
155°	1222	1220	1221	1226	1220	563
165°	1288	1286	1284	1292	1286	364
175°	1319	1314	1315	1322	1314	126
180°	1319	1319	1319	1319	1319	

TEST NUMBER: P1010874

CATALOG NUMBER: S123RDIP-B340D1025UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	554.6	554.6	554.6	554.6	554.6
2.5°	556.9	555.1	549.7	554.6	553.7
5°	554.6	552.4	547.0	551.0	550.1
7.5°	550.6	548.3	541.6	544.3	542.9
10°	545.2	542.0	533.9	534.4	532.1
12.5°	537.5	533.9	523.6	523.1	520.4
15°	529.0	524.0	511.4	509.2	506.0
17.5°	518.6	513.2	497.5	493.0	488.5
20°	506.9	499.7	482.7	476.8	471.4
22.5°	493.9	485.4	466.9	459.3	454.3
25°	481.3	470.1	449.4	439.9	435.0
27.5°	466.0	453.9	431.4	418.8	411.1
30°	450.3	436.8	411.6	396.3	389.1
32.5°	434.5	418.8	391.8	374.7	367.1
35°	416.5	400.3	372.4	353.1	345.0
37.5°	398.5	381.0	351.8	330.2	320.3
40°	381.4	361.7	329.7	306.3	296.0
42.5°	362.1	342.3	309.0	282.9	273.9
45°	342.3	322.1	287.4	261.8	251.0
47.5°	323.0	300.5	266.3	238.4	229.0
50°	301.4	280.2	243.8	215.9	205.6
52.5°	282.0	258.6	222.7	193.4	184.4
55°	260.0	238.0	199.7	173.6	164.6
57.5°	240.2	216.4	177.7	152.9	145.3
60°	219.5	194.8	157.4	133.1	125.5
62.5°	198.8	174.1	136.7	114.3	106.2
65°	177.7	152.9	117.9	95.8	90.9
67.5°	156.5	131.3	97.2	80.5	75.1
70°	135.8	111.6	80.1	64.3	59.4
72.5°	115.2	91.3	63.4	51.3	49.9
75°	94.0	72.4	47.7	43.2	42.3
77.5°	74.7	54.9	37.3	34.6	33.7
80°	56.2	37.8	28.3	27.0	26.1
82.5°	38.7	23.4	20.2	18.9	18.9
85°	23.8	13.9	12.6	11.7	11.7
87.5°	10.8	5.8	5.8	5.4	4.9
90°	1.0	10.8	23.5	27.4	29.4
92.5°	22.5	16.7	25.5	32.3	33.3
95°	59.8	19.6	30.4	37.2	37.2
97.5°	108.8	81.3	31.4	39.2	40.2
100°	165.6	185.2	32.3	40.2	41.2
102.5°	230.2	243.0	72.5	40.2	42.1
105°	292.0	302.7	214.6	41.2	43.1
107.5°	357.6	366.4	381.1	230.2	101.9
110°	423.3	431.1	441.9	409.5	269.4

TEST NUMBER: P1010874

CATALOG NUMBER: S123RDIP-B340D1025UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	486.0	492.8	503.6	512.4	510.5
115°	547.7	553.6	562.4	572.2	576.1
117.5°	608.4	615.3	620.2	628.0	629.0
120°	664.3	673.1	676.0	683.9	683.9
122.5°	721.1	728.0	731.9	736.8	737.8
125°	772.1	779.9	783.8	785.8	787.7
127.5°	823.0	830.8	835.7	838.7	836.7
130°	870.0	877.9	881.8	885.7	883.7
132.5°	915.1	922.9	925.9	929.8	926.9
135°	961.2	967.0	970.9	973.9	970.9
137.5°	1000.3	1008.2	1010.1	1015.0	1013.1
140°	1039.5	1045.4	1048.3	1052.3	1050.3
142.5°	1075.8	1081.7	1084.6	1087.5	1084.6
145°	1109.1	1116.0	1117.9	1119.9	1119.9
147.5°	1141.4	1146.3	1148.3	1150.2	1145.3
150°	1170.8	1173.8	1175.7	1177.7	1174.7
152.5°	1197.3	1198.3	1199.2	1203.2	1198.3
155°	1221.8	1219.8	1220.8	1225.7	1219.8
157.5°	1241.4	1241.4	1240.4	1246.3	1238.4
160°	1259.0	1258.0	1257.0	1262.9	1256.1
162.5°	1275.7	1272.7	1271.7	1278.6	1272.7
165°	1288.4	1285.5	1284.5	1292.3	1285.5
167.5°	1299.2	1295.3	1295.3	1303.1	1295.3
170°	1308.0	1304.1	1304.1	1311.9	1304.1
172.5°	1313.9	1309.0	1309.9	1317.8	1309.0
175°	1318.8	1313.9	1314.8	1321.7	1313.9
177.5°	1320.7	1315.8	1316.8	1324.6	1314.8
180°	1318.8	1318.8	1318.8	1318.8	1318.8

(END OF REPORT)