

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010876

Luminaire Tested: S123RDIP-B340D1025UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010876
REPORT IS A COMBINATION OF REPORTS P993132 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B340D1025UB2750-4F0-XX-W2A-F_3500K
Description: Define 3 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5344.0 lumens
Efficiency: N/A
Efficacy: 128.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010876

CATALOG NUMBER: S123RDIP-B340D1025UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1010876

CATALOG NUMBER: S123RDIP-B340D1025UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32
1	92	88	84	81	82	78	75	73	60	58	57	44	43	41	29	28	27
2	84	77	71	66	74	69	64	60	53	50	47	39	37	35	25	24	23
3	77	68	61	55	68	60	55	50	47	43	40	34	32	30	22	21	20
4	70	60	52	47	62	54	47	42	42	37	34	30	28	25	20	19	17
5	64	53	46	40	57	48	41	36	37	33	29	27	24	22	18	16	15
6	59	48	40	34	52	43	36	31	33	29	25	25	22	19	17	15	13
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	14	12	11
9	47	35	28	23	42	32	26	21	25	21	17	19	16	13	13	11	10
10	44	32	25	21	39	29	23	19	23	19	16	17	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6046	6046	6046
5°	6056	5833	5817
10°	6008	5613	5502
15°	5930	5342	5158
20°	5828	5047	4774
25°	5723	4741	4409
30°	5587	4415	3979
35°	5449	4095	3587
40°	5316	3747	3154
45°	5149	3407	2764
50°	4963	3044	2361
55°	4771	2656	1991
60°	4587	2257	1616
65°	4349	1849	1261
70°	4052	1398	901
75°	3621	947	714
80°	3089	658	501
85°	2315	356	262

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5149 cd/sqm

TEST NUMBER: P1010876

CATALOG NUMBER: S123RDIP-B340D1025UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.8	1.0
10°-20°	146.9	2.7
20°-30°	211.5	4.0
30°-40°	238.2	4.5
40°-50°	227.8	4.3
50°-60°	186.5	3.5
60°-70°	125.7	2.4
70°-80°	63.1	1.2
80°-90°	19.1	0.4
90°-100°	47.1	0.9
100°-110°	227.8	4.3
110°-120°	558.1	10.4
120°-130°	708.5	13.3
130°-140°	756.9	14.2
140°-150°	707.8	13.2
150°-160°	570.9	10.7
160°-170°	368.4	6.9
170°-180°	127.0	2.4
0°-30°	411.2	7.7
0°-40°	649.4	12.2
0°-60°	1063.7	19.9
0°-90°	1271.6	23.8
90°-120°	833.0	15.6
90°-150°	3006.1	56.3
90°-180°	4072.0	76.2
0°-180°	5344.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	562	562	562	562	562	
5°	562	559	554	558	557	53
15°	536	531	518	516	512	151
25°	488	476	455	446	440	224
35°	422	406	377	358	349	264
45°	347	326	291	265	254	268
55°	263	241	202	176	167	236
65°	180	155	119	97	92	178
75°	95	73	48	44	43	101
85°	24	14	13	12	12	26
90°	1	11	24	28	30	5
95°	60	20	31	38	38	72
105°	296	307	217	42	44	314
115°	555	561	570	580	584	548
125°	782	790	794	796	798	699
135°	974	980	984	986	984	750
145°	1123	1130	1132	1134	1134	703
155°	1238	1236	1237	1242	1236	570
165°	1305	1302	1301	1309	1302	369
175°	1336	1331	1332	1339	1331	127
180°	1336	1336	1336	1336	1336	

TEST NUMBER: P1010876

CATALOG NUMBER: S123RDIP-B340D1025UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	561.7	561.7	561.7	561.7	561.7
2.5°	564.0	562.2	556.7	561.7	560.8
5°	561.7	559.4	554.0	558.1	557.2
7.5°	557.6	555.3	548.5	551.2	549.9
10°	552.1	549.0	540.8	541.2	538.9
12.5°	544.4	540.8	530.3	529.8	527.1
15°	535.7	530.7	518.0	515.7	512.5
17.5°	525.3	519.8	503.9	499.3	494.7
20°	513.4	506.1	488.8	482.9	477.4
22.5°	500.2	491.6	472.9	465.1	460.1
25°	487.5	476.1	455.1	445.5	440.5
27.5°	472.0	459.7	436.9	424.1	416.4
30°	456.0	442.4	416.8	401.4	394.1
32.5°	440.1	424.1	396.8	379.5	371.7
35°	421.9	405.5	377.2	357.6	349.4
37.5°	403.6	385.9	356.3	334.4	324.4
40°	386.3	366.3	333.9	310.2	299.8
42.5°	366.7	346.7	313.0	286.5	277.4
45°	346.7	326.2	291.1	265.1	254.2
47.5°	327.1	304.3	269.7	241.4	231.9
50°	305.2	283.8	246.9	218.7	208.2
52.5°	285.6	261.9	225.5	195.9	186.8
55°	263.3	241.0	202.3	175.8	166.7
57.5°	243.3	219.1	179.9	154.9	147.1
60°	222.3	197.3	159.4	134.8	127.1
62.5°	201.4	176.3	138.5	115.7	107.5
65°	179.9	154.9	119.4	97.0	92.0
67.5°	158.5	133.0	98.4	81.5	76.1
70°	137.6	113.0	81.1	65.1	60.1
72.5°	116.6	92.5	64.2	51.9	50.6
75°	95.2	73.3	48.3	43.7	42.8
77.5°	75.6	55.6	37.8	35.1	34.2
80°	56.9	38.3	28.7	27.3	26.4
82.5°	39.2	23.7	20.5	19.1	19.1
85°	24.1	14.1	12.8	11.8	11.8
87.5°	10.9	5.9	5.9	5.5	5.0
90°	1.0	10.9	23.8	27.8	29.8
92.5°	22.8	16.9	25.8	32.8	33.7
95°	60.5	19.8	30.8	37.7	37.7
97.5°	110.2	82.4	31.8	39.7	40.7
100°	167.7	187.6	32.8	40.7	41.7
102.5°	233.2	246.1	73.4	40.7	42.7
105°	295.7	306.7	217.3	41.7	43.7
107.5°	362.2	371.2	386.1	233.2	103.2
110°	428.7	436.7	447.6	414.8	272.9

TEST NUMBER: P1010876

CATALOG NUMBER: S123RDIP-B340D1025UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	492.2	499.2	510.1	519.0	517.1
115°	554.8	560.7	569.7	579.6	583.5
117.5°	616.3	623.2	628.2	636.1	637.1
120°	672.9	681.8	684.8	692.7	692.7
122.5°	730.4	737.4	741.3	746.3	747.3
125°	782.0	790.0	793.9	795.9	797.9
127.5°	833.6	841.6	846.5	849.5	847.5
130°	881.3	889.2	893.2	897.2	895.2
132.5°	926.9	934.9	937.8	941.8	938.8
135°	973.6	979.5	983.5	986.5	983.5
137.5°	1013.3	1021.2	1023.2	1028.2	1026.2
140°	1053.0	1058.9	1061.9	1065.9	1063.9
142.5°	1089.7	1095.6	1098.6	1101.6	1098.6
145°	1123.4	1130.4	1132.4	1134.3	1134.3
147.5°	1156.2	1161.1	1163.1	1165.1	1160.2
150°	1186.0	1188.9	1190.9	1192.9	1189.9
152.5°	1212.7	1213.7	1214.7	1218.7	1213.7
155°	1237.6	1235.6	1236.6	1241.5	1235.6
157.5°	1257.4	1257.4	1256.4	1262.4	1254.4
160°	1275.3	1274.3	1273.3	1279.2	1272.3
162.5°	1292.1	1289.2	1288.2	1295.1	1289.2
165°	1305.0	1302.1	1301.1	1309.0	1302.1
167.5°	1316.0	1312.0	1312.0	1319.9	1312.0
170°	1324.9	1320.9	1320.9	1328.9	1320.9
172.5°	1330.8	1325.9	1326.9	1334.8	1325.9
175°	1335.8	1330.8	1331.8	1338.8	1330.8
177.5°	1337.8	1332.8	1333.8	1341.8	1331.8
180°	1335.8	1335.8	1335.8	1335.8	1335.8

(END OF REPORT)