

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011186

Luminaire Tested: S123DIP-B1000D585UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011186
REPORT IS A COMBINATION OF REPORTS P989249 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D585UB40-4F0-XX-W2A-F4
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6189.9 lumens
Efficiency: N/A
Efficacy: 99.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011186

CATALOG NUMBER: S123DIP-B1000D585UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1011186

CATALOG NUMBER: S123DIP-B1000D585UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66			
1	101	97	93	89	95	91	88	85	81	78	76	71	69	67	62	61	60	55			
2	92	85	78	73	86	80	74	69	71	66	63	62	59	56	55	52	50	46			
3	84	74	67	61	79	70	63	58	62	57	53	55	51	48	49	45	43	39			
4	77	66	58	51	72	62	55	49	55	50	45	49	45	41	43	40	37	34			
5	71	59	50	44	66	56	48	42	50	44	39	44	39	35	39	35	32	29			
6	65	53	44	38	61	50	42	37	45	39	34	40	35	31	35	31	28	26			
7	60	48	40	34	57	45	38	32	41	35	30	36	31	27	32	28	25	23			
8	56	43	35	30	53	41	34	29	37	31	27	33	28	25	30	26	22	20			
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	23	20	18			
10	49	37	29	24	46	35	28	23	32	26	22	28	24	20	26	21	18	17			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16841	16841	16841
5°	16884	16260	16236
10°	16733	15710	15549
15°	16500	15138	14799
20°	16234	14502	14058
25°	15889	13832	13264
30°	15511	13138	12430
35°	15115	12429	11601
40°	14701	11685	10784
45°	14245	10959	9933
50°	13783	10151	9078
55°	13187	9310	8211
60°	12575	8380	7288
65°	12000	7375	6326
70°	11173	6261	5204
75°	9978	4958	4041
80°	8616	3484	2858
85°	6724	1874	1432

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14245 cd/sqm

TEST NUMBER: P1011186

CATALOG NUMBER: S123DIP-B1000D585UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.5	2.4
10°-20°	416.5	6.7
20°-30°	615.1	9.9
30°-40°	718.4	11.6
40°-50°	722.2	11.7
50°-60°	634.4	10.2
60°-70°	472.5	7.6
70°-80°	268.9	4.3
80°-90°	78.0	1.3
90°-100°	159.5	2.6
100°-110°	445.8	7.2
110°-120°	434.7	7.0
120°-130°	346.2	5.6
130°-140°	273.3	4.4
140°-150°	203.9	3.3
150°-160°	142.2	2.3
160°-170°	83.5	1.3
170°-180°	27.2	0.4
0°-30°	1179.1	19.0
0°-40°	1897.5	30.7
0°-60°	3254.2	52.6
0°-90°	4073.6	65.8
90°-120°	1040.1	16.8
90°-150°	1863.4	30.1
90°-180°	2116.0	34.2
0°-180°	6189.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1565	1565	1565	1565	1565	
5°	1566	1559	1544	1558	1555	149
15°	1491	1485	1468	1478	1470	420
25°	1353	1345	1328	1329	1325	623
35°	1170	1162	1145	1137	1130	732
45°	959	954	936	920	914	741
55°	728	726	709	694	688	652
65°	496	490	476	466	461	490
75°	262	257	253	246	242	280
85°	70	67	67	65	65	75
90°	1	7	14	16	16	6
95°	19	63	337	98	66	20
105°	66	97	457	799	723	70
115°	116	145	350	766	879	115
125°	162	191	326	591	693	144
135°	190	226	322	487	562	147
145°	216	248	318	399	439	136
155°	246	265	307	349	364	113
165°	269	276	294	312	318	76
175°	280	280	282	286	286	27
180°	281	281	281	281	281	

TEST NUMBER: P1011186

CATALOG NUMBER: S123DIP-B1000D585UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1564.6	1564.6	1564.6	1564.6	1564.6
2.5°	1571.3	1566.0	1551.2	1564.6	1563.3
5°	1566.0	1559.2	1544.4	1557.9	1555.2
7.5°	1553.9	1547.1	1532.3	1544.4	1543.1
10°	1537.7	1531.0	1513.5	1525.6	1522.9
12.5°	1516.2	1510.8	1494.7	1502.7	1501.4
15°	1490.6	1485.2	1467.8	1478.5	1470.4
17.5°	1462.4	1455.6	1438.2	1446.2	1443.5
20°	1430.1	1422.0	1404.5	1409.9	1405.9
22.5°	1393.8	1385.7	1368.2	1372.2	1366.9
25°	1353.4	1345.3	1327.8	1329.2	1325.1
27.5°	1311.7	1303.6	1284.8	1286.1	1282.1
30°	1266.0	1259.2	1240.4	1240.4	1231.0
32.5°	1220.2	1210.8	1197.3	1187.9	1183.9
35°	1170.4	1162.4	1144.9	1136.8	1130.1
37.5°	1120.7	1109.9	1092.4	1083.0	1079.0
40°	1068.2	1060.1	1041.3	1030.5	1025.1
42.5°	1015.7	1006.3	987.5	976.7	971.3
45°	959.2	953.8	936.3	920.2	913.5
47.5°	904.1	896.0	879.8	863.7	858.3
50°	847.6	840.8	823.3	808.5	800.5
52.5°	788.4	784.3	765.5	753.4	745.3
55°	727.8	726.5	709.0	694.2	687.5
57.5°	671.3	665.9	652.5	639.0	631.0
60°	609.4	608.1	591.9	579.8	573.1
62.5°	554.3	550.2	534.1	522.0	518.0
65°	496.4	489.7	476.2	465.5	461.4
67.5°	434.5	429.2	418.4	409.0	403.6
70°	379.4	371.3	363.2	353.8	347.1
72.5°	321.5	316.2	306.7	298.7	296.0
75°	262.3	257.0	252.9	246.2	242.2
77.5°	209.9	207.2	201.8	196.4	196.4
80°	158.7	154.7	152.0	150.7	150.7
82.5°	109.0	109.0	109.0	106.3	104.9
85°	70.0	67.3	67.3	64.6	64.6
87.5°	35.0	30.9	29.6	28.3	28.3
90°	1.1	6.8	14.2	15.9	16.5
92.5°	8.5	34.1	105.7	36.1	30.1
95°	19.3	62.8	337.0	98.3	65.9
97.5°	30.7	71.9	518.2	247.2	135.2
100°	42.0	79.2	538.1	517.0	356.3
102.5°	54.0	87.8	501.2	692.4	564.2
105°	65.9	97.4	456.8	798.9	722.8
107.5°	78.4	108.8	417.6	845.8	826.2
110°	92.1	120.4	385.3	847.2	885.3

TEST NUMBER: P1011186

CATALOG NUMBER: S123DIP-B1000D585UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	104.6	132.6	363.7	815.1	897.2
115°	116.5	145.2	349.5	766.2	879.0
117.5°	128.4	157.1	339.8	714.0	839.3
120°	140.9	169.0	333.5	664.5	787.0
122.5°	151.7	180.4	329.6	625.6	738.1
125°	161.9	191.2	326.2	591.0	693.2
127.5°	169.9	201.4	324.5	562.6	654.6
130°	177.3	210.6	322.7	536.4	622.8
132.5°	183.0	218.8	322.2	512.0	591.5
135°	189.8	226.4	321.6	486.7	562.0
137.5°	196.0	232.7	320.5	462.8	530.7
140°	202.3	238.4	319.9	439.5	497.8
142.5°	209.1	243.4	318.8	418.2	467.1
145°	216.5	248.0	317.6	399.2	439.2
147.5°	223.9	252.8	315.9	384.4	415.4
150°	231.3	256.8	313.7	371.3	394.9
152.5°	238.7	261.1	310.8	360.0	377.9
155°	246.0	265.4	307.4	349.4	364.2
157.5°	251.7	269.0	304.6	339.2	351.2
160°	258.5	272.2	301.2	329.8	338.7
162.5°	263.7	274.4	297.7	321.0	327.3
165°	268.8	276.4	294.3	312.2	317.6
167.5°	272.7	278.2	290.9	304.5	308.0
170°	276.2	279.0	287.5	297.8	299.5
172.5°	278.4	279.8	284.7	291.8	291.5
175°	280.1	280.4	282.4	286.4	285.8
177.5°	281.3	280.7	280.7	283.0	281.8
180°	280.7	280.7	280.7	280.7	280.7

(END OF REPORT)