

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010883

Luminaire Tested: S123RDIP-B340D1195UB2750-4F0-XX-W2A-A_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010883
REPORT IS A COMBINATION OF REPORTS P993169 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B340D1195UB2750-4F0-XX-W2A-A_5000K
Description: Define 3 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5852.0 lumens
Efficiency: N/A
Efficacy: 121.9 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010883

CATALOG NUMBER: S123RDIP-B340D1195UB2750-4F0-XX-W2A-A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010883

CATALOG NUMBER: S123RDIP-B340D1195UB2750-4F0-XX-W2A-A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	100	100	100	100	89	89	89	89	68	68	68	48	48	48	30	30	30	30	30	22
1	92	88	84	81	81	78	75	72	59	58	56	43	41	40	27	26	26	26	26	19
2	84	77	71	66	74	68	64	60	52	49	46	38	36	34	24	23	22	22	22	16
3	76	68	61	55	67	60	55	50	46	42	39	33	31	29	21	20	19	19	19	14
4	70	60	52	47	62	53	47	42	41	37	34	30	27	25	19	18	17	17	17	12
5	64	53	46	40	57	48	41	36	37	32	29	27	24	22	17	16	15	15	15	11
6	59	48	40	35	52	43	36	31	33	29	25	24	21	19	16	14	13	13	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12	12	12	9
8	50	39	32	27	45	35	29	24	27	23	19	20	17	15	13	12	10	10	10	8
9	47	35	28	23	41	32	26	21	25	20	17	18	15	13	12	11	9	9	9	7
10	44	32	25	21	39	29	23	19	23	18	16	17	14	12	11	10	8	8	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5481	5481	5481	5481
5°	5486	6313	5500	4683
10°	5437	7621	5461	4091
15°	5381	8649	5381	3607
20°	5270	9329	5300	3200
25°	5190	8864	5180	2920
30°	5096	6141	5086	2645
35°	4982	3943	4960	2439
40°	4842	2784	4818	2233
45°	4596	2228	4591	2033
50°	4296	1864	4282	1800
55°	3957	1536	3926	1525
60°	3625	1269	3590	1297
65°	3234	1016	3256	1100
70°	2877	706	2954	889
75°	2438	524	2537	684
80°	1944	347	2106	512
85°	1383	164	1508	319

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 7318 cd/sqm

TEST NUMBER: P1010883

CATALOG NUMBER: S123RDIP-B340D1195UB2750-4F0-XX-W2A-A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.0	0.9
10°-20°	156.5	2.7
20°-30°	246.6	4.2
30°-40°	256.4	4.4
40°-50°	219.3	3.7
50°-60°	167.2	2.9
60°-70°	107.1	1.8
70°-80°	51.3	0.9
80°-90°	16.5	0.3
90°-100°	53.0	0.9
100°-110°	256.2	4.4
110°-120°	627.8	10.7
120°-130°	797.0	13.6
130°-140°	851.4	14.5
140°-150°	796.2	13.6
150°-160°	642.2	11.0
160°-170°	414.4	7.1
170°-180°	142.8	2.4
0°-30°	453.1	7.7
0°-40°	709.5	12.1
0°-60°	1096.0	18.7
0°-90°	1271.0	21.7
90°-120°	937.0	16.0
90°-150°	3381.6	57.8
90°-180°	4581.0	78.3
0°-180°	5852.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	509	509	509	509	509	
5°	509	605	510	449	509	48
15°	486	859	486	358	486	137
25°	442	886	441	292	442	204
35°	386	384	384	238	386	241
45°	310	205	309	187	310	238
55°	218	129	217	128	218	196
65°	134	74	135	80	134	134
75°	64	31	67	41	64	69
85°	14	7	16	14	14	16
90°	1	34	1	34	1	5
95°	68	42	68	42	68	81
105°	333	49	333	49	333	353
115°	624	656	624	656	624	616
125°	880	898	880	898	880	786
135°	1095	1106	1095	1106	1095	843
145°	1264	1276	1264	1276	1264	791
155°	1392	1390	1392	1390	1392	641
165°	1468	1465	1468	1465	1468	415
175°	1503	1497	1503	1497	1503	143
180°	1503	1503	1503	1503	1503	

TEST NUMBER: P1010883

CATALOG NUMBER: S123RDIP-B340D1195UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	510.5	514.0	516.6	518.4	522.7	525.4	527.5	531.5	531.5	532.3	534.1
5°	508.8	516.2	521.4	528.4	537.6	541.9	548.0	553.3	560.7	564.6	568.5
7.5°	504.9	515.3	526.2	536.7	550.2	558.9	565.0	578.5	588.1	599.9	609.1
10°	499.6	514.0	528.0	544.1	562.4	575.5	584.7	602.5	620.8	637.4	651.4
12.5°	493.1	510.5	530.6	550.2	575.9	589.0	603.8	626.1	652.2	673.2	691.9
15°	486.1	506.2	528.8	552.8	585.1	603.4	624.8	651.8	681.0	711.1	736.8
17.5°	475.2	500.5	525.8	560.7	598.6	609.5	627.8	664.9	701.1	728.1	759.5
20°	464.3	492.7	524.5	555.9	596.9	622.1	639.1	678.4	717.2	749.9	780.0
22.5°	454.3	483.9	517.1	556.7	595.1	620.4	641.8	682.7	727.7	764.3	801.3
25°	442.1	474.3	511.0	548.5	595.1	614.3	637.8	685.4	732.9	775.2	821.0
27.5°	429.0	461.7	497.9	536.3	579.0	607.3	630.4	681.4	739.4	784.8	831.9
30°	415.9	449.5	484.4	518.8	566.8	593.8	620.4	676.6	742.9	794.8	831.0
32.5°	403.3	431.6	466.1	499.6	547.2	576.8	606.9	671.8	744.2	787.8	805.3
35°	385.8	415.5	443.4	479.1	527.1	556.3	591.6	671.4	738.6	765.6	756.9
37.5°	369.7	394.6	421.2	453.0	502.2	540.2	576.8	660.1	719.8	721.5	672.3
40°	351.8	372.3	394.6	428.1	481.3	518.8	558.5	642.6	685.8	660.1	573.3
42.5°	331.3	349.7	367.1	399.8	457.8	499.6	542.4	620.8	636.5	577.2	487.0
45°	309.5	324.4	340.5	374.9	432.9	474.3	517.1	587.3	571.1	487.4	401.5
47.5°	286.9	299.5	315.2	346.6	406.3	448.6	489.2	539.3	498.3	408.5	336.6
50°	264.2	274.2	289.5	321.8	379.3	417.7	455.2	487.9	430.3	350.5	278.2
52.5°	242.0	249.8	265.5	293.0	348.8	385.4	412.4	425.1	366.7	289.5	241.5
55°	218.4	227.1	237.6	265.5	320.9	347.9	365.8	365.4	305.2	245.5	199.7
57.5°	195.8	203.6	212.8	240.7	285.6	303.9	319.1	311.7	254.6	201.0	171.3
60°	175.7	180.1	190.1	213.6	247.6	263.3	272.1	259.4	208.0	169.6	141.7
62.5°	153.9	158.3	166.5	188.8	209.7	218.0	225.4	209.3	171.8	138.2	121.2
65°	133.8	139.5	144.7	162.6	174.0	184.0	183.1	169.6	134.3	112.5	98.5
67.5°	116.4	118.6	122.9	133.8	139.1	146.5	146.9	131.7	108.1	91.6	83.3
70°	97.7	99.8	102.9	108.1	111.6	113.4	112.5	99.0	81.5	71.5	64.1
72.5°	81.5	81.1	83.3	83.3	86.8	86.3	83.7	73.2	61.9	53.6	49.3
75°	64.1	64.5	65.0	64.1	62.8	61.0	58.9	51.0	43.6	39.7	35.8
77.5°	50.1	49.3	49.7	46.6	44.9	43.2	40.1	36.2	30.1	29.2	27.5
80°	35.8	35.3	34.9	33.6	29.6	27.9	25.7	23.5	22.2	21.4	20.9
82.5°	24.0	24.0	23.1	20.5	18.3	17.0	16.6	15.7	14.4	14.4	14.0
85°	14.4	14.0	13.1	10.5	9.2	9.2	9.2	9.2	8.3	8.3	7.8
87.5°	5.7	5.2	3.9	3.9	3.5	3.5	3.5	3.1	3.1	2.6	2.6
90°	1.1	3.6	6.1	8.6	11.1	12.3	13.9	17.1	20.4	23.6	26.8
92.5°	25.7	24.2	22.7	21.2	19.7	19.0	20.1	22.3	24.6	26.8	29.0
95°	68.1	57.9	47.7	37.6	27.4	22.3	23.7	26.4	29.1	31.9	34.6
97.5°	123.9	117.0	110.0	103.1	96.2	92.7	86.4	73.7	61.0	48.4	35.7
100°	188.7	193.7	198.6	203.6	208.5	211.0	191.6	152.9	114.2	75.5	36.8
102.5°	262.4	265.6	268.8	272.1	275.3	276.9	255.3	212.1	169.0	125.8	82.6
105°	332.7	335.4	338.2	340.9	343.6	345.0	333.8	311.5	289.2	266.8	244.5
107.5°	407.5	409.7	411.9	414.2	416.4	417.5	419.4	423.1	426.8	430.6	434.3
110°	482.3	484.3	486.3	488.2	490.2	491.2	492.6	495.3	498.0	500.8	503.5

TEST NUMBER: P1010883

CATALOG NUMBER: S123RDIP-B340D1195UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	553.7	555.4	557.2	558.9	560.6	561.5	562.9	565.6	568.3	571.1	573.8
115°	624.1	625.6	627.1	628.6	630.1	630.8	631.9	634.1	636.4	638.6	640.8
117.5°	693.3	695.0	696.8	698.5	700.2	701.1	701.7	703.0	704.2	705.5	706.7
120°	756.9	759.1	761.4	763.6	765.9	767.0	767.4	768.1	768.8	769.6	770.3
122.5°	821.7	823.4	825.2	826.9	828.6	829.5	830.0	831.0	831.9	832.9	833.9
125°	879.7	881.7	883.7	885.6	887.6	888.6	889.1	890.1	891.1	892.1	893.1
127.5°	937.8	939.8	941.8	943.7	945.7	946.7	947.3	948.6	949.8	951.1	952.3
130°	991.4	993.4	995.4	997.3	999.3	1000.3	1000.8	1001.8	1002.8	1003.8	1004.8
132.5°	1042.7	1044.7	1046.7	1048.6	1050.6	1051.6	1052.0	1052.7	1053.5	1054.2	1055.0
135°	1095.2	1096.7	1098.2	1099.7	1101.2	1101.9	1102.4	1103.4	1104.3	1105.3	1106.3
137.5°	1139.8	1141.8	1143.8	1145.8	1147.8	1148.8	1149.0	1149.5	1150.0	1150.5	1151.0
140°	1184.5	1186.0	1187.5	1189.0	1190.5	1191.2	1191.6	1192.3	1193.0	1193.8	1194.5
142.5°	1225.8	1227.3	1228.8	1230.3	1231.8	1232.5	1232.9	1233.6	1234.3	1235.1	1235.8
145°	1263.8	1265.5	1267.3	1269.0	1270.7	1271.6	1271.8	1272.3	1272.8	1273.3	1273.8
147.5°	1300.6	1301.8	1303.1	1304.3	1305.6	1306.2	1306.4	1306.9	1307.4	1307.9	1308.4
150°	1334.1	1334.8	1335.6	1336.3	1337.0	1337.4	1337.7	1338.2	1338.7	1339.2	1339.7
152.5°	1364.2	1364.4	1364.7	1364.9	1365.2	1365.3	1365.4	1365.7	1366.0	1366.2	1366.5
155°	1392.1	1391.6	1391.1	1390.6	1390.1	1389.9	1390.0	1390.3	1390.5	1390.8	1391.0
157.5°	1414.5	1414.5	1414.5	1414.5	1414.5	1414.5	1414.4	1414.1	1413.9	1413.6	1413.4
160°	1434.6	1434.3	1434.1	1433.8	1433.5	1433.4	1433.3	1433.0	1432.8	1432.5	1432.3
162.5°	1453.5	1452.8	1452.0	1451.3	1450.6	1450.2	1450.1	1449.8	1449.6	1449.3	1449.1
165°	1468.1	1467.3	1466.6	1465.8	1465.1	1464.7	1464.6	1464.3	1464.1	1463.8	1463.6
167.5°	1480.3	1479.3	1478.3	1477.4	1476.4	1475.9	1475.9	1475.9	1475.9	1475.9	1475.9
170°	1490.4	1489.4	1488.4	1487.4	1486.4	1485.9	1485.9	1485.9	1485.9	1485.9	1485.9
172.5°	1497.1	1495.9	1494.6	1493.4	1492.1	1491.5	1491.6	1491.9	1492.1	1492.4	1492.6
175°	1502.7	1501.5	1500.2	1499.0	1497.7	1497.1	1497.2	1497.5	1497.7	1498.0	1498.2
177.5°	1504.9	1503.7	1502.4	1501.2	1499.9	1499.3	1499.4	1499.7	1499.9	1500.2	1500.4
180°	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7

TEST NUMBER: P1010883

CATALOG NUMBER: S123RDIP-B340D1195UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	537.6	537.6	541.5	545.4	543.2	544.5	549.3	547.6	551.1	550.6	552.0
5°	578.1	582.9	586.8	595.1	596.4	595.1	603.4	605.6	609.5	604.7	606.9
7.5°	623.9	633.9	643.5	655.7	659.6	660.5	664.9	671.0	676.2	666.6	671.4
10°	668.4	683.6	703.2	714.1	723.7	727.2	730.7	734.6	740.7	746.4	742.0
12.5°	716.3	738.6	757.3	776.9	788.7	787.4	797.4	800.0	804.8	806.1	807.9
15°	755.6	786.9	798.7	827.9	830.5	839.3	850.6	860.6	861.9	859.3	859.3
17.5°	793.0	820.1	841.0	864.6	869.3	876.8	891.1	895.9	897.7	897.2	897.2
20°	823.6	841.4	876.8	896.4	904.2	913.8	923.8	929.9	931.3	933.0	930.4
22.5°	843.6	870.7	899.4	915.6	922.1	925.6	932.1	933.9	931.7	932.1	932.6
25°	859.3	885.9	903.4	907.7	907.3	902.9	898.1	889.8	889.0	885.5	878.5
27.5°	863.7	873.7	871.5	853.7	835.8	834.0	805.3	789.6	771.7	774.3	764.3
30°	840.1	827.1	796.1	750.8	732.0	701.5	669.2	635.7	622.6	608.2	634.8
32.5°	782.6	735.9	681.0	622.1	590.8	563.7	529.3	504.9	490.9	479.1	501.8
35°	695.8	623.0	550.2	494.4	468.7	444.3	412.0	399.8	382.4	384.1	386.3
37.5°	584.2	504.0	449.1	394.1	377.1	367.1	343.6	324.8	318.7	317.0	317.0
40°	479.6	413.7	364.9	321.8	308.7	300.4	281.6	272.9	266.4	264.6	266.8
42.5°	396.7	340.5	302.6	273.8	264.6	254.2	246.3	235.4	234.1	231.1	235.0
45°	333.1	284.3	255.9	235.0	227.1	223.2	214.5	208.0	205.3	204.9	208.0
47.5°	282.5	244.6	219.7	206.7	200.6	196.6	189.2	186.6	184.0	184.9	183.5
50°	237.2	208.8	192.7	180.9	177.0	173.1	168.3	165.7	164.4	164.4	163.9
52.5°	203.6	180.1	169.6	158.7	157.0	154.8	149.5	147.8	145.6	145.2	146.9
55°	174.4	158.3	147.8	141.3	139.5	135.2	133.0	130.8	129.5	128.6	129.1
57.5°	149.1	136.9	129.9	124.3	121.2	119.5	115.5	115.1	114.2	114.2	113.8
60°	128.2	119.5	111.2	107.7	105.5	103.3	102.9	100.3	99.0	99.8	99.4
62.5°	108.6	101.6	96.8	92.9	91.6	89.8	88.5	87.6	86.3	86.8	86.8
65°	90.7	85.0	81.5	78.0	77.6	75.9	75.4	74.6	74.6	74.1	75.0
67.5°	74.6	70.6	67.6	65.4	64.1	64.5	62.8	61.5	61.5	61.0	62.3
70°	59.3	57.1	54.1	51.4	49.7	49.7	47.5	47.1	47.1	47.1	46.6
72.5°	45.8	41.9	40.5	39.7	39.7	39.7	38.8	38.8	38.4	38.8	38.4
75°	34.0	33.6	32.7	32.3	32.3	31.8	31.4	31.4	31.4	31.4	31.4
77.5°	26.6	26.6	25.7	25.3	25.3	25.3	24.9	24.9	24.4	24.4	24.4
80°	19.6	19.6	18.7	18.7	18.7	18.3	18.3	18.3	18.7	18.3	18.3
82.5°	13.5	13.5	13.1	13.5	13.1	12.6	12.6	12.6	12.2	12.6	12.6
85°	7.8	7.8	7.4	7.0	7.4	7.4	7.0	7.4	7.0	7.4	7.0
87.5°	3.1	2.6	2.6	2.6	2.2	2.6	2.2	2.2	2.6	2.2	2.6
90°	27.8	28.8	29.8	30.8	31.3	31.5	32.0	32.5	33.0	33.5	33.0
92.5°	30.7	32.5	34.2	35.9	36.8	36.9	37.2	37.5	37.7	38.0	37.7
95°	36.3	38.1	39.8	41.5	42.4	42.4	42.4	42.4	42.4	42.4	42.4
97.5°	37.7	39.7	41.7	43.7	44.7	44.8	45.1	45.3	45.6	45.8	45.6
100°	38.8	40.8	42.8	44.8	45.8	45.9	46.2	46.4	46.7	46.9	46.7
102.5°	74.4	66.2	58.1	49.9	45.8	46.0	46.5	47.0	47.5	48.0	47.5
105°	200.6	156.7	112.8	68.9	46.9	47.1	47.6	48.1	48.6	49.1	48.6
107.5°	396.1	357.9	319.7	281.5	262.4	246.1	213.6	181.1	148.6	116.1	148.6
110°	495.3	487.1	479.0	470.8	466.7	449.0	413.5	378.0	342.5	307.0	342.5

TEST NUMBER: P1010883

CATALOG NUMBER: S123RDIP-B340D1195UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	576.0	578.3	580.5	582.8	583.9	583.6	583.1	582.6	582.1	581.6	582.1
115°	643.3	645.8	648.3	650.8	652.0	652.5	653.5	654.4	655.4	656.4	655.4
117.5°	708.7	710.7	712.6	714.6	715.6	715.7	716.0	716.2	716.5	716.7	716.5
120°	772.3	774.3	776.2	778.2	779.2	779.2	779.2	779.2	779.2	779.2	779.2
122.5°	835.1	836.4	837.6	838.9	839.5	839.6	839.9	840.1	840.4	840.6	840.4
125°	893.6	894.1	894.6	895.1	895.3	895.6	896.1	896.6	897.1	897.6	897.1
127.5°	953.0	953.8	954.5	955.2	955.6	955.4	954.9	954.4	953.9	953.4	953.9
130°	1005.8	1006.8	1007.7	1008.7	1009.2	1009.0	1008.5	1008.0	1007.5	1007.0	1007.5
132.5°	1056.0	1057.0	1058.0	1059.0	1059.5	1059.1	1058.4	1057.6	1056.9	1056.1	1056.9
135°	1107.1	1107.8	1108.6	1109.3	1109.7	1109.3	1108.6	1107.8	1107.1	1106.3	1107.1
137.5°	1152.2	1153.5	1154.7	1156.0	1156.6	1156.3	1155.8	1155.3	1154.8	1154.3	1154.8
140°	1195.5	1196.5	1197.5	1198.5	1199.0	1198.8	1198.3	1197.8	1197.3	1196.8	1197.3
142.5°	1236.6	1237.3	1238.1	1238.8	1239.2	1238.8	1238.1	1237.3	1236.6	1235.8	1236.6
145°	1274.3	1274.8	1275.3	1275.8	1276.0	1276.0	1276.0	1276.0	1276.0	1276.0	1276.0
147.5°	1308.9	1309.4	1309.9	1310.4	1310.6	1310.0	1308.8	1307.5	1306.3	1305.1	1306.3
150°	1340.2	1340.7	1341.2	1341.7	1341.9	1341.5	1340.8	1340.1	1339.3	1338.6	1339.3
152.5°	1367.5	1368.5	1369.4	1370.4	1370.9	1370.3	1369.0	1367.8	1366.5	1365.3	1366.5
155°	1392.2	1393.5	1394.7	1396.0	1396.6	1395.9	1394.4	1392.9	1391.4	1389.9	1391.4
157.5°	1414.9	1416.4	1417.9	1419.4	1420.1	1419.1	1417.1	1415.1	1413.1	1411.1	1413.1
160°	1433.8	1435.3	1436.8	1438.3	1439.0	1438.1	1436.4	1434.7	1432.9	1431.2	1432.9
162.5°	1450.8	1452.6	1454.3	1456.0	1456.9	1456.2	1454.7	1453.2	1451.7	1450.2	1451.7
165°	1465.6	1467.6	1469.5	1471.5	1472.5	1471.6	1469.9	1468.2	1466.4	1464.7	1466.4
167.5°	1477.9	1479.9	1481.8	1483.8	1484.8	1483.8	1481.8	1479.9	1477.9	1475.9	1477.9
170°	1487.9	1489.9	1491.8	1493.8	1494.8	1493.8	1491.8	1489.9	1487.9	1485.9	1487.9
172.5°	1494.6	1496.6	1498.5	1500.5	1501.5	1500.4	1498.2	1495.9	1493.7	1491.5	1493.7
175°	1499.9	1501.7	1503.4	1505.1	1506.0	1505.0	1503.0	1501.1	1499.1	1497.1	1499.1
177.5°	1502.4	1504.4	1506.4	1508.4	1509.4	1508.2	1505.7	1503.2	1500.7	1498.2	1500.7
180°	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7

TEST NUMBER: P1010883

CATALOG NUMBER: S123RDIP-B340D1195UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	549.8	547.2	545.4	544.1	542.8	546.7	541.5	535.8	531.9	529.3	528.4
5°	607.3	601.7	596.9	592.9	593.8	593.8	584.7	574.6	565.9	561.1	555.9
7.5°	674.0	667.9	658.3	656.2	654.4	643.5	634.4	616.0	605.1	594.2	584.7
10°	740.3	732.4	723.3	720.2	715.9	702.4	688.4	664.9	651.4	631.3	618.7
12.5°	802.2	792.6	783.5	781.3	774.7	763.0	739.0	714.6	691.5	670.1	647.9
15°	854.1	851.5	837.5	828.8	814.4	798.3	793.0	759.9	730.7	708.5	668.4
17.5°	897.7	885.5	872.4	866.7	861.1	842.3	823.6	789.6	758.2	725.5	699.7
20°	932.6	919.0	909.9	901.6	899.0	877.6	848.0	817.9	783.5	746.8	713.3
22.5°	934.3	932.6	926.5	921.7	916.4	902.5	878.9	841.4	804.8	764.7	720.7
25°	898.1	895.5	912.9	908.6	912.1	906.8	894.2	862.8	820.1	773.0	728.5
27.5°	789.1	815.7	843.2	852.8	859.3	878.1	884.2	866.7	832.3	782.1	732.4
30°	640.9	676.2	720.7	744.7	763.0	797.8	843.2	848.9	832.7	792.6	731.6
32.5°	503.1	535.4	571.1	599.5	623.9	695.4	756.4	800.5	808.3	787.4	733.8
35°	405.5	419.4	453.4	480.5	513.6	574.6	646.6	717.6	765.6	768.2	727.2
37.5°	334.4	341.8	371.5	386.7	406.3	460.0	527.1	620.0	694.5	729.8	708.9
40°	276.8	293.9	310.9	319.6	333.5	370.6	435.1	507.9	600.3	665.7	680.6
42.5°	240.2	247.6	258.5	270.7	279.5	311.7	354.9	421.6	504.9	596.0	637.0
45°	211.9	214.5	225.8	233.7	242.8	265.5	296.0	351.8	425.1	514.9	584.7
47.5°	188.3	193.6	199.7	204.5	210.6	228.0	254.2	294.7	359.2	439.5	514.5
50°	167.4	170.5	178.3	180.5	184.9	197.1	217.1	248.1	301.3	365.4	443.0
52.5°	147.8	153.5	156.5	159.6	163.5	173.5	186.6	211.9	252.0	312.2	378.0
55°	132.5	134.3	138.6	141.3	144.3	151.3	162.6	181.4	212.8	260.7	323.1
57.5°	117.7	117.7	122.1	124.3	127.3	132.5	142.6	157.0	179.6	215.4	272.5
60°	102.0	102.5	105.9	108.6	109.4	114.7	122.9	134.3	151.7	177.9	224.5
62.5°	88.1	90.2	92.0	92.9	95.9	99.0	105.9	113.8	126.0	149.1	182.2
65°	76.3	76.7	78.0	78.9	80.2	83.7	88.9	94.2	104.6	121.6	148.7
67.5°	62.8	64.5	66.3	66.3	67.6	69.3	74.6	78.9	86.8	96.8	115.1
70°	47.1	48.0	50.6	51.9	53.6	56.7	59.3	61.9	68.0	75.4	89.4
72.5°	39.2	39.2	40.1	40.5	40.5	42.7	46.6	49.3	52.3	57.5	67.1
75°	31.4	31.4	32.7	32.3	33.1	34.0	34.4	36.2	37.9	41.9	47.5
77.5°	24.9	25.3	25.3	25.7	25.7	26.2	26.6	27.5	28.3	30.5	33.1
80°	18.3	18.7	18.7	19.2	19.2	19.6	20.1	20.5	21.4	22.2	23.5
82.5°	12.6	13.1	13.1	13.5	13.1	13.5	14.0	14.0	14.4	15.3	15.7
85°	7.4	7.4	7.8	7.4	7.4	7.4	7.8	7.8	8.3	9.6	9.6
87.5°	2.2	2.6	2.2	2.6	2.6	2.6	2.6	3.1	3.1	3.5	3.9
90°	32.5	32.0	31.5	31.3	30.8	29.8	28.8	27.8	26.8	23.6	20.4
92.5°	37.5	37.2	36.9	36.8	35.9	34.2	32.5	30.7	29.0	26.8	24.6
95°	42.4	42.4	42.4	42.4	41.5	39.8	38.1	36.3	34.6	31.9	29.1
97.5°	45.3	45.1	44.8	44.7	43.7	41.7	39.7	37.7	35.7	48.4	61.0
100°	46.4	46.2	45.9	45.8	44.8	42.8	40.8	38.8	36.8	75.5	114.2
102.5°	47.0	46.5	46.0	45.8	49.9	58.1	66.2	74.4	82.6	125.8	169.0
105°	48.1	47.6	47.1	46.9	68.9	112.8	156.7	200.6	244.5	266.8	289.2
107.5°	181.1	213.6	246.1	262.4	281.5	319.7	357.9	396.1	434.3	430.6	426.8
110°	378.0	413.5	449.0	466.7	470.8	479.0	487.1	495.3	503.5	500.8	498.0

TEST NUMBER: P1010883

CATALOG NUMBER: S123RDIP-B340D1195UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	582.6	583.1	583.6	583.9	582.8	580.5	578.3	576.0	573.8	571.1	568.3
115°	654.4	653.5	652.5	652.0	650.8	648.3	645.8	643.3	640.8	638.6	636.4
117.5°	716.2	716.0	715.7	715.6	714.6	712.6	710.7	708.7	706.7	705.5	704.2
120°	779.2	779.2	779.2	779.2	778.2	776.2	774.3	772.3	770.3	769.6	768.8
122.5°	840.1	839.9	839.6	839.5	838.9	837.6	836.4	835.1	833.9	832.9	831.9
125°	896.6	896.1	895.6	895.3	895.1	894.6	894.1	893.6	893.1	892.1	891.1
127.5°	954.4	954.9	955.4	955.6	955.2	954.5	953.8	953.0	952.3	951.1	949.8
130°	1008.0	1008.5	1009.0	1009.2	1008.7	1007.7	1006.8	1005.8	1004.8	1003.8	1002.8
132.5°	1057.6	1058.4	1059.1	1059.5	1059.0	1058.0	1057.0	1056.0	1055.0	1054.2	1053.5
135°	1107.8	1108.6	1109.3	1109.7	1109.3	1108.6	1107.8	1107.1	1106.3	1105.3	1104.3
137.5°	1155.3	1155.8	1156.3	1156.6	1156.0	1154.7	1153.5	1152.2	1151.0	1150.5	1150.0
140°	1197.8	1198.3	1198.8	1199.0	1198.5	1197.5	1196.5	1195.5	1194.5	1193.8	1193.0
142.5°	1237.3	1238.1	1238.8	1239.2	1238.8	1238.1	1237.3	1236.6	1235.8	1235.1	1234.3
145°	1276.0	1276.0	1276.0	1276.0	1275.8	1275.3	1274.8	1274.3	1273.8	1273.3	1272.8
147.5°	1307.5	1308.8	1310.0	1310.6	1310.4	1309.9	1309.4	1308.9	1308.4	1307.9	1307.4
150°	1340.1	1340.8	1341.5	1341.9	1341.7	1341.2	1340.7	1340.2	1339.7	1339.2	1338.7
152.5°	1367.8	1369.0	1370.3	1370.9	1370.4	1369.4	1368.5	1367.5	1366.5	1366.2	1366.0
155°	1392.9	1394.4	1395.9	1396.6	1396.0	1394.7	1393.5	1392.2	1391.0	1390.8	1390.5
157.5°	1415.1	1417.1	1419.1	1420.1	1419.4	1417.9	1416.4	1414.9	1413.4	1413.6	1413.9
160°	1434.7	1436.4	1438.1	1439.0	1438.3	1436.8	1435.3	1433.8	1432.3	1432.5	1432.8
162.5°	1453.2	1454.7	1456.2	1456.9	1456.0	1454.3	1452.6	1450.8	1449.1	1449.3	1449.6
165°	1468.2	1469.9	1471.6	1472.5	1471.5	1469.5	1467.6	1465.6	1463.6	1463.8	1464.1
167.5°	1479.9	1481.8	1483.8	1484.8	1483.8	1481.8	1479.9	1477.9	1475.9	1475.9	1475.9
170°	1489.9	1491.8	1493.8	1494.8	1493.8	1491.8	1489.9	1487.9	1485.9	1485.9	1485.9
172.5°	1495.9	1498.2	1500.4	1501.5	1500.5	1498.5	1496.6	1494.6	1492.6	1492.4	1492.1
175°	1501.1	1503.0	1505.0	1506.0	1505.1	1503.4	1501.7	1499.9	1498.2	1498.0	1497.7
177.5°	1503.2	1505.7	1508.2	1509.4	1508.4	1506.4	1504.4	1502.4	1500.4	1500.2	1499.9
180°	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7

TEST NUMBER: P1010883

CATALOG NUMBER: S123RDIP-B340D1195UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	527.1	524.9	522.7	522.7	517.9	513.6	511.4	512.3	509.7	506.2	502.7
5°	550.2	541.5	539.7	534.9	528.4	519.3	514.5	510.1	504.9	497.9	491.4
7.5°	571.6	560.2	554.1	549.3	536.7	524.0	513.6	506.6	497.5	487.0	479.1
10°	599.5	578.5	572.0	561.1	543.2	525.4	513.1	501.8	489.2	477.0	466.5
12.5°	621.7	597.7	585.5	574.6	551.5	528.8	508.4	494.4	479.1	465.6	452.1
15°	647.0	620.0	598.6	585.5	556.3	528.8	505.7	486.1	469.1	452.5	440.8
17.5°	659.2	625.2	615.6	596.9	554.6	527.1	498.8	477.8	457.3	438.2	424.2
20°	678.4	638.7	614.7	602.1	564.6	524.0	490.9	466.9	445.6	425.1	410.3
22.5°	679.7	636.5	620.8	596.9	550.6	514.9	483.9	454.7	429.9	410.7	395.4
25°	676.6	632.6	610.8	591.6	553.3	509.7	470.0	441.2	416.8	394.6	376.7
27.5°	675.3	621.3	600.8	581.6	538.4	494.4	461.7	429.0	401.1	381.5	363.2
30°	673.6	609.1	584.2	562.0	522.3	482.6	443.4	415.1	388.5	363.6	345.3
32.5°	662.3	592.5	567.2	543.7	500.9	461.3	430.3	400.2	371.5	348.3	331.8
35°	658.8	577.2	544.1	518.8	477.0	441.6	409.0	384.1	357.1	334.0	314.3
37.5°	648.7	561.5	525.8	493.5	449.9	416.4	392.4	367.5	341.4	316.5	300.8
40°	631.3	543.2	502.7	469.6	424.6	390.6	368.4	350.1	324.4	302.1	283.0
42.5°	605.6	524.5	480.9	446.0	396.3	364.5	346.2	328.7	306.9	283.8	268.1
45°	575.9	499.6	459.1	420.3	369.7	338.8	319.6	309.1	289.1	269.4	251.1
47.5°	535.4	473.9	433.8	393.7	342.2	312.2	296.9	286.4	272.5	251.1	236.3
50°	484.4	440.8	402.8	367.1	315.2	286.4	271.2	263.3	251.6	236.3	221.9
52.5°	427.7	402.4	371.0	337.9	287.7	260.7	246.8	240.7	231.9	217.6	205.3
55°	370.6	359.7	338.3	305.6	259.0	236.7	224.5	216.7	210.1	199.7	189.2
57.5°	319.6	314.3	299.5	274.2	235.0	211.9	201.4	196.2	191.0	183.1	172.6
60°	266.8	272.5	257.2	244.6	208.8	188.8	179.6	174.0	171.3	164.4	157.8
62.5°	221.0	226.3	217.6	208.0	182.7	164.8	159.1	153.9	152.2	146.1	139.5
65°	179.6	186.2	179.6	174.4	159.1	144.3	137.3	134.7	133.0	129.1	123.8
67.5°	143.0	149.5	146.5	139.9	135.2	122.9	119.0	116.4	115.5	112.5	108.1
70°	107.7	116.8	117.7	113.8	109.4	103.8	101.1	100.3	98.1	95.5	92.9
72.5°	77.6	88.1	88.5	88.5	85.9	85.9	83.3	82.0	82.0	79.3	76.3
75°	57.1	64.1	65.0	65.8	67.1	68.4	66.7	66.7	66.3	63.7	62.3
77.5°	37.9	44.0	46.2	49.3	51.0	51.0	51.9	52.8	51.9	50.6	49.7
80°	24.4	28.8	31.4	33.1	35.8	37.1	38.4	38.8	37.9	37.5	36.2
82.5°	16.1	17.4	18.7	20.9	24.0	26.2	26.2	25.7	26.6	26.2	25.7
85°	9.2	10.0	10.5	10.9	12.6	14.8	15.3	15.7	16.6	15.7	14.8
87.5°	3.5	3.9	3.9	3.9	4.8	5.2	6.5	8.3	7.8	7.0	7.0
90°	17.1	13.9	12.3	11.1	8.6	6.1	3.6	1.1	3.6	6.1	8.6
92.5°	22.3	20.1	19.0	19.7	21.2	22.7	24.2	25.7	24.2	22.7	21.2
95°	26.4	23.7	22.3	27.4	37.6	47.7	57.9	68.1	57.9	47.7	37.6
97.5°	73.7	86.4	92.7	96.2	103.1	110.0	117.0	123.9	117.0	110.0	103.1
100°	152.9	191.6	211.0	208.5	203.6	198.6	193.7	188.7	193.7	198.6	203.6
102.5°	212.1	255.3	276.9	275.3	272.1	268.8	265.6	262.4	265.6	268.8	272.1
105°	311.5	333.8	345.0	343.6	340.9	338.2	335.4	332.7	335.4	338.2	340.9
107.5°	423.1	419.4	417.5	416.4	414.2	411.9	409.7	407.5	409.7	411.9	414.2
110°	495.3	492.6	491.2	490.2	488.2	486.3	484.3	482.3	484.3	486.3	488.2

TEST NUMBER: P1010883

CATALOG NUMBER: S123RDIP-B340D1195UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	565.6	562.9	561.5	560.6	558.9	557.2	555.4	553.7	555.4	557.2	558.9
115°	634.1	631.9	630.8	630.1	628.6	627.1	625.6	624.1	625.6	627.1	628.6
117.5°	703.0	701.7	701.1	700.2	698.5	696.8	695.0	693.3	695.0	696.8	698.5
120°	768.1	767.4	767.0	765.9	763.6	761.4	759.1	756.9	759.1	761.4	763.6
122.5°	831.0	830.0	829.5	828.6	826.9	825.2	823.4	821.7	823.4	825.2	826.9
125°	890.1	889.1	888.6	887.6	885.6	883.7	881.7	879.7	881.7	883.7	885.6
127.5°	948.6	947.3	946.7	945.7	943.7	941.8	939.8	937.8	939.8	941.8	943.7
130°	1001.8	1000.8	1000.3	999.3	997.3	995.4	993.4	991.4	993.4	995.4	997.3
132.5°	1052.7	1052.0	1051.6	1050.6	1048.6	1046.7	1044.7	1042.7	1044.7	1046.7	1048.6
135°	1103.4	1102.4	1101.9	1101.2	1099.7	1098.2	1096.7	1095.2	1096.7	1098.2	1099.7
137.5°	1149.5	1149.0	1148.8	1147.8	1145.8	1143.8	1141.8	1139.8	1141.8	1143.8	1145.8
140°	1192.3	1191.6	1191.2	1190.5	1189.0	1187.5	1186.0	1184.5	1186.0	1187.5	1189.0
142.5°	1233.6	1232.9	1232.5	1231.8	1230.3	1228.8	1227.3	1225.8	1227.3	1228.8	1230.3
145°	1272.3	1271.8	1271.6	1270.7	1269.0	1267.3	1265.5	1263.8	1265.5	1267.3	1269.0
147.5°	1306.9	1306.4	1306.2	1305.6	1304.3	1303.1	1301.8	1300.6	1301.8	1303.1	1304.3
150°	1338.2	1337.7	1337.4	1337.0	1336.3	1335.6	1334.8	1334.1	1334.8	1335.6	1336.3
152.5°	1365.7	1365.4	1365.3	1365.2	1364.9	1364.7	1364.4	1364.2	1364.4	1364.7	1364.9
155°	1390.3	1390.0	1389.9	1390.1	1390.6	1391.1	1391.6	1392.1	1391.6	1391.1	1390.6
157.5°	1414.1	1414.4	1414.5	1414.5	1414.5	1414.5	1414.5	1414.5	1414.5	1414.5	1414.5
160°	1433.0	1433.3	1433.4	1433.5	1433.8	1434.1	1434.3	1434.6	1434.3	1434.1	1433.8
162.5°	1449.8	1450.1	1450.2	1450.6	1451.3	1452.0	1452.8	1453.5	1452.8	1452.0	1451.3
165°	1464.3	1464.6	1464.7	1465.1	1465.8	1466.6	1467.3	1468.1	1467.3	1466.6	1465.8
167.5°	1475.9	1475.9	1475.9	1476.4	1477.4	1478.3	1479.3	1480.3	1479.3	1478.3	1477.4
170°	1485.9	1485.9	1485.9	1486.4	1487.4	1488.4	1489.4	1490.4	1489.4	1488.4	1487.4
172.5°	1491.9	1491.6	1491.5	1492.1	1493.4	1494.6	1495.9	1497.1	1495.9	1494.6	1493.4
175°	1497.5	1497.2	1497.1	1497.7	1499.0	1500.2	1501.5	1502.7	1501.5	1500.2	1499.0
177.5°	1499.7	1499.4	1499.3	1499.9	1501.2	1502.4	1503.7	1504.9	1503.7	1502.4	1501.2
180°	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7

TEST NUMBER: P1010883

CATALOG NUMBER: S123RDIP-B340D1195UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	502.7	500.5	499.6	497.5	492.2	488.7	484.8	482.2	482.6	480.5	481.8
5°	487.0	486.6	483.5	479.1	471.7	467.8	460.8	457.3	455.6	456.0	453.4
7.5°	473.9	470.0	467.8	460.8	453.9	445.6	439.9	436.9	434.2	431.6	429.9
10°	459.1	455.6	452.1	444.7	435.1	427.3	419.4	416.4	412.4	410.7	409.4
12.5°	443.4	441.2	436.9	428.1	417.2	409.8	400.7	398.9	393.7	390.2	389.3
15°	429.0	427.7	419.8	409.8	398.9	391.5	383.7	378.4	369.7	371.5	368.4
17.5°	413.7	408.1	403.3	389.8	384.5	373.2	364.0	361.4	355.3	351.4	347.5
20°	396.7	393.3	387.2	378.4	365.8	352.7	345.7	341.4	337.9	331.8	330.0
22.5°	380.6	376.3	371.0	359.7	348.8	337.9	328.3	324.4	320.0	315.7	313.0
25°	368.0	361.4	355.8	341.8	330.9	321.8	315.7	309.1	303.0	300.4	299.5
27.5°	348.3	344.4	338.8	325.7	315.7	305.6	300.0	295.6	289.1	286.0	283.4
30°	335.7	327.9	321.3	310.9	300.8	289.9	284.7	279.5	275.5	271.6	268.6
32.5°	318.7	312.6	307.4	296.9	286.9	276.8	271.2	263.3	261.2	258.1	254.6
35°	302.1	298.2	292.5	281.2	270.3	263.3	257.2	249.8	247.2	245.0	242.0
37.5°	286.4	280.8	276.8	265.9	256.4	248.1	243.3	237.2	235.4	232.8	230.6
40°	272.9	267.3	263.3	252.4	242.4	233.7	230.6	224.5	221.9	218.9	217.6
42.5°	257.7	252.9	247.6	239.8	229.3	220.6	214.5	211.0	207.5	206.2	203.6
45°	241.5	237.2	233.2	224.5	213.6	207.5	202.3	197.5	194.9	192.7	191.0
47.5°	227.6	223.7	218.4	208.8	200.1	194.4	189.2	184.4	181.8	179.2	177.0
50°	211.5	209.3	203.6	194.4	186.2	179.6	174.8	170.5	168.7	165.7	162.2
52.5°	197.1	193.1	188.3	180.9	173.5	165.7	159.1	156.5	153.5	151.7	148.7
55°	180.1	177.4	172.2	165.7	157.8	151.3	146.5	143.0	139.1	137.3	133.4
57.5°	165.7	160.9	158.3	150.0	142.6	136.0	132.5	129.1	124.7	122.1	120.3
60°	150.0	145.6	141.7	134.7	129.5	122.5	117.3	114.2	111.2	107.7	105.9
62.5°	134.7	131.2	126.4	120.8	114.2	108.6	104.6	100.3	98.5	95.0	93.7
65°	118.2	115.5	111.6	105.1	99.8	95.0	91.1	87.6	85.9	84.6	83.7
67.5°	103.3	99.8	97.2	91.6	85.9	82.0	79.8	77.6	75.4	74.1	72.8
70°	88.1	85.5	82.8	77.6	73.7	70.2	68.4	66.7	65.4	64.1	62.8
72.5°	72.4	71.1	68.4	65.0	61.9	59.3	58.0	55.8	54.5	52.3	51.4
75°	59.7	57.5	56.2	53.2	50.6	48.4	46.6	44.0	42.3	41.4	41.0
77.5°	47.1	46.2	44.5	41.9	40.5	38.4	35.8	34.9	34.0	34.0	33.6
80°	35.3	34.0	32.7	30.5	29.2	27.5	27.5	27.5	27.0	27.5	27.0
82.5°	24.0	23.1	22.2	20.9	20.5	20.5	20.9	20.9	20.9	20.9	20.9
85°	14.0	14.0	14.0	14.4	14.0	14.0	14.4	14.8	14.4	14.4	14.0
87.5°	6.5	6.5	7.0	7.0	7.4	7.4	7.4	7.4	7.4	7.4	7.8
90°	11.1	12.3	13.9	17.1	20.4	23.6	26.8	27.8	28.8	29.8	30.8
92.5°	19.7	19.0	20.1	22.3	24.6	26.8	29.0	30.7	32.5	34.2	35.9
95°	27.4	22.3	23.7	26.4	29.1	31.9	34.6	36.3	38.1	39.8	41.5
97.5°	96.2	92.7	86.4	73.7	61.0	48.4	35.7	37.7	39.7	41.7	43.7
100°	208.5	211.0	191.6	152.9	114.2	75.5	36.8	38.8	40.8	42.8	44.8
102.5°	275.3	276.9	255.3	212.1	169.0	125.8	82.6	74.4	66.2	58.1	49.9
105°	343.6	345.0	333.8	311.5	289.2	266.8	244.5	200.6	156.7	112.8	68.9
107.5°	416.4	417.5	419.4	423.1	426.8	430.6	434.3	396.1	357.9	319.7	281.5
110°	490.2	491.2	492.6	495.3	498.0	500.8	503.5	495.3	487.1	479.0	470.8

TEST NUMBER: P1010883

CATALOG NUMBER: S123RDIP-B340D1195UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	560.6	561.5	562.9	565.6	568.3	571.1	573.8	576.0	578.3	580.5	582.8
115°	630.1	630.8	631.9	634.1	636.4	638.6	640.8	643.3	645.8	648.3	650.8
117.5°	700.2	701.1	701.7	703.0	704.2	705.5	706.7	708.7	710.7	712.6	714.6
120°	765.9	767.0	767.4	768.1	768.8	769.6	770.3	772.3	774.3	776.2	778.2
122.5°	828.6	829.5	830.0	831.0	831.9	832.9	833.9	835.1	836.4	837.6	838.9
125°	887.6	888.6	889.1	890.1	891.1	892.1	893.1	893.6	894.1	894.6	895.1
127.5°	945.7	946.7	947.3	948.6	949.8	951.1	952.3	953.0	953.8	954.5	955.2
130°	999.3	1000.3	1000.8	1001.8	1002.8	1003.8	1004.8	1005.8	1006.8	1007.7	1008.7
132.5°	1050.6	1051.6	1052.0	1052.7	1053.5	1054.2	1055.0	1056.0	1057.0	1058.0	1059.0
135°	1101.2	1101.9	1102.4	1103.4	1104.3	1105.3	1106.3	1107.1	1107.8	1108.6	1109.3
137.5°	1147.8	1148.8	1149.0	1149.5	1150.0	1150.5	1151.0	1152.2	1153.5	1154.7	1156.0
140°	1190.5	1191.2	1191.6	1192.3	1193.0	1193.8	1194.5	1195.5	1196.5	1197.5	1198.5
142.5°	1231.8	1232.5	1232.9	1233.6	1234.3	1235.1	1235.8	1236.6	1237.3	1238.1	1238.8
145°	1270.7	1271.6	1271.8	1272.3	1272.8	1273.3	1273.8	1274.3	1274.8	1275.3	1275.8
147.5°	1305.6	1306.2	1306.4	1306.9	1307.4	1307.9	1308.4	1308.9	1309.4	1309.9	1310.4
150°	1337.0	1337.4	1337.7	1338.2	1338.7	1339.2	1339.7	1340.2	1340.7	1341.2	1341.7
152.5°	1365.2	1365.3	1365.4	1365.7	1366.0	1366.2	1366.5	1367.5	1368.5	1369.4	1370.4
155°	1390.1	1389.9	1390.0	1390.3	1390.5	1390.8	1391.0	1392.2	1393.5	1394.7	1396.0
157.5°	1414.5	1414.5	1414.4	1414.1	1413.9	1413.6	1413.4	1414.9	1416.4	1417.9	1419.4
160°	1433.5	1433.4	1433.3	1433.0	1432.8	1432.5	1432.3	1433.8	1435.3	1436.8	1438.3
162.5°	1450.6	1450.2	1450.1	1449.8	1449.6	1449.3	1449.1	1450.8	1452.6	1454.3	1456.0
165°	1465.1	1464.7	1464.6	1464.3	1464.1	1463.8	1463.6	1465.6	1467.6	1469.5	1471.5
167.5°	1476.4	1475.9	1475.9	1475.9	1475.9	1475.9	1475.9	1477.9	1479.9	1481.8	1483.8
170°	1486.4	1485.9	1485.9	1485.9	1485.9	1485.9	1485.9	1487.9	1489.9	1491.8	1493.8
172.5°	1492.1	1491.5	1491.6	1491.9	1492.1	1492.4	1492.6	1494.6	1496.6	1498.5	1500.5
175°	1497.7	1497.1	1497.2	1497.5	1497.7	1498.0	1498.2	1499.9	1501.7	1503.4	1505.1
177.5°	1499.9	1499.3	1499.4	1499.7	1499.9	1500.2	1500.4	1502.4	1504.4	1506.4	1508.4
180°	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7

TEST NUMBER: P1010883

CATALOG NUMBER: S123RDIP-B340D1195UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	481.3	481.8	480.5	477.8	477.4	478.3	480.9	480.0	477.8	481.8	478.3
5°	454.7	452.5	451.7	452.5	449.9	448.6	451.2	449.9	451.2	451.7	453.0
7.5°	429.0	429.4	426.8	427.3	423.8	424.6	424.6	424.6	426.0	426.8	428.6
10°	406.8	407.6	404.6	405.0	402.4	400.7	402.0	404.6	404.6	404.6	405.5
12.5°	388.9	385.0	382.8	382.4	379.3	378.4	381.0	381.9	384.1	384.1	385.4
15°	366.7	365.8	364.0	364.0	356.6	358.4	359.2	362.3	366.7	363.2	364.0
17.5°	346.6	344.4	342.2	341.4	340.5	337.9	341.4	340.9	343.6	344.0	345.3
20°	328.7	327.0	322.6	323.1	323.9	320.0	322.2	322.2	324.8	327.4	330.5
22.5°	311.3	309.5	307.4	308.2	305.6	304.8	304.8	306.9	310.0	312.2	311.7
25°	297.8	294.7	293.4	292.1	290.8	291.7	290.4	292.5	294.7	296.0	294.7
27.5°	282.5	281.2	278.6	277.3	275.1	276.0	276.8	278.6	279.9	279.9	281.2
30°	267.7	265.9	265.1	263.8	263.8	262.0	262.5	264.2	265.5	266.8	268.6
32.5°	253.3	252.0	250.7	250.7	249.8	249.4	248.9	251.6	251.6	254.2	254.2
35°	241.5	239.4	239.4	237.2	238.0	237.6	236.7	238.5	238.9	240.7	240.2
37.5°	228.5	228.5	227.6	225.4	223.7	224.1	226.3	226.3	227.6	227.1	228.5
40°	215.4	214.5	214.5	213.2	212.8	212.3	212.8	213.2	215.4	214.9	215.4
42.5°	202.3	202.7	200.6	200.6	200.6	199.2	199.7	200.1	201.0	201.9	203.2
45°	189.7	188.8	188.3	187.5	186.6	187.0	186.6	188.3	187.9	188.8	190.1
47.5°	176.1	174.8	174.4	172.6	172.6	173.5	173.1	174.4	174.8	176.1	175.3
50°	163.1	161.3	160.0	160.4	157.8	158.7	158.7	160.0	161.3	161.7	162.6
52.5°	147.8	147.4	146.9	144.7	144.3	143.9	144.3	144.7	146.5	147.8	148.2
55°	133.0	132.5	129.9	129.1	127.7	127.7	128.6	129.1	132.1	132.5	134.3
57.5°	119.5	118.2	115.1	114.7	114.7	114.7	113.4	115.1	116.0	118.2	118.2
60°	104.6	104.6	102.0	102.0	102.5	102.0	102.0	102.5	102.5	104.2	105.1
62.5°	92.9	92.4	92.4	91.6	91.1	91.6	91.1	91.1	91.6	92.9	94.2
65°	82.4	82.0	81.5	81.1	80.2	80.2	80.7	81.5	81.5	82.4	82.8
67.5°	72.4	72.4	71.5	71.5	71.1	70.6	71.1	70.6	72.4	72.4	72.8
70°	62.3	61.9	60.6	60.2	58.9	59.3	59.3	60.6	61.0	61.9	62.8
72.5°	50.1	50.1	49.3	48.4	48.8	48.0	48.0	48.4	48.4	49.7	50.1
75°	41.4	40.5	40.1	40.5	40.1	41.0	40.1	40.1	41.0	41.0	41.0
77.5°	34.0	34.0	33.6	33.6	34.0	33.6	34.0	34.0	34.0	33.6	34.0
80°	27.9	27.5	27.5	27.5	27.0	27.0	27.0	27.0	27.0	27.0	27.0
82.5°	20.9	20.9	20.5	20.9	20.9	20.5	20.9	20.5	20.5	20.9	20.9
85°	14.0	14.8	14.0	14.0	14.4	14.4	14.8	14.4	14.8	14.0	14.4
87.5°	7.4	7.8	7.8	7.4	7.4	7.8	7.8	7.8	8.3	7.4	7.8
90°	31.3	31.5	32.0	32.5	33.0	33.5	33.0	32.5	32.0	31.5	31.3
92.5°	36.8	36.9	37.2	37.5	37.7	38.0	37.7	37.5	37.2	36.9	36.8
95°	42.4	42.4	42.4	42.4	42.4	42.4	42.4	42.4	42.4	42.4	42.4
97.5°	44.7	44.8	45.1	45.3	45.6	45.8	45.6	45.3	45.1	44.8	44.7
100°	45.8	45.9	46.2	46.4	46.7	46.9	46.7	46.4	46.2	45.9	45.8
102.5°	45.8	46.0	46.5	47.0	47.5	48.0	47.5	47.0	46.5	46.0	45.8
105°	46.9	47.1	47.6	48.1	48.6	49.1	48.6	48.1	47.6	47.1	46.9
107.5°	262.4	246.1	213.6	181.1	148.6	116.1	148.6	181.1	213.6	246.1	262.4
110°	466.7	449.0	413.5	378.0	342.5	307.0	342.5	378.0	413.5	449.0	466.7

TEST NUMBER: P1010883

CATALOG NUMBER: S123RDIP-B340D1195UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	583.9	583.6	583.1	582.6	582.1	581.6	582.1	582.6	583.1	583.6	583.9
115°	652.0	652.5	653.5	654.4	655.4	656.4	655.4	654.4	653.5	652.5	652.0
117.5°	715.6	715.7	716.0	716.2	716.5	716.7	716.5	716.2	716.0	715.7	715.6
120°	779.2	779.2	779.2	779.2	779.2	779.2	779.2	779.2	779.2	779.2	779.2
122.5°	839.5	839.6	839.9	840.1	840.4	840.6	840.4	840.1	839.9	839.6	839.5
125°	895.3	895.6	896.1	896.6	897.1	897.6	897.1	896.6	896.1	895.6	895.3
127.5°	955.6	955.4	954.9	954.4	953.9	953.4	953.9	954.4	954.9	955.4	955.6
130°	1009.2	1009.0	1008.5	1008.0	1007.5	1007.0	1007.5	1008.0	1008.5	1009.0	1009.2
132.5°	1059.5	1059.1	1058.4	1057.6	1056.9	1056.1	1056.9	1057.6	1058.4	1059.1	1059.5
135°	1109.7	1109.3	1108.6	1107.8	1107.1	1106.3	1107.1	1107.8	1108.6	1109.3	1109.7
137.5°	1156.6	1156.3	1155.8	1155.3	1154.8	1154.3	1154.8	1155.3	1155.8	1156.3	1156.6
140°	1199.0	1198.8	1198.3	1197.8	1197.3	1196.8	1197.3	1197.8	1198.3	1198.8	1199.0
142.5°	1239.2	1238.8	1238.1	1237.3	1236.6	1235.8	1236.6	1237.3	1238.1	1238.8	1239.2
145°	1276.0	1276.0	1276.0	1276.0	1276.0	1276.0	1276.0	1276.0	1276.0	1276.0	1276.0
147.5°	1310.6	1310.0	1308.8	1307.5	1306.3	1305.1	1306.3	1307.5	1308.8	1310.0	1310.6
150°	1341.9	1341.5	1340.8	1340.1	1339.3	1338.6	1339.3	1340.1	1340.8	1341.5	1341.9
152.5°	1370.9	1370.3	1369.0	1367.8	1366.5	1365.3	1366.5	1367.8	1369.0	1370.3	1370.9
155°	1396.6	1395.9	1394.4	1392.9	1391.4	1389.9	1391.4	1392.9	1394.4	1395.9	1396.6
157.5°	1420.1	1419.1	1417.1	1415.1	1413.1	1411.1	1413.1	1415.1	1417.1	1419.1	1420.1
160°	1439.0	1438.1	1436.4	1434.7	1432.9	1431.2	1432.9	1434.7	1436.4	1438.1	1439.0
162.5°	1456.9	1456.2	1454.7	1453.2	1451.7	1450.2	1451.7	1453.2	1454.7	1456.2	1456.9
165°	1472.5	1471.6	1469.9	1468.2	1466.4	1464.7	1466.4	1468.2	1469.9	1471.6	1472.5
167.5°	1484.8	1483.8	1481.8	1479.9	1477.9	1475.9	1477.9	1479.9	1481.8	1483.8	1484.8
170°	1494.8	1493.8	1491.8	1489.9	1487.9	1485.9	1487.9	1489.9	1491.8	1493.8	1494.8
172.5°	1501.5	1500.4	1498.2	1495.9	1493.7	1491.5	1493.7	1495.9	1498.2	1500.4	1501.5
175°	1506.0	1505.0	1503.0	1501.1	1499.1	1497.1	1499.1	1501.1	1503.0	1505.0	1506.0
177.5°	1509.4	1508.2	1505.7	1503.2	1500.7	1498.2	1500.7	1503.2	1505.7	1508.2	1509.4
180°	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7

TEST NUMBER: P1010883

CATALOG NUMBER: S123RDIP-B340D1195UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	481.8	483.5	481.8	478.3	481.8	483.9	486.1	489.6	491.4	491.4	494.0
5°	454.3	457.8	456.5	455.6	459.1	461.3	464.8	469.1	473.9	477.0	480.5
7.5°	429.9	432.1	434.2	434.2	437.7	442.5	447.8	453.0	459.1	463.4	466.1
10°	408.5	410.3	411.6	413.3	418.5	423.8	430.7	437.3	442.5	447.3	451.7
12.5°	388.0	390.6	393.7	395.0	398.9	405.5	412.0	419.8	428.1	432.9	437.3
15°	368.4	369.7	373.2	377.1	380.6	387.6	395.9	404.2	411.1	418.5	422.5
17.5°	348.3	348.8	357.9	355.8	367.1	373.6	378.0	385.8	397.2	403.3	409.4
20°	328.7	333.1	337.0	339.2	345.3	352.7	365.4	371.5	380.6	386.3	391.5
22.5°	313.5	320.0	320.0	325.2	328.3	335.3	344.4	356.2	366.2	370.1	377.6
25°	300.0	303.0	308.2	310.0	315.7	321.8	327.9	340.5	351.4	356.6	361.9
27.5°	282.5	286.4	293.4	293.4	300.8	307.4	314.8	323.1	334.0	341.4	347.0
30°	269.0	272.9	276.0	280.8	283.8	289.9	303.0	309.1	318.7	325.2	332.2
32.5°	256.4	259.4	262.0	267.3	270.7	277.7	284.7	295.6	303.9	310.0	317.4
35°	242.4	245.5	248.9	252.9	258.1	264.6	271.2	280.3	288.6	294.3	300.4
37.5°	229.3	231.5	236.7	239.4	243.7	249.8	258.1	267.7	275.1	279.5	285.6
40°	216.7	218.4	222.4	227.1	230.2	235.0	243.7	252.0	261.2	266.4	271.2
42.5°	203.2	205.3	208.8	213.6	218.4	223.7	228.5	238.0	246.3	250.7	255.9
45°	191.4	192.7	195.3	200.1	204.9	208.8	216.2	225.0	232.8	236.3	242.0
47.5°	177.4	178.8	182.7	184.9	190.1	195.3	202.7	211.5	218.4	221.9	227.1
50°	163.1	164.4	167.0	171.8	175.3	180.9	187.5	194.9	203.6	208.4	211.5
52.5°	149.1	151.7	153.9	157.8	162.2	167.9	174.0	180.9	188.3	193.1	196.6
55°	135.2	137.3	139.9	142.1	147.4	152.6	159.6	166.1	172.6	177.0	180.9
57.5°	119.5	122.5	125.1	129.5	133.4	137.8	145.6	150.8	158.7	161.7	165.2
60°	105.9	109.0	111.2	114.7	118.2	123.8	129.1	135.6	142.1	146.1	150.4
62.5°	94.6	95.9	97.2	100.7	104.2	109.4	114.7	121.2	128.2	130.4	133.8
65°	83.3	84.6	86.8	89.8	92.4	95.5	101.1	106.4	112.9	116.4	117.7
67.5°	73.7	75.0	75.4	77.6	79.8	83.3	86.3	91.6	97.7	99.8	102.5
70°	62.8	65.0	65.4	67.1	68.0	70.2	73.7	77.6	82.4	86.3	88.5
72.5°	50.1	53.2	54.1	56.7	58.0	60.2	62.8	65.8	68.9	70.6	72.4
75°	41.0	41.9	42.3	44.5	46.6	49.7	51.0	52.8	55.4	57.5	59.3
77.5°	34.0	34.4	34.9	34.9	35.3	37.1	39.7	41.9	43.6	44.5	45.8
80°	27.5	27.0	27.0	27.5	27.5	27.5	28.3	31.4	32.3	34.4	34.0
82.5°	21.4	20.5	20.9	20.5	20.5	20.5	20.5	20.9	20.9	22.2	23.1
85°	14.0	14.4	14.0	14.0	13.5	14.0	13.5	13.5	13.1	13.1	12.6
87.5°	7.4	7.8	7.4	7.4	7.0	7.4	7.0	7.0	6.5	6.5	5.7
90°	30.8	29.8	28.8	27.8	26.8	23.6	20.4	17.1	13.9	12.3	11.1
92.5°	35.9	34.2	32.5	30.7	29.0	26.8	24.6	22.3	20.1	19.0	19.7
95°	41.5	39.8	38.1	36.3	34.6	31.9	29.1	26.4	23.7	22.3	27.4
97.5°	43.7	41.7	39.7	37.7	35.7	48.4	61.0	73.7	86.4	92.7	96.2
100°	44.8	42.8	40.8	38.8	36.8	75.5	114.2	152.9	191.6	211.0	208.5
102.5°	49.9	58.1	66.2	74.4	82.6	125.8	169.0	212.1	255.3	276.9	275.3
105°	68.9	112.8	156.7	200.6	244.5	266.8	289.2	311.5	333.8	345.0	343.6
107.5°	281.5	319.7	357.9	396.1	434.3	430.6	426.8	423.1	419.4	417.5	416.4
110°	470.8	479.0	487.1	495.3	503.5	500.8	498.0	495.3	492.6	491.2	490.2

TEST NUMBER: P1010883

CATALOG NUMBER: S123RDIP-B340D1195UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	582.8	580.5	578.3	576.0	573.8	571.1	568.3	565.6	562.9	561.5	560.6
115°	650.8	648.3	645.8	643.3	640.8	638.6	636.4	634.1	631.9	630.8	630.1
117.5°	714.6	712.6	710.7	708.7	706.7	705.5	704.2	703.0	701.7	701.1	700.2
120°	778.2	776.2	774.3	772.3	770.3	769.6	768.8	768.1	767.4	767.0	765.9
122.5°	838.9	837.6	836.4	835.1	833.9	832.9	831.9	831.0	830.0	829.5	828.6
125°	895.1	894.6	894.1	893.6	893.1	892.1	891.1	890.1	889.1	888.6	887.6
127.5°	955.2	954.5	953.8	953.0	952.3	951.1	949.8	948.6	947.3	946.7	945.7
130°	1008.7	1007.7	1006.8	1005.8	1004.8	1003.8	1002.8	1001.8	1000.8	1000.3	999.3
132.5°	1059.0	1058.0	1057.0	1056.0	1055.0	1054.2	1053.5	1052.7	1052.0	1051.6	1050.6
135°	1109.3	1108.6	1107.8	1107.1	1106.3	1105.3	1104.3	1103.4	1102.4	1101.9	1101.2
137.5°	1156.0	1154.7	1153.5	1152.2	1151.0	1150.5	1150.0	1149.5	1149.0	1148.8	1147.8
140°	1198.5	1197.5	1196.5	1195.5	1194.5	1193.8	1193.0	1192.3	1191.6	1191.2	1190.5
142.5°	1238.8	1238.1	1237.3	1236.6	1235.8	1235.1	1234.3	1233.6	1232.9	1232.5	1231.8
145°	1275.8	1275.3	1274.8	1274.3	1273.8	1273.3	1272.8	1272.3	1271.8	1271.6	1270.7
147.5°	1310.4	1309.9	1309.4	1308.9	1308.4	1307.9	1307.4	1306.9	1306.4	1306.2	1305.6
150°	1341.7	1341.2	1340.7	1340.2	1339.7	1339.2	1338.7	1338.2	1337.7	1337.4	1337.0
152.5°	1370.4	1369.4	1368.5	1367.5	1366.5	1366.2	1366.0	1365.7	1365.4	1365.3	1365.2
155°	1396.0	1394.7	1393.5	1392.2	1391.0	1390.8	1390.5	1390.3	1390.0	1389.9	1390.1
157.5°	1419.4	1417.9	1416.4	1414.9	1413.4	1413.6	1413.9	1414.1	1414.4	1414.5	1414.5
160°	1438.3	1436.8	1435.3	1433.8	1432.3	1432.5	1432.8	1433.0	1433.3	1433.4	1433.5
162.5°	1456.0	1454.3	1452.6	1450.8	1449.1	1449.3	1449.6	1449.8	1450.1	1450.2	1450.6
165°	1471.5	1469.5	1467.6	1465.6	1463.6	1463.8	1464.1	1464.3	1464.6	1464.7	1465.1
167.5°	1483.8	1481.8	1479.9	1477.9	1475.9	1475.9	1475.9	1475.9	1475.9	1475.9	1476.4
170°	1493.8	1491.8	1489.9	1487.9	1485.9	1485.9	1485.9	1485.9	1485.9	1485.9	1486.4
172.5°	1500.5	1498.5	1496.6	1494.6	1492.6	1492.4	1492.1	1491.9	1491.6	1491.5	1492.1
175°	1505.1	1503.4	1501.7	1499.9	1498.2	1498.0	1497.7	1497.5	1497.2	1497.1	1497.7
177.5°	1508.4	1506.4	1504.4	1502.4	1500.4	1500.2	1499.9	1499.7	1499.4	1499.3	1499.9
180°	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7	1502.7

TEST NUMBER: P1010883

CATALOG NUMBER: S123RDIP-B340D1195UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	509.2	509.2	509.2	509.2
2.5°	496.1	499.2	505.3	510.5
5°	485.7	490.5	499.6	508.8
7.5°	473.0	480.5	492.2	504.9
10°	460.8	470.4	484.8	499.6
12.5°	448.6	458.7	473.9	493.1
15°	434.2	444.7	463.0	486.1
17.5°	421.6	435.5	452.1	475.2
20°	408.1	418.5	439.9	464.3
22.5°	391.1	408.5	428.6	454.3
25°	377.6	392.8	412.9	442.1
27.5°	361.0	378.9	403.3	429.0
30°	347.5	362.3	385.0	415.9
32.5°	331.8	349.2	372.8	403.3
35°	317.8	332.7	354.9	385.8
37.5°	301.3	317.4	342.2	369.7
40°	286.9	302.6	326.1	351.8
42.5°	269.4	286.0	309.5	331.3
45°	255.5	270.7	289.5	309.5
47.5°	238.5	254.6	272.9	286.9
50°	223.2	238.0	252.4	264.2
52.5°	206.7	220.2	233.2	242.0
55°	191.4	201.9	212.3	218.4
57.5°	173.5	183.5	192.3	195.8
60°	157.8	166.1	171.8	175.7
62.5°	141.3	147.4	151.7	153.9
65°	125.1	129.5	131.7	133.8
67.5°	108.6	112.5	113.8	116.4
70°	91.1	95.5	96.4	97.7
72.5°	78.0	78.0	79.8	81.5
75°	62.3	63.2	64.1	64.1
77.5°	48.8	48.8	49.7	50.1
80°	35.8	36.2	36.2	35.8
82.5°	24.4	25.3	24.4	24.0
85°	13.5	15.3	14.4	14.4
87.5°	5.7	5.7	6.5	5.7
90°	8.6	6.1	3.6	1.1
92.5°	21.2	22.7	24.2	25.7
95°	37.6	47.7	57.9	68.1
97.5°	103.1	110.0	117.0	123.9
100°	203.6	198.6	193.7	188.7
102.5°	272.1	268.8	265.6	262.4
105°	340.9	338.2	335.4	332.7
107.5°	414.2	411.9	409.7	407.5
110°	488.2	486.3	484.3	482.3

TEST NUMBER: P1010883

CATALOG NUMBER: S123RDIP-B340D1195UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	558.9	557.2	555.4	553.7
115°	628.6	627.1	625.6	624.1
117.5°	698.5	696.8	695.0	693.3
120°	763.6	761.4	759.1	756.9
122.5°	826.9	825.2	823.4	821.7
125°	885.6	883.7	881.7	879.7
127.5°	943.7	941.8	939.8	937.8
130°	997.3	995.4	993.4	991.4
132.5°	1048.6	1046.7	1044.7	1042.7
135°	1099.7	1098.2	1096.7	1095.2
137.5°	1145.8	1143.8	1141.8	1139.8
140°	1189.0	1187.5	1186.0	1184.5
142.5°	1230.3	1228.8	1227.3	1225.8
145°	1269.0	1267.3	1265.5	1263.8
147.5°	1304.3	1303.1	1301.8	1300.6
150°	1336.3	1335.6	1334.8	1334.1
152.5°	1364.9	1364.7	1364.4	1364.2
155°	1390.6	1391.1	1391.6	1392.1
157.5°	1414.5	1414.5	1414.5	1414.5
160°	1433.8	1434.1	1434.3	1434.6
162.5°	1451.3	1452.0	1452.8	1453.5
165°	1465.8	1466.6	1467.3	1468.1
167.5°	1477.4	1478.3	1479.3	1480.3
170°	1487.4	1488.4	1489.4	1490.4
172.5°	1493.4	1494.6	1495.9	1497.1
175°	1499.0	1500.2	1501.5	1502.7
177.5°	1501.2	1502.4	1503.7	1504.9
180°	1502.7	1502.7	1502.7	1502.7

(END OF REPORT)