

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010888

Luminaire Tested: S123RDIP-B340D1195UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010888
REPORT IS A COMBINATION OF REPORTS P993174 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B340D1195UB2750-4F0-XX-W2A-F_5000K
Description: Define 3 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5799.0 lumens
Efficiency: N/A
Efficacy: 120.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010888

CATALOG NUMBER: S123RDIP-B340D1195UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010888

CATALOG NUMBER: S123RDIP-B340D1195UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	29	29	29
1	91	87	84	80	81	77	74	72	59	57	55	42	41	40	26	26	25
2	83	76	71	66	74	68	63	59	52	49	46	37	35	33	23	22	21
3	76	67	60	55	67	60	54	49	46	42	39	33	30	28	21	19	18
4	69	59	52	46	61	53	47	42	41	36	33	29	26	24	19	17	16
5	64	53	45	39	56	47	41	36	36	32	28	26	23	21	17	15	14
6	59	47	40	34	52	42	36	31	32	28	24	24	21	18	15	13	12
7	54	42	35	30	48	38	31	27	29	25	21	21	18	16	14	12	11
8	50	38	31	26	44	34	28	24	27	22	19	19	16	14	13	11	10
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9
10	43	32	25	20	38	29	23	19	22	18	15	16	13	11	11	9	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5789	5789	5789
5°	5798	5584	5569
10°	5752	5374	5268
15°	5678	5114	4939
20°	5580	4832	4571
25°	5479	4539	4222
30°	5349	4227	3810
35°	5216	3921	3434
40°	5091	3588	3019
45°	4929	3262	2647
50°	4752	2915	2260
55°	4568	2543	1906
60°	4393	2162	1548
65°	4165	1770	1208
70°	3878	1338	864
75°	3469	906	684
80°	2959	630	480
85°	2219	340	250

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4929 cd/sqm

TEST NUMBER: P1010888

CATALOG NUMBER: S123RDIP-B340D1195UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.6	0.9
10°-20°	140.6	2.4
20°-30°	202.5	3.5
30°-40°	228.0	3.9
40°-50°	218.1	3.8
50°-60°	178.6	3.1
60°-70°	120.4	2.1
70°-80°	60.4	1.0
80°-90°	18.8	0.3
90°-100°	53.0	0.9
100°-110°	256.2	4.4
110°-120°	627.8	10.8
120°-130°	797.0	13.7
130°-140°	851.4	14.7
140°-150°	796.2	13.7
150°-160°	642.2	11.1
160°-170°	414.4	7.1
170°-180°	142.8	2.5
0°-30°	393.7	6.8
0°-40°	621.7	10.7
0°-60°	1018.4	17.6
0°-90°	1218.0	21.0
90°-120°	937.0	16.2
90°-150°	3381.6	58.3
90°-180°	4581.0	79.0
0°-180°	5799.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	538	538	538	538	538	
5°	538	536	530	534	533	51
15°	513	508	496	494	491	145
25°	467	456	436	427	422	215
35°	404	388	361	342	334	253
45°	332	312	279	254	243	256
55°	252	231	194	168	160	226
65°	172	148	114	93	88	171
75°	91	70	46	42	41	97
85°	23	14	12	11	11	25
90°	1	12	27	31	34	5
95°	68	22	35	42	42	81
105°	333	345	244	47	49	353
115°	624	631	641	652	656	616
125°	880	889	893	895	898	786
135°	1095	1102	1106	1110	1106	843
145°	1264	1272	1274	1276	1276	791
155°	1392	1390	1391	1397	1390	641
165°	1468	1465	1464	1472	1465	415
175°	1503	1497	1498	1506	1497	143
180°	1503	1503	1503	1503	1503	

TEST NUMBER: P1010888

CATALOG NUMBER: S123RDIP-B340D1195UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	537.8	537.8	537.8	537.8	537.8
2.5°	540.0	538.2	533.0	537.8	536.9
5°	537.8	535.6	530.4	534.3	533.4
7.5°	533.9	531.7	525.2	527.8	526.5
10°	528.6	525.6	517.7	518.2	516.0
12.5°	521.2	517.7	507.7	507.3	504.7
15°	512.9	508.1	495.9	493.8	490.7
17.5°	502.9	497.7	482.4	478.1	473.7
20°	491.6	484.6	468.0	462.3	457.1
22.5°	478.9	470.6	452.8	445.3	440.5
25°	466.7	455.8	435.7	426.6	421.8
27.5°	451.9	440.1	418.3	406.1	398.7
30°	436.6	423.5	399.1	384.3	377.3
32.5°	421.3	406.1	379.9	363.3	355.9
35°	403.9	388.2	361.2	342.4	334.5
37.5°	386.5	369.4	341.1	320.2	310.6
40°	369.9	350.7	319.7	297.0	287.0
42.5°	351.1	331.9	299.7	274.4	265.6
45°	331.9	312.3	278.7	253.9	243.4
47.5°	313.2	291.4	258.2	231.2	222.0
50°	292.2	271.7	236.4	209.4	199.3
52.5°	273.5	250.8	215.9	187.6	178.8
55°	252.1	230.7	193.7	168.4	159.6
57.5°	232.9	209.8	172.3	148.3	140.9
60°	212.9	188.9	152.7	129.1	121.7
62.5°	192.8	168.8	132.6	110.8	102.9
65°	172.3	148.3	114.3	92.9	88.1
67.5°	151.8	127.4	94.2	78.1	72.8
70°	131.7	108.2	77.6	62.4	57.6
72.5°	111.7	88.5	61.5	49.7	48.4
75°	91.2	70.2	46.2	41.9	41.0
77.5°	72.4	53.2	36.2	33.6	32.7
80°	54.5	36.6	27.5	26.2	25.3
82.5°	37.5	22.7	19.6	18.3	18.3
85°	23.1	13.5	12.2	11.3	11.3
87.5°	10.5	5.7	5.7	5.2	4.8
90°	1.1	12.3	26.8	31.3	33.5
92.5°	25.7	19.0	29.0	36.8	38.0
95°	68.1	22.3	34.6	42.4	42.4
97.5°	123.9	92.7	35.7	44.7	45.8
100°	188.7	211.0	36.8	45.8	46.9
102.5°	262.4	276.9	82.6	45.8	48.0
105°	332.7	345.0	244.5	46.9	49.1
107.5°	407.5	417.5	434.3	262.4	116.1
110°	482.3	491.2	503.5	466.7	307.0

TEST NUMBER: P1010888

CATALOG NUMBER: S123RDIP-B340D1195UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	553.7	561.5	573.8	583.9	581.6
115°	624.1	630.8	640.8	652.0	656.4
117.5°	693.3	701.1	706.7	715.6	716.7
120°	756.9	767.0	770.3	779.2	779.2
122.5°	821.7	829.5	833.9	839.5	840.6
125°	879.7	888.6	893.1	895.3	897.6
127.5°	937.8	946.7	952.3	955.6	953.4
130°	991.4	1000.3	1004.8	1009.2	1007.0
132.5°	1042.7	1051.6	1055.0	1059.5	1056.1
135°	1095.2	1101.9	1106.3	1109.7	1106.3
137.5°	1139.8	1148.8	1151.0	1156.6	1154.3
140°	1184.5	1191.2	1194.5	1199.0	1196.8
142.5°	1225.8	1232.5	1235.8	1239.2	1235.8
145°	1263.8	1271.6	1273.8	1276.0	1276.0
147.5°	1300.6	1306.2	1308.4	1310.6	1305.1
150°	1334.1	1337.4	1339.7	1341.9	1338.6
152.5°	1364.2	1365.3	1366.5	1370.9	1365.3
155°	1392.1	1389.9	1391.0	1396.6	1389.9
157.5°	1414.5	1414.5	1413.4	1420.1	1411.1
160°	1434.6	1433.4	1432.3	1439.0	1431.2
162.5°	1453.5	1450.2	1449.1	1456.9	1450.2
165°	1468.1	1464.7	1463.6	1472.5	1464.7
167.5°	1480.3	1475.9	1475.9	1484.8	1475.9
170°	1490.4	1485.9	1485.9	1494.8	1485.9
172.5°	1497.1	1491.5	1492.6	1501.5	1491.5
175°	1502.7	1497.1	1498.2	1506.0	1497.1
177.5°	1504.9	1499.3	1500.4	1509.4	1498.2
180°	1502.7	1502.7	1502.7	1502.7	1502.7

(END OF REPORT)