

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010895

Luminaire Tested: S123RDIP-B340D365UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010895
REPORT IS A COMBINATION OF REPORTS P993211 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B340D365UB2750-4F0-XX-W2A-F_3000K
Description: Define 3 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2723.0 lumens
Efficiency: N/A
Efficacy: 122.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010895

CATALOG NUMBER: S123RDIP-B340D365UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010895

CATALOG NUMBER: S123RDIP-B340D365UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53			46
1	97	93	89	86	89	86	82	80	72	69	67	59	57	56	47	46	45			40
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	42	40	39			34
3	81	72	65	59	74	66	60	55	56	51	48	46	43	40	37	35	33			29
4	74	64	56	50	68	59	52	47	50	45	41	41	38	35	34	31	29			25
5	68	57	49	43	63	53	46	41	45	39	35	37	33	30	30	27	25			22
6	63	51	43	38	58	47	40	35	40	35	31	34	30	27	28	25	22			19
7	58	46	38	33	53	43	36	31	37	31	27	31	27	24	25	22	20			17
8	54	42	34	29	50	39	32	28	33	28	24	28	24	21	23	20	18			16
9	50	38	31	26	46	36	29	25	31	25	22	26	22	19	22	18	16			14
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15			13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6018	6018	6018
5°	6028	5804	5789
10°	5980	5586	5477
15°	5902	5316	5134
20°	5801	5023	4752
25°	5695	4719	4388
30°	5561	4394	3960
35°	5423	4075	3570
40°	5292	3729	3138
45°	5124	3391	2751
50°	4940	3029	2350
55°	4749	2643	1981
60°	4566	2247	1609
65°	4329	1840	1256
70°	4032	1391	897
75°	3606	943	711
80°	3078	656	499
85°	2305	354	262

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5124 cd/sqm

TEST NUMBER: P1010895

CATALOG NUMBER: S123RDIP-B340D365UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.6	1.9
10°-20°	146.2	5.4
20°-30°	210.5	7.7
30°-40°	237.1	8.7
40°-50°	226.7	8.3
50°-60°	185.6	6.8
60°-70°	125.1	4.6
70°-80°	62.8	2.3
80°-90°	17.4	0.6
90°-100°	16.9	0.6
100°-110°	81.6	3.0
110°-120°	200.0	7.3
120°-130°	253.8	9.3
130°-140°	271.2	10.0
140°-150°	253.6	9.3
150°-160°	204.5	7.5
160°-170°	132.0	4.8
170°-180°	45.5	1.7
0°-30°	409.2	15.0
0°-40°	646.3	23.7
0°-60°	1058.7	38.9
0°-90°	1263.9	46.4
90°-120°	298.5	11.0
90°-150°	1077.0	39.6
90°-180°	1459.0	53.6
0°-180°	2723.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	559	559	559	559	559	
5°	559	557	551	555	554	53
15°	533	528	516	513	510	150
25°	485	474	453	443	438	223
35°	420	404	375	356	348	263
45°	345	325	290	264	253	266
55°	262	240	201	175	166	235
65°	179	154	119	97	92	177
75°	95	73	48	44	43	101
85°	24	14	13	12	12	26
90°	0	4	8	10	11	3
95°	22	7	11	14	14	26
105°	106	110	78	15	16	112
115°	199	201	204	208	209	196
125°	280	283	284	285	286	250
135°	349	351	352	353	352	269
145°	402	405	406	406	406	252
155°	443	443	443	445	443	204
165°	468	466	466	469	466	132
175°	479	477	477	480	477	46
180°	479	479	479	479	479	

TEST NUMBER: P1010895

CATALOG NUMBER: S123RDIP-B340D365UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	559.1	559.1	559.1	559.1	559.1
2.5°	561.3	559.5	554.1	559.1	558.1
5°	559.1	556.8	551.3	555.4	554.5
7.5°	555.0	552.7	545.9	548.6	547.3
10°	549.5	546.4	538.2	538.6	536.4
12.5°	541.8	538.2	527.8	527.3	524.6
15°	533.2	528.2	515.5	513.3	510.1
17.5°	522.8	517.3	501.5	496.9	492.4
20°	511.0	503.7	486.5	480.6	475.2
22.5°	497.8	489.2	470.6	462.9	457.9
25°	485.1	473.8	453.0	443.4	438.4
27.5°	469.7	457.5	434.8	422.1	414.4
30°	453.9	440.3	414.9	399.5	392.2
32.5°	438.0	422.1	394.9	377.7	370.0
35°	419.9	403.5	375.4	355.9	347.8
37.5°	401.7	384.0	354.6	332.8	322.8
40°	384.5	364.5	332.3	308.8	298.3
42.5°	365.0	345.0	311.5	285.2	276.1
45°	345.0	324.6	289.7	263.9	253.0
47.5°	325.5	302.9	268.4	240.3	230.8
50°	303.8	282.5	245.7	217.6	207.2
52.5°	284.3	260.7	224.4	195.0	185.9
55°	262.1	239.9	201.3	175.0	165.9
57.5°	242.1	218.1	179.1	154.2	146.5
60°	221.3	196.3	158.7	134.2	126.5
62.5°	200.4	175.5	137.8	115.2	107.0
65°	179.1	154.2	118.8	96.6	91.6
67.5°	157.8	132.4	97.9	81.2	75.7
70°	136.9	112.4	80.7	64.8	59.8
72.5°	116.1	92.0	63.9	51.7	50.3
75°	94.8	73.0	48.1	43.5	42.6
77.5°	75.3	55.3	37.6	34.9	34.0
80°	56.7	38.1	28.6	27.2	26.3
82.5°	39.0	23.6	20.4	19.0	19.0
85°	24.0	14.1	12.7	11.8	11.8
87.5°	10.9	5.9	5.9	5.4	5.0
90°	0.4	3.9	8.5	10.0	10.7
92.5°	8.2	6.0	9.2	11.7	12.1
95°	21.7	7.1	11.0	13.5	13.5
97.5°	39.5	29.5	11.4	14.2	14.6
100°	60.1	67.2	11.7	14.6	14.9
102.5°	83.6	88.2	26.3	14.6	15.3
105°	106.0	109.9	77.9	14.9	15.6
107.5°	129.8	133.0	138.3	83.6	37.0
110°	153.6	156.5	160.4	148.6	97.8



TEST NUMBER: P1010895

CATALOG NUMBER: S123RDIP-B340D365UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	176.4	178.9	182.8	186.0	185.3
115°	198.8	200.9	204.1	207.7	209.1
117.5°	220.8	223.3	225.1	227.9	228.3
120°	241.1	244.3	245.3	248.2	248.2
122.5°	261.7	264.2	265.6	267.4	267.7
125°	280.2	283.0	284.5	285.2	285.9
127.5°	298.7	301.5	303.3	304.4	303.7
130°	315.7	318.6	320.0	321.4	320.7
132.5°	332.1	334.9	336.0	337.4	336.4
135°	348.8	350.9	352.4	353.4	352.4
137.5°	363.0	365.9	366.6	368.4	367.7
140°	377.3	379.4	380.5	381.9	381.2
142.5°	390.4	392.5	393.6	394.7	393.6
145°	402.5	405.0	405.7	406.4	406.4
147.5°	414.2	416.0	416.7	417.4	415.7
150°	424.9	426.0	426.7	427.4	426.3
152.5°	434.5	434.9	435.2	436.6	434.9
155°	443.4	442.7	443.0	444.8	442.7
157.5°	450.5	450.5	450.2	452.3	449.4
160°	456.9	456.6	456.2	458.3	455.8
162.5°	463.0	461.9	461.5	464.0	461.9
165°	467.6	466.5	466.2	469.0	466.5
167.5°	471.5	470.1	470.1	472.9	470.1
170°	474.7	473.3	473.3	476.1	473.3
172.5°	476.8	475.0	475.4	478.2	475.0
175°	478.6	476.8	477.2	479.7	476.8
177.5°	479.3	477.5	477.9	480.7	477.2
180°	478.6	478.6	478.6	478.6	478.6

(END OF REPORT)