

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011204

Luminaire Tested: S123DIP-B1000D805UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011204
REPORT IS A COMBINATION OF REPORTS P989267 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D805UB27-4F0-XX-W2A-F4
Description: Define 3 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6881.6 lumens
Efficiency: N/A
Efficacy: 101.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011204

CATALOG NUMBER: S123DIP-B1000D805UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1011204

CATALOG NUMBER: S123DIP-B1000D805UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64
1	100	95	91	88	93	89	86	83	77	75	73	67	65	63	57	56	54
2	91	83	77	72	84	78	72	68	68	64	60	59	55	53	50	48	46
3	83	73	66	60	77	69	62	57	60	55	50	52	48	45	44	41	39
4	76	65	57	51	70	61	54	48	53	47	43	46	42	38	40	36	33
5	70	58	49	43	65	54	47	41	48	42	37	41	37	33	36	32	29
6	64	52	44	38	60	49	41	36	43	37	32	37	33	29	32	29	26
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23
8	55	43	35	29	51	40	33	28	36	30	25	31	26	23	27	23	20
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18
10	48	36	28	24	45	34	27	23	30	24	21	27	22	19	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16792	16792	16792
5°	16833	16212	16188
10°	16684	15663	15503
15°	16451	15092	14756
20°	16186	14460	14016
25°	15842	13791	13225
30°	15465	13098	12392
35°	15071	12392	11566
40°	14657	11650	10753
45°	14204	10928	9903
50°	13742	10122	9050
55°	13149	9282	8186
60°	12537	8356	7267
65°	11966	7354	6308
70°	11140	6244	5189
75°	9951	4944	4027
80°	8594	3475	2849
85°	6705	1869	1427

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14204 cd/sqm

TEST NUMBER: P1011204

CATALOG NUMBER: S123DIP-B1000D805UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.1	2.1
10°-20°	415.3	6.0
20°-30°	613.3	8.9
30°-40°	716.3	10.4
40°-50°	720.1	10.5
50°-60°	632.6	9.2
60°-70°	471.1	6.8
70°-80°	268.1	3.9
80°-90°	78.3	1.1
90°-100°	212.5	3.1
100°-110°	594.0	8.6
110°-120°	579.2	8.4
120°-130°	461.2	6.7
130°-140°	364.0	5.3
140°-150°	271.6	3.9
150°-160°	189.5	2.8
160°-170°	111.3	1.6
170°-180°	36.2	0.5
0°-30°	1175.6	17.1
0°-40°	1891.9	27.5
0°-60°	3244.6	47.1
0°-90°	4062.1	59.0
90°-120°	1385.7	20.1
90°-150°	2482.5	36.1
90°-180°	2819.0	41.0
0°-180°	6881.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1560	1560	1560	1560	1560	
5°	1561	1555	1540	1553	1551	148
15°	1486	1481	1463	1474	1466	419
25°	1349	1341	1324	1325	1321	622
35°	1167	1159	1142	1134	1127	730
45°	956	951	934	918	911	738
55°	726	724	707	692	685	650
65°	495	488	475	464	460	488
75°	262	256	252	246	241	279
85°	70	67	67	64	64	75
90°	2	9	19	21	22	7
95°	26	84	449	131	88	27
105°	88	130	609	1064	963	93
115°	155	193	466	1021	1171	154
125°	216	255	434	787	924	192
135°	253	302	428	648	749	195
145°	288	330	423	532	585	181
155°	328	354	410	466	485	151
165°	358	368	392	416	423	101
175°	373	374	376	382	381	35
180°	374	374	374	374	374	

TEST NUMBER: P1011204

CATALOG NUMBER: S123DIP-B1000D805UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1560.0	1560.0	1560.0	1560.0	1560.0
2.5°	1566.7	1561.3	1546.6	1560.0	1558.7
5°	1561.3	1554.6	1539.9	1553.3	1550.6
7.5°	1549.3	1542.6	1527.8	1539.9	1538.5
10°	1533.2	1526.5	1509.0	1521.1	1518.4
12.5°	1511.7	1506.3	1490.3	1498.3	1497.0
15°	1486.2	1480.9	1463.4	1474.2	1466.1
17.5°	1458.1	1451.4	1433.9	1442.0	1439.3
20°	1425.9	1417.8	1400.4	1405.7	1401.7
22.5°	1389.7	1381.6	1364.2	1368.2	1362.8
25°	1349.4	1341.4	1323.9	1325.3	1321.2
27.5°	1307.8	1299.8	1281.0	1282.3	1278.3
30°	1262.2	1255.5	1236.7	1236.7	1227.3
32.5°	1216.6	1207.2	1193.8	1184.4	1180.4
35°	1167.0	1158.9	1141.5	1133.5	1126.7
37.5°	1117.4	1106.6	1089.2	1079.8	1075.8
40°	1065.0	1057.0	1038.2	1027.5	1022.1
42.5°	1012.7	1003.3	984.6	973.8	968.5
45°	956.4	951.0	933.6	917.5	910.8
47.5°	901.4	893.3	877.3	861.2	855.8
50°	845.1	838.4	820.9	806.2	798.1
52.5°	786.0	782.0	763.2	751.2	743.1
55°	725.7	724.3	706.9	692.1	685.4
57.5°	669.3	664.0	650.6	637.1	629.1
60°	607.6	606.3	590.2	578.1	571.4
62.5°	552.6	548.6	532.5	520.4	516.4
65°	495.0	488.3	474.8	464.1	460.1
67.5°	433.3	427.9	417.2	407.8	402.4
70°	378.3	370.2	362.2	352.8	346.1
72.5°	320.6	315.2	305.8	297.8	295.1
75°	261.6	256.2	252.2	245.5	241.4
77.5°	209.3	206.6	201.2	195.8	195.8
80°	158.3	154.3	151.6	150.2	150.2
82.5°	108.7	108.7	108.7	106.0	104.6
85°	69.8	67.1	67.1	64.4	64.4
87.5°	34.9	30.9	29.5	28.2	28.2
90°	1.5	9.0	18.9	21.2	22.0
92.5°	11.4	45.4	140.8	48.0	40.1
95°	25.7	83.6	448.9	131.0	87.8
97.5°	40.9	95.8	690.4	329.2	180.2
100°	56.0	105.6	716.9	688.8	474.6
102.5°	71.9	117.0	667.7	922.4	751.7
105°	87.8	129.8	608.6	1064.4	962.9
107.5°	104.5	145.0	556.4	1126.8	1100.7
110°	122.6	160.5	513.2	1128.7	1179.4



TEST NUMBER: P1011204

CATALOG NUMBER: S123DIP-B1000D805UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	139.3	176.8	484.5	1086.0	1195.3
115°	155.2	193.4	465.6	1020.8	1171.1
117.5°	171.1	209.3	452.7	951.2	1118.1
120°	187.7	225.2	444.4	885.3	1048.4
122.5°	202.1	240.4	439.1	833.4	983.3
125°	215.7	254.7	434.5	787.3	923.5
127.5°	226.3	268.4	432.2	749.4	872.1
130°	236.2	280.4	430.0	714.6	829.7
132.5°	243.8	291.5	429.2	682.0	788.0
135°	252.8	301.6	428.5	648.3	748.7
137.5°	261.2	310.0	426.9	616.6	707.0
140°	269.5	317.6	426.2	585.6	663.1
142.5°	278.6	324.4	424.7	557.2	622.2
145°	288.4	330.4	423.2	531.8	585.2
147.5°	298.3	336.8	420.9	512.2	553.4
150°	308.1	342.2	417.9	494.7	526.1
152.5°	317.9	347.8	414.1	479.6	503.4
155°	327.8	353.5	409.5	465.6	485.2
157.5°	335.3	358.5	405.7	451.9	467.8
160°	344.4	362.6	401.2	439.4	451.2
162.5°	351.2	365.6	396.7	427.7	436.0
165°	358.1	368.2	392.1	416.0	423.2
167.5°	363.4	370.5	387.6	405.8	410.3
170°	367.9	371.6	383.0	396.6	398.9
172.5°	370.9	372.8	379.3	388.7	388.3
175°	373.2	373.6	376.2	381.5	380.8
177.5°	374.7	374.0	374.0	377.0	375.5
180°	374.0	374.0	374.0	374.0	374.0

(END OF REPORT)