

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010898

Luminaire Tested: S123RDIP-B340D365UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010898
REPORT IS A COMBINATION OF REPORTS P993214 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B340D365UB2750-4F0-XX-W2A-F_5000K
Description: Define 3 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2619.0 lumens
Efficiency: N/A
Efficacy: 117.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010898

CATALOG NUMBER: S123RDIP-B340D365UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010898

CATALOG NUMBER: S123RDIP-B340D365UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53			46
1	97	93	89	86	89	86	82	80	72	69	67	59	57	56	47	46	45			40
2	89	82	76	71	81	75	70	66	63	59	56	52	50	47	42	40	39			34
3	81	72	65	59	74	66	60	55	56	51	48	46	43	40	37	35	33			29
4	74	64	56	50	68	59	52	47	50	45	41	41	38	35	34	31	29			25
5	68	57	49	43	63	53	46	41	45	39	35	37	33	30	30	28	25			22
6	63	51	43	38	58	47	40	35	40	35	31	34	30	27	28	25	22			19
7	58	46	38	33	53	43	36	31	37	31	27	31	27	24	25	22	20			17
8	54	42	34	29	50	39	32	28	34	28	24	28	24	21	23	20	18			16
9	50	38	31	26	46	36	29	25	31	26	22	26	22	19	22	18	16			14
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15			13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5789	5789	5789
5°	5798	5584	5569
10°	5752	5374	5268
15°	5678	5114	4939
20°	5580	4832	4571
25°	5479	4539	4222
30°	5349	4227	3810
35°	5216	3921	3434
40°	5091	3588	3019
45°	4929	3262	2647
50°	4752	2915	2260
55°	4568	2543	1906
60°	4393	2162	1548
65°	4165	1770	1208
70°	3878	1338	864
75°	3469	906	684
80°	2959	630	480
85°	2219	340	250

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4929 cd/sqm

TEST NUMBER: P1010898

CATALOG NUMBER: S123RDIP-B340D365UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.6	1.9
10°-20°	140.6	5.4
20°-30°	202.5	7.7
30°-40°	228.0	8.7
40°-50°	218.1	8.3
50°-60°	178.6	6.8
60°-70°	120.4	4.6
70°-80°	60.4	2.3
80°-90°	16.7	0.6
90°-100°	16.2	0.6
100°-110°	78.5	3.0
110°-120°	192.3	7.3
120°-130°	244.1	9.3
130°-140°	260.8	10.0
140°-150°	243.8	9.3
150°-160°	196.7	7.5
160°-170°	126.9	4.8
170°-180°	43.7	1.7
0°-30°	393.7	15.0
0°-40°	621.7	23.7
0°-60°	1018.4	38.9
0°-90°	1215.9	46.4
90°-120°	287.0	11.0
90°-150°	1035.7	39.5
90°-180°	1403.0	53.6
0°-180°	2619.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	538	538	538	538	538	
5°	538	536	530	534	533	51
15°	513	508	496	494	491	145
25°	467	456	436	427	422	215
35°	404	388	361	342	334	253
45°	332	312	279	254	243	256
55°	252	231	194	168	160	226
65°	172	148	114	93	88	171
75°	91	70	46	42	41	97
85°	23	14	12	11	11	25
90°	0	4	8	10	10	3
95°	21	7	11	13	13	25
105°	102	106	75	14	15	108
115°	191	193	196	200	201	189
125°	269	272	274	274	275	241
135°	335	338	339	340	339	258
145°	387	390	390	391	391	242
155°	426	426	426	428	426	196
165°	450	449	448	451	449	127
175°	460	458	459	461	458	44
180°	460	460	460	460	460	

TEST NUMBER: P1010898

CATALOG NUMBER: S123RDIP-B340D365UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	537.8	537.8	537.8	537.8	537.8
2.5°	540.0	538.2	533.0	537.8	536.9
5°	537.8	535.6	530.4	534.3	533.4
7.5°	533.9	531.7	525.2	527.8	526.5
10°	528.6	525.6	517.7	518.2	516.0
12.5°	521.2	517.7	507.7	507.3	504.7
15°	512.9	508.1	495.9	493.8	490.7
17.5°	502.9	497.7	482.4	478.1	473.7
20°	491.6	484.6	468.0	462.3	457.1
22.5°	478.9	470.6	452.8	445.3	440.5
25°	466.7	455.8	435.7	426.6	421.8
27.5°	451.9	440.1	418.3	406.1	398.7
30°	436.6	423.5	399.1	384.3	377.3
32.5°	421.3	406.1	379.9	363.3	355.9
35°	403.9	388.2	361.2	342.4	334.5
37.5°	386.5	369.4	341.1	320.2	310.6
40°	369.9	350.7	319.7	297.0	287.0
42.5°	351.1	331.9	299.7	274.4	265.6
45°	331.9	312.3	278.7	253.9	243.4
47.5°	313.2	291.4	258.2	231.2	222.0
50°	292.2	271.7	236.4	209.4	199.3
52.5°	273.5	250.8	215.9	187.6	178.8
55°	252.1	230.7	193.7	168.4	159.6
57.5°	232.9	209.8	172.3	148.3	140.9
60°	212.9	188.9	152.7	129.1	121.7
62.5°	192.8	168.8	132.6	110.8	102.9
65°	172.3	148.3	114.3	92.9	88.1
67.5°	151.8	127.4	94.2	78.1	72.8
70°	131.7	108.2	77.6	62.4	57.6
72.5°	111.7	88.5	61.5	49.7	48.4
75°	91.2	70.2	46.2	41.9	41.0
77.5°	72.4	53.2	36.2	33.6	32.7
80°	54.5	36.6	27.5	26.2	25.3
82.5°	37.5	22.7	19.6	18.3	18.3
85°	23.1	13.5	12.2	11.3	11.3
87.5°	10.5	5.7	5.7	5.2	4.8
90°	0.3	3.8	8.2	9.6	10.3
92.5°	7.9	5.8	8.9	11.3	11.6
95°	20.9	6.8	10.6	13.0	13.0
97.5°	38.0	28.4	10.9	13.7	14.0
100°	57.8	64.6	11.3	14.0	14.4
102.5°	80.4	84.8	25.3	14.0	14.7
105°	101.9	105.7	74.9	14.4	15.0
107.5°	124.8	127.9	133.0	80.4	35.6
110°	147.7	150.4	154.2	142.9	94.0



TEST NUMBER: P1010898

CATALOG NUMBER: S123RDIP-B340D365UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	169.6	172.0	175.8	178.8	178.1
115°	191.1	193.2	196.3	199.7	201.1
117.5°	212.3	214.7	216.4	219.2	219.5
120°	231.8	234.9	235.9	238.7	238.7
122.5°	251.7	254.1	255.4	257.1	257.5
125°	269.4	272.2	273.5	274.2	274.9
127.5°	287.2	290.0	291.7	292.7	292.0
130°	303.6	306.4	307.7	309.1	308.4
132.5°	319.4	322.1	323.1	324.5	323.5
135°	335.4	337.5	338.9	339.9	338.9
137.5°	349.1	351.8	352.5	354.2	353.6
140°	362.8	364.8	365.9	367.2	366.6
142.5°	375.4	377.5	378.5	379.5	378.5
145°	387.1	389.5	390.1	390.8	390.8
147.5°	398.4	400.1	400.7	401.4	399.7
150°	408.6	409.6	410.3	411.0	410.0
152.5°	417.8	418.2	418.5	419.9	418.2
155°	426.4	425.7	426.0	427.8	425.7
157.5°	433.2	433.2	432.9	434.9	432.2
160°	439.4	439.0	438.7	440.7	438.4
162.5°	445.2	444.2	443.8	446.2	444.2
165°	449.6	448.6	448.3	451.0	448.6
167.5°	453.4	452.0	452.0	454.8	452.0
170°	456.5	455.1	455.1	457.8	455.1
172.5°	458.5	456.8	457.2	459.9	456.8
175°	460.2	458.5	458.9	461.3	458.5
177.5°	460.9	459.2	459.6	462.3	458.9
180°	460.2	460.2	460.2	460.2	460.2

(END OF REPORT)