

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010928

Luminaire Tested: S123RDIP-B560D1025UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010928
REPORT IS A COMBINATION OF REPORTS P993334 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D1025UB2750-4F0-XX-W2A-F_5000K
Description: Define 3 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5944.0 lumens
Efficiency: N/A
Efficacy: 113.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010928

CATALOG NUMBER: S123RDIP-B560D1025UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010928

CATALOG NUMBER: S123RDIP-B560D1025UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	75	75	75	58	58	58	42	42	42
1	95	90	87	83	85	82	79	76	66	64	62	51	50	48	37	36	36
2	86	79	73	68	78	72	67	63	58	54	51	45	43	41	33	32	30
3	79	70	63	57	71	63	57	52	51	47	43	40	37	35	29	28	26
4	72	62	54	48	65	56	50	45	45	41	37	36	32	30	26	24	23
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	24	22	20
6	61	49	42	36	55	45	38	33	37	32	28	29	25	23	22	19	18
7	56	44	37	31	51	41	34	29	33	28	25	26	23	20	20	17	16
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14
9	49	37	30	25	44	34	27	23	28	23	19	22	19	16	17	14	13
10	45	34	27	22	41	31	25	20	25	21	17	20	17	14	16	13	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9734	9734	9734
5°	9750	9389	9364
10°	9673	9037	8858
15°	9547	8600	8305
20°	9383	8126	7685
25°	9213	7632	7099
30°	8996	7108	6406
35°	8771	6593	5774
40°	8559	6033	5077
45°	8288	5486	4450
50°	7991	4901	3801
55°	7681	4275	3206
60°	7385	3634	2602
65°	7003	2977	2032
70°	6523	2250	1451
75°	5831	1523	1149
80°	4978	1059	806
85°	3737	571	423

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8288 cd/sqm

TEST NUMBER: P1010928

CATALOG NUMBER: S123RDIP-B560D1025UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.0	1.4
10°-20°	236.5	4.0
20°-30°	340.5	5.7
30°-40°	383.4	6.5
40°-50°	366.8	6.2
50°-60°	300.2	5.1
60°-70°	202.4	3.4
70°-80°	101.5	1.7
80°-90°	29.1	0.5
90°-100°	45.1	0.8
100°-110°	218.0	3.7
110°-120°	534.3	9.0
120°-130°	678.2	11.4
130°-140°	724.6	12.2
140°-150°	677.5	11.4
150°-160°	546.5	9.2
160°-170°	352.7	5.9
170°-180°	121.5	2.0
0°-30°	662.0	11.1
0°-40°	1045.4	17.6
0°-60°	1712.5	28.8
0°-90°	2045.5	34.4
90°-120°	797.4	13.4
90°-150°	2877.8	48.4
90°-180°	3898.0	65.6
0°-180°	5944.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	904	904	904	904	904	
5°	904	901	892	898	897	86
15°	862	854	834	830	825	243
25°	785	766	733	717	709	361
35°	679	653	607	576	562	425
45°	558	525	469	427	409	431
55°	424	388	326	283	268	380
65°	290	249	192	156	148	287
75°	153	118	78	70	69	163
85°	39	23	20	19	19	43
90°	1	10	23	27	28	6
95°	58	19	30	36	36	69
105°	283	294	208	40	42	300
115°	531	537	545	555	559	524
125°	749	756	760	762	764	669
135°	932	938	942	944	942	718
145°	1076	1082	1084	1086	1086	673
155°	1185	1183	1184	1188	1183	546
165°	1249	1246	1246	1253	1246	353
175°	1279	1274	1275	1282	1274	122
180°	1279	1279	1279	1279	1279	

TEST NUMBER: P1010928

CATALOG NUMBER: S123RDIP-B560D1025UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	904.3	904.3	904.3	904.3	904.3
2.5°	908.0	905.0	896.2	904.3	902.8
5°	904.3	900.6	891.8	898.4	897.0
7.5°	897.7	894.0	883.0	887.4	885.2
10°	888.9	883.8	870.6	871.3	867.6
12.5°	876.4	870.6	853.7	853.0	848.6
15°	862.5	854.4	833.9	830.2	825.1
17.5°	845.6	836.8	811.2	803.8	796.5
20°	826.6	814.8	787.0	777.4	768.6
22.5°	805.3	791.4	761.3	748.8	740.8
25°	784.8	766.4	732.7	717.3	709.2
27.5°	759.8	740.0	703.4	682.8	670.3
30°	734.2	712.2	671.1	646.1	634.4
32.5°	708.5	682.8	638.8	610.9	598.5
35°	679.2	652.7	607.3	575.7	562.5
37.5°	649.8	621.2	573.5	538.3	522.2
40°	621.9	589.7	537.6	499.5	482.6
42.5°	590.4	558.1	503.9	461.3	446.7
45°	558.1	525.1	468.7	426.9	409.3
47.5°	526.6	489.9	434.2	388.7	373.3
50°	491.4	456.9	397.5	352.0	335.2
52.5°	459.9	421.7	363.0	315.4	300.7
55°	423.9	388.0	325.6	283.1	268.4
57.5°	391.6	352.8	289.7	249.4	236.9
60°	357.9	317.6	256.7	217.1	204.6
62.5°	324.2	283.8	223.0	186.3	173.1
65°	289.7	249.4	192.2	156.2	148.2
67.5°	255.2	214.2	158.4	131.3	122.5
70°	221.5	181.9	130.5	104.9	96.8
72.5°	187.8	148.9	103.4	83.6	81.4
75°	153.3	118.1	77.7	70.4	68.9
77.5°	121.7	89.5	60.9	56.5	55.0
80°	91.7	61.6	46.2	44.0	42.5
82.5°	63.1	38.1	33.0	30.8	30.8
85°	38.9	22.7	20.5	19.1	19.1
87.5°	17.6	9.5	9.5	8.8	8.1
90°	1.0	10.5	22.8	26.6	28.5
92.5°	21.9	16.2	24.7	31.4	32.3
95°	58.0	19.0	29.5	36.1	36.1
97.5°	105.5	78.9	30.4	38.0	39.0
100°	160.6	179.6	31.4	39.0	39.9
102.5°	223.3	235.6	70.3	39.0	40.9
105°	283.1	293.6	208.1	39.9	41.8
107.5°	346.8	355.3	369.6	223.3	98.8
110°	410.4	418.0	428.5	397.1	261.3

TEST NUMBER: P1010928

CATALOG NUMBER: S123RDIP-B560D1025UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	471.2	477.9	488.3	496.9	495.0
115°	531.1	536.8	545.3	554.8	558.6
117.5°	590.0	596.6	601.4	609.0	609.9
120°	644.1	652.7	655.5	663.1	663.1
122.5°	699.2	705.9	709.7	714.4	715.4
125°	748.6	756.2	760.0	761.9	763.8
127.5°	798.0	805.6	810.4	813.2	811.3
130°	843.6	851.2	855.0	858.8	856.9
132.5°	887.4	895.0	897.8	901.6	898.8
135°	932.0	937.7	941.5	944.4	941.5
137.5°	970.0	977.6	979.5	984.3	982.4
140°	1008.0	1013.7	1016.6	1020.4	1018.5
142.5°	1043.2	1048.9	1051.7	1054.6	1051.7
145°	1075.5	1082.1	1084.0	1085.9	1085.9
147.5°	1106.8	1111.6	1113.5	1115.4	1110.6
150°	1135.3	1138.2	1140.1	1142.0	1139.1
152.5°	1161.0	1161.9	1162.9	1166.7	1161.9
155°	1184.7	1182.8	1183.8	1188.5	1182.8
157.5°	1203.7	1203.7	1202.8	1208.5	1200.9
160°	1220.8	1219.9	1218.9	1224.6	1218.0
162.5°	1237.0	1234.1	1233.2	1239.8	1234.1
165°	1249.3	1246.5	1245.5	1253.1	1246.5
167.5°	1259.8	1256.0	1256.0	1263.6	1256.0
170°	1268.3	1264.5	1264.5	1272.1	1264.5
172.5°	1274.0	1269.3	1270.2	1277.8	1269.3
175°	1278.8	1274.0	1275.0	1281.6	1274.0
177.5°	1280.7	1275.9	1276.9	1284.5	1275.0
180°	1278.8	1278.8	1278.8	1278.8	1278.8

(END OF REPORT)