

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011237

Luminaire Tested: S123DIP-B1000D805UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011237
REPORT IS A COMBINATION OF REPORTS P989318 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D805UB50-4F0-XX-W2A-F4
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6673.3 lumens
Efficiency: N/A
Efficacy: 98.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011237

CATALOG NUMBER: S123DIP-B1000D805UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1011237

CATALOG NUMBER: S123DIP-B1000D805UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64
1	100	95	91	88	93	89	86	83	77	75	73	67	65	63	57	56	54
2	91	83	77	72	84	78	72	68	68	64	60	59	55	53	50	48	46
3	83	73	66	60	77	69	62	57	60	55	50	52	48	45	44	41	39
4	76	65	57	51	70	61	54	48	53	47	43	46	42	38	40	36	33
5	70	58	49	43	65	54	47	41	48	42	37	41	37	33	36	32	29
6	64	52	44	38	60	49	41	36	43	37	32	37	33	29	32	29	26
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23
8	55	43	35	29	51	40	33	28	36	30	25	31	26	23	27	23	20
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18
10	48	36	28	24	45	34	27	23	30	24	21	27	22	19	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16283	16283	16283
5°	16323	15721	15697
10°	16178	15189	15033
15°	15953	14635	14309
20°	15696	14022	13592
25°	15362	13373	12824
30°	14997	12702	12018
35°	14614	12016	11216
40°	14214	11298	10428
45°	13773	10596	9603
50°	13326	9815	8776
55°	12751	9001	7939
60°	12158	8103	7047
65°	11603	7132	6116
70°	10802	6054	5032
75°	9647	4793	3906
80°	8333	3369	2763
85°	6493	1810	1383

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13773 cd/sqm

TEST NUMBER: P1011237

CATALOG NUMBER: S123DIP-B1000D805UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	142.6	2.1
10°-20°	402.7	6.0
20°-30°	594.7	8.9
30°-40°	694.6	10.4
40°-50°	698.3	10.5
50°-60°	613.4	9.2
60°-70°	456.8	6.8
70°-80°	260.0	3.9
80°-90°	75.9	1.1
90°-100°	206.1	3.1
100°-110°	576.0	8.6
110°-120°	561.7	8.4
120°-130°	447.2	6.7
130°-140°	353.1	5.3
140°-150°	263.4	3.9
150°-160°	183.8	2.8
160°-170°	107.9	1.6
170°-180°	35.1	0.5
0°-30°	1140.0	17.1
0°-40°	1834.6	27.5
0°-60°	3146.3	47.1
0°-90°	3939.0	59.0
90°-120°	1343.8	20.1
90°-150°	2407.5	36.1
90°-180°	2734.0	41.0
0°-180°	6673.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1513	1513	1513	1513	1513	
5°	1514	1508	1493	1506	1504	144
15°	1441	1436	1419	1430	1422	406
25°	1308	1301	1284	1285	1281	603
35°	1132	1124	1107	1099	1093	708
45°	927	922	905	890	883	716
55°	704	702	686	671	665	630
65°	480	474	460	450	446	474
75°	254	248	244	238	234	271
85°	68	65	65	62	62	73
90°	2	9	18	21	21	7
95°	25	81	435	127	85	26
105°	85	126	590	1032	934	90
115°	150	188	452	990	1136	149
125°	209	247	421	764	896	186
135°	245	293	416	629	726	189
145°	280	320	410	516	568	175
155°	318	343	397	452	471	146
165°	347	357	380	403	410	98
175°	362	362	365	370	369	34
180°	363	363	363	363	363	

TEST NUMBER: P1011237

CATALOG NUMBER: S123DIP-B1000D805UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1512.7	1512.7	1512.7	1512.7	1512.7
2.5°	1519.2	1514.0	1499.7	1512.7	1511.4
5°	1514.0	1507.5	1493.2	1506.2	1503.6
7.5°	1502.3	1495.8	1481.5	1493.2	1491.9
10°	1486.7	1480.2	1463.3	1475.0	1472.4
12.5°	1465.9	1460.7	1445.1	1452.9	1451.6
15°	1441.2	1436.0	1419.1	1429.5	1421.7
17.5°	1413.9	1407.4	1390.5	1398.3	1395.7
20°	1382.7	1374.9	1358.0	1363.2	1359.3
22.5°	1347.6	1339.7	1322.8	1326.7	1321.5
25°	1308.5	1300.7	1283.8	1285.1	1281.2
27.5°	1268.2	1260.4	1242.2	1243.5	1239.6
30°	1224.0	1217.5	1199.3	1199.3	1190.2
32.5°	1179.8	1170.7	1157.6	1148.5	1144.6
35°	1131.6	1123.8	1106.9	1099.1	1092.6
37.5°	1083.5	1073.1	1056.2	1047.1	1043.2
40°	1032.8	1025.0	1006.8	996.4	991.2
42.5°	982.0	972.9	954.7	944.3	939.1
45°	927.4	922.2	905.3	889.7	883.2
47.5°	874.1	866.3	850.7	835.1	829.9
50°	819.5	813.0	796.0	781.7	773.9
52.5°	762.2	758.3	740.1	728.4	720.6
55°	703.7	702.4	685.5	671.2	664.7
57.5°	649.1	643.9	630.9	617.8	610.0
60°	589.2	587.9	572.3	560.6	554.1
62.5°	535.9	532.0	516.4	504.7	500.8
65°	480.0	473.5	460.5	450.1	446.1
67.5°	420.1	414.9	404.5	395.4	390.2
70°	366.8	359.0	351.2	342.1	335.6
72.5°	310.9	305.7	296.6	288.8	286.2
75°	253.6	248.4	244.5	238.0	234.1
77.5°	202.9	200.3	195.1	189.9	189.9
80°	153.5	149.6	147.0	145.7	145.7
82.5°	105.4	105.4	105.4	102.8	101.5
85°	67.6	65.0	65.0	62.4	62.4
87.5°	33.8	29.9	28.6	27.3	27.3
90°	1.5	8.8	18.4	20.6	21.3
92.5°	11.0	44.0	136.5	46.6	38.9
95°	25.0	81.1	435.3	127.0	85.2
97.5°	39.6	92.9	669.5	319.4	174.7
100°	54.3	102.4	695.2	668.0	460.3
102.5°	69.7	113.4	647.5	894.6	729.0
105°	85.2	125.9	590.2	1032.2	933.8
107.5°	101.3	140.6	539.6	1092.8	1067.4
110°	118.9	155.6	497.7	1094.6	1143.8

TEST NUMBER: P1011237

CATALOG NUMBER: S123DIP-B1000D805UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	135.1	171.4	469.8	1053.1	1159.2
115°	150.5	187.6	451.5	990.0	1135.7
117.5°	165.9	203.0	439.0	922.4	1084.3
120°	182.1	218.4	430.9	858.6	1016.8
122.5°	196.0	233.1	425.8	808.3	953.6
125°	209.2	247.0	421.4	763.5	895.6
127.5°	219.5	260.2	419.2	726.8	845.7
130°	229.1	272.0	417.0	693.0	804.6
132.5°	236.4	282.6	416.3	661.4	764.2
135°	245.2	292.6	415.5	628.8	726.1
137.5°	253.3	300.6	414.1	598.0	685.7
140°	261.4	308.0	413.3	567.8	643.1
142.5°	270.2	314.6	411.9	540.3	603.5
145°	279.7	320.4	410.4	515.8	567.5
147.5°	289.2	326.6	408.2	496.6	536.7
150°	298.8	331.8	405.2	479.8	510.2
152.5°	308.3	337.4	401.6	465.1	488.2
155°	317.9	342.8	397.2	451.5	470.6
157.5°	325.2	347.6	393.5	438.3	453.7
160°	334.0	351.6	389.1	426.2	437.5
162.5°	340.6	354.6	384.7	414.8	422.9
165°	347.2	357.2	380.3	403.4	410.4
167.5°	352.4	359.4	375.9	393.5	397.9
170°	356.8	360.4	371.5	384.7	386.9
172.5°	359.7	361.5	367.8	377.0	376.6
175°	361.9	362.3	364.9	370.0	369.3
177.5°	363.4	362.7	362.7	365.6	364.1
180°	362.7	362.7	362.7	362.7	362.7

(END OF REPORT)